# **DISPLAY SOLUTIONS**





# Mounting Solutions for Flat-Panel and Curved Displays

Optimize viewing angles, add mobility to displays, deter theft of HDTVs and enhance ergonomics in home, office, commercial, industrial, education and healthcare environments:

- Home Theaters
- Office Workstations
- Conference Areas
- Meeting Rooms
- Digital Signage
- Information Kiosks
- Point-of-Sale Areas

- Security Stations
- Production Studios
- Control Rooms
- Classrooms
- Auditoriums
- Waiting Rooms
- Patient Rooms





ergonomics in home, office, commercial, industrial, education and health

environments • Optimize viewing angles, add mobility to displays, deter thef

HDTVs and enhance ergonomics in home, office, commercial, industrial, edu

CONTENTS

CONTENTS	
Specifications	2 - 3
Mobile Floor Stands	4
Security Wall Mounts	5
Desktop & Clamp-On Mounts	6 – 7
Adjustable-Height Workstation	s 8-9
Dual-Monitor Adapter	9
AC/USB Charging Clip	9
CPU & Thin-Client Mounts	10
Tablet Mounts	10
Wall Mounts (Fixed)	11
Ceiling Mounts	12
Wall Mounts (Tilt)	12 - 13
Wall Mounts (Swivel/Tilt/Rotate)	14 – 15
Rail Wall Mounts	15
Monitor Risers	16

and healthcare environments • Optimize viewing angles, add mobility to displa

# TRIPP-LITE DISPLAY SOLUTIONS



#### High-Quality Display Solutions from a Market Leader

As a market leader in display solutions, Tripp Lite has the experience and expertise to help you optimize viewing angles in your environment. You can add mobility to your display, deter theft, enhance ergonomics and fine-tune the positioning of digital signage and point-of-sale screens to communicate your message more effectively.

VESA compliance (where applicable) makes it simple to choose a mount that will work with your display. All models include mounting hardware to make installation quick, easy and secure. Wall mounts include fasteners for walls with timber or masonry construction. Most mounts have a sturdy steel or aluminum frame to withstand the stress of repeated adjustments and tolerate use in public areas.

<b>SPECI</b>	EIC/	TIO	NIC
	1 10	1110	IVJ

Model	Previous Model	Supported Screen Sizes	Weight Capacity	Mounting Profile (Surface to Display)	VESA Compliance	Tilt	Swivel	Rotate/ Screen Level	Feature Focus (pp. 4-16)
MOBILE FLOOR	STANDS								
DMCS3770L	_	37 to 70 in.	88 lb.	_	200x200, 300x300, 400x200, 400x400, 600x400	-10° to +10°	_	_	4A
DMCS3270XP	_	32 to 70 in.	150 lb.	_	200x200, 300x300, 400x200, 400x400, 600x400	-12° to +5°	_	90°	4B
DMCS60100XX	_	60 to 100 in.	220 lb.	_	200x200, 300x300, 400x200, 400x400, 600x400, 800x400, 800x600, 1000x600	-10° to +5°	_		4C
WWSSRC	_	_	4 x 33 lb.	_	N/A	_	_	_	4D
<b>SECURITY WALL</b>	. MOUNTS FO	unction- and weight	tested to higher val	ue in accordance with	UL Standard 2442.				
DWFSC3255MUL	_	32 to 55 in.	99 lb./150 lb.*	1 in.	200x200, 300x300, 400x200, 400x400	_	_	_	5A
DWFSC3780MUL	_	37 to 80 in.	88 lb./200 lb.*	0.9 in.	300x300, 400x200, 400x400, 600x400	_	_	_	5B
DWTSC3255MUL	_	32 to 55 in.	99 lb./150 lb.*	2.3 in.	200x200, 300x300, 400x200, 400x400	-15° to +10°	_	_	5C
DWTSC3780MUL	_	37 to 80 in.	88 lb./200 lb.*	2 in.	300x300, 400x200, 400x400, 600x400	-10° to +5°	_	_	5D
DWMSC3780MUL	_	37 to 80 in.	88 lb./200 lb.*	3 to 21.6 in.	300x300, 400x200, 400x400, 600x400, 800x400	-10° to +5°	180°	-4° to +4°	5E
<b>DESKTOP MOUN</b>	TS								
DDR1032SE	_	10 to 32 in.	36 lb.	_	75x75, 100x100	-15° to +15°	180°	360°	6A
DDR1026SD	_	10 to 26 in.	2 x 30 lb.	_	75x75, 100x100	-15° to +15°	180°	360°	6B
DDR1026MQ	_	10 to 26 in.	4 x 30 lb.	_	75x75, 100x100	-15° to +15°	180°	360°	6C
DDR1327SDD	DDR1326SD	13 to 27 in.	2 x 25 lb.	_	75x75, 100x100	-45° to +45°	15°	360°	6D
DDR1527SDC**	_	15 to 27 in.	2 x 20 lb.	_	75x75, 100x100	-20° to +20°	20°	360°	6E
CLAMP-ON MOU	NTS					<u></u>			
DDR1327S	DDR1323S	13 to 27 in.	20 lb.	_	75x75, 100x100	-40° to +90°	180°	360°	7A
DDR1327SFC	_	13 to 27 in.	22 lb.	_	75x75, 100x100	-15° to +15°	180°	360°	7B
DDR1327SDFC	_	13 to 27 in.	2 x 22 lb.	_	75x75, 100x100	-15° to +15°	180°	360°	7C
DDR1327SQFC	_	13 to 27 in.	4 x 22 lb.	_	75x75, 100x100	-15° to +15°	180°	360°	7D
DDR1327DCS	_	13 to 27 in.	2 x 22 lb.	_	75x75, 100x100	-80° to +90°	180°	360°	7E
DDR1327NBMSC	_	13 to 27 in. (monitor)/Up to 15 in. (laptop)	22 lb. (monitor)/ 11 lb. (laptop)	_	75x75, 100x100	-80° to +90° (monitor)/ 25° (laptop)	180°	360°	7F
DDR1527SDC**	_	15 to 27 in.	2 x 20 lb.	_	75x75, 100x100	-20° to +20°	20°	360°	6E
WORKWISE™ AD	JUSTABLE-H	IEIGHT WORK	STATIONS Mour	iting profile is the maxi	mum extension of the workstation.				
WWSS1327CP	_	13 to 27 in.	29 lb.	49.8 in.	75x75, 100x100	-13° to +45°	150°	360°	8A
WWSS1332C	_	13 to 32 in.	17.6 lb.	45.3 in.	75x75, 100x100	-15° to +15°	180°	360°	8B
WWSS1332W	_	13 to 32 in.	17.6 lb.	41.7 in.	75x75, 100x100	-15° to +15°	180°	360°	8C
WWSS1327RWTC	_	13 to 27 in.	13.2 lb.	32.8 in.	75x75, 100x100	-15° to +15°	180°	360°	8D
WWSSDT	_	_	29 lb.	_	N/A	_	_	_	9A
WWSSDC	_	_	29 lb.	_	N/A	_	_	_	9B
WWSSD3622	_	_	33 lb.	_	N/A	_	_	_	9C
WWSSRC	_	_	4 x 33 lb.	_	N/A	_	_	_	4D
<b>DUAL-MONITOR</b>	ADAPTER_								
DMA1327SD	_	13 to 27 in.	2 x 22 lb.	_	75x75, 100x100	-45° to +45°	-15° to +15°	180°	9D
AC/USB CHARGI	NG CLIP								
DMACUSB					N/A				9E

# TRIPP-LITE DISPLAY SOLUTIONS

#### **SPECIFICATIONS Continued**

SPECIFICALI	SPECIFICATIONS Continued								T =======
Model	Previous Model	Supported Screen Sizes	Weight Capacity	Mounting Profile (Surface to Display)	VESA Compliance	Tilt	Swivel	Rotate/ Screen Level	Feature Focus (pp. 4-16)
CPU MOUNT		'							
DCPU1	_	_	40 lb.	_	N/A	_	_	_	10A
THIN-CLIENT MO	TALLO				-9				
DMATC	_	_	11 lb.	_	75x75, 100x100	_			10B
TABLET MOUNTS			TTID.		73773, 1007100				100
	Ī	0.5 to 40 in	0.0.15	0.0 :	NI/A	 	l	0000	100
DDR0310SC		3.5 to 10 in.	2.2 lb.	9.8 in.	N/A	_	_	360°	10C
DDR1013SC	_	10 to 13.5 in.	3.1 lb.	23.4 in.	N/A	_	_	360°	10D
DDR0710SC	_	7 to 10 in.	2.2 lb.	4.8 in.	N/A	-90° to +90°	360°	360°	10E
DDR0810TRI	_	8 to 10 in.	2.2 lb.	_	N/A	-30° to +30°	30°	360°	10F
<b>WALL MOUNTS</b>	(FIXED)								
DWF1327M	DWF1323M	13 to 27 in.	88 lb.	0.6 in.	50x50, 75x75, 100x100	_	_	_	11A
DWF2655X	DWF2647X	26 to 55 in.	165 lb.	1.2 in.	200x200, 300x300, 400x200, 400x400	_	_	_	11B
DWFSC3255MUL		32 to 55 in.	99 lb./150 lb.*	1 in.	200x200, 300x300, 400x200, 400x400	_	_	_	5A
DWF3270X	DWF3260X	32 to 70 in.	165 lb.	1.2 in.	200x200, 300x300, 400x200, 400x400, 600x400	_		_	11C
	DWF3200A				, , , , , , , , , , , , , , , , , , , ,	_			
DWF3770L		37 to 70 in.	143 lb.	0.8 in.	300x300, 400x200, 400x400, 600x400, 800x400	_	_	_	11D
DWFSC3780MUL	_	37 to 80 in.	88 lb./200 lb.*	0.9 in.	300x300, 400x200, 400x400, 600x400	_	_	_	5B
DWF4585X	_	45 to 85 in.	200 lb.	1.4 in.	200x200, 300x300, 400x200, 400x400, 600x400, 800x400	_	_	_	11E
DWF60100XX	_	60 to 100 in.	350 lb.	1.3 in.	200x200, 300x300, 400x200, 400x400, 600x400, 800x400, 800x600, 900x600	_	_	_	11F
<b>CEILING MOUNT</b>	S								
DCTM		23 to 42 in.	66 lb.	24 to 34 in.	75x75, 100x100, 100x200, 200x200	-20° to 0°	90°	_	12A
DUNVPJT		20 (U 72 III.	55 lb.	27 to 04 III.	N/A	-20° to +20°	360°		12B
	(TU T)	_	ວວ ເມ.	_	IV/A	-20 10 +20	300	_	IZD
WALL MOUNTS	<u> </u>	l		T		<u>'</u>			
DWT1327S	DWT1323S	13 to 27 in.	88 lb.	1.4 in.	75x75, 100x100	-15° to +10°	_	_	12C
DWT2655XE	DWT2647XE	26 to 55 in.	165 lb.	1.8 in.	200x200, 300x300, 400x200, 400x400	-10° to 0°	_	_	12D
DWT2655XP	DWT2647XP	26 to 55 in.	165 lb.	2.5 in.	200x200, 300x300, 400x200, 400x400	-10° to +10°	_	_	13A
DWTSC3255MUL	_	32 to 55 in.	99 lb./150 lb.*	2.3 in.	200x200, 300x300, 400x200, 400x400	-15° to +10°	_	_	5C
DWT3270X	DWT3260X	32 to 70 in.	165 lb.	1.8 in.	200x200, 300x300, 400x200, 400x400, 600x400	-10° to 0°	_	_	13B
DWT3770X	DWT3763X	37 to 70 in.	200 lb.	1.8 in.	200x200, 300x300, 400x200, 400x400, 600x400, 800x400	-10° to 0°	_	_	13C
DWT3780XUL	_	37 to 80 in.	165 lb.	1.8 in.	200x200, 300x300, 400x200, 400x400, 600x400, 800x400	-10° to 0°	_	_	13D
DWTSC3780MUL		37 to 80 in.	88 lb./200 lb.*	2 in.	300x300, 400x200, 400x400, 600x400	-10° to +5°			5D
DWT4585X	_	45 to 85 in.	200 lb.	2.5 in.	200x200, 300x300, 400x400, 400x400, 600x400, 800x400	-10° to +10°	_	_	13E
DWT60100XX	_	60 to 100 in.	350 lb.	5.1 in.	200x200, 300x300, 400x200, 400x400, 600x400, 800x400, 800x600, 1000X400, 1000x600, 1000x800	-15° to +15°	_	_	13F
WALL MOUNTS	(SWIVEL/THE	/POTATE)							
	· · ·		99.11	444 45 04		4504 450	4000		4.4.5
DWM1327SE	DWM1323SE	13 to 27 in.	33 lb.	4.1 to 15.9 in.	75x75, 100x100	-15° to +15°	180°	_	14A
DWM1327SP	DWM1323SP	13 to 27 in.	33 lb.	2.2 to 22.8 in.	75x75, 100x100	-15° to +15°	180°	-2° to +2°	14B
DWM1742S	DWM1737S	17 to 42 in.	44 lb.	2.2 to 22.8 in.	100x100, 200x100, 200x200	-15° to +15°	180°	-3° to +3°	14C
DWM1742MA	DWM1737MA	17 to 42 in.	77 lb.	2.2 to 20.1 in.	75x75, 100x100, 200x100, 200x200	-15° to +15°	180°	-3° to +3°	14D
DWM1742MN	DWM1737MN	17 to 42 in.	115 lb.	3.5 in.	75x75, 100x100, 200x100, 200x200	-15° to +15°	80°	-4° to +4°	14E
DWM2655M	DWM2342M	26 to 55 in.	110 lb.	4.9 to 20.3 in.	200x200, 300x300, 400x200, 400x400	-15° to +15°	120°	-5° to +5°	14F
DWM3750S	_	37 to 50 in.	40 lb.	2.7 to 24.9 in.	75x75, 100x100, 200x200, 400x400	-15° to +15°	180°	360°	15A
DWM3770X		37 to 70 in.	165 lb.	4.6 to 20.6 in.	200x200, 300x300, 400x200, 400x400, 600x400	-15° to +15°	120°	-3° to +3°	15B
DWM3770PLX		37 to 70 in.	110 lb.	1.8 in.	200x200, 300x300, 400x200, 400x400, 600x400	.0 10 110		90°	15C
						10° to 15°	1000		
DWMSC3780MUL DWM60100XX	_	37 to 80 in. 60 to 100 in.	88 lb./200 lb.* 275 lb.	3 to 21.6 in. 2.8 to 24.6 in.	300x300, 400x200, 400x400, 600x400, 800x400 200x200, 300x300, 400x200, 400x400, 600x400,	-10° to +5° -15° to +5°	180° 90°	-4° to +4° -3° to +3°	15D
RAIL WALL MOL	JNTS				600x900, 800x400, 800x600				
DMR1024X2	_	10 to 24 in.	2 x 17.6 lb.	3.35 in.	75x75, 100x100	-15° to +15°	20°	360°	15E
DMR1015X3		10 to 15 in.	3 x 17.6 lb.	3.35 in.	75x75, 100x100	-15° to +15°	20°	360°	15F
MONITOR RISER	29	10 10 10 111.	0 X 17.0 lb.	0.00 III.	10/10, 100/100	10 10 10		000	101
	10		40 15		NI/A				404
MR1612	_	_	40 lb.	_	N/A	_			16A
MR1612D1	_	_	40 lb.	_	N/A	_	_	_	16B
MR1208TRAY	_		40 lb.	_	N/A	_		_	16C
MR1815SWVL	_	_	88 lb.	_	N/A	_	360°	_	16D
MR1220M	_	_	44 lb.	_	N/A	_	_	_	16E
MR1411M	_	_	44 lb.	_	N/A	_	_	_	16F
MR1812M	_	_	44 lb.	_	N/A	_	_	_	16G
MR2208G	_	_	40 lb.	_	N/A				16H
122000			TO ID.		TN/T				1011

#### **Mobile Floor Stands**

- Bring the message to the audience with the convenience and placement versatility of an A/V stand on wheels.
- Display height is adjustable for optimized viewing.
- DMCS60100XX accommodates displays and popular brands of interactive whiteboards.














## **Security Wall Mounts**




- Deter theft of displays, especially in public areas with unguarded traffic.
- Solid steel security bar slides through the mounting brackets and is secured with a combination lock (included).
- Display keeps the mount and security features out of sight for a sleek, professional appearance.











# **Desktop & Clamp-On Mounts**

- Increase available desk/table space in office workstation applications.
- Convenient one-touch display adjustment provides easy view optimization and improved ergonomics for varied tasks throughout the workday.



































# WorkWise™ Adjustable-Height Workstations

- Adjust workstation height to alternate between sitting and standing throughout the workday.
- Convert a fixed-height desk or other flat work surface into a custom-height workstation.
- Extra-large keyboard tray accommodates most popular brands.









17.6 lb.

75x75, 100x100



#### **Potential Benefits of Standing**

Initial studies and user reports suggest that standing for part of the day has a range of potential benefits:

29 lb

- Improved alertness, concentration and productivity
- Lower blood pressure and reduced risk of diabetes and heart disease
- Increased comfort, improved morale and reduced absenteeism
- Improved posture and toning of key muscle groups
- Decreased risk of repetitive stress injuries
- Reduced fatigue, eyestrain, aches and pains





#### 9C WWSSD3622 (Desktop Workstation)



Monitor Platform Height Adjusts Up to 16 in. Above Work Surface

> Monitor Platform is  $36 \times 22$  in. Keyboard Tray is  $27 \times 9$  in.



#### **Dual-Monitor Adapter**

- Modify a single-screen mount to accommodate two monitors without using additional desk/table space.
- Adapter attaches to a VESA mount.



#### **AC/USB Charging Clip**

- Mount clip to a display-mount pole for convenient access to charging power.
- Two NEMA 5-15R outlets (one in rear) and two USB ports (3.4A total) make it easy to keep devices charged.



# **CPU Mount & Thin-Client Mount**

- Computer mounts save space in workstations.
- DCPU1 allows CPU to be mounted on a wall, desk or rail.
- DMATC secures a thin-client computer to a pole or wall, under a desk or to a display mount's VESA plate.







### **Tablet Mounts (Full Motion)**

- View your tablet without using desk/table space.
- Convenient one-touch display adjustment provides easy view optimization and improved ergonomics for varied tasks throughout the day.










#### Wall Mounts (Fixed)

- Low-profile mounting keeps the unit out of sight for a sleek, professional appearance.
- Horizontal adjustment compensates for off-center wall studs.
- For fixed security wall mounts, see DWFSC3255MUL and DWFSC3780MUL on page 5.














Bubble

Adjustable Display


**Brackets** 

800x600, 900x600

## Ceiling Mounts (Full Motion)

- Full-motion articulation provides the most flexible view optimization.
- Mount for displays frees up wall and floor space in digital signage applications.
- Mount for projectors allows precise image positioning in classroom, boardroom and commercial settings.







# Wall Mounts (Tilt)

- Tilt adjustment provides improved viewing angles for applications where the audience is below the display.
- Low-profile mounting keeps the unit out of sight for a sleek, professional appearance.
- Horizontal adjustment compensates for off-center wall studs.
- For security wall mounts with tilt adjustment, see DWTSC3255MUL and DWTSC3780MUL on page 5.



200x200, 300x300,

400x200, 400x400














## Wall Mounts (Tilt) continued














# Wall Mounts (Swivel/Tilt/Rotate)

- Full-motion articulation provides the most flexible view optimization.
- Increase available desk/table space in office applications.
- One-touch repositioning provides convenient display adjustment for varied tasks throughout the workday.
- For a full-motion security wall mount, see DWMSC3780MUL on page 5.


























# Monitor Risers • Elevate screens to reduce neck and eye strain. • Risers accommodate most monitors.












For the most complete, up-to-date specifications, visit www.tripplite.com.

Copyright © 2019 Tripp Lite. All trademarks are the sole property of their respective owners. Photos and illustrations may differ from actual products. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice











**Tripp Lite Corporate Headquarters** 

1111 W. 35th Street, Chicago, IL 60609 USA | 773.869.1773 www.tripplite.com