

EMEA Tripp Lite Series

Providing your customers with the full solution



Powering Business Worldwide

Table of Contents

IT Infrastructure	5-47
Server Racks & Cabinets	6-16
Floor-Standing Enclosures	6
Open-Frame Racks	7
Wall-Mount Enclosures	8-9
Aisle Containment Systems	10
Rack Accessories	11-16
KVM Switches & Console Servers	17-22
Console KVM Switches	17
Rackmount KVM Switches	18
Secure NIAP KVM Switches	19
Console Servers	20
KVM Accessories	21-22
Copper Networks	23-31
Copper Patch Panels	23
Copper Couplers	24
Cat5e Copper Cables	25
Cat6 Copper Cables	26-27
Cat6a Copper Cables	28-29
Cat8 Copper Cables	30
Cisco Console Rollover Cables	31
Fiber Networks	32-43
Fiber Patch Panels	32
Fiber Cassette Enclosures & Sleeves	32
Fiber Cassettes	33
Preloaded Fiber Panels	34
OS2 Singlemode Patch Cables	35-36
OM3 Multimode Fiber Patch Cables	37
OM4 Multimode Fiber Patch Cables	38
OM5 Multimode Fiber Patch Cables	39
MTP/MTO Cables	40-41
Fiber Couplers	42
Network Adapters	43
Media Converters	44
Transceiver Modules	45
Direct Attach Cables (DACs)	46
Power Cords	47
Work from anywhere (WFA), Retail & Education	48-68
Docking Stations, USB Hubs & Multiport Adapters	49-51
Docking Stations	49
USB Hubs	50
Multiport Adapters	51
Power Solutions	52-53
Desktop Charging Stations	52
Charging Stations & Carts	52
Desktop KVM Switches	53
USB Cables	54-60
USB-A 2.0 Cables	54
USB-A 2.0 Extension Cables	54
USB-C Cables	55
Lightning Cables	56
USB 3.1 Gen 1 Cables	57
USB 3.2 Gen 2 Cables	58
USB-C 3.0 Extension Cables	59
Thunderbolt Cables	60
USB Couplers	60

USB Adapters	61-62
USB Adapters	61
USB Panel Mounts	62
USB Extenders	63
Power Cords	64
Height-Adjustable Workstations	65
Desktop Monitor Mounts and Mobile Workstations	66-68
Desktop Monitor Mounts	66
Rolling TV Stands and Cart	67
Mobile Workstations	68
Pro AV & Digital signage	69-95
Mounts, stand and carts, workstations	70-73
Wall Mounts	70-71
TV Stands and Carts	72
Tablet & Smartphone Mounts	73
DVI	74-73
DVI Splitters	74
DVI Cables	74
DVI Adapter Cables	75
DVI Adapters	75
VGA	76-77
VGA Switches	76
VGA Extenders	76
VGA Cables	77
HDMI	78-85
HDMI Splitters	78
HDMI Video Extenders	79-80
HDMI Cables	81-82
HDMI Adapters Cables	83
HDMI Adapters	84
HDMI Switches	85
DisplayPort	86-91
DisplayPort Splitters	86
DisplayPort Switches	86
DisplayPort Cables	87
DisplayPort Adapter Cables	88
DisplayPort Adapters	89-90
DisplayPort Extenders	91
Audio	92-93
Audio Cables	92
Audio Adapter Cables	93
Wireless Video Extenders	94
Video Couplers	95
Industrial-Grade IT Solutions	96-108
Server Racks & Cabinets	97
SmartRack Industrial Enclosures	97
Copper Network Cables	98-99
Cat5e Copper Cables	98
Cat6 Copper Cables	98
M12 X-Code Cat6 Copper Cables	99
M12 X-Code Cat6a Copper Cables	100
Fiber Network Cables	101
OM3 Multimode Fiber Patch Cables	101
Industrial Network Switches	102
Transceivers	103
USB Cables	104-105
USB 3.1 Gen 1 Cables	104
USB Adapters	104
USB Hubs	105

USB Extenders	105
AV Solutions	106
HDMI Cables	106
Couplers	106
Power over Ethernet (PoE)	107-108
PoE Injectors & Extenders	107
WAP Enclosures	108
Healthcare	109-111
Power Solutions	110-111
UPS Systems	110
Isolation Transformers	110
Power Inverter/Chargers	111



Only for Outside of EU

A photograph of two men in a server room. One man is seen from the back, wearing a dark blue shirt. The other man, wearing glasses and a dark sweater, is looking at something in his hands. The background is filled with server racks and bright overhead lights, creating a blue-toned, professional atmosphere.

IT Infrastructure

Server Racks & Cabinets

KVM Switches & Console Servers

Copper Networks

Fiber Networks

Media Converters

Transceiver Modules

Direct Attach Cables (DACs)

Power Cords

Floor-Standing Enclosures

Eaton's premium-grade floor and wall mount server racks and cabinets organize and secure IT equipment wherever it is located, from high-density data centers to the tightest of spaces at the edge of your network.



Key points:

- Compatible designs
- Tool-less mounting / Essential equipment included
- Vertical cable management bars
- Fully assembled

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Dimensions (cm)				Static load (Kg)	Doors		Side panels	Mounting rails	Color
	Height		Width (cm)	Depth		Type				
	U	(cm)		Rack Depth						
SR12UB	12U	64 cm	60 cm	Mid	85 cm	454 kg	Vented	Yes	Square	Black
SR14UBDP	14U	72 cm	60 cm	Standard	111 cm	454 kg	Vented	Yes	Square or 10-32 holess	Black
SR18UB	18U	90 cm	60 cm	Mid	85 cm	454 kg	Vented	Yes	Square	Black
SR24UB	24U	116 cm	60 cm	Mid	85 cm	454 kg	Vented	Yes	Square	Black
SR25UB	25U	124 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR42UB	42U	199 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR42UBDP	42U	199 cm	60 cm	Deep	123 cm	1361 kg	Vented	Yes	Square	Black
SR42UBDP48	42U	199 cm	60 cm	Extra Deep	120 cm	1361 kg	Vented	Yes	Square	Black
SR42UBDPWD	42U	199 cm	75 cm	Deep	123 cm	1361kg	Vented	Yes	Square	Black
SR42UBEXP	42U	199 cm	60 cm	Standard	109 cm	1361 kg	Vented	-	Square or 10-32 holes	Black
SR42UBG	42U	199 cm	60 cm	Standard	109 cm	1361 kg	Acrylic	Yes	Square or 10-32 holes	Black
SR42UBMD	42U	199 cm	60 cm	Mid	91 cm	1361 kg	Vented	Yes	Square	Black
SR42UBSD	42U	199 cm	60 cm	Shallow	83 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR42UBWD	42U	199 cm	75 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR42UBWDVRT	42U	199 cm	75 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR45UB	45U	213 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR45UBDPWD	45U	213 cm	75 cm	Deep	123 cm	1361 kg	Vented	Yes	Square	Black
SR45UBSD	45U	213 cm	60 cm	Shallow	83 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR48UB	48U	226 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR48UBDP48	48U	226 cm	60 cm	Extra Deep	121 cm	1361 kg	Vented	Yes	Square	Black
SR48UBDPWD	48U	226 cm	75 cm	Deep	123 cm	1361 kg	Vented	Yes	Square	Black
SR48UBEXPND	48U	226 cm	60 cm	Standard	109 cm	1361 kg	-	-	Square or 10-32 holes	Black
SR48UBWD	48U	226 cm	75 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black

Rack on a Shock Pallet

SR25UBSP1	25U	124 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR42UBSP1	42U	199 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
SR48UBSP1	48U	226 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black

Knock-Down (Ships unassembled)

SR42UBKD	42U	199 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
----------	-----	--------	-------	----------	--------	---------	--------	-----	-----------------------	-------

Seismic-Certified

SR42UBZ4	42U	199 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
----------	-----	--------	-------	----------	--------	---------	--------	-----	-----------------------	-------

Quiet Racks

SRQP42UB	42U	199 cm	60 cm	Standard	109 cm	1088 kg	Solid	Yes	Square or 10-32 holes	Black
----------	-----	--------	-------	----------	--------	---------	-------	-----	-----------------------	-------

Co-Location

SR42UBCL	42U	199 cm	60 cm	Standard	109 cm	1361 kg	Vented	Yes	Square or 10-32 holes	Black
----------	-----	--------	-------	----------	--------	---------	--------	-----	-----------------------	-------

Open-Frame Racks

Free-standing open-frame-post rack stores and organizes U of 19-inch rack equipment in labs, test setups, network closets and other secure IT areas with limited floor space where you need easy access to equipment.



Key points:

- Compatible designs
- Tool-less mounting / Essential equipment included
- Fully assembled

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Dimensions (cm)					Number of Vertical Mounting Rails	Static load (Kg)	Mounting rails	Color
	Height		Width (cm)	Depth					
	U	(cm)		Rack Depth	(cm)				
SR2POST12	12U	8 cm	9 cm	Standard	63 cm	2	50 kg	M6 square	Black
SR2POST13	13U	71 cm	52 cm	Extra Deep	12 cm	2	363 kg	12-24 threaded	Black
SR2POST25	25U	124 cm	51 cm	Extra Deep	12 cm	2	363 kg	12-24 threaded	Black
SR2POST	45U	213 cm	52 cm	Extra Deep	12 cm	2	363 kg	12-24 threaded	Black
SR4POST13	13U	71 cm	51 cm	Standard	56-91 cm	4	454 kg	M6 square	Black
SR4POST25	25U	125 cm	51 cm	Standard	56-91 cm	4	454 kg	M6 square	Black
SR4POST	45U	214 cm	51 cm	Standard	56-91 cm	4	454 kg	M6 square	Black
SR4POST48HD	48U	229 cm	61 cm	Standard	90 cm	4	1360 kg	M6 square	Black
SR4POST50HD	50U	236 cm	61 cm	Standard	90 cm	4	1360 kg	M6 square	Black
SR4POST52HD	52U	246 cm	61 cm	Standard	90 cm	4	1360 kg	M6 square	Black
Expandable									
SR42BMDEXPNDR3	42U	201 cm	66 cm	Mid	91 cm	4	1 360 kg	10 - 32 hole	Black
SR42UBEXPND	42U	199 cm	66 cm	Standard	105 cm	4	1 360 kg	10 - 32 hole	Black
Expandable & Knock-Down (Ships unassembled)									
SR12UBEXPNDKD	12U	65 cm	51 cm	Standard	91 cm	4	454 kg	Square	Black

Wall-Mount Enclosures

Connects a PC or server to a PDU or UPS system in a data rack or cabinet.



Key points:

- Fully assembled
- Horizontal and Vertical mounting system
- Hinged back for easy access
- Wide selection of sizes
- PCI / EIA / TIA compliant
- 5 years warranty

Ideal for:

- Network closets
- Network equipment
- Server rooms
- White space

Part number	Dimensions (cm)					Static load (Kg)	Doors		Side panels	Mounting rails	Cable entry	Color
	Height		Width (cm)	Depth			Front	Rear				
	U	(cm)		Rack Depth	(cm)							
Horizontal-Mount												
SRW6U	6U	37 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black
SRW6UDP	6U	37 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black
SRW6UG	6U	37 cm	60 cm	Shallow	45 cm	91 kg	Acrylic	Static	Yes	Square or 12-24 holess	Top and bottom routing ports	Black
SRW6UW	6U	37 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			White
SRW6UWG	6U	37 cm	60 cm	Shallow	45 cm	91 kg	Acrylic	Static	Yes			White
SRW9U	9U	51 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black
SRW9UDP	9U	51 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black
SRW9UDPW	9U	51 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes	Square or 12-24 holess	Top and bottom routing ports	White
SRW9UG	9U	51 cm	60 cm	Shallow	45 cm	91 kg	Acrylic	Static	Yes			Black
SRW9UDPVRT	9U	51 cm	75 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black
SRW10US	10U	55 cm	60 cm	Shallow	55 cm	91 kg	Vented	Hinged	Yes	Square or 12-24 holess	Top and bottom routing ports	Black
SRW10USG	10U	55 cm	60 cm	Shallow	60 cm	91 kg	Acrylic	Hinged	Yes			Black
SRW012UBRKTSHL	12U	63 cm	50 cm	Shallow	38 cm	68 kg	Open	Hinged	-			Black
SRW12U	12U	64 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black
SRW12U13	12U	64 cm	60 cm	Shallow	33 cm	91 kg	Vented	Static	Yes			Black
SRW12U13G	12U	64 cm	60 cm	Shallow	33 cm	91 kg	Acrylic	Static	Yes			Black
SRW12UDP	12U	64 cm	60 cm	Shallow	55 cm	91 kg	Vented	Static	Yes			Black
SRW12UG	12U	64 cm	60 cm	Shallow	45 cm	91 kg	Acrylic	Static	Yes			Black
SRW12UHD	12U	67 cm	63 cm	Mid	92 cm	227 kg	Vented	Static	Yes			Black
SRW12US	12U	64 cm	60 cm	Shallow	55 cm	91 kg	Vented	Hinged	Yes	Square or 12-24 holess	Top and bottom routing ports	Black
SRW12US33	12U	64 cm	60 cm	Mid	85 cm	113 kg	Vented	Hinged	Yes			Black
SRW12US33G	12U	64 cm	60 cm	Mid	85 cm	113 kg	Acrylic	Hinged	Yes			Black
SRW12USDP	12U	64 cm	60 cm	Shallow	65 cm	91 kg	Vented	Hinged	Yes			Black
SRW12USDPG	12U	64 cm	60 cm	Shallow	65 cm	91 kg	Acrylic	Hinged	Yes			Black
SRW12USG	12U	64 cm	60 cm	Shallow	55 cm	91 kg	Acrylic	Hinged	Yes			Black
SRW15US	15U	77 cm	60 cm	Shallow	55 cm	91 kg	Vented	Hinged	Yes			Black
SRW15USG	15U	77 cm	60 cm	Shallow	55 cm	91 kg	Acrylic	Hinged	Yes			Black

Part number	Dimensions (cm)					Static load (Kg)	Doors		Side panels	Mounting rails	Cable entry	Color		
	Height		Width (cm)	Depth			Front	Rear						
	U	(cm)		Rack Depth	(cm)									
Open-frames														
SRW012UHD	12U	63 cm	51 cm	Shallow	46 cm	91 kg	Open	-	-	12-24 holess	Top and bottom routing ports	Black		
SRW012US	12U	78 cm	50 cm	Shallow	52 cm	68 kg	Open	-	-			Black		
SRW18UHD	18U	94 cm	63 cm	Mid	92 cm	227 kg	Vented	Static	Yes	Square holess / 12-24 threaded holes	Top and bottom routing ports Side	Black		
SRW18US	18U	90 cm	60 cm	Shallow	55 cm	113 kg	Vented	Hinged	Yes			Black		
SRW18US13	18U	90 cm	60 cm	Shallow	33 cm	113 kg	Vented	Hinged	Yes			Black		
SRW18USDP	18U	90 cm	60 cm	Shallow	66 cm	113 kg	Vented	Hinged	Yes			Black		
SRW18USDPG	18U	90 cm	60 cm	Shallow	66 cm	113 kg	Acrylic	Hinged	Yes			Black		
SRW18USG	18U	90 cm	60 cm	Shallow	55 cm	113 kg	Acrylic	Hinged	Yes			Black		
SRW21U	21U	104 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black		
SRW26US	26U	100 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black		
SRW26USDP	26U	126 cm	60 cm	Shallow	65 cm	113 kg	Vented	Hinged	Yes			Black		
Expandable 8/12/22U														
SRW08U22	8U		51 cm	Shallow	46 cm	68 kg	Open	Static	-	Threaded 12-24 holes	Top and bottom routing ports	Black		
SRW08U22DP	8U	45 cm (8U) 63 cm (12U)	51 cm	Shallow	61 cm	68 kg	Open	Static	-			Black		
SRW08U22MD	8U	107 cm (22U)	51 cm	Shallow	30 cm	68 kg	Open	Static	-			Black		
SRW08U22SD	8U		51 cm	Shallow	45 cm	68 kg	Open	Static	-			Black		
SRW08UBRKTSHLF	8U	44 cm	50 cm	Shallow	38 cm	68 kg	Open	Hinged	-			Black		
Knock-Down (Ships unassembled)														
SRW6UKD	6U	37 cm	60 cm	Shallow	45 cm	91 kg	Vented	Static	Yes			Black		
Vertical-Mount														
SRWF2U	2U	73 cm	65 cm	Shallow	11 cm	68 kg	Vented	Static	Yes	Supports M6 and 12-24 mounting	Top and bottom routing ports Side	Black		
SRWF2U36	2U	109 cm	65 cm	Standard	11 cm	68 kg	Vented	Static	Yes			Black		
SRWF6UMOD	3U	90 cm	51 cm	Shallow	18 cm	68 kg	Vented	Static	Yes			Black		
SRWF4U	4U	73 cm	65 cm	Shallow	20 cm	68 kg	Vented	Static	Yes			Black		
SRWF4U36	4U	109 cm	65 cm	Standard	20 cm	68 kg	Vented	Static	Yes			Black		
SRWF5U	5U	81 cm	74 cm	Shallow	33 cm	68 kg	Vented	Static	Yes			Black		
SRWF5U36	5U	110 cm	65 cm	Shallow	25 cm	68 kg	Vented	Static	Yes			Black		
SRWF6U	6U	73 cm	65 cm	Shallow	29 cm	68 kg	Vented	Static	Yes			Black		
SRWF6U36	6U	110 cm	68 cm	Standard	30 cm	68 kg	Vented	Static	Yes			Black		
SRWF12U38	12U	97 cm	50 cm	Standard	41 cm	181 kg	Vented	Static	Yes			Black		
SRWF16U38	16U	97 cm	50 cm	Standard	59 cm	181 kg	Vented	Static	Yes			Black		
SRW02UBRKT	2U	54 cm	51 cm	Shallow	11 cm	34 kg	Vented	Static	Yes			Square holes	Open top and bottom	Black
SRW04UBRKT	4U	54 cm	51 cm	Shallow	20 cm	34 kg	Vented	Static	Yes			Square holes		Black

Part number	Description	Enclosure	
		Floor-Standing Open-Frames	Wall-Mount
Wall Shelves & Brackets			
SRW04UBRKTSHLF	4U Wall-Mount Bracket with Shelf for Small Switches and Patch Panels, Hinged	-	Yes
SRWALLBRKT2U	SmartRack 2U Vertical Wall-Mount Rack Bracket	-	Yes
SRWALLBRKT4U	SmartRack 4U Vertical Wall-Mount Rack Bracket	-	Yes
SRWALLBRKT6U	SmartRack 6U Vertical Wall-Mount Rack Bracket	-	Yes

Aisle Containment System

Keeps hot and cool air separated for better temperature control and equipment performance in hot aisle/cold aisle configurations.






Key points:

- Self standing structure
- Flexible and expandable
- Fast assembly







Ideal for:







- Server Room
- Data Center
- White Space










	Part number	Description	Enclosure
			Floor Standing Open-Frames
600 mm Racks			
	SRCTMTCVR600	Roof Panel Kit for Hot/Cold Aisle Containment System - Standard 600 mm Racks	Yes
	SRCTMTFRM	Frame End Kit for Hot/Cold Aisle Containment System	Yes
	SRCTMTR600SH	Short Riser Panels for Hot/Cold Aisle Containment System - Standard 600 mm Racks, Set of 2	Yes
	SRCTMTR600TL	Tall Riser Panels for Hot/Cold Aisle Containment System - Standard 600 mm Racks, Set of 2	Yes
	SRCTMTSDD	Sliding Double-Door Kit for Hot/Cold Aisle Containment System	Yes
	SRCTMTLBM	Telescopic Beam Kit for Hot/Cold Aisle Containment System	
750 mm Racks			
	SRCTMTCVR750	Roof Panel Kit for Hot/Cold Aisle Containment System - Wide 750 mm Racks	Yes
	SRCTMTR750SH	Short Riser Panels for Hot/Cold Aisle Containment System - Wide 750 mm Racks, Set of 2	Yes
	SRCTMTR750TL	Tall Riser Panels for Hot/Cold Aisle Containment System - Wide 750 mm Racks, Set of 2	Yes
Racks			
	SRCTMTCVR300	Roof Panel Kit for Hot/Cold Aisle Containment System - Standard 300 mm Rack Coolers	Yes
	SRCTMTR300SH	Short Riser Panels for Hot/Cold Aisle Containment System - Standard 300 mm Rack Coolers, Set of 2	Yes
	SRCTMTR300TL	Tall Riser Panels for Hot/Cold Aisle Containment System - Standard 300 mm Rack Coolers, Set of 2	Yes

Rack Accessories











Accessories for your rack for a tidy and professional look






	Part number	Description	Enclosure	
			Floor-Standing Open-Frames	Wall-Mount
Cable management				
	NCM-JHW08-25	J-Hook Cable Support - 3/4", Wall Mount, Galvanized Steel, 25 Pack	-	-
	NCM-JHW40-25	J-Hook Cable Support - 4", Wall Mount, Galvanized Steel, 25 Pack	-	-
	P350-10N-10	Hook-and-Loop Cable Ties, 10" L x 5/8" W - 10-Pack	Yes	Yes
	P352-07N-100	7.5" Nylon Cable Ties - 100-Pack	Yes	Yes
	SRCABLEDUCT1U	SmartRack 1U Horizontal Cable Manager - Finger duct with cover	Yes	Yes
	SRCABLEDUCT1UHD	SmartRack 1U High Capacity Horizontal Cable Manager - Finger duct with dual-hinge cover	Yes	Yes
	SRCABLEDUCT2UHD	SmartRack 2U High Capacity Horizontal Cable Manager - Finger duct with dual-hinge cover	Yes	Yes
	SRCABLEDUCTVRT	SmartRack 6 ft. (1.83 m) Vertical Cable Manager - Double finger duct with cover & toolless mounting	Yes	-
	SRCABLERING1U	SmartRack 1U Horizontal Cable Manager - Flexible ring type	Yes	Yes
	SRCABLERING2U	SmartRack 2U Horizontal Cable Manager - Flexible ring type	Yes	Yes
	SRCABLERINGLG	Cable Management D-Rings for Rack Enclosures - Button Mount, Large, 3 x 4 in., 12 Pack	Yes	Yes
	SRCABLERINGSM	Cable Management Rings for Rack Enclosures - Button Mount, Small, 2 x 4 in., 12 Pack	Yes	Yes
	SRCABLERINGVRT	SmartRack 6 ft. (1.83 m) Vertical Cable Manager - Flexible ring type & toolless mounting	Yes	-
	SRCABLETRAY1U	SmartRack 1U Horizontal Cable Management Tray	Yes	Yes
	SRCABLEVRT12	SmartRack 12-in. (30.48 cm) Width High Capacity Vertical Cable Manager - Double finger duct with cover	Yes	-
	SRCABLEVRT3	SmartRack 3-in. (7.62 cm) Wide High Capacity Vertical Cable Manager - Double finger duct	Yes	-
	SRCABLEVRT6	SmartRack 6-in. (15.24 cm) Wide High Capacity Vertical Cable Manager - Double finger duct with cover	Yes	-
	SRVRTBAR	SmartRack 42U Vertical Cable Management Bars	Yes	-
	SRVRTBAR45	SmartRack 45U Vertical Cable Management Bars	Yes	-
	SRVRTBAR48	SmartRack 48U Vertical Cable Management Bars	Yes	-

	Part number	Description	Enclosure	
			Floor-Standing Open-Frames	Wall-Mount
Roof Mounted Cable Routing				
	SRLADDERATTACH	SmartRack Hardware Kit - Connects SRCABLELADDER to a wall or Open Frame Rack	Yes	
Locking System				
	SRHANDLE1	Replacement Lock for SmartRack Server Rack Cabinets - Front and Back Doors, 2 Keys, Version 1	Yes	-
	SRHANDLE2	Replacement Lock for SmartRack Server Rack Cabinets - Front and Back Doors, 2 Keys, Version 2	Yes	-
	SRHANDLE3	Replacement Lock for SmartRack Server Rack Cabinets - Front and Back Doors, 2 Keys, Version 3	Yes	-
	SRHANDLE4	Replacement Lock for SmartRack Server Rack Cabinets - Front and Back Doors, 2 Keys, Version 4	Yes	-
	SRRAILDPTH1U	SmartRack 1U Mounting Rail Deep Adapter Kit for Server Racks, 4 in. (10.2 cm)	Yes	-
	SRRAILDPTH2U	SmartRack 2U Mounting Rail Deep Adapter Kit for Server Racks, 4 in. (10.2 cm)	Yes	-
	SRSWITCH	SmartRack Magnetic Door Switch Kit for front and rear doors; requires ENVIROSENSE, TLNETEM, E2MTHDI or E2MTDI	Yes	-
	SRSWITCH	SmartRack Magnetic Door Switch Kit for front and rear doors; requires ENVIROSENSE, TLNETEM, E2MTHDI or E2MTDI	Yes	-
	SRWCOMBO	Replacement Combination Lock for SmartRack Wall-Mount Server Rack Cabinets - Front Door	-	Yes
	SRCOMBO	SmartRack Door Handles with Combination Lock - 2-pack for front and rear doors with bypass key	Yes	-
	SRGP1KO	SmartRack Cable Gland Plate for NEMA-Rated Enclosure Cabinets, 6 Ports	-	Yes
	SRGP2KO	SmartRack Cable Gland Plate for NEMA-Rated Enclosure Cabinets, 3 Ports	-	Yes
	SRGP3RM	SmartRack Cable Entry Gland Plate for NEMA-Rated Enclosure Cabinets, 21-Port Membrane	-	Yes
	SRGP4PLASTIC	SmartRack Cable Entry Gland Plate for NEMA-Rated Enclosure Cabinets, Waterproof	-	Yes


	Part number	Description	Enclosure	
			Floor-Standing Open-Frames	Wall-Mount
Airflow Management				
	SRXFAN3U	SmartRack 3U Fan Panel - 3 208-240V high-performance fans; 315 CFM; C14 inlet	Yes	Yes
	SRXFANROOF	SmartRack Roof-Mounted Fan Panel - 6 208/240V high-performance fans; 420 CFM; C14 inlet	Yes	-
	SRXFANWM	Wall-Mount Roof Fan Kit - Dual 230V High-Performance Fans, 210 CFM, 3 ft. (0.91 m) Cord, C14 Input	-	Yes
	SR1UBRUSH	1U Cable Pass-Through Panel with Brush Strip	Yes	Yes
	SR1UPANEL10	1U Blanking Panel Kit, Toolless-Mounting, 10 pieces	Yes	Yes
	SR1UPANEL50	1U Blanking Panel Kit, Toolless-Mounting, 50 pieces	Yes	Yes
	SR1UPANEL200	1U Blanking Panel Kit, Toolless-Mounting, 200 pieces	Yes	Yes
	SRBRUSHWM	SmartRack Brush Strip Plate for Wall-Mount Racks	Yes	Yes
	SRXUPANEL	19 in. Blanking Panel Kit, 4 Pieces	Yes	Yes
	SRCOOLMVKIT	SmartRack Magnetic Vinyl Kit for Rack Airflow Management	Yes	-
	SRDUCTN7009	9U Air Inlet Duct Kit - Nexus 7000-Series Switches and Tripp Lite Wide Racks	Yes	-
	SRFILTER	SmartRack Enclosure Filter Kit	Yes	-
	SRSKIRT	SmartRack Enclosure Skirt Kit	Yes	-
	SRSKIRT3	SmartRack Enclosure Skirt Kit - use with 3 in. casters	Yes	-
	SRSKIRTEU	SmartRack Enclosure Skirt Kit for Euro-Series Wide Server Rack, 800 mm Width	Yes	-
	SRSWITCHDUCT	SmartRack Side Airflow Ducting Kit for Network Switches	Yes	-



	Part number	Description	Enclosure	
			Floor-Standing Open-Frames	Wall-Mount
Mounting Options				
	B018-000-1P5	1U Rack-Mount Device Rack Extension Bracket, 1.5 in.	Yes	Yes
	SR2319ADAPT	Adapter Kit for Mounting 19 in. Rack Equipment in 23 in. Racks	Yes	-
	SRBOLTDOWN	SmartRack Bolt-Down Kit - Secures stabilizing brackets or plates to facility floor	Yes	Yes
	SRCAGENUTSMM	SmartRack Square Hole Hardware Kit with 50 M5 screws and washers	Yes	Yes
	SRCAGENUTS	SmartRack Square Hole Hardware Kit with 50 M6 screws and washers	Yes	Yes
	SRCAGENUTS1224	SmartRack Square Hole Hardware Kit with 50 pcs 12-24 screws and washers	Yes	Yes
	SRCASTER	SmartRack Rolling Caster Kit, 4 pack	Yes	-
	SRCASTERHDKIT	SmartRack Heavy-Duty Rolling Caster Kit, 4 pack	Yes	-
	SRDINRAIL2U	Adjustable Rack-Mount DIN Rail Kit – Top Hat, Mini Top Hat and G-Style Rails	Yes	Yes
	SREXTENDER	SmartRack Rack Enclosure Extension Frame - Increases rack external & maximum mounting depth	Yes	-
	SRSCREWS	SmartRack Threaded Hole Hardware Kit - 50 each #12-24 screws	Yes	Yes
	SRSTABILIZE	SmartRack Anti-Tip Stabilizing Plate Kit - Provides extra stability for standalone enclosures	Yes	-
	SRVTRAIL23	SmartRack 23 in. Wide Mounting Rail Kit		


Part number	Description	Enclosure	
		Floor-Standing Open-Frames	Wall-Mount
Shelves			
	SR16SHELF 3U Rack-Mount Configurable Storage Shelf for Personal Electronics	Yes	Yes
	SRDRAWER2U SmartRack 2U Locking Rack-Mount Storage Drawer	Yes	Yes
	SRDRAWER4U SmartRack 4U Locking Rack-Mount Storage Drawer	Yes	Yes
	SRSHelf2P SmartRack 2U Cantilever Fixed Shelf (60 lbs / 27.2 kgs capacity; 18-in. / 457 mm depth.)	Yes	Yes
	SRSHelf2P1U SmartRack 1U Cantilever Fixed Shelf (40 lbs / 18.1 kgs capacity; 12-in. / 305 mm depth.)	Yes	Yes
	SRSHelf2P1USHRT SmartRack Cantilever Fixed Steel Rack Shelf - 1U, Vented, 7 in. (17.8 cm) Deep, Holds up to 40 lb. (18 kg)	Yes	Yes
	SRSHelf2P1UTM SmartRack 1U Cantilever Toolless Mount Fixed Shelf (30 lbs / 13.6 kgs capacity; 12 in./305 mm depth)	Yes	Yes
	SRSHelf2PCENTER SmartRack Center-Mounted Steel Rack Shelf - 2U, Vented, 21.5 in. Deep, Holds up to 100 lb. (45 kg)	Yes	Yes
	SRSHelf2PDP 2U Cantilever Fixed Shelf (60 lbs / 27.2 kgs capacity; 21 in. / 533.4 mm depth.)	Yes	-
	SRSHelf2PTM SmartRack 2U Cantilever Toolless Mount Fixed Shelf (50 lbs /22.7 kgs capacity; 18 in./457 mm depth)	Yes	-
	SRSHelf2PUNIV SmartRack Universal-Mount Steel Rack Shelf - 2U, Vented, 21.7 in. Deep, Holds up to 100 lb. (45 kg)	Yes	Yes
	SRSHelf2PX2 SmartRack 2U Cantilever Double-sided Fixed Shelf (60 lbs / 27.2 kgs capacity each side; 36 in./914 mm depth)	Yes	-
	SRSHelf4PHD SmartRack Heavy-Duty Fixed Shelf (250 lbs / 113.4 kgs capacity; 26 in/660 mm depth)	Yes	-
	SRSHelf4PHDTM SmartRack Fixed Heavy-Duty Toolless Mount Shelf (250 lbs / 113.4 kgs capacity; 26 in./660 mm depth)	Yes	-
SRSHelf4PHDVENT SmartRack Adjustable-Deep Steel Rack Shelf - 1U, Vented, 250 lb. (113 kg) Capacity	Yes	-	
SRSHelf4PKYBD SmartRack Keyboard Shelf (25 lbs / 11.3 kgs capacity; 16 in / 406 mm depth)	Yes	-	
SRSHelf4PSL SmartRack Standard Sliding Shelf (50 lbs / 22.7 kgs capacity; 28.3 in/719 mm depth)	Yes	-	
SRSHelf4PSLHD SmartRack Heavy-Duty Sliding Shelf (200 lbs / 90.7 kgs capacity; 28.3 in/719 mm depth.)	Yes	-	
SRSHelf4PSLVENT SmartRack Sliding Steel Rack Shelf - 1U, Vented, 28.3 in. Deep, Holds up to 50 lb. (23 kg)	Yes	-	
SRWSHELF4P1U Cantilevered Steel Rack Shelf - 1U, Vented, Integrated Cable Rings, 14.2 in. Deep, Holds up to 50 lbs (22.2 kgs)	Yes	Yes	
	SRWO4UBRKTSHelf 4U Wall-Mount Bracket with Shelf for Small Switches and Patch Panels, Hinged	-	Yes

Cooling


Part number	Description
	SRXCOOL12KEU Portable Air Conditioning Unit for Server Rooms - 12,000 BTU (3.5kW), 230V, R290, Schuko CEE7 Input
SRXCOOL12KEUB	Portable Air Conditioning Unit for Server Rooms 12,000 BTU (3.5kW), 230V, R290, British Input
SRCOOLNETLX	LX Platform SNMP/Web Interface Module - Remote Cooling Management for SRCOOL12K Models
SRCOOLNET2LX	LX Platform SNMP/Web Interface Module - Remote Cooling Management for Select Models




Wall Brackets

	Part number	Description	Enclosure	
			Floor-Standing Open-Frames	Wall-Mount
	SRWALLBRKT2U	SmartRack 2U Vertical Wall-Mount Rack Bracket	-	Yes
	SRWALLBRKT4U	SmartRack 4U Vertical Wall-Mount Rack Bracket	-	Yes
	SRWALLBRKT6U	SmartRack 6U Vertical Wall-Mount Rack Bracket	-	Yes


Fiber Routing System

	Part number	Description
	SRFC10CAP	Toolless End Cap for Fiber Routing System, 240 mm
	SRFC10CPL10	Toolless Coupler for Fiber Routing System, 240 mm
	SRFC10JUNT	Toolless Horizontal 90-Degree T-Junction for Fiber Routing System, 240 mm
	SRFC10STR48	Toolless Straight Channel Section for Fiber Routing System, 240 x 120 x 1220 mm
	SRFC4WTRFL	Toolless Movable Waterfall Adapter Kit for Fiber Routing System, 130 mm
	SRFC4WTRFL36	Toolless Movable Waterfall Adapter Kit with 36 in. Pipe for Fiber Routing System, 130 mm

Roof Mounted Cable Routing

	Part number	Description	Enclosure	
			Floor-Standing Open-Frames	Wall-Mount
	SRCABLELADDER	SmartRack 10-ft. x 1-ft. (3 m x 0.3 m) Cable Ladder, 2 sections - SRCABLETRAY/SRLADDERATTACH needed	Yes	-
	SRCABLETRAY	SmartRack Roof-Mounted Cable Trough - Provides cable routing and power/data cable segregation	Yes	-
	SRCABLETRAY1U	SmartRack 1U Horizontal Cable Management Tray	Yes	-
	SRCABLETRAYEXP	SmartRack Roof-Mounted Cable Trough Vertical Expansion Plates - Requires SRCABLETRAY	Yes	-

PDU Accessories

	Part number	Description	Enclosure	
			Floor-Standing Open-Frames	Wall-Mount
	SRPDU2PBRKT	Vertical PDU Mounting Bracket Accessory Kit for 2-Post and 4-Post Open Frame Racks		

Console KVMs

Control and Manage Multiple PCs and Servers from a Single Keyboard/Video/Mouse. Increase efficiency. Prevent downtime. Save rack space and money.



Key points:

- Keyboard, Touchpad and color LCD monitor in 1U
- 8 or 16 KVM ports
- Multi-platform - VGA/HDMI/DisplayPort
- With or without built-in IP Remote Access
- English, French and German keyboard support

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	KVM ports	Concurrent Users	PC/Server Connections	Video Supported	LCD	Peripheral Sharing	Cables/Cable Kits/SIUs
With a KVM Switch (With or without remote access over IP)							
B020-U08-19-IP	8	1	VGA, USB	LCD: 1280x1024 Remote: 1920x1080	19"	-	P778-XXX
B020-U08-19-K	8	1	VGA, USB	1280x1024	19"	-	Included
B020-U16-19-IP	16	1	VGA, USB	LCD: 1280x1024 Remote: 1920x1080	19"	-	P778-XXX
B020-U16-19-IPF	16	1	VGA, USB French KB	LCD: 1280x1024 Remote: 1920x1080	19"	-	P778-XXX
B020-U16-19-IPG	16	1	VGA, USB German KB	LCD: 1280x1024 Remote: 1920x1080	19"	-	P778-XXX
B020-U16-19-K	16	1	VGA, USB	LCD: 1280x1024 External: 2048x1536	19"	-	(x8) P778-006 included
B020-U16-19-KF	16	1	VGA, USB French KB	LCD: 1280x1024 External: 2048x1536	19"	-	(x8) P778-006 included
B020-U16-19-KG	16	1	VGA, USB German KB	"LCD: 1280x1024 External: 2048x1536"	19"	-	(x8) P778-006 included
B030-008-17-IP	8	1	HDMI, USB	1920x1080	17"	-	P782-XXX-HA
B030-DP08-17D	8	1	DisplayPort, USB	1920x1080	17"	-	P580-XXX; U022-XXX
B030-DP08-17DIP	8	1	DisplayPort, USB	1920x1080	17"	-	P580-XXX; U022-XXX
B030-DP16-17D	16	1	DisplayPort, USB	1920x1080	17"	-	P580-XXX; U022-XXX
B030-DP16-17DIP	16	1	DisplayPort, USB	1920x1080	17"	-	P580-XXX; U022-XXX
B040-008-19	8	1	VGA, USB, PS/2	1366x768	19"	-	P780-XXX
B040-016-19	16	1	VGA, USB, PS/2	1366x768	19"	-	P780-XXX
B064C-16-1-IP	16	1	VGA, USB,	1920x1080	19"	Yes, VM	B055-XXX
B064C-16-1X1-IP	16	2	VGA, USB	1920x1080	19"	Yes, VM	B055-XXX
B070-008-19	8	1	VGA, USB, PS/2	1366x768	19"	-	B078-101-USB-1
B070-016-19	16	1	VGA, USB, PS/2	1366x768	19"	-	B078-101-USB-1
Without a KVM Switch							
B021-000-19	-	1	VGA, USB, PS/2	1366x768	19"	-	Included
B021-000-19-HD2	-	1	VGA/DVI, USB	1920x1080	19"	Yes Pass-through	Included
B021-SWHD-K	-	1	HDMI, USB	1920x1080	18.5"	Yes Pass-through	Included

Looking for Desktop KVM Switches?

Go to the Work from anywhere (WFA), Retail & Education section, page 53.

Rackmount KVM Switches

Control and Manage Multiple PCs and Servers from a Single Keyboard/Video/Mouse. Increase efficiency. Prevent downtime. Save rack space and money.



Key points:

- 1U Rack-Mount
- 8/16/32 KVM ports
- Multi-platform - VGA/DVI/HDMI/DisplayPort
- With or without built-in IP Remote Access

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	KVM ports	Concurrent Users	PC/Server Connections	Video Supported	LCD	Peripheral Sharing	Cables/Cable Kits/SIUs
With Remote Access over IP							
B064-008-01-IPG	8	2 (1 Local + 1 Remote)	VGA, USB	1920x1200	-	Yes, VM	B055-001-XXX
B064-016-01-IPG	16	2 (1 Local + 1 Remote)	VGA, USB	1920x1200	-	Yes, VM	B055-001-XXX
B064-000-STN	1 port Remote-User Console Station	1	HDMI, USB	1920 x 1200 @60Hz	-	Yes, VM	
B064-016-02-IPH	16	3 users (2 remote, 1 local)	DVI, VGA, Serial, USB	1920 x 1200 @60 Hz	-	Yes, VM	B055-001-XXX
B064-016-04-IPH	16	4 users (remote + 1 local)	DVI, VGA, Serial, USB	1920 x 1200 @60 Hz	-	Yes, VM	B055-001-XXX
B064-032-01-IPH	32	2 users (1 remote, 1 local)	DVI, VGA, Serial, USB	1920 x 1200 @60 Hz	-	Yes, VM	B055-001-XXX
B064-032-02-IPH	32	3 users (2 remote, 1 local)	DVI, VGA, Serial, USB	1920 x 1200 @60 Hz	-	Yes, VM	B055-001-XXX
B064-032-04-IPH	32	4 users (3 remote + 1 local)	DVI, VGA, Serial, USB	1920 x 1200 @60 Hz	-	Yes, VM	B055-001-XXX
Without Remote Access over IP							
B024-DPU08	8	1	DisplayPort, USB	4K	-	Yes	ADD P312-006
B024-DPU16	16	1	DisplayPort, USB	4K	-	Yes	P312-006
B024-H4U08	8	1	HDMI, USB	4K	-	Yes	P312-006
B024-H4U16	16	1	HDMI, USB	4K	-	Yes	P312-006

Secure NIAP KVM Switches

Lets you access multiple computers from a single console while protecting data from accidental or unauthorized transfer between them.



Key points:

- Physically separates the data channels passing through the KVM
- Requires physical access to push buttons on the KVM to switch
- Disables itself if the housing is opened (tamper-evident seals)
- Continuously clears keyboard buffer or prevent memory mining

Ideal for:

- Government
- Military
- Healthcare
- Private sector

Part number	KVM ports	Concurrent Users	PC/Server Connections	Video Supported	LCD	Peripheral Sharing	Cables/Cable Kits/SIUs
B002-DP1A4-N4	4	1	DisplayPort, USB, Audio	4K	-	-	P783-006
B002-DP1AC4-N4	4	1	DisplayPort, USB, Audio, CAC	4K	-	Yes - only CAC	P783-006-U
B002-DP1AC8-N4	8	1	DisplayPort, USB, Audio, CAC	4K	-	Yes - only CAC	P783-006-U
B002-DP2A2-N4	2	1	DisplayPort, USB, Audio	4K	-	-	P783-006-DP
B002-DP2A4-N4	4	1	DisplayPort, USB, Audio	4K	-	-	P783-006-DP
B002-DP2AC2-N4	2	1	DisplayPort, USB, Audio, CAC	4K	-	Yes - only CAC	P783-006-DPU
B002-DP2AC4-N4	2	1	DisplayPort, USB, Audio, CAC	4K	-	Yes - only CAC	P783-006-DPU
B002-DV1A2-N4	2	1	DVI-I, USB, Audio	1560 X 1600	-	-	P560-XXX / P312-xxx
B002-DV1AC8-N4	8	1	DVI-I, USB, Audio, CAC	1561 X 1600	-	Yes - only CAC	P560-XXX / P312-xxx
B002-DV2A4-N4	4	1	DVI-I, USB, Audio	1562 X 1600	-	-	P560-XXX / P312-xxx
B002-DV2AC4-N4	4	1	DVI-I, USB, Audio, CAC	1563 X 1600	-	Yes - only CAC	P560-XXX / P312-xxx
B002-H2A2-N4	2	1	HDMI, USB, Audio	4K	-	-	-
B002-H2A4-N4	4	1	HDMI, USB, Audio	4K	-	-	-
B002-H2AC2-N4	2	1	HDMI, USB, Audio, CAC	4K	-	Yes - only CAC	-
B002-H2AC4-N4	4	1	HDMI, USB, Audio, CAC	4K	-	Yes - only CAC	P782-006-HA / P568-006
B002-HD1AC4-N4	4	1	HDMI, USB, Audio, CAC	4K	-	Yes - only CAC	P783-006-U

CAC: Common Access Card

Console Servers

Secure in-band and out-of-band remote access to serial- and network-connected devices.



Key points:

- Manage routers, UPS systems and other serial-based equipment from anywhere 24/7
- Validated to meet FIPS 140-2 standards to ensure utmost protection of private data
- Dual Gigabit Ethernet ports for primary network connection and automatic failover
- Designed for standard Cat5e/6 patch cable when connecting to Cisco devices






Ideal for:


- Network Closet
- Server Room
- Data Center
- White Space


Part number	Number of Ports	Concurrent Users	Connections		Network Compatibility	Memory	Port Selection	Built-in Modem
			Connector A	Connector B				
B093-004-2E4U	4	Multi-users	2x RJ45 (F)	RJ45 (F) USB-A (F)	1 Gbps	4 Gbps	GUI	-
B093-008-2E4U	8	Multi-users	2x RJ45 (F)	2x RJ45 (F) 4x USB-A (F)	1 Gbps	4 Gbps	GUI	-
B093-008-2E4U-M	8	Multi-users	RJ11 (F) 2x RJ45 (F) 2x SFP+ (F)	8x RJ45 (F) 4x USB-A (F)	1 Gbps	4 Gbps	GUI	-
B097-016	16	Multi-users	RJ45 (F) 2x USB-A (F)	16x RJ45 (F) 2x RJ45 (F)	1 Gbps	4 Gbps	CLI/GUI	-
B097-048	48	Multi-users	RJ45 (F) 2x USB-A (F)	48x RJ45 (F) 2x RJ45 (F)	1 Gbps	4 Gbps	CLI/GUI	-
B098-016	16	Multi-users	2x USB-A (F) RJ45 (F) SD (F) RJ11 (F)	16x RJ45 (F) 2x RJ45 (F) 2x SFP (F)	1 Gbps	16 Gbps	CLI/GUI	Yes
B098-048	48	Multi-users	2x USB-A (F) RJ45 (F) SD (F) RJ11 (F)	48x RJ45 (F) 2x RJ45 (F) 2x SFP (F)	1 Gbps	16 Gbps	CLI/GUI	Yes


KVM Accessories


Accessories to connect a KVM to a server , PC or AV kit

	Part number	Description
KVM accessories and cables		
	B019-000	2-Post Rack-Mount Bracket, B020, B021, B040, and B070 Consoles & KVM Consoles
	B015-000	USB to PS/2 Adapter for Keyboard and Mouse
B002 Series Secure KVM cables/kits		
	P782-006-HA	HDMI KVM Cable Kit - 4K HDMI, USB 2.0, 3.5 mm Audio (M/M), Black, 1.83 m
	P782-010-HA	HDMI KVM Cable Kit - 4K HDMI, USB 2.0, 3.5 mm Audio (M/M), Black, 3.05 m
	P783-006	DisplayPort KVM Cable Kit, 3 in 1 - 4K DisplayPort, USB, 3.5 mm Audio (3xM/3xM), 4:4:4, 1.83 m, Black
	P783-006-DP	Dual DisplayPort KVM Cable Kit - DP, USB, 3.5 mm Audio (3xM/3xM) + DP (M/M), 4K, 4:4:4, 1.83 m, Black
	P783-006-DPU	DisplayPort KVM Cable Kit - DP, USB, 3.5 mm Audio (3xM/3xM) + USB (M/M) + DP (M/M), 4K, 1.83 m, Black
	P783-006-U	DisplayPort KVM Cable Kit - DP, USB, 3.5 mm Audio (3xM/3xM) + USB (M/M), 4K, 4:4:4, 1.83 m, Black
	P560-006	DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 1.83 m
	P560-010	DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 3.05 m
	U022-006	USB 2.0 A/B Cable (M/M), 1.83 m
	U022-010	USB 2.0 A/B Cable (M/M), 3.05 m
B005 Series KVM cable kits		
	P785-DPKIT06	DisplayPort KVM Cable Kit for Tripp Lite B005-DPUA2-K and B005-DPUA4 KVM, 4K DP, USB 3.2, 3.5 mm, 1.83 m
	P785-DPKIT10	DisplayPort KVM Cable Kit for Tripp Lite B005-DPUA2-K and B005-DPUA4 KVM, 4K DP, USB 3.2, 3.5 mm, 3.05 m
	P785-HKIT06	HDMI KVM Cable Kit for Tripp Lite B005-HUA2-K and B005-HUA4 KVM, 4K HDMI, USB 3.2 Gen 1, 3.5 mm, 1.83 m
	P785-HKIT10	HDMI KVM Cable Kit for Tripp Lite B005-HUA2-K and B005-HUA4 KVM, 4K HDMI, USB 3.2 Gen 1, 3.5 mm, 3.05 m
B020 Series KVM Cable Kits		
	P772-015	Daisy Chain Cable for NetDirector KVM Switch B020-Series and KVM B022-Series, 4.57 m
	P778-006	USB/PS2 Combo Cable for NetDirector KVM Switches B020-U08/U16, 1.83 m
	P778-006-DP	VGA to DisplayPort and USB-A Adapter Cable Kit for Tripp Lite B020-U KVM, 1.8 m
	P778-010	USB/PS2 Combo Cable for NetDirector KVM Switch B020-U08/U16, 3.05 m
	P778-015	USB/PS2 Combo Cable for NetDirector KVM Switches B020-U08/U16 , 4.57 m
B024 Series KVM Cables		
	P580-006	DisplayPort Cable with Latches, 4K @ 60 Hz, (M/M), 1.83 m
	P580-010	DisplayPort Cable with Latches, 4K @ 60 Hz, (M/M), 3.05 m
	P569-006	High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio (M/M), 1.83 m
	P569-010	High Speed HDMI Cable with Ethernet, UHD 4K, Digital Video with Audio (M/M), 3.05 m
	P312-001	3.5mm Mini Stereo Audio Cable for Microphones, Speakers and Headphones (M/M), 0.31 m
	P312-006	3.5mm Mini Stereo Audio Cable for Microphones, Speakers and Headphones (M/M), 1.83 m
	U022-006	USB 2.0 A/B Cable (M/M), 1.83 m
	U022-010	USB 2.0 A/B Cable (M/M), 3.05 m

	Part number	Description
B030 Series KVM Cables		
	P782-006-HA	HDMI KVM Cable Kit - 4K HDMI, USB 2.0, 3.5 mm Audio (M/M), Black,(1.83 m)
	P782-010-HA	HDMI KVM Cable Kit - 4K HDMI, USB 2.0, 3.5 mm Audio (M/M), Black,(3.05 m)
	P580-006	DisplayPort Cable with Latches, 4K @ 60 Hz, (M/M),(1.83 m)
	P580-010	DisplayPort Cable with Latches, 4K @ 60 Hz, (M/M),(3.05 m)
	U022-006	USB 2.0 A to B Cable (M/M),(1.83 m)
	U022-010	USB 2.0 A to B Cable (M/M),(3.05 m)

B040 Series KVM Cable Kits		
	P780-006	USB/PS2 Combo Cable Kit for NetController KVM Switches B040-Series , 1.83 m
	P780-010	USB/PS2 Combo Cable Kit for NetController KVM Switches B040-Series, 3.05 m
	P780-015	USB/PS2 Combo Cable Kit for NetController KVM Switches B040-Series, 4.57 m
	P781-010	Daisy Chain Cable for NetController KVM Switches B040-Series, 3.05 m

B064 Series KVM Server Interface Units (SIU)		
	B055-001-C	NetDirector USB-C Server Interface Unit with Virtual Media Support (B064 Series)
	B055-001-PS2	NetDirector PS/2 Server Interface Unit (B064-Series)
	B055-001-SER	NetDirector PS/2 Server Interface Unit (B064-Serie)
	B055-001-UDP	NetDirector DisplayPort USB Server Interface Unit with Virtual Media and CAC Support (B064-IPG Series)
	B055-001-UDV	NetDirector DVI USB Server Interface Unit with Virtual Media and CAC Support (B064-IPG Series), USB and DVI
	B055-001-UHD	NetDirector HDMI USB Server Interface Unit with Virtual Media and CAC Support (B064-IPG Series), USB and HDMI
	B055-001-USB	NetDirector USB Server Interface Unit (B064-Series)
	B055-001-USB-V2	NetDirector USB Server Interface Unit with Virtual Media Support (B064-Series)
	B055-001-USB-VA	NetDirector USB Server Interface Unit with Virtual Media Support and Audio (B064-IPG Series)
B055-001-UV2CAC	NetDirector USB Server Interface Unit with Virtual Media & CAC Support (B064-Series)	

B070 & B072 Series KVM Server Interface Units (SIU)		
	B078-101-PS2	NetCommander PS/2 Server Interface Unit (SIU)
	B078-101-USB-1	NetCommander USB Server Interface Unit (SIU) - Single
	B078-101-USB2	NetCommander USB Server Interface Unit (SIU) with Virtual Media up to 12Mbps

Copper Patch Panels

PoE+ or ++ compliant patch panel manages and organizes data/power cable connections in your high-density network.



Key points:

- 12, 24 & 48 port options
- 1U & 2U options
- Punchdown, Feed-through, Keystone
- PoE+ (30W) or PoE++ (100W) models
- STP Patch panels

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Number of Ports	Height (U)	Product Type	Technology				Cable		PoE Type
				Cat5/5e	Cat6	Cat6a	Cat8	Connector A (Front)	Connector B (Rear)	
Blank										
N062-012-KJ	12	1U	Blank	Keystone Jack Cutout						-
N062-016-KJ	16	1U	Blank	Keystone Jack Cutout						-
N062-024-KJ	24	2U	Blank	Keystone Jack Cutout						-
N062-024-KJ-SH	24	1U	Blank	Keystone Jack Cutout						-
N062-048-KJ	48	1U	Blank	Keystone Jack Cutout						-
Punchdown										
N250-012	12	0U	Punchdown	Yes	Yes	-	-	RJ45 (F)	110 IDC	Type 2 PoE+ (30W)
N250-P12	12	0U	Punchdown	Yes	Yes	-	-	RJ45 (F)	110 IDC	Type 4 PoE++ (100W)
N052-024	24	1U	Punchdown	Yes	-	-	-	RJ45 (F)	110 IDC	Type 2 PoE+ (30W)
N052-048	48	2U	Punchdown	Yes	-	-	-	RJ45 (F)	110 IDC	Type 2 PoE+ (30W)
N052-P24	24	1U	Punchdown	Yes	-	-	-	RJ45 (F)	110 IDC	Type 4 PoE++ (100W)
N252-012	12	1U	Punchdown	Yes	Yes	-	-	RJ45 (F)	110 IDC	Type 2 PoE+ (30W)
N252-024	24	1U	Punchdown	Yes	Yes	-	-	RJ45 (F)	110 IDC	Type 2 PoE+ (30W)
N252-P24	24	1U	Punchdown	Yes	Yes	-	-	RJ45 (F)	110 IDC	Type 4 PoE++ (100W)
N252-024-6A	24	1U	Punchdown	Yes	Yes	Yes	-	RJ45 (F)	110 IDC	Type 4 PoE++ (100W)
N252-024-6A-SH	24	1U	Punchdown	Yes	Yes	Yes	-	RJ45 (F)	110 IDC	Type 4 PoE++ (100W)
N252-048-1U	48	1U	Punchdown	Yes	Yes	-	-	RJ45 (F)	110 IDC	Type 2 PoE+ (30W)
N252-048	48	2U	Punchdown	Yes	Yes	-	-	RJ45 (F)	110 IDC	Type 2 PoE+ (30W)
Feed-Through										
N054-024	24	1U	Feed-Through	Yes	-	-	-	RJ45 (F)	RJ45 (F)	Type 4 PoE++ (100W)
N254-024	24	1U	Feed-Through	Yes	Yes	-	-	RJ45 (F)	RJ45 (F)	Type 4 PoE++ (100W)
N254-024-6A	24	1U	Feed-Through	Yes	Yes	Yes	-	RJ45 (F)	RJ45 (F)	Type 4 PoE++ (100W)
N254-024-6A-OF	24	1U	Feed-Through	Yes	Yes	Yes	-	RJ45 (F)	RJ45 (F)	Type 4 PoE++ (100W)
N254-024-SH	24	1U	Feed-Through	Yes	Yes	-	-	RJ45 (F)	RJ45 (F)	Type 4 PoE++ (100W)
N254-024-SH-6A	24	1U	Feed-Through	Yes	Yes	Yes	-	RJ45 (F)	RJ45 (F)	Type 4 PoE++ (100W)
N254-048-SH-6A	48	1U	Feed-Through	Yes	Yes	Yes	-	RJ45 (F)	RJ45 (F)	Type 4 PoE++ (100W)

Accessories



Part number	Description	Height (U)
N060-001	SmartRack 1U Hinged Wall-Mount Patch Panel Bracket	1U
N060-004	SmartRack 4U Hinged Wall-Mount Patch Panel Bracket, TAA	4U

Copper Couplers

Extend the length of copper patch cords.



Key points:

- Backwards compatible
- Gold contacts
- Protective shielded housing reduces EMI/RFI interference

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Cable						
	Connector A (Front)	Connector B (Rear)	Shielding	CatX type	PoE Type	Angle	Color
N235-001	Rj45 (F)	Rj45 (F)	No	Cat5e/Cat6	Type 4 PoE++ (100W)	-	Black
N235-001-6A	Rj45 (F)	Rj45 (F)	No	Cat5e/Cat6/Cat6a	Type 4 PoE++ (100W)	-	White
N235-001-SH-6A	Rj45 (F)	Rj45 (F)	Yes	Cat5e/Cat6/Cat6a	Type 4 PoE++ (100W)	-	Silver
N235-001-SH-D	Rj45 (F)	Rj45 (F)	Yes	Cat5e/Cat6		90° down	Silver
RJ45 Toolless Keystone Jack							
N238-001-GY-TFA	Rj45 (F)	-	No	Cat6a	Type 4 PoE++ (100W)	-	Gray
N238-001-SH-TF	Rj45(F)	-	Yes	Cat5e/Cat6	Type 4 PoE++ (100W)	-	Silver
N238-001-SH-TFA	Rj45(F)	-	No	Cat6a	Type 4 PoE++ (100W)	-	Silver
Pack 10 units							
N238-010-BK	Rj45(F)	Rj45(F)	Yes	Cat5e/Cat6		-	Black

Cat5e Copper Cables

Used for 1000Base-T (1Gbps Ethernet) networks and can distribute data, video and telephone signals.



Key points:

- Provides EMI/RFI shielding in Ethernet networks
- Shielded RJ45 connectors with gold-plated contacts
- Molded boot for extra strain-relief and durability
- Type 2 PoE+
- Molded connectors

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Shielding		Length	Network compatibility	Conductor material	Color
	Yes /No	Type				
Crossover						
N002-001-BL	No	UTP	31 cm	1 Gbps	Stranded Copper	Blue
N002-002-BL	No	UTP	61 cm	1 Gbps	Stranded Copper	Blue
N002-003-BL	No	UTP	91 cm	1 Gbps	Stranded Copper	Blue
N002-005-BL	No	UTP	1,52 m	1 Gbps	Stranded Copper	Blue
N002-006-BL	No	UTP	1,83 m	1 Gbps	Stranded Copper	Blue
N002-010-BL	No	UTP	3,05 m	1 Gbps	Stranded Copper	Blue
N002-015-BL	No	UTP	4,57 m	1 Gbps	Stranded Copper	Blue
N002-025-BL	No	UTP	7,62 m	4 Gbps	Stranded Copper	Blue
N002-001-GY	No	UTP	31 cm	1 Gbps	Stranded Copper	Gray
N002-002-GY	No	UTP	61 cm	1 Gbps	Stranded Copper	Gray
N002-003-GY	No	UTP	91 cm	1 Gbps	Stranded Copper	Gray
N002-005-GY	No	UTP	1,52 m	1 Gbps	Stranded Copper	Gray
N002-006-GY	No	UTP	1,83 m	3 Gbps	Stranded Copper	Gray
N002-010-GY	No	UTP	3,05 m	1 Gbps	Stranded Copper	Gray
N002-015-GY	No	UTP	4,57 m	2 Gbps	Stranded Copper	Gray
N002-025-GY	No	UTP	7,62 m	1 Gbps	Stranded Copper	Gray

Cat6 Copper Cables

Ideal for connecting high-speed network components, such as computers, printers, video game systems, Blu-ray™ players, copy machines, routers and modems.



Key points:

- Shielding
- Molded connectors

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Shielding		Length	Network compatibility	Conductor material	Color
	Yes / No	Type				
Snagless						
N201-001-BL	No	UTP	31 cm	1 Gbps	Stranded Copper	Blue
N201-002-BL	No	UTP	61 cm	1 Gbps	Stranded Copper	Blue
N201-003-BL	No	UTP	91 cm	1 Gbps	Stranded Copper	Blue
N201-005-BL	No	UTP	1,52 m	1 Gbps	Stranded Copper	Blue
N201-006-BL	No	UTP	1,83 m	1 Gbps	Stranded Copper	Blue
N201-010-BL	No	UTP	3,05 m	1 Gbps	Stranded Copper	Blue
N201-015-BL	No	UTP	4,57 m	1 Gbps	Stranded Copper	Blue
N201-025-BL	No	UTP	7,62 m	1 Gbps	Stranded Copper	Blue
N201-001-BK	No	UTP	31 cm	1 Gbps	Stranded Copper	Black
N201-002-BK	No	UTP	61 cm	1 Gbps	Stranded Copper	Black
N201-003-BK	No	UTP	91 cm	1 Gbps	Stranded Copper	Black
N201-005-BK	No	UTP	1,52 m	1 Gbps	Stranded Copper	Black
N201-006-BK	No	UTP	1,83 m	1 Gbps	Stranded Copper	Black
N201-010-BK	No	UTP	3,05 m	1 Gbps	Stranded Copper	Black
N201-015-BK	No	UTP	4,57 m	1 Gbps	Stranded Copper	Black
N201-025-BK	No	UTP	7,62 m	1 Gbps	Stranded Copper	Black
N201-001-GY	No	UTP	31 cm	1 Gbps	Stranded Copper	Gray
N201-002-GY	No	UTP	61 cm	1 Gbps	Stranded Copper	Gray
N201-003-GY	No	UTP	91 cm	1 Gbps	Stranded Copper	Gray
N201-005-GY	No	UTP	1,52 m	1 Gbps	Stranded Copper	Gray
N201-006-GY	No	UTP	1,83 m	1 Gbps	Stranded Copper	Gray
N201-010-GY	No	UTP	3,05 m	1 Gbps	Stranded Copper	Gray
N201-015-GY	No	UTP	4,57 m	1 Gbps	Stranded Copper	Gray
N201-025-GY	No	UTP	7,62 m	5 Gbps	Stranded Copper	Gray

Angled - No Snagless

N204-001-BL-DN	No	UTP	31 cm	Down	1 Gbps	Stranded Copper	Blue
N204-001-BL-LA	No	UTP	31 cm	Left	1 Gbps	Stranded Copper	Blue
N204-001-BL-RA	No	UTP	31 cm	Right	1 Gbps	Stranded Copper	Blue
N204-001-BL-UD	No	UTP	31 cm	Up/Down	1 Gbps	Stranded Copper	Blue
N204-001-BL-UP	No	UTB	31 cm	Up	1 Gbps	Stranded Copper	Blue
N204-003-BL-DN	No	UTP	91 cm	Down	1 Gbps	Stranded Copper	Blue
N204-003-BL-LA	No	UTP	91 cm	Left	1 Gbps	Stranded Copper	Blue
N204-003-BL-RA	No	UTP	91 cm	Right	1 Gbps	Stranded Copper	Blue
N204-003-BL-UD	No	UTP	91 cm	Up/Down	1 Gbps	Stranded Copper	Blue
N204-003-BL-UP	No	UTP	91 cm	Up	1 Gbps	Stranded Copper	Blue
N204-005-BL-DN	No	UTP	1,52 m	Down	1 Gbps	Stranded Copper	Blue
N204-005-BL-LA	No	UTP	1,52 m	Left	1 Gbps	Stranded Copper	Blue
N204-005-BL-RA	No	UTP	1,52 m	Right	1 Gbps	Stranded Copper	Blue
N204-005-BL-UP	No	UTP	1,52 m	Up	1 Gbps	Stranded Copper	Blue
N204-005-BL-UD	No	UTP	1,52 m	Down	6 Gbps	Stranded Copper	Blue
N204-010-BL-DN	No	UTP	3,05 m	Down	1 Gbps	Stranded Copper	Blue
N204-010-BL-LA	No	UTP	3,05 m	Left	1 Gbps	Stranded Copper	Blue
N204-010-BL-RA	No	UTP	3,05 m	Right	1 Gbps	Stranded Copper	Blue
N204-010-BL-UP	No	UTP	3,05 m	Up	1 Gbps	Stranded Copper	Blue
N204-015-BL-DN	No	UTP	4,57 m	Down	1 Gbps	Stranded Copper	Blue
N204-015-BL-LA	No	UTP	4,57 m	Left	1 Gbps	Stranded Copper	Blue
N204-015-BL-RA	No	UTP	4,57 m	Right	1 Gbps	Stranded Copper	Blue
N204-015-BL-UP	No	UTP	4,57 m	Up	1 Gbps	Stranded Copper	Blue

Pack of 50 units

N201-001-BL50BP	No	UTP	31 cm		1 Gbps	Stranded Copper	Blue
N201-002-BL50BP	No	UTP	61 m		1 Gbps	Stranded Copper	Blue
N201-003-BL50BP	No	UTP	91 cm		1 Gbps	Stranded Copper	Blue
N201-005-BL50BP	No	UTP	1,52 m		1 Gbps	Stranded Copper	Blue
N201-003-BK50BP	No	UTP	91 cm		1 Gbps	Stranded Copper	Black

Cat6a Copper Cables

Ethernet cable with Power over Ethernet (PoE) connects critical components, such as servers, switches, routers and hubs, in high-density 10Gbps networks.



Key points:

- Ideal for Your High-Density 10 Gbps Ethernet Network
- Premium Protection from EMI/RFI Line Noise
- Snagless RJ45 Male Connectors Add Extra Protection
- Type 2 PoE+ (30W)
- Shielding models available

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Shielding		Length	Network compatibility	Conductor material	Color
	Yes / No	Type				
Snagless						
N261-001-BL	No	UTP	31 cm	10 Gbps	Stranded Copper	Blue
N261-002-BL	No	UTP	61 cm	10 Gbps	Stranded Copper	Blue
N261-003-BL	No	UTP	91 cm	10 Gbps	Stranded Copper	Blue
N261-005-BL	No	UTP	1,52 m	10 Gbps	Stranded Copper	Blue
N261-006-BL	No	UTP	1,83 m	10 Gbps	Stranded Copper	Blue
N261-010-BL	No	UTP	3,05 m	10 Gbps	Stranded Copper	Blue
N261-015-BL	No	UTP	4,57 m	10 Gbps	Stranded Copper	Blue
N261-025-BL	No	UTP	7,62 m	10 Gbps	Stranded Copper	Blue
N261-001-BK	No	UTP	31 cm	10 Gbps	Stranded Copper	Black
N261-002-BK	No	UTP	61 cm	10 Gbps	Stranded Copper	Black
N261-003-BK	No	UTP	91 cm	10 Gbps	Stranded Copper	Black
N261-005-BK	No	UTP	1,52 m	10 Gbps	Stranded Copper	Black
N261-006-BK	No	UTP	1,83 m	10 Gbps	Stranded Copper	Black
N261-010-BK	No	UTP	3,05 m	10 Gbps	Stranded Copper	Black
N261-015-BK	No	UTP	4,57 m	10 Gbps	Stranded Copper	Black
N261-025-BK	No	UTP	7,62 m	10 Gbps	Stranded Copper	Black
N262-001-BL	Yes	STP	31 cm	10 Gbps	Stranded Copper	Blue
N262-003-BL	Yes	STP	91 cm	10 Gbps	Stranded Copper	Blue
N262-005-BL	Yes	STP	1,52 m	10 Gbps	Stranded Copper	Blue
N262-006-BL	Yes	STP	1,83 m	10 Gbps	Stranded Copper	Blue
N262-010-BL	Yes	STP	3,05 m	10 Gbps	Stranded Copper	Blue
N262-015-BL	Yes	STP	4,54 m	10 Gbps	Stranded Copper	Blue
N262-025-BL	Yes	STP	7,62 m	10 Gbps	Stranded Copper	Blue
N262-001-BK	Yes	STP	31 cm	10 Gbps	Stranded Copper	Black
N262-002-BK	Yes	STP	61 cm	10 Gbps	Stranded Copper	Black
N262-003-BK	Yes	STP	91 cm	10 Gbps	Stranded Copper	Black
N262-005-BK	Yes	STP	1,52 m	10 Gbps	Stranded Copper	Black
N262-006-BK	Yes	STP	1,83 m	10 Gbps	Stranded Copper	Black
N262-010-BK	Yes	STP	3,05 m	10 Gbps	Stranded Copper	Black
N262-015-BK	Yes	STP	4,57 m	10 Gbps	Stranded Copper	Black
N262-025-BK	Yes	STP	7,62 m	10 Gbps	Stranded Copper	Black
N262-001-GY	Yes	STP	31 cm	10 Gbps	Stranded Copper	Gray
N262-002-GY	Yes	STP	61 cm	10 Gbps	Stranded Copper	Gray
N262-003-GY	Yes	STP	91 cm	10 Gbps	Stranded Copper	Gray
N262-005-GY	Yes	STP	1,52 m	10 Gbps	Stranded Copper	Gray
N262-006-GY	Yes	STP	1,83 m	10 Gbps	Stranded Copper	Gray

Part number	Shielding		Length	Network compatibility	Conductor material	Color
	Yes / No	Type				
N262-010-GY	Yes	STP	3,05 m	10 Gbps	Stranded Copper	Gray
N262-015-GY	Yes	STP	4,57 m	10 Gbps	Stranded Copper	Gray
N262-025-GY	Yes	STP	7,62 m	10 Gbps	Stranded Copper	Gray

Snagless Slim

N262-S01-BL	Yes	STP	31 cm	10 Gbps	Stranded Copper	Blue
N262-S03-BL	Yes	STP	91 cm	10 Gbps	Stranded Copper	Blue
N262-S05-BL	Yes	STP	1,52 m	10 Gbps	Stranded Copper	Blue
N262-S06-BL	Yes	STP	1,83 m	10 Gbps	Stranded Copper	Blue
N262-S10-BL	Yes	STP	3,05 m	10 Gbps	Stranded Copper	Blue
N262-S15-BL	Yes	STP	4,57 m	10 Gbps	Stranded Copper	Blue
N262-S25-BL	Yes	STP	7,62 m	10 Gbps	Stranded Copper	Blue

Cat8 Copper Cables

Shielded Cat8 cable connects 25G/40G equipment in your top-of-the-line 40GBase-T data center.



Key points:

- Up to 4 Times Faster Than Cat6a
- Supports Power over Ethernet (PoE) to Cut Down on Power Supplies
- Premium Protection from EMI/RFI Line Noise

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Shielding		Length	Network compatibility	Conductor material	Color
	Yes / No	Type				
Snagless						
N272-003-WH	Yes	S/FTP	91 cm	40 Gbps	Solid Copper	White
N272-006-WH	Yes	S/FTP	1,83 m	40 Gbps	Solid Copper	White
N272-010-WH	Yes	S/FTP	3,05 m	40 Gbps	Solid Copper	White
N272-015-WH	Yes	S/FTP	4,57 m	40 Gbps	Solid Copper	White
N272-025-WH	Yes	S/FTP	7,62 m	40 Gbps	Solid Copper	White
N272-030-WH	Yes	S/FTP	9,14 m	40 Gbps	Solid Copper	White
N272-040-WH	Yes	S/FTP	12,19 m	40 Gbps	Solid Copper	White
N272-050-WH	Yes	S/FTP	15,24 m	40 Gbps	Solid Copper	White
N272-060-WH	Yes	S/FTP	18,29 m	40 Gbps	Solid Copper	White

Cisco Console Rollover Cables

Converts a standard Ethernet cable into a serial rollover cable for connecting to Cisco or other hardware that requires rolled cables.



Key points:

- Recommended for Cisco modems, routers, switches and other serial devices
- Internally rolls the pins to convert straight-through cable to rollover cable
- Narrow male RJ45 plug connects to device without blocking adjacent ports

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Technology				Connectors		Data Rate	Length	Cable Jacket Material	Colors	
	Cat5/5e	Cat6	Cat6a	Cat8	Connector 1	Connector 2				Cable Jacket	Connector
N034-05N-BL	Yes	Yes	-	-	RJ45 (M)	RJ45 (M)	-	Pigtail	-	Blue	Blue
N205-006-BL-FCR	Yes	Yes	-	-	RJ45 (M)	RJ45 (M)	1 Gbps	1,83 m	PVC	Blue	Blue
N205-010-BL-FCR	Yes	Yes	-	-	RJ45 (M)	RJ45 (M)	1 Gbps	3,05 m	PVC	Blue	Blue
U009-006-RJ45-X	Yes	-	-	-	USB-A (M)	RJ45 (M)	Up to 12 Mbps	1,83 m	PVC	Black	Black
U009-010-RJ45-X	Yes	-	-	-	USB-A (M)	RJ45 (M)	Up to 12 Mbps	3,05 m	PVC	Black	Black
U009-015-RJ45-X	Yes	-	-	-	USB-A (M)	RJ45 (M)	Up to 12 Mbps	4,57 m	PVC	Black	Black

Fiber Patch Panels

PoE+-compliant patch panel manages and organizes data/power cable connections in your high-density network.



Key points:

- 8 to 64 ports
- Single and Multimode
- LC,ST,SC connectors

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Number of Ports	Height (U)	Product Type	Technology		Cable		Fiber Type	Endface Polish
				Singlemode	Multimode	Connector A (Front)	Connector B (Rear)		
N48LSM-16X16	32	1U	Spine-Leaf	-	Yes	16x 12-STRAND MTP/MPO	16x 12-STRAND MTP/MPO	50/125	PC
N48LSM-32X32	64	1U	Spine-Leaf	-	OM4	32x 12-STRAND MTP/MPO	32x 12-STRAND MTP/MPO	50/125	PC
N48LSS-16X16	32	1U	Spine-Leaf	OS2	-	16x 12-STRAND MTP/MPO	16x 12-STRAND MTP/MPO	9/125	APC
N48LSS-32X32	64	1U	Spine-Leaf	OS2	-	32x 12-STRAND MTP/MPO	32x 12-STRAND MTP/MPO	9/125	APC
N490-016-LCLC	16	1U	Feed-Through	Yes	Yes	LC (F)	LC (F)	-	-
N490-016-SCSC	16	1U	Feed-Through	Yes	Yes	SC (F)	SC (F)	-	-
N492-036-LCLC-E	36	1U	Feed-Through	Yes	Yes	LC (F)	LC (F)	-	-
Adapter									
N492-08D-LC	8	-	-	Yes	Yes	LC (F)	LC (F)	-	-
N492-08S-ST	8	-	-	Yes	Yes	ST (F)	ST (F)	-	-

Fiber Cassette Enclosures & Sleeves

Cost-Effective, Space-Saving Solution for Adding a Fiber Cassette to Your System.



Key points:

- Helps you interconnect any combo of 10 Gb, 40 Gb and 100/120 Gb network equipment
- Made from heavy-duty cold-rolled steel
- No added heat or cooling load

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Technology	Accessory Type	Number of U	Cassette Capacity
N482-00U	Multimode	Sleeve/ Pass-Through Panel	0U	1
N482-01U	Singlemode/Multimode	Rackmount	1U	5
N482-02U	Singlemode/Multimode	Rackmount	2U	14
N482-04U	Singlemode/Multimode	Rackmount	4U	28
N484-01U	Cat5/5e, Cat6/Cat6a, Multimode	Pass-Through Panel	1U	4

Fiber Cassettes

Installs in select fiber enclosure panels to connect fiber cables with MTP/MPO connections in high-density network applications



Key points:

- Install N482 and N484 Series chassis
- Helps You Monitor and Analyze Network Data
- Easy to Install with Compatible Enclosure

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Technology	Optical mode	Connectors		Number of ports	Number of fibers	Network compatibility
			Input Ports	Output Ports			
N482-3M8L12S-B	Singlemode		3x 8 MTP/MPO	12x LC (F)	12	-	40/100Gb
N482TAP-4SM73LC	Singlemode		4x LC (F)	4x LC (F)	-	8	
N482TAP-4SM73M8	Singlemode		12x MTP/MPO	12x MTP/MPO		32	
N482-2M12-LC12	Multimode	OM4	2x MTP/MPO (M)	12x LC (F)		12	40Gb to 10Gb
N482-3M8-LC12	Multimode	OM4	3x 8 MTP/MPO (M)	LC (F)		12	40/100Gb
N482TAP-4MM73LC	Multimode	OM4	4x LC	4x LC		4	40/100Gb
N482TAP-4MM73M8	Multimode	OM4	12x MTP/MPO	12x MTP/MPO		32	40/100Gb
N484-12LC	Multimode		LC (F)	LC (F)	12	-	10Gb
N484-12M12	-		12x MTP/MPO (F)	12x MTP/MPO (F)			40Gb
N484-1M24-LC12	Multimode	OM4	24x STRAND MTP/MPO (M)	LC (F)	12	-	100Gb/120Gb to 10Gb
N484-3M8L12S	Singlemode		8x STRAND MTP/MPO (M)	LC (F)	12	-	40/100Gb
N484-3M8-LC12	Multimode		8x STRAND MTP/MPO (M)	LC (F)	12	-	40/100Gb

Preloaded Fiber Panels

Patch panel comes with spools of multimode fiber cable that allow you to extend the exact length required and store the excess out of sight.



Key points:

- LC and MTP options
- Single and multimode
- All necessary cabling is included.
- Use only as much cabling as you need

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Height (U)	Optical Mode		Cable		Panel cable		Fiber Type	Endface Polish
				Connector A (Front)	Connector B (Rear)	Number	Length (m)		
Singlemode									
N48S-24M8L4-10	3U	OS2	-	24x MTP/MPO (F)	96x LC (F)	24	10 m	9/125	APC/UPC
N48S-2L24L-10	1U	OS2	-	12x LC (M)	12x LC (M)	2	10 m	9/125	UPC
N48S-2L24L-20	1U	OS2	-	12x LC (M)	12x LC (M)	2	20 m	9/125	UPC
N48S-2M24L12-10	1U	OS2	-	MTP/MPO (F)	12x LC (M)	2	10 m	9/125	APC/UPC
N48S-2M24L12-20	1U	OS2	-	MTP/MPO (F)	12x LC (M)	2	20 m	9/125	APC/UPC
N48S-2M3X8M-20	1U	OS2	-	3x MTP/MPO (F)	3x MTP/MPO (F)	2	20 m	9/125	APC
N48S-2M8L4-20	1U	OS2	-	MTP/MPO (F)	4x LC (M)	2	20 m	9/125	APC/UPC
N48S-32M8L4-03	2U	OS2	-	32x MTP/MPO (F)	128x LC (F)	32	3 m	9/125	APC/UPC
N48S-48M8L4-05	3U	OS2	-	48x MTP/MPO (F)	192x LC (F)	48	5 m	9/125	APC/UPC
N48S-4L16L-10	1U	OS2	-	8x LC (M)	8x LC (M)	4	10 m	9/125	UPC
N48S-4M3X8M-10	1U	OS2	-	3x MTP/MPO (F)	3x MTP/MPO (F)	4	10 m	9/125	APC
N48S-4M8L4-10	1U	OS2	-	MTP/MPO (F)	4x LC	4	10 m	9/125	APC/UPC
N48S-64M8L4-03	1U	OS2	-	64x MTP/MPO (F)	256x LC	64	3 m	9/125	APC/UPC
N48S-6L8L-10	1U	OS2	-	4x LC (M)	4x LC (M)	6	10 m	9/125	UPC
N48S-8L2L-10	1U	OS2	-	LC (M)	LC (M)	8	10 m	9/125	UPC
Multimode									
N48M-24M8L4-10	3U	-	OM4	24x MTP/MPO (M)	96x LC (M)	24	10 m	50/125	PC
N48M-2L24L-10	1U	-	OM4	12x LC (M)	12x LC (M)	2	10 m	50/125	PC
N48M-2L24L-20	1U	-	OM4	12x LC (M)	12x LC (M)	2	20 m	50/125	PC
N48M-2M24L12-10	1U	-	OM4	MTP/MPO (F)	12x LC (M)	2	10 m	50/125	PC
N48M-2M24L12-20	1U	-	OM4	MTP/MPO (F)	12x LC (M)	2	20 m	20/125	PC
N48M-2M3X8M-20	1U	-	OM4	3x MTP/MPO (F)	3x MTP/MPO (F)	2	20 m	50/125	PC
N48M-2M8L4-20	1U	-	OM4	MTP/MPO (F)	4x LC (M)	2	20 m	50/125	PC
N48M-32M8L4-03	2U	-	OM4	32x MTP/MPO (F)	128x LC (F)	32	3 m	50/125	PC
N48M-48M8L4-05	3U	-	OM4	48x MTP/MPO (F)	192x LC (F)	48	5 m	50/125	PC
N48M-4L16L-10	1U	-	OM4	8x LC (M)	8x LC (M)	4	10 m	50/125	PC
N48M-4M3X8M-10	1U	-	OM4	3x MTP/MPO (F)	3x MTP/MPO (F)	4	10 m	50/125	PC
N48M-4M8L4-10	1U	-	OM4	MTP/MPO (F)	4x LC (M)	4	10 m	50/125	PC
N48M-64M8L4-03	3U	-	OM4	64x MTP/MPO (F)	256x LC (F)	64	3 m	50/125	PC
N48M-6L8L-10	1U	-	OM4	4x LC (M)	4x LC (M)	6	10 m	50/125	PC
N48M-8L2L-10	1U	-	OM4	LC (M)	LC (M)	8	10 m	50/125	PC
N48K-15M8L60-B	1U	-	OM4	MTP/MPO (F)	LC (F)		2 m	50/125	

OS2 Singlemode Fiber Patch Cables

Duplex Singlemode 9/125 Fiber Patch Cable.



Key points:

- OS2 - Manufactured from 9/125 duplex (zipcord) fiber
- Yellow Jacket Helps Avoid Misidentification That Can Cause Costly Downtime
- Fiber made from glass (not a polymer)

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
	Connector 1	Connector 2		Cable Jacket	Connector	Material	Rating			
ST/ST										
N352-01M	ST	ST	1 m	Yellow	Black	LSZH	OFNR	2	9/125	UPC
N352-02M	ST	ST	2 m	Yellow	Black	LSZH	OFNR	2	9/125	UPC
N352-03M	ST	ST	3 m	Yellow	Black	LSZH	OFNR	2	9/125	UPC
N352-05M	ST	ST	5 m	Yellow	Black	LSZH	OFNR	2	9/125	UPC
SC/ST										
N354-01M	SC	ST	1 m	Yellow	Black/Blue	LSZH	OFNR	2	9/125	UPC
N354-02M	SC	ST	2 m	Yellow	Black/Blue	LSZH	OFNR	2	9/125	UPC
N354-03M	SC	ST	3 m	Yellow	Black/Blue	LSZH	OFNR	2	9/125	UPC
N354-05M	SC	ST	5 m	Yellow	Black/Blue	LSZH	OFNR	2	9/125	UPC
N354-15M	SC	ST	15 m	Yellow	Black/Blue	LSZH	OFNR	2	9/125	UPC
SC/SC										
N356-01M	SC	SC	1 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N356-02M	SC	SC	2 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N356-03M	SC	SC	3 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N356-05M	SC	SC	5 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N356-10M	SC	SC	10 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
LC/SC										
N366-01M	LC	SC	1 m	Yellow	Blue/Blue/White	LSZH	OFNR	2	9/125	UPC
N366-02M	LC	SC	2 m	Yellow	Blue/Blue/White	LSZH	OFNR	2	9/125	UPC
N366-03M	LC	SC	3 m	Yellow	Blue/Blue/White	LSZH	OFNR	2	9/125	UPC
N366-05M	LC	SC	5 m	Yellow	Blue/Blue/White	LSZH	OFNR	2	9/125	UPC
N366-10M	LC	SC	10 m	Yellow	Blue/Blue/White	LSZH	OFNR	2	9/125	UPC
N366-15M	LC	SC	15 m	Yellow	Blue/Blue/White	LSZH	OFNR	2	9/125	UPC
LC/ST										
N368-01M	LC	ST	1 m	Yellow	Black/Blue/White	LSZH	OFNR	2	9/125	UPC
N368-02M	LC	ST	2 m	Yellow	Black/Blue/White	LSZH	OFNR	2	9/125	UPC
N368-03M	LC	ST	3 m	Yellow	Black/Blue/White	LSZH	OFNR	2	9/125	UPC

N368-05M	LC	ST	5 m	Yellow	Black/Blue/White	LSZH	OFNR	2	9/125	UPC
N368-10M	LC	ST	10 m	Yellow	Black/Blue/White	LSZH	OFNR	2	9/125	UPC
N368-15M	LC	ST	15 m	Yellow	Black/Blue/White	LSZH	OFNR	2	9/125	UPC

LC/LC

N370-01M	LC	LC	1 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N370-02M	LC	LC	2 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N370-03M	LC	LC	3 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N370-05M	LC	LC	5 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N370-10M	LC	LC	10 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N370-15M	LC	LC	15 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N370-20M	LC	LC	20 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC

40/100/400 Gbps CABLES

LC/LC

N370X-01M	LC	LC	1 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N370X-02M	LC	LC	2 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N370X-03M	LC	LC	3 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N370X-05M	LC	LC	5 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC
N370X-10M	LC	LC	10 m	Yellow	Blue	LSZH	OFNR	2	9/125	UPC

SN/SN

N3835-01M	SN	SN	1 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N3835-02M	SN	SN	2 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N3835-03M	SN	SN	3 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC
N3835-05M	SN	SN	5 m	Yellow	Blue/White	LSZH	OFNR	2	9/125	UPC

OM3 Multimode Fiber Patch Cables

Duplex Multimode 50/125 OM3 Fiber Patch Cables



Key points:

- Low-Smoke, Zero Halogen (LSZH) Aqua jacket
- Backward compatible with existing 50/125 fiber

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
	Connector 1	Connector 2		Cable Jacket	Connector	Material	Rating			
For 10 Gbps applications										
SC/ST										
N806-01M	SC	SC	1 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N806-02M	SC	SC	2 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N806-03M	SC	SC	3 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N806-05M	SC	SC	5 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N806-10M	SC	SC	10 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N806-15M	SC	SC	15 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
SC/LC										
N816-01M	SC	LC	1 m	Aqua	White/Beige	LSZH	OFNR	2	50/125	PC
N816-02M	SC	LC	2 m	Aqua	White/Beige	LSZH	OFNR	2	50/125	PC
N816-03M	SC	LC	3 m	Aqua	White/Beige	LSZH	OFNR	2	50/125	PC
N816-05M	SC	LC	5 m	Aqua	White/Beige	LSZH	OFNR	2	50/125	PC
N816-10M	SC	LC	10 m	Aqua	White/Beige	LSZH	OFNR	2	50/125	PC
N816-15M	SC	LC	15 m	Aqua	White/Beige	LSZH	OFNR	2	50/125	PC
LC/ST										
N818-01M	LC	ST	1 m	Aqua	White/Black	LSZH	OFNR	2	50/125	PC
N818-02M	LC	ST	2 m	Aqua	White/Black	LSZH	OFNR	2	50/125	PC
N818-03M	LC	ST	3 m	Aqua	White/Black	LSZH	OFNR	2	50/125	PC
N818-05M	LC	ST	5 m	Aqua	White/Black	LSZH	OFNR	2	50/125	PC
N818-10M	LC	ST	10 m	Aqua	White/Black	LSZH	OFNR	2	50/125	PC
LC/LC										
N820-01M	LC	LC	1 m	Aqua	White	LSZH	OFNR	2	50/125	PC
N820-02M	LC	LC	2 m	Aqua	White	LSZH	OFNR	2	50/125	PC
N820-03M	LC	LC	3 m	Aqua	White	LSZH	OFNR	2	50/125	PC
N820-05M	LC	LC	5 m	Aqua	White	LSZH	OFNR	2	50/125	PC
N820-10M	LC	LC	10 m	Aqua	White	LSZH	OFNR	2	50/125	PC
N820-15M	LC	LC	15 m	Aqua	White	LSZH	OFNR	2	50/125	PC
N820-20M	LC	LC	20 m	Aqua	White	LSZH	OFNR	2	50/125	PC
N820-25M	LC	LC	25 m	Aqua	White	LSZH	OFNR	2	50/125	PC
For 400 Gbps applications										
LC/LC										
N820X-01M	LC	LC	1 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N820X-02M	LC	LC	2 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N820X-03M	LC	LC	3 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N820X-05M	LC	LC	5 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC
N820X-10M	LC	LC	10 m	Aqua	Beige	LSZH	OFNR	2	50/125	PC

OM4 Multimode Fiber Patch Cables

Duplex Multimode 50/125 OM4 Fiber Optic Cable



Key points:

- Push/pull tab connectors install/remove with one hand
- Slim, space-saving uniboot design for neat cable management
- Premium-grade ceramic ferrules designed for fast applications
- Backward Compatible with existing 50/125 fiber

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
	Connector 1	Connector 2		Cable Jacket	Connector	Material	Rating			
For 40/100 Gbps applications										
N820-01M-OM4	LC	LC	1 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820-02M-OM4	LC	LC	2 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820-03M-OM4	LC	LC	3 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820-05M-OM4	LC	LC	5 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820-10M-OM4	LC	LC	10 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820-15M-OM4	LC	LC	15 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820-20M-OM4	LC	LC	20 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820-25M-OM4	LC	LC	25 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N845X-01M-8L-MG	12F MTP/MPO	4x LC	1 m	Magenta	Aqua/Magenta/Black	LSZH	OFNR	8	50/125	PC
N845X-02M-8L-MG	12F MTP/MPO	4x LC		Magenta	Aqua/Magenta/Black	LSZH	OFNR	8	50/125	PC
N845X-03M-8L-MG	12F MTP/MPO	4x LC		Magenta	Aqua/Magenta/Black	LSZH	OFNR	8	50/125	PC
N845X-05M-8L-MG	12F MTP/MPO	4x LC		Magenta	Aqua/Magenta/Black	LSZH	OFNR	8	50/125	PC
For 100 Gbps applications										
N821-15M-AQ-AR	LC	LC	15 m	Aqua	Aqua/White	LSZH	OFNR	2	50/125	PC
For 400 Gbps applications										
N820X-01M-OM4	LC	LC	1 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820X-02M-OM4	LC	LC	2 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820X-03M-OM4	LC	LC	3 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820X-05M-OM4	LC	LC	5 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC
N820X-10M-OM4	LC	LC	10 m	Aqua	Aqua	LSZH	OFNR	2	50/125	PC

OM5 Multimode Fiber Patch Cables

Rated OM5, this 50/125 multimode fiber cable with duplex LC connectors carries signals in 40/100 Gb Ethernet networks.



Key points:

- Laser-optimized for use with cost-effective VCSEL light sources
- Lime green jacket for easy OM5 identification
- Backward compatible with OM3 and OM4 applications

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
	Connector 1	Connector 2		Cable Jacket	Connector	Material	Rating			
N820-01M-OM5	LC	LC	1 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC
N820-02M-OM5	LC	LC	2 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC
N820-03M-OM5	LC	LC	3 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC
N820-05M-OM5	LC	LC	5 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC
N820-10M-OM5	LC	LC	10 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC
N820-15M-OM5	LC	LC	15 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC
N820-20M-OM5	LC	LC	20 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC
N820-25M-OM5	LC	LC	25 m	Lime Green	Aqua	LSZH	OFNR	2	50/125	PC

MTP/MTO Cables

Premium singlemode or multimode fiber optic cabling for transmitting 40/100/400 Gb data and voice signals over long distances.



Key points:

- Converts Singlemode to Multimode
- Available in a variety of connector combinations

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Optical mode	Connectors		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
		Connector 1	Connector 2		Cable Jacket	Connector	Material	Rating			
N390-01M-12-AP	OS2	MTP/MPO	MTP/MPO	1 m	Yellow	Green/Black	PVC	OFNP	12	9/125	APC
N390-02M-12-AP	OS2	MTP/MPO	MTP/MPO	2 m	Yellow	Green/Black	PVC	OFNP	12	9/125	APC
N390-03M-12-AP	OS2	MTP/MPO	MTP/MPO	3 m	Yellow	Green/Black	PVC	OFNP	12	9/125	APC
N390-05M-12-AP	OS2	MTP/MPO	MTP/MPO	5 m	Yellow	Green/Black	PVC	OFNP	12	9/125	APC
N390-01M-8LC-AP	OS2	MTP/MPO	8x LC	1 m	Yellow	Blue/Green/Black	PVC	OFNP	8	9/125	APC/UPC
N390-02M-8LC-AP	OS2	MTP/MPO	8x LC	2 m	Yellow	Blue/Green/Black	PVC	OFNP	8	9/125	APC/UPC
N390-03M-8LC-AP	OS2	MTP/MPO	8x LC	3 m	Yellow	Blue/Green/Black	PVC	OFNP	8	9/125	APC/UPC
N390-05M-8LC-AP	OS2	MTP/MPO	8x LC	5 m	Yellow	Blue/Green/Black	PVC	OFNP	8	9/125	APC/UPC
N844-01M-8LC-PT	OM3	MTP/MPO	8x LC	1 m	Aqua	Aqua/Black	PVC	OFNP	8	50/125	PC
N844-02M-8LC-PT	OM3	MTP/MPO	8x LC	2 m	Aqua	Aqua/Black	PVC	OFNP	8	50/125	PC
N844-03M-8LC-PT	OM3	MTP/MPO	8x LC	3 m	Aqua	Aqua/Black	PVC	OFNP	8	50/125	PC
N844-05M-8LC-PT	OM3	MTP/MPO	8x LC	5 m	Aqua	Aqua/Black	PVC	OFNP	8	50/125	PC
N844B-01M-12-P	OM3	MTP/MPO	MTP/MPO	1 m	Aqua	Black	LSZH	OFNR	12	50/125	PC
N844B-02M-12-P	OM3	MTP/MPO	MTP/MPO	2 m	Aqua	Black	LSZH	OFNR	12	50/125	PC
N844B-03M-12-P	OM3	MTP/MPO	MTP/MPO	3 m	Aqua	Black	LSZH	OFNR	12	50/125	PC
N844B-05M-12-P	OM3	MTP/MPO	MTP/MPO	5 m	Aqua	Black	LSZH	OFNR	12	50/125	PC
N844B-10M-12-P	OM3	MTP/MPO	MTP/MPO	10 m	Aqua	Black	LSZH	OFNR	12	50/125	PC
N844X-01M-8L-P	OM3	MTP/MPO	4x LC	1 m	Aqua	Beige/Black	LSZH	OFNR	8	50/125	PC
N844X-02M-8L-P	OM3	MTP/MPO	4x LC	2 m	Aqua	Beige/Black	LSZH	OFNR	8	50/125	PC
N844X-03M-8L-P	OM3	MTP/MPO	4x LC	3 m	Aqua	Beige/Black	LSZH	OFNR	8	50/125	PC
N844X-05M-8L-P	OM3	MTP/MPO	4x LC	5 m	Aqua	Beige/Black	LSZH	OFNR	8	50/125	PC
N845-02M-8L-MG	OM4	MTP/MPO	8x LC	2 m	Magenta	Aqua/Magenta/Black	PVC	OFNP	8	50/125	PC
N845-03M-8L-MG	OM4	MTP/MPO	8x LC	3 m	Magenta	Aqua/Magenta/Black	PVC	OFNP	8	50/125	PC
N845-05M-8L-MG	OM4	MTP/MPO	8x LC	5 m	Magenta	Aqua/Magenta/Black	PVC	OFNP	8	50/125	PC
N845B-01M-12-MG		12F MTP/MPO	12F MTP/MPO	1 m	Magenta	Magenta/Black	LSZH	OFNR	12	50/125	PC
N845B-02M-12-MG		12F MTP/MPO	12F MTP/MPO	2 m	Magenta	Magenta/Black	LSZH	OFNR	12	50/125	PC
N845B-03M-12-MG		12F MTP/MPO	12F MTP/MPO	3 m	Magenta	Magenta/Black	LSZH	OFNR	12	50/125	PC
N845B-05M-12-MG		12F MTP/MPO	12F MTP/MPO	5 m	Magenta	Magenta/Black	LSZH	OFNR	12	50/125	PC
N845B-10M-12-MG		12F MTP/MPO	12F MTP/MPO	10 m	Magenta	Magenta/Black	LSZH	OFNR	12	50/125	PC
N845B-15M-12-MG		12F MTP/MPO	12F MTP/MPO	15 m	Magenta	Magenta/Black	LSZH	OFNR	12	50/125	PC

Part number	Optical mode	Connectors		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
		Connector 1	Connector 2		Cable Jacket	Connector	Material	Rating			
Push/Pull Tabs											
40/100/400 Gbps Cables											
N846B-01M-24-P	OM3	24-STRAND MTP/MPO	24-STRAND MTP/MPO	1 m	Aqua	Aqua/Black/Blue	LSZH	OFNR	24	50/125	PC
N846B-02M-24-P	OM3	24-STRAND MTP/MPO	24-STRAND MTP/MPO	2 m	Aqua	Aqua/Black/Blue	LSZH	OFNR	24	50/125	PC
N846B-03M-24-P	OM3	24-STRAND MTP/MPO	24-STRAND MTP/MPO	3 m	Aqua	Aqua/Black/Blue	LSZH	OFNR	24	50/125	PC
N846B-05M-24-P	OM3	24-STRAND MTP/MPO	24-STRAND MTP/MPO	5 m	Aqua	Aqua/Black/Blue	LSZH	OFNR	24	50/125	PC
N846B-10M-24-P	OM3	24-STRAND MTP/MPO	24-STRAND MTP/MPO	10 m	Aqua	Aqua/Black/Blue	LSZH	OFNR	24	50/125	PC
N846B-15M-24-P	OM3	24-STRAND MTP/MPO	24-STRAND MTP/MPO	15 m	Aqua	Aqua/Black/Blue	LSZH	OFNR	24	50/125	PC
N858B-10M-3X8MG	OM4	12-STRAND MTP/MPO	24-STRAND MTP/MPO	10 m	Magenta	Black/Magenta	LSZH	OFNR	24	50/125	PC
N858B-15M-3X8MG	OM4	12-STRAND MTP/MPO	24-STRAND MTP/MPO	15 m	Magenta	Black/Magenta	LSZH	OFNR	24	50/125	PC

Part number	Connectors		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
	Connector 1	Connector 2		Cable Jacket	Connector	Material	Rating			
40/100 Gbps Cables										
N390B-01M-12-AP	12F MTP/MPO	12F MTP/MPO	1 m	Yellow	Black	LSZH	OFNR	2	9/125	APC
N390B-02M-12-AP	12F MTP/MPO	12F MTP/MPO	2 m	Yellow	Black	LSZH	OFNR	2	9/125	APC
N390B-03M-12-AP	12F MTP/MPO	12F MTP/MPO	3 m	Yellow	Black	LSZH	OFNR	2	9/125	APC
N390B-05M-12-AP	12F MTP/MPO	12F MTP/MPO	5 m	Yellow	Black	LSZH	OFNR	2	9/125	APC
N390-01M-4S-AP	12F MTP/MPO	4x SN	1 m	Yellow	Black/Blue Green/ White	LSZH	OFNR	12	9/125	APC/ UPC
N390-02M-4S-AP	12F MTP/MPO	4x SN	2 m	Yellow	Black/Blue Green/ White	LSZH	OFNR	12	9/125	APC/ UPC
N390-02M-8S-AP	12F MTP/MPO	4x SN	2 m	Yellow	Black/Blue Green/ White	LSZH	OFNR	16	9/125	APC/ UPC
N390-03M-4S-AP	12F MTP/MPO	4x SN	3 m	Yellow	Black/Blue Green/ White	LSZH	OFNR	12	9/125	APC/ UPC
N390-03M-8S-AP	12F MTP/MPO	4x SN	3 m	Yellow	Black/Blue Green/ White	LSZH	OFNR	16	9/125	APC/ UPC
N390X-01M-8L-AP	12F MTP/MPO	4x LC	1 m	Yellow	Blue/Green/Black	LSZH	OFNR	2	9/125	APC/ UPC
N390X-02M-8L-AP	12F MTP/MPO	4x LC	2 m	Yellow	Blue/Green/Black	LSZH	OFNR	2	9/125	APC/ UPC
N390X-03M-8L-AP	12F MTP/MPO	4x LC	3 m	Yellow	Blue/Green/Black	LSZH	OFNR	2	9/125	APC/ UPC
N390X-05M-8L-AP	12F MTP/MPO	4x LC	5 m	Yellow	Blue/Green/Black	LSZH	OFNR	2	9/125	APC/ UPC

Fiber Couplers

Provides a simple and easy way to link together two fiber optic cables.



Key points:

- High precision mating structure with low insertion loss
- Duplex adapter accepts two simplex connectors or one duplex connector

Ideal for:

- Server room
- Data Center
- IP room
- White space

Part number	Optical Mode		Cable		Number of Fibers	Color
			Connector A (Front)	Connector B (Rear)		
N452-000	-	Yes	SC (F)	SC (F)	2	Light Gray
N455-000	-	Yes	LC (F)	LC (F)	2	Light Gray
N455-000-PM	-	Yes	LC (F)	LC (F)	2	Light Gray
N455-000-S	Yes	-	LC (F)	LC (F)	2	Light Gray
N456-000	-	Yes	SC (F)	ST (F)	2	Light Gray

Network Adapters

Connect between different platforms or connectors to keep your devices up and running at all times.



Key points:

- USB to Ethernet
- Fiber to fiber
- Serial to Ethernet

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Length	Number of Fibers	Optical Mode	Colors		Cable Jacket		Fiber Type (microns)
	Connector 1	Connector 2				Cable Jacket	Connector	Material	Rating	
Fiber										
N457-001-62	LC (M)	ST (F)	31 cm	2	Multimode	Orange	Beige	LSZH	OFNR	62.5 / 125
N458-001-62	LC (M)	SC (F)	31 cm	2	Multimode	Orange	Beige			62.5 / 125
N458-001-9	LC (M)	SC (F)	31 cm	2	Singlemode	Yellow	Blue			9 / 125

Media Converters

Extends your 10/100/1000 Mbps Gigabit Ethernet connection up to 20 km using fast singlemode or multimode fiber optic cabling.



Key points:

- LEDs indicate Ethernet and fiber link status at a quick glance
- Supports Power over Ethernet to Save You Money and Give You More Installation Choices
- Completely Plug-and-Play with No Additional Software Required for Connection

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Data Transfer Rate			Working Mode	Transmission Distance	PoE Capability
	Connector 1	Connector 2	10/100 Mbps (no compatible with Gbps)	10/100/1000 Mbps (Up to 1 Gbps but compatible with 10 Mbps & 100 Mbps)	Gigabits (1.000 Mbps)			
Singlemode (long distance)								
N785-INT-SC-SM	RJ45 (F)	SC (F)	Yes	Yes	Yes	Full/Half Duplex	20 km	-
Multimode (short distance)								
N785-INT-LC-MM	RJ45 (F)	LC (F)	Yes	Yes	Yes	Full/Half Duplex	550 m	-
N785-INT-PLCMM1	RJ45 (F)	LC (F)	Yes	Yes	Yes	Full/Half Duplex	550 m	Type 1 PoE (15,4W) Type 2 PoE+ (30W)
N785-INT-PSCMM2	SC (F)	RJ45 (F)	Yes	Yes	Yes	Full/Half Duplex	2 km	Type 1 PoE (15,4W) Type 2 PoE+ (30W)
N785-INT-SC	RJ45 (F)	SC (F)	Yes	Yes	Yes	Full/Half Duplex	2 km	-
N785-INT-SC-MM	RJ45 (F)	SC (F)	Yes	Yes	Yes	Full/Half Duplex	550 m	-
SFP								
N785-INT-PSFP	RJ45 (F)	SFP (F)	-	-	-	Full/Half Duplex	-	Type 1 PoE (15,4W) Type 2 PoE+ (30W)

Transceiver Modules

Connects a single or multimode Gigabit Ethernet fiber optic network cable to a switch or server's SFP port.



Key points:

- Supports data transfer rates up to 400 Gbps
- 100% compatible with Arista, Cisco, Juniper, HP, networking hardware

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Data Transfer Rate	Optical mode	Transmission Distance	Brand Compatibility
	Connector 1	Connector 2				
Singlemode						
N286-01GLX-SLX	SFP+ (M)	LC (M)	1 Gbps	-	10 km	HP
Multimode						
N286-01GSX-MDLC	SFP+ (M)	LC (M)	1 Gbps	-	10 km	HP
N286-01G-SX-A	SFP (M)	LC (M)	1,25 Gbps	OM2	550 m	Arista
N286-01G-SX-C	SFP (M)	LC (M)	1,25 Gbps	OM2	550 m	Cisco
N286-01G-SX-G	SFP (M)	LC (M)	1,25 Gbps	OM2	550 m	Cisco
N286-01G-SX-J	SFP (M)	LC (M)	1,25 Gbps	OM2	550 m	Juniper
N286-100G-SR4SA	QSFP28(M)	12 STRAND MTP/MPO (M)	100 Gbps	OM4	100 m	Arista
N286-100G-SR4SC	QSFP28(M)	12 STRAND MTP/MPO (M)	100 Gbps	OM4	100 m	Cisco
N286-100G-SR4SG	QSFP28(M)	12 STRAND MTP/MPO (M)	100 Gbps	OM4	100 m	Cisco
N286-100G-SR4SJ	QSFP28(M)	12 STRAND MTP/MPO (M)	100 Gbps	OM4	100 m	Juniper
N286-10G-SR-A	SFP+ (M)	LC (M)	10 Gbps	OM4	400 m	Arista
N286-10G-SR-C	SFP+ (M)	LC (M)	10 Gbps	OM4	400 m	Cisco
N286-10G-SR-G	SFP+ (M)	LC (M)	10 Gbps	OM4	400 m	Cisco
N286-10G-SR-J	SFP+ (M)	LC (M)	10 Gbps	OM4	400 m	Cisco
N286-25G-SRS-G	SFP28(M)	LC (F)	25 Gbps	OM4	100 m	Juniper
N286-400G-SR8-C	QSFP-DD	16 STRAND MTP/MPO (F)	400 Gbps	OM4	100 m	Cisco
N286-400G-SR8-G	QSFP-DD	16 STRAND MTP/MPO (F)	400 Gbps	OM4	100 m	Cisco
N286-40G-ESR4-A	QSFP+(M)	16 STRAND MTP/MPO (M)	40 Gbps	OM4	400 m	Arista
N286-40G-ESR4-C	QSFP+(M)	16 STRAND MTP/MPO (M)	40 Gbps	OM4	400 m	Cisco
N286-40G-ESR4-G	QSFP+(M)	16 STRAND MTP/MPO (M)	40 Gbps	OM4	400 m	Cisco
N286-40G-ESR4-J	QSFP+(M)	16 STRAND MTP/MPO (M)	40 Gbps	OM4	400 m	Juniper
N286-40GSR4-MTP	QSFP+(M)	12 STRAND MTP/MPO (M)	40 Gbps	OM4	150 m	Cisco
N286-01GSX-MLC	SFP+ (M)	LC (F)	1 Gbps	-	550 m	HP
N286-01GLCLH5MD	SFP (M)	LC (M)	1 Gbps	-	10 km	Cisco
N286-01GLC-TE	SFP (M)	RJ45 (F)	1 Gbps	-	100 m	Cisco
N286-01GTX	SFP+ (M)	LC (F)	1 Gbps	-	100 m	Cisco
N286-10G-LRM	SFP+ (M)	LC (F)	10 Gbps	-	220 m	Cisco
N286-10G-LR-S	SFP+ (M)	LC (F)	10 Gbps	-	10 km	Cisco
N286-10GLR-SLC	SFP+ (M)	LC (F)	10 Gbps	-	10 km	Cisco
N286-10GSR-MDLC	SFP+ (M)	LC (F)	10 Gbps	-	300 m	Cisco
N286-10G-SR-S	SFP+ (M)	LC (F)	10 Gbps	-	300 m	Cisco
N286-10G-TC	SFP+ (M)	RJ45 (F)	10 Gbps	-	30 m	Cisco
N286-25G-LR-S	SFP28 (M)	LC (F)	25 Gbps	-	10 km	
N286-40G-PLR4	QSFP+ (M)	MTP/MPO (F)	40 Gbps	-	10 km	

Direct Attach Copper Cables (DACs)

Low cost alternative to Fiber Optic cables.



Key points:

- Ergonomic pull tabs for fast hot-swap connections/disconnections in crowded networks
- Simpler alternative to fiber optics in short-range network connections

Ideal for:

- Network Closet
- Server Room
- Data Center
- White Space

Part number	Connectors		Length	Optical Mode	Number of Fibers	Network Compatibility	Cable Type	Colors		Cable Jacket		Compatible Brand
	Connector 1	Connector 2						Cable Jacket	Connector	Material	Rating	
N280-20N-BK	SFP+	SFP+	50 cm	-	-	10 Gbps	Passive	Black	Black	PVC	-	
N280-01M-BK	SFP+	SFP+	1 m	-	-	10 Gbps	Passive	Black	Black	PVC	-	
N280-005-BK	SFP+	SFP+	1,52 m	-	-	10 Gbps	Passive	Black	Black	PVC	-	
N280-02M-BK	SFP+	SFP+	2 m	-	-	10 Gbps	Passive	Black	Black	PVC	-	Arista Broadcom Cisco Dell-EMC Emulex Extreme Finisar IBM Juniper QLogic Voltaire
N280-03M-BK	SFP+	SFP+	3 m	-	-	10 Gbps	Passive	Black	Black	PVC	-	
N280-03M-GN	SFP+	SFP+	3 m	-	-	10 Gbps	Passive	Green	Green	PVC	-	
N280-05M-BK	SFP+	SFP+	5 m	-	-	10 Gbps	Passive	Black	Black	PVC	-	
N280-06M-BK	SFP+	SFP+	6 m	-	-	10 Gbps	Passive	Black	Black	PVC	-	
N280-07M-BK	SFP+	SFP+	7 m	-	-	10 Gbps	Passive	Black	Black	PVC	-	
N280-01M-28-BK	SFP28	SFP28	1 m	-	-	25 Gbps	Passive	Black	Black	PVC	CM	
N280-02M-28-BK	SFP28	SFP28	2 m	-	-	25 Gbps	Passive	Black	Black	PVC	CM	Arista Cisco Dell Juniper
N280-03M-28-BK	SFP28	SFP28	3 m	-	-	25 Gbps	Passive	Black	Black	PVC	CM	
N280-04M-28-BK	SFP28	SFP28	4 m	-	-	25 Gbps	Passive	Black	Black	PVC	CM	
N280-05M-28-BK	SFP28	SFP28	5 m	-	-	25 Gbps	Passive	Black	Black	PVC	CM	
N281-03M-BK	QSFP+	4x SFP+	3 m	-	-	40 Gbps	Passive	Black	Black	PVC	-	
N282-01M-BK	QSFP+	QSFP+	1 m	-	-	40 Gbps	Passive	Black	Black	PVC	-	Cisco
N282-02M-BK	QSFP+	QSFP+	2 m	-	-	40 Gbps	Passive	Black	Black	PVC	-	Cisco
N282-03M-BK	QSFP+	QSFP+	3 m	-	-	40 Gbps	Passive	Black	Black	PVC	-	Cisco
N282-20N-28-BK	QSFP+	QSFP+	50cm	-	-	100 Gbps	Passive	Black	Black	PVC	-	Cisco
N282-01M-28-BK	QSFP+	QSFP+	1 m	-	-	100 Gbps	Passive	Black	Black	PVC	-	Cisco
N282-02M-28-BK	QSFP+	QSFP+	2 m	-	-	100 Gbps	Passive	Black	Black	PVC	-	Cisco
N282-03M-28-BK	QSFP+	QSFP+	3 m	-	-	100 Gbps	Passive	Black	Black	PVC	-	Cisco
N28H-10M-AQ	QSFP28	QSFP28	10 m	OM3	8	100 Gbps	-	Aqua	Aqua	PVC	OFNP	-

Power Cords

Connects a PC or server to a PDU or UPS system in a data rack or cabinet.



Key points:

- Fully VDE-compatible for European IT applications
- Ideal replacement for worn-out or missing power cable

Ideal for:

- Data Center
- Server room
- PDU & ATS connection

Part number	Connectors		Length	Input		COLORS		PHYSICAL		Rack configuration
	Connector 1	Connector 2		Max Amps	Voltage Compatibility (VAC)	Power Cord	Plug Color	Cable Jacket Material	Power Cord Jacket Type	
P004-P5M-EU	C13	C14	50 cm	10 A	250 V	Black	Black	PVC	H05SW-F	PDU & ATS
P004-01M-EU	C13	C14	1 m	10 A	250 V	Black	Black	PVC	H05SW-F	PDU & ATS
P004-02M-EU	C13	C14	2 m	10 A	250 V	Black	Black	PVC	H05SW-F	PDU & ATS
P036-02M-EU	C20	C19	2 m	16 A	250 V	Black	Black	PVC	H05SW-F	PDU & ATS
P050-2P5M-EU	Schuko	C19	2.5m	16 A	250 V	Black	Black	PVC	H05SW-F	-
P052-2P5M-UK	BS1363	C19	2.5m	16 A	250 V	Black	Black	PVC	H05SW-F	-
P054-01M-EU	Schuko	C13	1 m	10 A	100-250 V	Black	Black	PVC	H05SW-F	-
P054-02M-EU	Schuko	C13	2 m	10 A	100-250 V	Black	Black	PVC	H05SW-F	-
P054-03M-EU	Schuko	C13	3 m	10 A	100-250 V	Black	Black	PVC	H05SW-F	-
P056-01M-UK	BS1363	C13	1 m	10 A	250 V	Black	Black	PVC	H05SW-F	-
P056-02M-UK	BS1363	C13	2 m	10 A	250 V	Black	Black	PVC	H05SW-F	-
P056-03M-UK	BS1363	C13	3 m	10 A	250 V	Black	Black	PVC	H05SW-F	-



Work from anywhere (WFA), Retail & Education

- Docking Stations, USB Hubs & Multiport Adapters
- Power Solutions
- USB Cables
- USB Adapters
- USB Extenders
- Power Cords
- Height-Adjustable Workstations
- Desktop Monitor Mounts and Mobile Workstations



Docking Stations

Expand the potential of your Windows laptop, smartphone or PC's USB-C or Thunderbolt 3 port.



Key points:

- Connects up to 3 displays at the same time: extended & mirror modes
- Get fast Power Delivery (PD) charging up to 100W
- Transfer data at up to USB 3.1 Gen 2 speeds (10 Gbps)
- International power adapters (BS 1363 U.K., CEE 7/7 Schuko EU)

Ideal for:

- SoHo (Small Office, Home Office)
- Mobility

Part number	Host Connector (M)	Max resolution supported	Display		Data										Audio port	Ethernet port	Color
			Video Ports					Ports					Storage				
			VGA	Mini DP	DP	DVI	HDMI	USB-A 2.0	USB-A 3.1 Gen 1	USB-A 3.2 Gen 1	USB-C	USB-C PD Charging	SD	Micro SD			
Single display																	
U442-DOCK5D-GY⁽¹⁾	USB-C	4K @ 30Hz	-	-	-	-	1	-	-	3	1	100W	1	1	-	1 Gbps	Gray
U442-DOCK40-6	USB-C	8K @ 30Hz	-	-	-	-	1	-	-	2	2	100W	-	-	-	1 Gbps	Gray
Dual displays																	
U442-DOCK8G-GG	USB-C	4K @ 30Hz	-	-	-	-	2	-	-	3	-	100W	1	1	-	1 Gbps	Gray
MTB3-DOCK-04	Thunderbolt 3	4K @ 60Hz	-	-	1	-	1	-	-	2	1	60W	-	-	1	1 Gbps	Black
Triple displays																	
U442-DOCK7D-B⁽¹⁾	USB-C	4K @ 30Hz	1	-	1	-	1	-	1	1	2	100W	1	1	1	1 Gbps	Black
U442-DOCK16-B	USB-C	4K @ 30Hz	1	1	-	-	1	-	-	2	1	60W	-	-	-	1 Gbps	Black
External Power Supply models																	
U442-DOCK4-INT	USB-C	4K @ 30Hz	1	-	1	-	1	2	1	1	1	100W	-	-	2	1 Gbps	Silver

⁽¹⁾ With Detachable Cord.

USB Hubs

Connect up to 8 USB devices via a single USB port on your desktop, laptop, or tablet.

Key points:

- USB data transfer rates up to 10 Gbps
- International power adapters (BS 1363 U.K., CEE 7/7 Schuko EU)

Ideal for:

- SoHo (Small Office, Home Office)
- Mobility



Part number	Host Connector (M)	Data ports						Storage		Ethernet port	Color
		USB-A 2.0	USB-A 3.1 Gen 1	USB-A 3.2 Gen 1	USB-B	USB-C	USB-C PD Charging	SD	Micro SD		
USB hubs											
U360-004-SLIM	USB-A	-	4	-	-	-	-	-	-	-	Black
U360-007-AL-INT	USB-A	-	-	7	-	-	-	-	-	-	Black
U460-003-3A1GB	USB-C	-	3	-	-	-	-	-	-	1 Gbps	Black
U460-003-3AGALC	USB-C	-	-	-	-	3	100W	-	-	1 Gbps	Gray
U460-004-2A2C-2	USB-C	-	-	2	-	2	-	-	-	-	Black
External Power Supply models											
U360-007-INT	USB-A	-	-	7	-	-	-	-	-	-	Black
U360-010C-2X3	USB-A	8	-	2	-	-	-	-	-	-	White

Multiport Adapters

Adds USB-A, USB-C PD charging and memory card ports to the USB-C or Thunderbolt 3 port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.



Key points:

- Gain USB-A or USB-C ports for connecting to peripherals
- HD or UHD (4K) video output
- Extended and Mirror modes for AV models
- Single Display

Ideal for:

- SoHo (Small Office, Home Office)
- Mobility

Part number	Host Connector (M)	Display Max resolution supported	Data Ports										Ethernet port	Color		
			Video Ports					USB-A 2.0	USB-A 3.0 5 Gbps	USB-A 3.0 10 Gbps	USB-C	USB-C PD Charging			SD	Micro SD
			VGA	Mini DP	DP	DVI	HDMI									
U444-06N-HGU-C	USB-C	Full HD 1080p	-	-	-	-	1	-	-	1	1	60W	-	-	1 Gbps	White
U444-06N-HU-C	USB-C	Full HD 1080p	-	-	-	-	1	-	1	-	1	60W	-	-	-	White
U444-06N-H4GUBC	USB-C	4K @ 30Hz	-	-	-	-	1	-	-	1	1	60W	-	-	1 Gbps	White
U444-06N-H4UBC2	USB-C	4K @ 60Hz	-	-	-	-	1	-	-	1	1	100W	-	-	-	Black

What are you looking for?
Find the right Docking Station, Multiports adapter or Hubs & Switches thands to our online configurator.



Desktop Charging Stations

USB charger keeps electronic devices, including tablets, smartphones and laptops, at full capacity via USB connection.



Key points:

- Charge anywhere AC power is available - no computer required
- Charge Up to 10 Devices at the Same Time
- 14 Brackets are adjustable to accommodate number and size of devices being charged
- Protect against overheating, overcurrent and overcharging

Ideal for:

- Healthcare
- Commercial
- SoHo (Small Office, Home Office)
- Office configuration

Part number	Device Compatibility	Number of devices	Charging Method	Connections		Total Charging Amps/Watts	Input Plug Type	Input Plug Type Details
				Ports type	Number of Charging ports			
U280-010-ST-CEE	Phone Tablet Amazon Kindle	Up to 10	USB	USB-A	10x 2.4A	8A / 96W	-	C5 to CEE 7/7 Schuko Power

Charging Stations & Carts

Charge, Sync, Secure and Organize All Your Mobile Devices.



Key points:

- High-speed USB or AC charging
- Convenient Syncing for updates and backups
- Steel enclosure and locks for comprehensive protection
- Clutter-reducing organization of devices and cables

Ideal for:

- Healthcare
- Commercial
- Office configuration
- Education

Part number	Device Capacity	Max. Screen size	Charging Method	Charging Capacity	Security	AC Input	Input cord Type
AC Charging Carts with locking casters included							
CSCXB36AC	36 Laptops	38 cm / 15 in.	AC	2,300W	3-Point Locks (Front and Rear)	230V 50 Hz	C13 to BS 1363
CSCXS36AC	36 Laptops	38 cm / 15 in.	AC	2,300W	3-Point Locks (Front and Rear)	230V 50 Hz	C13 to Schuko CEE 7/7
USB Charging Stations with wall mount slots							
CSCXB16USB	16 Tablets	30 cm / 12 in.	USB 2.0	5V / 2.4A per port	3-Point Locks Padlock Hasp	230V 50 Hz	C13 to BS 1363
CSCXS16USB	16 Tablets	30 cm / 12 in.	USB 2.0	5V / 2.4A per port	3-Point Locks Padlock Hasp	230V 50 Hz	C13 to Schuko CEE 7/7
CSDXB32USB	32 Smartphones	9.30 cm / 3.66 in.	USB 2.0	5V / 2.4A per port	3-Point Locks Padlock Hasp	230V 50 Hz	C13 to BS 1363
CSDXS32USB	32 Smartphones	9.30 cm / 3.66 in.	USB 2.0	5V / 2.4A per port	3-Point Locks Padlock Hasp	230V 50 Hz	C13 to Schuko CEE 7/7
Rackmount USB Chargers							
U280-016-RMINT	16 Devices	Per Rack size	USB 2.0	5V / 2.4A per port	Per Rack lock	230V 50 Hz	C13 to Schuko CEE 7/7 & BS 1363
U280-032-RMINT	32 Devices	Per Rack size	USB 2.0	5V / 2.4A per port	Per Rack lock	230V 50 Hz	C13 to Schuko CEE 7/7 & BS 1363

Accessories

Part number	Description
CSHANDLEKIT2	Mobile Cart Conversion Kit with Handle, Casters and Power Cord Manager for 16-Device AC and USB Charging Stations
CSHANDLERKIT	Mobile Cart Conversion Kit with Handle, Casters and Power Cord Manager for Tablet/Chromebook Charging Stations



Desktop KVM Switches

Controls up to 4 desktop or notebook computers using one centralized video monitor and USB keyboard/mouse.



Key points:

- Controls 2 or 4 desktop or notebook computers using one centralized monitor and USB keyboard/mouse
- Connect USB 3.0 peripherals, such as hard drives and webcams, and share them between computers

Ideal for:

- Healthcare
- Digital Signage
- SoHo (Small Office, Home Office)
- Office open space

Part number	Number of ports	Concurrent Users	PC/Server Connections		Video			Cables/Cable Kits/SIUs
			Side A	Side B	Ports	Details	Max resolution supported	
B004-DP2UA2-K	2	1	2x DisplayPort (F) 2x 3.5mm (F) 2x USB-B (F)	DisplayPort (F) 3.5mm (F) 2x USB-A (F)	-	DP 1.2	4K @60Hz	Included
B004-DPUA2-K	2	1	2x DisplayPort (F) 2x USB-B 3.0 (F) 4x 3.5mm (F)	DisplayPort (F) 2x USB-A 3.0 (F) 2x USB-A (F) 2x 3.5mm (F)	-	DP 1.1	2K @60Hz	Included
B004-DPUA4-K	4	1	4x DisplayPort (F) 4x USB-B 3.0 (F) 8x 3.5mm (F)	DisplayPort (F) 2x USB-A 3.0 (F) 2x USB-A (F) 2x 3.5mm (F)	-	DP 1.1	2K @60Hz	Included
B004-VUA2-K-R	2	1	2x HD15 (F)	HD15 (F) 2x USB-A (F) 2x 3.5mm (F) 2x USB Mini-B (F)	3x HD15 (F)	-	2048x1436 px @60Hz	Included
B005-DPUA2-K	2	1	3x 3.5mm (F) 2x USB-A 3.0 (F)	2x USB-A (F) HDMI (F) 3x DisplayPort (F) 2x USB-B 3.0 (F) 6x 3.5mm (F) 3.5mm x 1.35mm	-	DP 1.4 HDCP 1.4; 2.2	4K @60Hz	Included
B005-DPUA4	4	1	3x 3.5mm (F) 2x USB-A 3.0 (F)	2x USB-A (F) HDMI (F) 4x USB-B 3.0 (F) 5x DisplayPort (F) 10x 3.5mm (F) 3.5mm x 1.35mm	-	DP 1.4 HDCP 1.4; 2.2	4K @60Hz	P785-DPKITxx
B005-HUA2-K	2	1	(3) 3.5MM (F) (2) USB 3.0 A (F)	(2) USB-A (F) (3) HDMI (F) (6) 3.5MM (F) (2) USB 3.0 B (F) 3.5mm x 1.35mm	-	HDCP 1.4; 2.2	4K	Included
B005-HUA4	4	1	(3) 3.5MM (F) (2) USB 3.0 A (F)	(2) USB A (F) (5) HDMI (F) (4) USB 3.0 B (F) (10) 3.5MM (F)	-	HDCP 1.4; 2.2	4K	P785-HKITxx
B032-DPUA2	2	1		DP, USB			4K	Built-in cables
B032-HUA2	2	1		HDMI, USB			1920x1200	Built-in cables
B032-VU1	1	1		VGA, USB			1920x1200	Built-in cables
B032-VU2	2	1		VGA, USB			2048x1536	Built-in cables



Looking for more KVM Switches?

Go to the IT Infrastructure section, page 17.

USB-A 2.0 Cables

Make the connection between a USB device and your computer's USB port.



Key points:

- All USB port types from 31 cm up to 4,57 m
- Data Transfer rate: up to 480 Mbps
- Heavy-Duty models with Aramid Fiber jacket
- MFi-Certified for Broad Device Compatibility / RoHS compliant

Ideal for:

- Commercial
- Office settings

Part number	connections		Cable type	Connector Style	Length	PLATING		Cable Jacket Color	
	Connector A	Connector B				Connector	Contact		
U022-006	USB-A (M)	USB-B (M)	Passive	Straight	1,83 m	Gold	Gold	Black	
U022-010	USB-A (M)	USB-B (M)	Passive	Straight	3,05 m	Gold	Gold	Black	
U022-015	USB-A (M)	USB-B (M)	Passive	Straight	4,57 m	Gold	Gold	Black	
U023-003	USB-A (M)	USB-B (M)	Passive	Ferrite Chokes	Straight	91 cm	Gold	Gold	Black
U023-006	USB-A (M)	USB-B (M)	Passive	Ferrite Chokes	Straight	1,83 m	Gold	Gold	Black
U030-003	USB-A (M)	USB Mini-B 5 Pin (M)	Passive	Straight	91 cm	Gold	Gold	Black	
U030-006	USB-A (M)	USB Mini-B 5 Pin (M)	Passive	Straight	1,83 m	Gold	Gold	Black	
All-in-one cables									
M101-006-LMC-BK	USB-A (M)	Lightning (M) Micro USB-B (M) USB-C (M)	Passive	Straight	1,83 m	Nickel	Gold	Black	

USB-A 2.0 Extension Cables

Extend distances of the fast USB 2.0.



Key points:

- Male / Female cables
- Data Transfer rate: up to 480 Mbps
- RoHS compliant
- Gold plated connectors provide superior conductivity

Ideal for:

- Commercial
- Office settings
- WFA

Part number	Connections		Cable type	Length	Cable Jacket Color
	Connector A	Connector B			
Reversible					
UR024-001	USB-A	USB-A	Passive	31 cm	Black
UR024-006	USB-A	USB-A	Passive	1,83m	Black
UR024-010	USB-A	USB-A	Passive	3,05 m	Black

USB-C Cables

Connect smartphones, computers, wall chargers and other USB-C devices.



Key points:

- RoHS, REACH & UKCA compliant

Ideal for:

- Commercial
- Office settings

Part number	Connections		Cable type	Length	Cable Jacket Color
	Connector A	Connector B			
U040-C1M-C-5A	USB-C	USB-C	Passive	1m	Black
U040-C2M-C-5A	USB-C	USB-C	Passive	2m	Black
U040-C3M-C-5A	USB-C	USB-C	Passive	3m	Black

Lightning Cables

Charges and synchronizes your Apple iPhone, iPad or iPod using the USB port on your computer or wall/car charger.



Key points:

- MFi-Certified for Broad Device Compatibility
- USB port types from 25 cm up to 3,05 m
- Angled cables
- RoHS, REACH & UKCA compliant

Ideal for:

- Commercial
- Office settings

Part number	Connections		Cable type	Length	Cable Jacket Color
	Connector A	Connector B			
M100-003-WH	USB-A	Lightning	Passive	91 cm	White
M100-010-WH	USB-A	Lightning	Passive	3,05 m	White
M102-003-WH	USB-C	Lightning	Passive	91 cm	White
M102-02M-BK	USB-C	Lightning	Passive	2m	Black
M102-03M-BK	USB-C	Lightning	Passive	3m	Black
M102-01M-WH	USB-C	Lightning	Passive	1m	White
M102-02M-WH	USB-C	Lightning	Passive	2m	White
M102AB-01M-WH	USB-C	Lightning		1 m	White
M102AB-02M-WH	USB-C	Lightning		2 m	White

Heavy-duty (Aramid fiber)

M100-003-HD	USB-A	Lightning	Passive	91 cm	Black / White
M100-006-HD	USB-A	Lightning	Passive	1,83m	Black / White
M100-010-HD	USB-A	Lightning	Passive	3,05 m	Black / White
M102-003-HD	USB- C	Lightning	Passive	91 cm	Black / White
M102-006-HD	USB- C	Lightning	Passive	1,83 m	Black / White
M102-010-HD	USB-C	Lightning	Passive	3,05 m	Black / White

USB 3.1 Gen 1 Cables

Connects peripherals and patch bays with female USB-A ports to your computer, laptop or other compatible USB 3.0 device.



Key points:

- Thunderbolt 3 Compatible
- Up to 5 Gbps
- RoHS, REACH & UKCA compliant

Ideal for:

- Commercial
- Office settings

Part number	Connections		Cable type	Length	Cable Jacket Color
	Connector A	Connector B			
U322-003-BK	USB-A	USB-B	Passive	91 cm	Black
U322-006-BK	USB-A	USB-B	Passive	1,83m	Black
U322-010-BK	USB-A	USB-B	Passive	3,05 m	Black
U322-015-BK	USB-A	USB-B	Passive	4,57m	Black
U325-006	USB-A	USB-A	Panel Mount Couplers	1,83m	Black
U325-010	USB-A	USB-A	Panel Mount Couplers	3,05 m	Black
U325-015	USB-A	USB-A	Panel Mount Couplers	4,57m	Black
U326-001-BK	USB-A	Micro-B	Passive	30cm	Black
U326-003-BK	USB-A	Micro-B	Passive	91 cm	Black
U326-006-BK	USB-A	Micro-B	Passive	1,83m	Black
U328-025	USB-A	USB-B	Active Repeater	7,62m	Black
U328-036	USB-A	USB-B	Active Repeater	10,97m	Black
U420-003	USB-C	USB-C	Passive	91 cm	Black
U420-006	USB-C	USB-C	Passive	1,83m	Black
U420-010	USB-C	USB-C	Passive	3,05 m	Black
U428-003	USB-C	USB-A	Passive	91 cm	Black
U428-006	USB-C	USB-A	Passive	1,83m	Black
Angled					
U428-003-CRA	USB-C (M) Right Angle	USB-A (M)	Passive	91 cm	Black

USB 3.2 Gen 2 Cables

USB 3.2 to USB cable connects a smartphone or other USB-C device to the port on your computer, wall charger or car charger.



Key points:

- Thunderbolt 3 Compatible
- Up to 10 Gbps
- RoHS, REACH & UKCA compliant

Ideal for:

- Commercial
- Office settings

Part number	Connections		Cable type	Length	Cable Jacket Color
	Connector A	Connector B			
U420-003-G2-5A	USB-C (M)	USB-C (M)	Passive 5A / 100W	91 cm	Black
U420-C03-G2-5A	USB-C (M)	USB-C (M)	Passive 5A / 100W USB-IF	91 cm	Black
U422-003-G2	USB-C (M)	USB-B (M)	Passive	91 cm	Black
U428-003-G2	USB-C (M)	USB-A (M)	Passive	91 cm	Black
U428-C03-G2	USB-C (M)	USB-A (M)	Passive	91 cm	Black
Plenum-Rated Fiber Active Optical Cable					
U328F-15M	USB-A	USB-B	Active (AOC)	15m	Black
U328F-20M	USB-A	USB-B	Active (AOC)	20m	Black
U328F-30M	USB-A	USB-B	Active (AOC)	30m	Black
U420F-10M-V	USB-C (M)	USB-C (M)	Active (AOC) Backward Compatible 4K @ 60 Hz	10 m	Black
U420F-15M-V	USB-C (M)	USB-C (M)	Active (AOC) Backward Compatible 4K @ 60 Hz	15 m	Black
U420F-30M-V	USB-C (M)	USB-C (M)	Active (AOC) Backward Compatible 4K @ 60 Hz	30 m	Black
U420F-10M-D321	USB-C (M)	USB-C (M)	Active (AOC) Backward Compatible	10 m	Black
U420F-15M-D321	USB-C (M)	USB-C (M)	Active (AOC) Backward Compatible	15 m	Black
Angled					
U420-01M-G25ARA	USB-C (M) Right Angle	USB-C (M)	Passive 5A / 100W	1 m	Black

USB-C 3.0 Extension Cables

High-speed USB extension cable extends the distance between two USB devices.



Key points:

- USB-C Male / Female cables
- Up to 5 Gbps (3.1 Gen 1) & up to 10 Gbps (3.2 Gen 2)
- RoHS, REACH & UKCA compliant

Ideal for:

- Commercial
- Office settings

Part number	Connections		Cable type	Length	Cable Jacket Color
	Connector A	Connector B			
3.2 Gen 2 USB cable					
U428F-10M-D321	USB-A	USB-C	Active (AOC) Backward Compatible	10m	Black
U428F-15M-D321	USB-A	USB-C	Active (AOC) Backward Compatible	15m	Black

Thunderbolt Cables

Connects 2 Thunderbolt 3 devices, including MacBooks and Chromebooks, for charging them or transmitting up to 8K video at 20 or 40 Gbps.



Key points:

- Compatible with all USB-C and Thunderbolt 3 devices
- Provide 5A (100W) power output for charging and powering large-capacity mobile devices
- Reversible Thunderbolt 3 plugs connect in either direction for immediate no-fuss use

Ideal for:

- Apple's devices
- Commercial
- Office settings

Part number	Connections		Cable				Video		Color
	Connector A	Connector B	Type	Data Transfer Rate	Power Delivery	Length	Max Supported Video Resolution	DP	
U521-1P0M-WH	Thunderbolt 3 (Type-C(M))	Thunderbolt 3 (Type-C (M))	Passive	40Gbps	240W	1 m	8K @ 60 Hz	2.1	White
U521-1P2M-BK	Thunderbolt 3 (Type-C(M))	Thunderbolt 3 (Type-C (M))	Passive	40Gbps	240W	1,2 m	8K @ 60 Hz	2.1	Black
U521-1P0M-WH20G	Thunderbolt 3 (Type-C(M))	Thunderbolt 3 (Type-C (M))	Passive	20Gbps	240W	2 m	4K x 2K @ 60 Hz	2.1	White

USB Couplers

Converts a standard USB port into a more convenient down-angled USB port in tight spaces, such as behind furniture or against a wall.



Key points:

- Supports USB 3.0 SuperSpeed data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Durable one-piece molded adapter fits easily in pocket or bag for connecting anywhere
- Plug-and-play

Ideal for:

- Powering computers
- Printers
- Home/office peripherals

Part number	Connections			Data transfer rate (up to)	Angled
	Connector A	Connector B	USB generation		
U324-000-DN	USB-A (M)	USB-A (F)	3.0	5 Gbps	Down
U324-000-UP	USB-A (M)	USB-A (F)	3.0	5 Gbps	Up
U420-000-F-UD	USB-C (M)	USB-C (F)	3.0	10 Gbps	Right

USB Adapters

Easily connect your PC, laptop or tablet to a Gigabit Ethernet network, Serial, Audio, Video or Memory card devices.

Key points:

- Data transfer speeds up to 5 Gbps—10 times faster than USB 2.0
- Gold-plated contacts for maximum conductivity and minimum data loss
- Backward compatible with previous USB generations

Ideal for:

- Office configuration
- SoHo



Part number	Connections		USB generation	Data transfer rate (up to)	VIDEO			Cable	
	Connector A	Connector B			Max Supported Video Resolution	HDCP	DP	Type	Cable Length (m)
Serial / Ethernet									
USA-19HS	USB-A (M)	DB89 (M)	2.0	480 Mbps	-	-	-	-	91 cm
USA-19HS-C	USB-C (M)	DB89 (M)		230 Kbps	-	-	-	-	91 cm
EU U209-006-2	USB-A (M)	2x DB89 (M)	2.0	480 Mbps	-	-	-	-	1,83 m
U209-006-RJ45-X	USB-A (M)	RJ45 (M)	2.0	480 Mbps	-	-	-	-	1,83 m
EU U209-006-RJ45XC	USB-C (M)	RJ45 (M)	2.0	480 Mbps	-	-	-	-	1,83 m
USB									
U261-001-BT4	USB-A (M)	-	2.0	480 Mbps	-	-	-	Bluetooth 4.0	-
U329-000	USB-A (M)	USB-C (F)	3.0	5 Gbps	-	-	-	-	-
EU U329-000-10G	USB-A (M)	USB-C (F)	3.0	10 Gbps	-	-	-	-	-
U428-000-F	USB-C (M)	USB-A (F)	3.0	5 Gbps	-	-	-	-	-
Ethernet (Cat5/5e, Cat6, Cat6a)									
U436-06N-GB-C	USB-C (M)	USB-C (F) RJ45 (F)	3.0	5 Gbps	-	-	-	-	Pigtail
U436-06N-GBW-RA	USB-C (M)	RJ45 (F)	3.0	5 Gbps	-	-	-	Right Angle	Pigtail
Fiber									
U336-MMF-1G-LC	USB-A (M)	LC (F)	3.0	5 Gbps	-	-	-	Multimode	550 m
Memory Card Readers									
U352-000-SD-R	USB-A (M)	SD (F)	3.0	5 Gbps	-	-	-	-	-
Video									
U444-06N-DP4K6B	USB-C (M)	DisplayPort (F)	3.0	5 Gbps	4K @ 60Hz	2.2	1.3	-	Pigtail
U444-06N-DP8B	USB-C (M)	DisplayPort (F) 1.2	3.0	5 Gbps	8K @ 30Hz	1.4 2.2	1.2 1.4	Active	Pigtail
U444-06N-HD4K6B	USB-C (M)	HDMI (F)	3.0	5 Gbps	(4K x 2K) @ 60Hz	2.2	-	-	Pigtail
U444-06N-HD8KW	USB-C (M)	HDMI (F)	3.0	5 Gbps	8K @ 30Hz	1.4 2.3	1.4	-	Pigtail
U444-06N-HDR4-B	USB-C (M)	HDMI (F)	3.0	5 Gbps	4K @ 60Hz	2.2	-	Active	Pigtail
U444-06N-HDR-B	USB-C (M)	HDMI (F)	3.0	5 Gbps	4K @ 60Hz	2.2	-	Active	Pigtail
U444-06N-MDP8W	USB-C (M)	DisplayPort (F)	3.0	5 Gbps	8K @ 30Hz	1.4 2.2	1.2 1.4	Active	Pigtail
U444-003-H	USB-C (M)	HDMI (M)	3.0	5 Gbps	4K @ 30Hz	1.4	-	Active	91 cm
U444-006-DP-BD	USB-C (M)	DisplayPort (M)	3.0	5 Gbps	4K @ 60Hz	2.2	1.2	Active	1,83 m
U444-006-H	USB-C (M)	HDMI (M)	3.0	5 Gbps	4K @ 30Hz	1.4	-	Active	1,83 m
EU U444-006-H4K6BM	USB-C (M)	HDMI (M)	3.0	5 Gbps	4K @ 60Hz	2.2	-	Active	1,83 m
EU U444-010-H4K6BM	USB-C (M)	HDMI (M)	3.0	5 Gbps	4K @ 60Hz	2.2	-	Active	3,1 m
EU U444-015-H4K6BM	USB-C (M)	HDMI (M)	3.0	5 Gbps	4K @ 60Hz	2.2	-	Active	4,6 m
With alternate mode - DP 1.2									
U444-06N-HDB-AM	USB-C (M)	HDMI (F)	3.0	5 Gbps	4K @ 24/25/30Hz	1.4	1.2	-	Pigtail
U444-06N-VGA-AM	USB-C (M)	HD15 (F)	3.0	5 Gbps	1920 x 1200 (1080p) @ 60Hz	-	1.2	-	Pigtail

USB Panel Mount

Combine USB ports with universal keystone jacks or panels.





Key points:

- Extra versatility for installing in tight spaces
- Professional, clutter-free look

Ideal for:

- Motherboard
- Podium
- Kiosk

Part number	Connections		Cable			
	Connector A	Connector B	USB generation	Data transfer rate	Type	Cable Length (m)
Cables						
 U024-06N-PM	USB-A (M)	USB-A (F) - Panel Mount	2.0	Up to 480 Mbps	Passive	Pigtail
 U025-001-PM	USB-B (M)	USB-B (F) - Panel Mount	2.0	Up to 480 Mbps	Passive	31 cm
Panels						
U324-006	USB-A (M)	USB-A (F)	3.0	Up to 5 Gbps	Passive	1,83 m
U324-010	USB-A (M)	USB-A (F)	3.0	Up to 5 Gbps	Passive	3,05 m

USB Extenders

Connects your home/office PC or laptop to a webcam, printer, hard drive or other USB peripheral located up to 50 m away.





Key points:

- Daisy-chain 2 cables
- Backward compatible with previous USB generations

Ideal for:

- Lecture halls
- Conference rooms
- Webcam applications

Part number	Connections				Cable			Number of Ports	Power Source Type
	Connector A	Connector B	USB generation	Data transfer rate	Max distance	Type	Cable Length (m)		
Over Ethernet Cable									
B202-150	USB-A (M) RJ45 (F)	USB-A (M) RJ45 (F)	2.0	Up to 480 Mbps	45,72 m	Passive	-	1	USB
B203-101-PNPINT	USB-A (M) RJ45 (F)	USB-A (M) RJ45 (F)	2.0	Up to 480 Mbps	50 m	Passive	-	1	Int AC Adapter
B203-101-POC	USB-A (M) RJ45 (F) Micro USB-B (F)	RJ45 (F)	2.0	Up to 480 Mbps	50 m	Passive	-	1	USB
 B203-104-PNP	USB-A (M) RJ45 (F)	4x USB-A (F) RJ45 (F)	2.0	Up to 480 Mbps	50 m	Passive	-	4	USB
 B203-104-POC	4x USB-A (F) RJ45 (F) Micro USB-B (F)	RJ45 (F)	2.0	Up to 480 Mbps	50 m	Passive	-	4	USB
Extension Repeater Cable									
U026-10M	USB-A (M)	USB-A (F)	2.0	Up to 480 Mbps	-	Active	10 m	-	USB
U026-15M	USB-A (M)	USB-A (F)	2.0	Up to 480 Mbps	-	Active	15 m	-	USB
U026-20M	USB-A (M)	USB-A (F)	2.0	Up to 480 Mbps	-	Active	20 m	-	USB
U042-036	USB-A (M)	USB-B (M)	2.0	Up to 480 Mbps	-	Active	10,97 m	-	USB
U042-050	USB-A (M)	USB-B (M)	2.0	Up to 480 Mbps	-	Active	15,24 m	-	USB
U330-05M	USB-A (M)	USB-A (F)	3.0	Up to 5 Gbps	-	Active	5 m	-	USB
U330-10M	USB-A (M)	USB-A (F)	3.0	Up to 5 Gbps	-	Active	10 m	-	USB
U330-15M	USB-A (M)	USB-A (F)	3.0	Up to 5 Gbps	-	Active	15 m	-	USB
U330-20M	USB-A (M)	USB-A (F)	3.0	Up to 5 Gbps	-	Active	20 m	-	USB

Power Cords

Connects your notebook computer or laptop with a 3-slot C6 power inlet to a PDU or UPS system



Key points:

- Ideal replacement for a worn-out or missing laptop adapter power cable
- VDE-compliant H03VV-F jacket allows use in European IT applications

Ideal for:

- Home/Office peripherals
- Commercial

Part number	Connectors		Length	Input		COLORS		PHYSICAL		Rack configuration
	Connector 1	Connector 2		Max Amps	Voltage Compatibility (VAC)	Power Cord	Plug Color	Cable Jacket Material	Power Cord Jacket Type	
P014-P15M-EU	C14	C5	15 cm	2.5 A	250 V	Black	Black	PVC	H05VV-F	PDU & ATS
P014-02M-EU	C14	C5	2 m	2.5 A	250 V	Black	Black	PVC	H05VV-F	PDU & ATS
P058-02M-EU	Schuko	C5	2 m	2.5 A	250 V	Black	Black	PVC	H05VV-F	PDU & ATS
P060-02M-UK	BS1363	C5	2 m	2.5 A	250 V	Black	Black	PVC	H05VV-F	-

Height-Adjustable Workstations

Sit-stand workstation transforms your desk space into an ergonomic working environment without modifying the surface.



Key points:

- Desktop & Wall mounting location
- Fixed and Mobile Workstations
- Height-adjustable models
- Single display configuration
- Integrated Thin-Client Mount and Cable Management

Ideal for:

- Healthcare
- Commercial
- Industrial
- Office settings

Part number	Screen size		Mounting Location		VESA Pattern (mm)		Max Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
	Min	Max			Min	Max					
WWSS1327RWTC	13"	27"	Wall	-	75x75 mm	100x100 mm	8 kg	Full	Tilt: -15/+15 Swivel: -90/+90 Rotate: 360°	Yes	Silver
WWSS1332W	13"	32"	Wall	-	75x75 mm	100x100 mm	8 kg	Full	Swivel: 180° Rotate: 360°	Yes	Silver
Mobile Workstations											
WWSS1DWSTAA	-	-	Floor	-	75x75 mm	100x100 mm	7 kg	Swivel Tilt	Swivel: 360° Tilt: 60°	Yes	Ivory

(1) Mobile Workstation with 2x Adjustable Shelves, 2x Metal Drawers.

Accessories

Part number	Accessory Type	Screen size		Mounting Location	VESA Pattern (mm)		Max Weight Capacity	Motion	Degrees of Motion
		Min	Max		Min	Max			
DMA1327SD	Dual Bar Mount	13"	27"	Desktop Desk Clamp	75x75 mm	100x100 mm	10 kg	Full	Tilt: 15/+15° Rotate: 360°



Desktop Monitor Mounts

Get an ergonomic sit-stand workstation without modifying the entire work surface.







Key points:

- Monitor stand with heavy-duty base remains stable on your desk during adjustment
- Durable steel construction blends into any décor and supports up to 12 kg per monitor

Ideal for:

- Healthcare
- Commercial
- SoHo (Small Office, Home Office)
- Office configuration

Part number	Screen size (")		Mounting Location	VESA Pattern (mm)		Max Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
	Min	Max		Min	Max					
Single Display 										
DDV1727S	17"	27"	Freestanding	75x75 mm	100x100 mm	6 kg	Swivel Tilt	Tilt: -20/+60 Swivel: 30° Rotate: 360°	Yes	Black
DDR1732SAL	17"	32"	Desk Clamps & Grommets	75x75 mm	100x100 mm	9 kg	Full-motion arms	Tilt: -90/+90 Swivel: 90° Rotate: 90°	Yes	Silver
Dual Displays 										
DDR1527SDC	15"	27"	Freestanding	75x75 mm	100x100 mm	8 kg	Full	Tilt: -20/+20 Swivel: 20° Rotate: 360°	Yes	Black
DDR1327SDD	13"	27"	Freestanding	75x75 mm	100x100 mm	12 kg	Full	Tilt: -45/+45 Swivel: 180° Rotate: 360°	Yes	Black
DDR1327SDFC-1	13"	27"	Desk Clamp	75x75 mm	100x100 mm	8 kg	Full	Tilt: -30/+30 Swivel: 180° Rotate: 360° (head)	Yes	Black
DDR1727DC	17"	27"	Desk Clamps & Grommets	75x75 mm	100x100 mm	7 kg	Swivel Tilt	Tilt: -10/+10 Swivel: 10° Rotate: 360°	Yes	Black
DDR1732DAL	17"	32"	Desk Clamps & Grommets	75x75 mm	100x100 mm	9 kg	Full	Tilt: -90/+90 Swivel: 90° Rotate: 90°	Yes	Silver
DMPDD1735AM	17"	35"	Desk Clamps & Grommets	75x75	100x100	10 kg	Full	-22/+45 Tilt 32° Swivel 90° Rotate	Yes	Black
Triple Displays 										
DDR1730TAL	17"	30"	Desk Clamps & Grommets	75x75 mm	100x100 mm	7 kg	Full	Tilt: -90/+90 Swivel: 90° Rotate: 90°	Yes	Silver
DMPDT1732AM	17"	32"	Desk Clamps & Grommets	75x75	100x100	6 kg	Full	-22/+45 Tilt 32° Swivel 90° Rotate	Yes	Black
Quad Displays 										
DDR1327MQ	13"	27"	Freestanding	75x75 mm	100x100 mm	8 kg	Full	-45/+45 Tilt 180° Swivel 360° Rotate	-	Black

Rolling TV Stands and Carts

HDMI cable with antibacterial properties connects audio/video components to a 4K display.



Key points:

- Antibacterial material: connectors & PVC jacket

Ideal for:

- Digital signage
- Retail
- WFA

Part number	Mounting Location	VESA Pattern (mm)		Number of Displays	Heavy-Duty	Maximum Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
		Min	Max							
DMCS70120AMUL	Floor	200x200	1000x600	1	Yes	120 kg	Full	360°	Yes	Black

⁽¹⁾With Ethernet

Mobile Workstations

Mobile Workstation with Monitor Mount - For 17" to 32" Displays, Height Adjustable



Key points:

- All-in-one workstation you can roll from room to room.
- -15° to +15° tilt adjustment improves viewing angles
- Swivel casters allow easy rolling over thresholds

Ideal for:

- Office
- Hospital & Clinic
- Classroom

Part number	Screen size		VESA Pattern (mm)		Max Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
	Min	Max	Min	Max					
DMCS1732S	17"	32"	75x75	100x100	8 kg	Tilt	-30/+30 Tilt	Yes	Black



Pro AV & Digital Signage

Mounts, stand and carts, workstations

DVI

VGA

HDMI

Display Port

Audio

Wall Mounts

Low-profile mount hangs a flat-panel television, monitor or other display on the wall.



Key points:

- Security Wall Mount Hangs Your Flat-Panel or Curved-Screen TV or Monitor on the Wall
- Optimize viewing angles
- Horizontal adjustment compensates for off-center wall studs.
- Fixed / Swivel / Tilt / Rotate models
- Increase available desk/table space in office applications.

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Screen size		VESA Pattern (mm)		Max Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
	Min	Max	Min	Max					
Fixed									
DWF1327M	13"	27"	50x50	200x200	40 kg	Fixed	-	-	Black
DWF3770L	37"	70"	300x200	800x400	65 kg	Fixed	-	-	Black
DWF4585X	45"	85"	200x200	800x400	91 kg	Fixed	-	-	Black
DWF60100XX	60"	100"	200x200	900x600	159 kg	Fixed	-	-	Black
Tilt									
DWT1327S	13"	27"	75x75	100x100	40 kg	Tilt	-15/+10 Tilt	-	Black
DWT2655XP	26"	55"	200x200	400x400	75 kg	Tilt	-10/+10 Tilt	-	Black
DWT3770X	37"	70"	200x200	800x400	91 kg	Tilt	-10/+0 Tilt	-	Black
DWT60100XX	60"	100"	100x100	1000x800	159 kg	Tilt	-15/+15 Tilt	-	Black
Full									
DWM1327SE	13"	27"	75x75	100x100	15 kg	Full	-15/+15 Tilt 180 Swivel	-	Black
DWM1327SP	13"	27"	75x75	100x100	15 kg	Full	-15/+15 Tilt 180 Swivel -2/+2 Level Adjustment	-	Black / Silver
DMC1342S	13"	42"	100x100	200x200	20 kg	Full	-15/+15 Tilt 180 Swivel -3/+3 Level Adjustment	Yes	Black / Silver
DWM2355S	23"	55"	75x75	400x400	23 kg	Full	-15/+15 Tilt 180 Swivel	-	Black
DWM2655M	26"	55"	100x100	400x400	50 kg	Full	-15/+15 Tilt 120 Swivel -5/+5 Level Adjustment	-	Black
DWM3770X	37"	70"	100x100	600x400	75 kg	Full	-15/+15 Tilt 120 Swivel -3/+3 Level Adjustment	-	Black
DMWC3770M	37"	70"	100x100	600x400	45 kg	Full	90 Swivel -8/+5 Level Adjustment	-	Black
DWM60100XX	60"	100"	100x100	600x400	75 kg	Full	-15/+15 Tilt 120 Swivel -3/+3 Level Adjustment	-	Black

Part number	Screen size		VESA Pattern (mm)		Max Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
	Min	Max	Min	Max					
Pop-Out									
DMVWSC4570XUL	45"	70"	200x200	600x400	70 kg	Fixed	-	-	Black
Heavy-Duty									
DWFSC3255MUL	32"	55"	200x200	400x400	68 kg	Fixed	-	-	Black
DWFSC3780MUL	37"	80"	300x200	600x400	91 kg	Fixed	-	-	Black
DWTPSC4555M	45"	55"	200x100	400x600	50 kg	Tilt	-	-	Black
DWTSC3255MUL	32"	55"	200x200	400x400	68 kg	Tilt	-15/+10 Tilt	-	Black
DWTSC3780MUL	37"	80"	300x200	600x400	91 kg	Tilt	-10/+5 Tilt	-	Black
Outdoor									
DWM3270XOUT	32"	70"	200x200	400x400	50 kg	Full	-20/+10 Tilt 180° Swivel -3/+3 Level Adjustment	No	Black
DWM3780XOUT	37"	80"	200x200	600x400	50 kg	Full	-20/+10 Tilt 180° Swivel -3/+3 Level Adjustment		Black

What are you looking for?
Find the right solutions through our mount finder.



TV Stands and Carts

Height-adjustable mobile cart with upscale, professional look lets you smoothly roll your display from one room to another.



Key points:

- Durable aluminum/steel frame blends into any room décor
- Adjustable feet levelers provide a stable and safe foundation
- Cable management clips keep cords organized and prevent cable clutter
- Single display models

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Screen size		VESA Pattern (mm)		Max Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
	Min	Max	Min	Max					
Single display									
DMC1342S	13"	42"	75x75	200x200	20 kg	Tilt	0/+10 Tilt	Yes	Black
DMCS3770L	37"	70"	200x200	600x400	40 kg	Tilt	-10/+10 Tilt	Yes	Black
Rotating Portrait/Landscape									
DMCS3270XP	32"	70"	200x200	600x400	68 kg	Full	360° Rotate	Yes	Black / Silver
DMCS3770ROT	37"	70"	200x200	600x400	70 kg	Full	360° Rotate	Yes	Black
Wide Legs									
DMCS60100XX	60"	100"	200x200	1000x600	100 kg	Tilt	-10/+5 Tilt	Yes	Black / Silver
DMCS60105XXDD	60"	105"	200x200	1000x600	150 kg	Fixed	-	Yes	Black
Premier Series									
DMCS3255SG62	32"	55"	75x75	400x400	59 kg	Fixed	-45/+45 Tilt	Yes	Black / Silver
DMCS3255SG62W	32"	55"	75x75	400x400	59 kg	Fixed	-45/+45 Tilt	Yes	White
DMCS3770SG75	37"	70"	100x100	600x400	79 kg	Fixed	-45/+45 Tilt	Yes	Black / Silver
DMCS3770SG75W	37"	70"	100x100	600x400	79 kg	Fixed	-45/+45 Tilt	Yes	White

Tablet & Smartphone Mounts

Suspends a digital projector from the ceiling, which saves valuable wall and floor space.



Key points:

- Mount tablets or smartphones for hands-free viewing
- Choose from desktop stands, wall mounts and floor stands

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Devices	Max Weight Capacity	Motion	Degrees of Motion	Height adjustable	Color
DMTBS911	Tablet	1 kg	Full	-90/+90 Tilt	No	Black / Silver
DMTBD413	Smartphone Tablet	1 kg	Full	-160/+210 Tilt -52/+52 Swivel 180° Rotate	Yes Flexible Long-Arm	White

⁽¹⁾ Secure freestanding tablet mount.

DVI Splitters

DVI splitter transmits 1080p video with audio from a DVI-D source to two DVI-D display devices past the 4.88 m distance limitation.






Key points:

- Superior molded connectors for long life use
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p (60Hz)
- Easy plug-and-play operation for immediate connection right from the box

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Input x Output	Resolution	Number of ports	Cable	Length	Daisy-chainable Cascadable
	Connector A	Connector B				Type		
 B116-002A-INT	DVI-D (F) 3.5MM (M)	2x DVI-D (F) 2x 3.5MM (M)	1 x 2	1920 x 1200px	2	-	-	Up to 3 levels
 P564-001	DVI-D Dual Link (M)	2x DVI-D Dual Link (M) (Wired to DVI-D Single Link)	1 x 2	Up to 1920 x 1080px	-	Passive	31 cm	-
 P564-06N-DV	DVI-I Dual Link (M)	DVI-I Dual Link (F)	1 x 2	Full HD @ 60Hz	-	Passive	Pigtail	-

DVI Cables

Deliver the high performance and high bandwidth needed for today's digital video displays.



Key points:

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600

Ideal for:

- WFA / Office
- Hospital & Clinic
- Classroom
- Event / Tradeshow

Part number	Connections		Cable	Length	Color
	Connector A	Connector B	Type		
P560-003	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	91 cm	Black
P560-006	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	1,83 m	Black
P560-010	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	3,05 m	Black
P560-015	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	4,57 m	Black
P560-020	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	6,09 m	Black
P560-025	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	7,62 m	Black
P560-050	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	15,24 m	Black
P561-006	DVI-D Single Link (M)	DVI-D Single Link (M)	Passive	1,83 m	Black
P561-006-SLI	DVI-I Single Link (M)	DVI-I Single Link (M)	Passive	1,83 m	Black
P561-010	DVI-D Single Link (M)	DVI-D Single Link (M)	Passive	3,05 m	Black
P561-015	DVI-D Single Link (M)	DVI-D Single Link (M)	Passive	4,57 m	Black
P561-050	DVI-D Single Link (M)	DVI-D Single Link (M)	Passive	15,24 m	Black

Extension Cable

P562-006	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	1,83 m	Black
P562-006-SL	DVI-D Single Link (M)	DVI-D Dual Link (F)	Passive	1,83 m	Black
P562-010	DVI-D Dual Link (M)	DVI-D Dual Link (M)	Passive	3,05 m	Black

DVI Adapter Cables

Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and DVI-enabled display.



Key points:

- Premium double shielded digital video cable protects against EMI/RFI noise.
- Gold plated connectors and contacts provide optimal signal transfer.
- Supports high-def video resolutions up to 1920 x 1080 @60Hz (1080p).
- Supports a bandwidth up to 5Gbps

Ideal for:

- WFA
- Office
- Hospital & Clinic
- Classroom
- Event / Tradeshow

Part number	Connections		Cable Type	Length	Cable Jacket		Color
	Connector A	Connector B			Material	Rating	
P556-006	DVI-A(M)	HD15 (M)	Passive	1,83 m	PVC	WW-1	Black
P556-010	DVI-A(M)	HD15 (M)	Passive	3,1 m	PVC	WW-1	Black
P566-003	HDMI (M)	DVI-D Single Link (M)	Passive	91 cm	PVC	WW-1	Black
P566-006	HDMI (M)	DVI-D Single Link (M)	Passive	1,83 m	PVC	WW-1	Black
P566-010	HDMI (M)	DVI-D Single Link (M)	Passive	3,1 m	PVC	WW-1	Black

DVI Adapters

Convert a DVI digital signal to VGA, Micro-HDMI or HDMI analog to provide compatibility between a monitor and a computer with DVI output.



Key points:

- Compact size for installation in tight spaces
- View presentations, Videos or pictures on a DVI monitor or projector
- Fully shielded and molded construction

Ideal for:

- Office
- Classroom
- Co-nference room
- Trade show
- Lobbies

Part number	Connections		Max Supported Video Resolution	Length	Color
	Connector A	Connector B			
P132-08N	DVI-I Dual Link (F) (Wired to DVI-D Single Link)	HDMI (M)		20,32 cm	Black



VGA Switches

Optimal solution for connecting two computers to one monitor or two monitors to one computer.



Key points:

- 2-port HD15 VGA/SVGA Push-Button Switch
- Connects two computers to one monitor or two monitors to one computer
- Fully-shielded rugged metal case with front-panel push button switch

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Connections			Max Resolution	Number of Ports	Power Source Type
	Connector A	Connector B	Input x Output			
B112-002-R	2x HD12 (F)	HD15 (F)	2 x 1	1920 x 1080 @ 60Hz	2	Silver

VGA Extenders

Allows VGA display devices to be connected up to 152 m away from the source computer, well beyond the standard VGA cable range.



Key points:

- Extends a 1920 x 1440 (60 Hz) signal up to 106 m, or a 1024 x 768 (60 Hz) signal up to 152 m
- USB-powered...no external AC power needed
- Built-in VGA dongles...no need for additional VGA cables
- Uses readily available Cat5e or Cat6 solid conductor cable

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Connections		Video			Power Source Type
	Connector A	Connector B	Max Resolution	Number of Displays	Number of Ports	
B130-101-U	HD15 (M) RJ45 (F) USB-A (M)	HD15 (M) RJ45 (F)	1920 x 1440 @ 60Hz	1	1	USB



VGA Cables

Allows Connection Between VGA-Enabled Computer and Monitor.



Key points:

- 2-port HD15 VGA/SVGA Push-Button Switch
- Connects two computers to one monitor or two monitors to one computer
- Fully-shielded rugged metal case with front-panel push button switch

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Connections		Cable		Length	Angled	Color
	Connector A	Connector B	Technology	Type			
P502-003	HD15 (M)	HD15 (M)	Coax, VGA/SVGA	Passive	91 cm	-	Black
P502-006	HD15 (M)	HD15 (M)	Coax, VGA/SVGA	Passive	1,83 m	-	Black
P502-010	HD15 (M)	HD15 (M)	Coax, VGA/SVGA	Passive	3,05 m	-	Black
P502-015	HD15 (M)	HD15 (M)	Coax, VGA/SVGA	Passive	4,57 m	-	Black
P504-006	HD15 (M) + 3.5MM(M)	HD15 (M) + 3.5MM(M)	Coax, VGA/SVGA Stereo Audio	Passive	1,83 m	-	Black
P504-010	HD15 (M) + 3.5MM(M)	HD15 (M) + 3.5MM(M)	Coax, VGA/SVGA Stereo Audio	Passive	3,05 m	-	Black
P504-015	HD15 (M) + 3.5MM(M)	HD15 (M) + 3.5MM(M)	Coax, VGA/SVGA Stereo Audio	Passive	4,57 m	-	Black

HDMI Splitters

Transmit 4K video and audio from one HDMI source to up to 8 HDMI displays at the same time.



Key points:

- Support up to 4K @60Hz video resolutions
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Power over Cable (PoC) technology provides power to receivers via Cat6 cable

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Video			Number of ports	Daisy-chainable cascadable	Int AC Adapter
	Connector A	Connector B	Input x Output	Max Resolution	HDCP			
B118-002-HDR-V2	HDMI (M)	2x HDMI (F) Micro USB-B (F)	1 x 2	4K @ 60Hz	2.2	2		-
B118-002-UHD-2	HDMI (F)	2x HDMI (F)	1 x 2	4K @ 60Hz	2.2	2	Yes	Yes
B118-002-UHDINT	HDMI (M)	2x HDMI (F)	1 x 2	4K @ 30Hz	1.4	2		Yes
B118-004-HDR	HDMI (F)	4x HDMI (F)	1 x 4	4K @ 60Hz	2.2	4		Yes
B118-004-UHD-2	HDMI (F)	4x HDMI (F)	1 x 4	4K @ 60Hz	2.2	4		Yes
Over Cat6 Cable (Max Signal Range: 70 m)								
B127A-002-BH	HDMI (F) / 2x RJ45 (F)	HDMI (F)	1 x 2	4K x 2K @ 60Hz	1.4 / 2.2	2 displays	-	Yes
B127A-002-BHHP2	HDMI (F) / 2x RJ45 (F)	2x HDMI (M) / 2x RJ45 (F)	1 x 2	4K @ 60Hz	1.4 / 2.2	2 displays	-	Yes
B127A-004-BH	HDMI (F)	HDMI (F) / 4x RJ45 (F)	1 x 4	4K @ 60Hz	1.4 / 2.2	4	-	Yes
B127A-008-BH	HDMI (F)	HDMI (F) / 8x RJ45 (F)	1 x 8	4K x 2K @ 60Hz	2.2	10	-	Yes
B127M-004-H	HDMI (F)	HDMI (F) / 4x RJ45 (F)	1 x 4	4K @ 60Hz		4 displays	-	Yes

HDMI Video Extenders

Extend 4K Audio/video signals over Cat5e/6 cable up to 70m away.




Key points:

- Transmits Crystal-Clear 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color
- Pig tail or box models for flexible installation
- Power over Cable (PoC) technology provides power to the receiver via Cat6 cable (in select models)

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Connections		Video				Number of Ports	Daisy-chainable Cascadable	Power Source Type
	Connector A	Connector B	Number of Monitors	Max Resolution	HDCP	Max Signal range			
Signal booster									
 B122-000-4K6	HDMI (F) Micro USB-B (F)	HDMI (F)	1	4K @ 60Hz 3D Video Supported	2.2	15 m	-	-	USB
Over Cat6 Cable									
B013-HU-4K	RJ45 (F) HDMI (F) 2x USB-A (F)	RJ45 (F) HDMI (F) 2x USB-A (F)	1	4k @ 30Hz	1.4	70 m	-	-	Int AC Adapters
B127A-004-BHPH3	2x HDMI (F) 4x RJ45 (F)	3x RJ45 (F) 3x HDMI (M)	4	4K @ 60Hz Video Supported	1.4.2.2	70 m	4	-	Int AC Adapters
B127A-110-BH	RJ45 (F) 3.5MM (F)	HDMI (F) RJ45 (F) 3.5MM (F) Toslink (F)	1	4K @ 60Hz Video Supported	1.4.2.2	70 m	-	-	Int AC Adapters
B127A-111-BHTH	2x HDMI (F) RJ45 (F) 2x 3.5MM (F)	2x RJ45 (F) HDMI (F) 2x 3.5MM (F) Toslink (F)	1	4K @ 60Hz Video Supported	1.4.2.2	70 m	-	Yes up to 4 units	Int AC Adapters
B127A-1A0-BH	RJ45 (F) HDMI (F)	Toslink (F)	1	4K @ 60Hz Video Supported	1.4.2.2	70 m	-	-	Transmitter end only
B127A-1A0-FH	RJ45 (F)	HDMI (F)	1	4K x 2K @ 60 Hz Video supported	1.4.2.2	70 m	-	-	

Part number	Connections		Video				Number of Ports	Daisy-chainable Cascadable	Power Source Type	Form Factor
	Connector A	Connector B	Number of Monitors	Max Resolution	HDCP	Max Signal range				
B127A-1A1-BCBH	2x USB-C (F) HDMI (F) RJ45 (F) 2x 3.5MM (F) Micro USB-B (F) HDMI (F)	HDMI (F) RJ45 (F) 2x USB-A (F) Toslink (F) 2x 3.5MM 2x USB-A (F)	1	4K @ 60Hz Video Supported	1.4 2.2	70 m	-	-	USB	-
B127A-1A1-BHBH	2x HDMI (F) RJ45 (F) 2x 3.5MM (F) Micro USB-B (F)	HDMI (F) RJ45 (F) 2x USB-A (F) Toslink (F) 2x3.5MM (F) 2x USB-A (F)	1	4K @ 60Hz Video Supported	2.2	70 m	-	-	Int AC Adapters	-
B127A-1A1-BHFH	2x HDMI (F) RJ45 (F)	HDMI (F)	2	4K @ 60Hz Video Supported	1.4 2.2	70 m	-	-	Int AC Adapters	Wallplate
B127A-1A1-BHPH	2x HDMI (F) RJ45 (F) 2x 3.5MM (F)	HDMI (M) RJ45 (F)	1	4K @ 60Hz Video Supported	2.2	70 m	-	-	Int AC Adapters	-
B127A-1A1-FHFH	2x HDMI (F) RJ45 (F) 2x 3.5MM (F)	HDMI (F) RJ45 (F) 2x 3.5MM (F)	2	4K x 2K @ 60 Hz	2.2	70 m	-	-	Int AC Adapters	Wallplate
B127A-1P0-PH	RJ45 (F)	HDMI (F)	1	4K x 2K @ 60 Hz	1.4 2.2	70 m	-	-	Transmitter end only**	-
B127A-2A1-BHBH	2x HDMI (F) RJ45 (F)	2x HDMI (F) RJ45 (F)	2	4K @ 60Hz Video Supported	1.4 2.2	70 m	-	-	Int AC Adapters	-
B127A-4X2-BH2PH	2x HDMI (F)	4x RJ45 (F)	2	4K @ 60Hz Video Supported	2.2	70 m	-	-	Int AC Adapters	Rackmountable
B127E-1A1-HH	2x HDMI (F) RJ45 (F)	HDMI (F) RJ45 (F) 2x USB-A (F)	1	4K @ 60Hz Video Supported	2.2	100 m	-	-	Int AC Adapters	-
B127F-1A1-MM-HH	Micro USB-B (F) 2x HDMI (F) LC (F)	2x USB-A (F) HDMI (F) LC (F)	1	4K @ 60Hz Video Supported	2.2	300 m	-	-	Int AC Adapters	-
B127M-101-H	2x HDMI(f) RJ45 (F)	HDMI (F) RJ45 (F)	1	4K @ 60Hz Video Supported	1.4 2.2	70 m	-	-	Int AC Adapters	-

*Optional

HDMI Cables

Transmits digital audio/video and Ethernet signals from an HDMI source to a 4K-enabled television, projector or monitor.



Key points:

- Supports UHD video resolutions up to 8K
- Premium foil and braid shielding protects against EMI/RFI noise

Ideal for:

- WFA / Office
- Classroom
- Conference room
- Trade show
- Theatrer

Part number	Connections		Cable		HDCP Spec	Max Supported Video Resolution	Length	Color
	Connector A	Connector B	Type					
HDMI HD - Angled								
P568-006-RA	HDMI (M)	HDMI (M)	Passive - Bidirectional	Right-Angled	1.4 2.2	Full HD	1,83 m	Black
P568-006-RA2	HDMI (M)	HDMI (M)	Passive - Bidirectional	2 Right-Angled	1.4 2.2	Full HD	1,83 m	Black
HDMI 4k @ 30Hz								
P568-003	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @30 Hz	91 cm	Black
P568-006	HDMI (M)	HDMI (M)	Passive - Bidirectional		1.3	4K @30 Hz	1,83 m	Black
P568-010	HDMI (M)	HDMI (M)	Passive - Bidirectional		1.3	4K @30 Hz	3,05 m	Black
P568-012	HDMI (M)	HDMI (M)	Passive - Bidirectional		1.4 2.2	4K @30 Hz	3,66 m	Black
P568-016	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @30 Hz	4,88 m	Black
P568-020	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @30 Hz	6,09 m	Black
P568-025	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @30 Hz	7,62 m	Black
P568-030	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @30 Hz	9,14 m	Black
P568-006-BK-GRP	HDMI (M)	HDMI (M)	Passive - Bidirectional	Gripping connectors 3D Video Supported	1.4 2.2	4K @30 Hz	1,83 m	Black
P568-010-BK-GRP	HDMI (M)	HDMI (M)	Passive - Bidirectional	Gripping connectors 3D Video Supported	1.4 2.2	4K @30 Hz	3,05 m	Black
P568-025-BK-GRP	HDMI (M)	HDMI (M)	Passive - Bidirectional	Gripping connectors 3D Video Supported	1.4 2.2	4K @30 Hz	7,62 m	Black
P569-003	HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	91 cm	Black	
P569-006	HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	1,83 m	Black	
P569-010	HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	3,05 m	Black	
P569-020	HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	6,09 m	Black	
P569-025	HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	7,62 m	Black	
P569-050	HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	15,24 m	Black	
HDMI 8k @ 60Hz								
P568-003-8K6	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	8K @60 Hz	91 cm	Black
P568-006-8K6	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	8K @60 Hz	1,83 m	Black
P568-010-8K6	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	8K @60 Hz	3,05 m	Black
HDMI 4k @ 60Hz								
P568-01M-2A	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @60Hz	1 m	Black/Gray
P568-02M-2A	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @60Hz	2 m	Black/Gray
P568-03M-2A	HDMI (M)	HDMI (M)	Passive - Bidirectional	3D Video Supported	1.4 2.2	4K @60Hz	3 m	Black/Gray
P569-006-CERT	HDMI (M)	HDMI (M)	Passive - Bidirectional	Gripping connector	4K @60 Hz	1,83 m		Black/ Burgundy
P569-015-CERT	HDMI (M)	HDMI (M)	Passive - Bidirectional	Gripping connector	4K @60 Hz	3,05 m		Black/ Burgundy
P569-010-CERT	HDMI (M)	HDMI (M)	Passive - Bidirectional	Gripping connector	4K @60 Hz	3,05 m		Black/ Burgundy

Part number	Connections		Cable		HDCP Spec	Max Supported Video Resolution	Length	Color
	Connector A	Connector B	Type					
HDMI Fiber Active Cable (AOC)								
P568-05M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	5 m	Black
P568-100M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	100 m	Black
P568-10M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	10 m	Black
P568-15M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	15 m	Black
P568-20M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	20 m	Black
P568-30M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	30 m	Black
P568-40M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	40 m	Black
P568-50M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	50 m	Black
P568-60M-FBR	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	1.4 2.2	4K @60Hz	60 m	Black
P568F-10M-8K6	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	2.3	8K @60Hz	10 m	Black
P568F-15M-8K6	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	2.3	8K @60Hz	15 m	Black
P568F-20M-8K6	HDMI (M)	HDMI (M)	Active Optical Cable (AOC)	3D Video Supported	2.3	8K @60Hz	20 m	Black

HDMI to Micro HDMI, Mini HDMI

P570-006-MICRO	Micro HDMI (M)	HDMI (M)	Passive - Bidirectional	Ethernet	Full HD	1,83 m	Black
P572-006	Mini HDMI (M)	Mini HDMI (M)	Passive - Bidirectional		Full HD	1,83 m	Black
P571-006-MINI	Mini HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	1,83 m	Black
P571-010-MINI	Mini HDMI (M)	HDMI (M)	Passive - Bidirectional		4K @30 Hz	3,05 m	Black

Extension Cables

P569-006-MF	HDMI (M)	HDMI (F)	Passive - Bidirectional		4k @ 30Hz	91 cm	Black
P569-006-2B-MF	HDMI (M)	HDMI (F)	Passive - Bidirectional		4k @ 60Hz	91 cm	Beige/Black
P569-010-2B-MF	HDMI (M)	HDMI (F)	Passive - Bidirectional		4k @ 60Hz	3,05 m	Beige/Black
P569-020-2B-MF	HDMI (M)	HDMI (F)	Passive - Bidirectional		4k @ 60Hz	6,09 m	Beige/Black

Accessories

Part number	Description
 P568-000-LOCK	HDMI Cable Lock - Clamp/Tie/Screw

HDMI Adapter Cables

Connects your device's USB-C ,Thunderbolt 3, Micro USB-B or VGA port to an HDMI monitor or TV.



Ideal for:

- WFA
- Office
- Hospital & Clinic
- Classroom
- Event / Tradeshow

Part number	Connections			Cable Type	Max Supported Video Resolution	Length	Cable Jacket		Color
	Connector A	Connector B	Connector C				Material	Rating	
P566-003-VGA	HDMI (M)	HD15 (M) - Low profile Micro USB-B (F)	-	Active	Full HD	91 cm	PVC	VW-1	Black
P566-006-VGA	HDMI (M)	HD15 (M) - Low profile Micro USB-B (F)	-	Active	Full HD	1,83 cm	PVC	VW-1	Black
P566-010-VGA	HDMI (M)	HD15 (M) - Low profile Micro USB-B (F)	-	Active	Full HD	3,1m	PVC	VW-1	Black
P566-015-VGA	HDMI (M)	HD15 (M) - Low profile Micro USB-B (F)	-	Active	Full HD	4,6 m	PVC	VW-1	Black
U444-006-H4K6BE	USB-C (M)	HDMI (M)	-	Passive	(4K x 2K) @ 60Hz	1,83 m	PVC	VW-1	Black
U444-006-HDR2BE	USB-C (M)	HDMI (F)	-	Active	4K @ 60Hz	1,83 m	TPE	-	Black
U444F3-10M-H4K6	USB-C (M)	HDMI (M)	-	Active	4K @ 60Hz	10 m	PVC	CL3	Black
U444F3-15M-H4K6	USB-C (M)	HDMI (M)	-	Active	4K @ 60Hz	15 m	PVC	CL3	Black
U444F3-20M-H4K6	USB-C (M)	HDMI (M)	-	Active	4K @ 60Hz	20 m	PVC	CL3	Black
U444F3-30M-H4K6	USB-C (M)	HDMI (M)	-	Active	4K @ 60Hz	30 m	PVC	CL3	Black
U444F3-50M-H4K6	USB-C (M)	HDMI (M)	-	Active	4K @ 60Hz	50 m	PVC	CL3	Black

HDMI Adapters

Connect a PC, laptop or ultrabook with a HDMI port to a VGA display and speakers



Key points:

- Supports video resolutions up to 1920 x 1200 (WUXGA)
- Supports 3.5 mm. Mini Stereo Audio
- Supports 2-channel analog audio output
- Plug-and-Play

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Video Max Resolution	HDCP	Cable		Int AC Adapter	Color
	Connector A	Connector B			Length	ANGLED		
P130-000-AUDIO	HDMI (F)	HDMI (F) Toslink (F) 3.5MM (F) RCA (F)	4k x 2K @30 Hz	1.3	-	-	-	Black
P130-06N-AUDIO	HDMI (F)	HDMI (F) Toslink (M) 3.5MM (F) Micro USB-B (F)	4k x 2K @30 Hz	1.4	Pigtail	-	-	Black
P131-000	HDMI (M)	HD15 (F)	1920 x 1200 (1080p)	-	-	-	-	Black/Blue
P131-000-A	HDMI (M)	3.5MM (F) HD15 (F) Micro USB-B (F)	1920 x 1200 (1080p)	1.4	-	-	-	Black
P131-000-A-DISP	HD15 (M)	3.5MM (F) HDMI (F) Micro USB-B (F)	1920 x 1200 (1080p)	1.4	-	-	-	Black
P131-06N	HDMI (M)	HD15 (F)	1920 x 1200 (WUXGA)	-	Pigtail	-	-	Black
P131-06N-2VA-U	HDMI (M)	2x HD15 (F) 2x 3.5MM (F) HD15 (F)	1920 x 1200 (1080p)	-	Pigtail	-	-	Black
P131-06N-MICROA	Micro-HDMI (M)	HD15 (F) 3.5MM (F)	1920 x 1200 (1080p)	-	Pigtail	-	-	Black
P131-06N-MINI	Mini-HDMI (M)	HD15 (M)	1920 x 1200 (1080p)	-	Pigtail	-	-	Black
P142-000-MICRO	Micro-HDMI (M)	HDMI (F)	1920 x 1200 (1080p)	-	-	-	-	Black
P142-000-MINI	Mini-HDMI (M)	HDMI (F)	1920 x 1200 (1080p)	-	-	-	-	Black
P142-000-UD	HDMI (F)	HDMI (M) - Swivel	-	-	-	Up / Down	-	Black
P142-000-UP	HDMI (F)	HDMI (M)	-	-	-	Up	-	Black
P142-06N-MICRO	HDMI (F)	Micro-HDMI (M)	-	-	-	-	-	Black
U444-2H-MST4K6	USB-C (M)	2 x HDMI (F)	8K 30Hz	-	-	-	-	-

HDMI Switches

Shares 4K video/audio from up to 5 video/audio sources.





Key points:

- Transmits Crystal-Clear 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color
- Extends a 4K AV Transmission up to 70 m or more
- Plug-and-Play Operation for Quick Setup and Immediate Use

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Connections		Video				HDCP	DP	Number of Ports	Power Source Type	Form Factor
	Connector A	Connector B	Input x Output	Number of Monitors	Max Resolution						
 B119-003-UHD-MN	3x HDMI (F)	HDMI (F)	3 x 1	1	4K @ 30 Hz 3D Video Supported	1.4	-	3	USB	-	
 B119-005-UHD	5x HDMI (F)	HDMI (F)	5 x 1	1	4K @ 60 Hz 3D Video Supported	2.2	-	5	Int AC Adapter	-	
B302-4HX4H-4K	3.5MM (F) DB89 (F) 4x HDMI (F) RJ45 (F)	4x 3.5MM (F) 4x HDMI (F)	4 x 4	4	4K @ 60Hz 3D Video Supported	2.2	-	4	Int AC Adapter	-	
Over Cat6 Cable											
B127A-4X4-BH4PH	4x HDMI (F) RJ45 (F) 3.5MM (F)	HDMI (F) RJ45 (F) Toslink (F)	4 x 1	4	4K @ 60 Hz 3D Video Supported	2.2	-	4	Int AC Adapter	Wall Plate/ Box	
B320-4X1-MHB-K	2x 3.5MM (F) DB89 (F) DisplayPort (F) HD15 (F) HDMI (F) RJ45 (F) 2x USB-C (F)	HDMI (M) RJ45 (M)	4 x 1	1	HDMI/DP/USB Type-C: 4096 x 2160 @60Hz VGA: 1920 x 1080 @60Hz	2.2	1.2a	4	Int AC Adapter	-	
B320-4X1-MHE-K	2x 3.5MM (F) DB89 (F) DisplayPort (F) HD15 (F) HDMI (F) RJ45 (F) 2x USB-C (F)	HDMI (M) RJ45 (M)	4 x 1	1	HDMI/DP/USB Type-C: 4096 x 2160 @60Hz VGA: 1920 x 1080 @60Hz	2.2	1.2a	4	Int AC Adapter	-	

DisplayPort Splitters

Displays the same image on 2 monitors, extends the desktop across both, or combines both into one large monitor.





Key points:

- Supports video resolutions up to 1080p @ 60 Hz (1920 x 1080)
- Compact enough for easy carrying in backpack or laptop bag
- Plug and play—no software or drivers required

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Input x Output	Resolution	Length	Number of ports
	Connector A	Connector B				
 B157-002-HD	DisplayPort (M) 1.2 / Micro USB-B (F)	2x HDMI (F)	1 x 2	Full HD @ 60Hz	-	2
 B157-002-VGA	DisplayPort (M) 1.2 / Micro USB-B (F)	2x HD15 (F)	1 x 2	Full HD @ 60Hz	-	2

DisplayPort Switches

Connects 4 different audio/video source devices (HDMI/DP/USB-C/VGA) to one HDMI display, eliminating the need for multiple adapters.



Key points:

- 4-in-1 Multi-Format Presentation Adapter Allows Convenient Connection to an HDMI Display
- HDMI, DisplayPort and USB-C cables support true 4K resolutions @ 60 Hz (4:4:4)
- USB-C PD 3.0 port supports 20V 5A (100W) power output for charging host device
- Plug-and-play

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Connections			Video				Number of Ports	Power Source Type
	Connector A	Connector B	Input x Output	Number of Monitors	Max Resolution	HDCP	DP		
B321-4X1-HDVC	HDMI (M) USB-A (M) USB-C (M)DB15 (M)	DisplayPort (M) HDMI (M) USB-C (M)	4 x 1	1	HDMI/DP/USB Type-C: 4096 x 2160 @ 60Hz VGA: 1920 x 1080 @ 60Hz 3D Video Supported	2.2	1.2a	1	USB

DisplayPort Cables

High-speed cable connects A/V components up to an 8K display in your digital signage application, auditorium or security system.



Key points:

- Digital Video and Audio in one cable
- From 31 cm up to 15,24 m
- DisplayPort 1.2 4K @60Hz / DisplayPort 1.4 @ 30Hz & 60Hz
- Supports High Definition Content Protection (HDCP)

Ideal for:

- WFA / Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Cable	Max Supported Video Resolution	Length	Latching connector	Color
	Connector A	Connector B	Type				
4K @ 60Hz							
P579-003	DisplayPort 1.2 (M)	DisplayPort 1.2 (F)	Passive - Bidirectional	4k @ 60Hz	91 cm	Yes	Black
P579-006	DisplayPort (M)	DisplayPort (F)	Passive	4K @ 60Hz	1,83 m	Yes	Black
P579-010	DisplayPort (M)	DisplayPort (F)	Passive	4K @ 60Hz	3,05 m	Yes	Black
P579-015	DisplayPort (M)	DisplayPort (F)	Passive	4K @ 60Hz	4,57 m	Yes	Black
P580-003	DisplayPort 1.2 (M)	DisplayPort 1.2 (M)	Passive - Bidirectional	4k @ 60Hz	91 cm	Yes	Black
P580-006	DisplayPort 1.2 (M)	DisplayPort 1.2 (M)	Passive - Bidirectional	4k @ 60Hz	91 cm	Yes	Black
P580-010	DisplayPort 1.2 (M)	DisplayPort 1.2 (M)	Passive - Bidirectional	4k @ 60Hz	3,1 m	Yes	Black
P580-015	DisplayPort 1.2 (M)	DisplayPort 1.2 (M)	Passive - Bidirectional	4k @ 60Hz	4,57 m	Yes	Black
With Repeater							
P579-010-4K6	DisplayPort (M)	DisplayPort (F)	Passive / Active Repeater	4K @ 60Hz	3,05 m	Yes	Black/Gray
P579-015-4K6	DisplayPort (M)	DisplayPort (F)	Passive / Active Repeater	4K @ 60Hz	4,57 m	Yes	Black/Gray
P579-020-4K6	DisplayPort (M)	DisplayPort (F)	Passive / Active Repeater	4K @ 60Hz	6,1 m	Yes	Black/Gray
8K @ 60 Hz - WithActive Repeater							
P579-009-8K6	DisplayPort 1.4 (M)	DisplayPort 1.4 (M)	Passive / Active Repeater	8k @ 60Hz	2,7 m	Yes	Black/Blue
8K @ 60Hz 40 Gbps							
P580-003-8K6-2	DisplayPort 2.1 (M)	DisplayPort 2.1 (M)	Passive	8k @ 60Hz	91 cm	Yes	Black
P580-006-8K6-2	DisplayPort 2.1 (M)	DisplayPort 2.1 (M)	Passive	8k @ 60Hz	1,83 m	Yes	Black
8K @ 60Hz AOC							
P580F3-10M-8K6	DisplayPort (M)	DisplayPort (M)	Active Optical Cable (AOC)	8k @ 60Hz	10 m	Yes	Black
P580F3-15M-8K6	DisplayPort (M)	DisplayPort (M)	Active Optical Cable (AOC)	8k @ 60Hz	15 m	Yes	Black
P580F3-20M-8K6	DisplayPort (M)	DisplayPort (M)	Active Optical Cable (AOC)	8k @ 60Hz	20 m	Yes	Black
P580F3-25M-8K6	DisplayPort (M)	DisplayPort (M)	Active Optical Cable (AOC)	8k @ 60Hz	25 m	Yes	Black
P580F3-30M-8K6	DisplayPort (M)	DisplayPort (M)	Active Optical Cable (AOC)	8k @ 60Hz	30 m	Yes	Black

DisplayPort Adapter Cables

Connects a DisplayPort monitor or projector to the HDMI or VGA port on the A/V source.



Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Cable		Length	Cable Jacket		Color
	Connector A	Connector B	Type	Max Supported Video Resolution		Material	Rating	
P581-003-V2	DisplayPort (M)	DVI-D Single Link (M)	Active	Full HD	91 cm	PVC	VW-1	Black
P581-003-VGA-V2	DisplayPort (M)	HD15 (M)	Active	Full HD	91 cm	PVC	VW-1	Black
P581-006-V2	DisplayPort (M)	DVI-D Single Link (M)	Active	Full HD	1,83 m	PVC	VW-1	Black
P581-006-VGA-V2	DisplayPort (M)	HD15 (M)	Active	Full HD	1,83 m	PVC	VW-1	Black
P581-010-VGA-V2	DisplayPort (M)	HD15 (M)	Active	Full HD	3,1 m	PVC	VW-1	Black
P582-003	DisplayPort (M) 1.2	HDMI (M)	Passive	Full HD	91 cm	PVC	VW-1	Black
P582-003-HD-V2A	DisplayPort (M) 1.2	HDMI (M)	Active	4K @ 60Hz	91 cm	PVC	VW-1	Black
P582-003-HD-V4A	DisplayPort (M) 1.4	HDMI (M)	Active	4K @ 60Hz	91 cm	PVC	VW-1	Black
P582-003-V2	DisplayPort (M) 1.2	HDMI (M)	Passive	4K @ 60Hz	91 cm	PVC	VW-1	Black
P582-006	DisplayPort (M) 1.2	HDMI (M)	Passive	Full HD	1,83 m	PVC	VW-1	Black
P582-006-HD-V2A	DisplayPort (M) 1.2	HDMI (M)	Active	4K @ 60Hz	1,83 m	PVC	VW-1	Black
P582-006-HD-V4A	DisplayPort (M) 1.4	HDMI (M)	Active	4K @ 60Hz	1,83 m	PVC	VW-1	Black
P582-006-V2	DisplayPort (M) 1.2	HDMI (M)	Passive	4K @ 60Hz	1,83 m	PVC	VW-1	Black
P582-010	DisplayPort (M) 1.2	HDMI (M)	Passive	Full HD	3,05 m	PVC	VW-1	Black
P582-010-HD-V2A	DisplayPort (M) 1.2	HDMI (M)	Active	4K @ 60Hz	3,05 m	PVC	VW-1	Black
P582-010-HD-V4A	DisplayPort (M) 1.4	HDMI (M)	Active	4K @ 60Hz	3,05 m	PVC	VW-1	Black
P582-015	DisplayPort (M) 1.2	HDMI (M)	Passive	Full HD	4,6 m	PVC	VW-1	Black
P582-015-HD-V2A	DisplayPort (M) 1.2	HDMI (M)	Active	4K @ 60Hz	4,6 m	PVC	VW-1	Black
P582-015-HD-V4A	DisplayPort (M) 1.4	HDMI (M)	Active	4K @ 60Hz	4,6 m	PVC	VW-1	Black
P583-003-BK	DisplayPort (M)	Mini DisplayPort (M)	Passive Bidirectional	4K @ 60Hz	91 cm	PVC	VW-1	Black
P583-006-BK	DisplayPort (M)	Mini DisplayPort (M)	Passive Bidirectional	4K @ 60Hz	1,8 m	PVC	VW-1	Black
P583-010-BK	DisplayPort (M)	Mini DisplayPort (M)	Passive Bidirectional	4K @ 60Hz	3,05 m	PVC	VW-1	Black
P586-003-HDMI	Mini DisplayPort (M)	HDMI (M)	Active	Full HD	91 cm	PVC	VW-1	Black
P586-006-HDMI	Mini DisplayPort (M)	HDMI (M)	Active	Full HD	1,8 m	PVC	VW-1	Black

Display Port | Pro AV & Digital signage

DisplayPort Adapters

Connects a DisplayPort output to an HDMI, DVI or VGA monitor.

Key points:













- Keep using your existing HDMI, DVI or VGA monitor

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies



Part number	Connections		Max Supported Video Resolution	Length
	Connector A	Connector B		
P126-000	DVI-I (F)	HD15 (M)		-
P130-000	DVI-D Single Link (F)	HDMI (F)	Full HD	-
P132-000	DVI-D Dual Link (F)	HDMI (M)		-
P134-000	DisplayPort (M) 1.2	DVI-D Dual Link (F) (Wired to DVI-D Single Link)	Full HD - 1920 x 1200 (1080p)	Pigtail
P134-000-VGA-V2	DisplayPort (M) 1.2	HD15 (F)	Full HD - 1920 x 1200 (1080p)	-
P134-001-GC	DisplayPort (M) 1.1	DVI-D Dual Link (F) (Wired to DVI-D Single Link)	Full HD - 1920 x 1200 (1080p)	31 cm
P134-003	DisplayPort (M)	DVI-I (F)	Full HD - 1920 x 1200 (1080p)	91 cm
P134-06N-DVI-V2	DisplayPort (M) 1.2	DVI-I Dual Link (F) (Wired to DVI-D Single Link)	HD - 1920 x 1080 (1080p)	Pigtail
P134-06N-MDP	DisplayPort (M)	Mini DisplayPort (F)	(4K x 2K) @ 60 Hz	Pigtail
P134-06N-VGA	DisplayPort (M) 1.2	HD15 (F)	Full HD - 1920 x 1200 (1080p)	Pigtail
P134-06N-VGA-V2	DisplayPort (M) 1.2	HD15 (F)	HD - 1920 x 1080 (1080p)	Pigtail
P136-000	DisplayPort (M)	HDMI (F)	HD - 1920 x 1080 (1080p)	Pigtail
P136-000-1	DisplayPort (M)	HDMI (F)	Full HD - 1920 x 1200 (1080p)	-
P136-000-UHD-V2	DisplayPort (M) 1.2	HDMI (F) 1.4	4K x 2K @ 24/30 Hz	-
P136-001	DisplayPort (M)	HDMI (F)	Full HD - 1920 x 1200 (1080p)	31 cm
P136-06N-H2V2	DisplayPort (M) 1.2	HDMI (F)	4K @ 60 Hz	Pigtail
P136-06N-H2V2LB	DisplayPort (M) 1.2	HDMI (F)	4K @ 60 Hz	Pigtail
P136-06N-HDV-4K	DisplayPort (M)	DVI-I Dual Link (F) (Wired to DVI-D Single Link)	4K @ 30 Hz	Pigtail
P136-06N-HDV4K6	DisplayPort (M)	DVI-D Single Link (F) HD15 (F) / HDMI (F)	4K @ 60 Hz	Pigtail
P136-06N-HV-V2	DisplayPort (M) 1.2	HD15 (F) HDMI (F)	Full HD - 1920 x 1200 (1080p)	Pigtail
P136-06N-UHD-V2	DisplayPort (M) 1.2	HDMI (F)	4K @ 30 Hz	Pigtail
U444-2DP-MST4K6	DisplayPort 1.4	USB-C	8K @ 30Hz	-
U444-06N-HVDPW	DisplayPort 1.2	USB-C	4K @ 60 Hz	-

Part number	Connections		Max Supported Video Resolution	Length	Color
	Connector A	Connector B			
 P137-06N-DVI	Mini DisplayPort (M)	DVI-I (F)	Full HD - 1920 x 1200 (1080p)	Pigtail	White
 P137-06N-DVI-V2	Mini DisplayPort (M)	DVI-I Dual Link (F) (Wired to DVI-D Single Link)	1920 x 1080 (1080p)	Pigtail	White
 P137-06N-HD4K6B				Pigtail	
 P137-06N-HDMI				Pigtail	
 P137-06N-HDR-W				Pigtail	
 P137-06N-HD-UHD				Pigtail	
 P137-06N-HDV-4K				Pigtail	
 P137-06N-HDVW				Pigtail	
 P137-06N-HV-V2W				Pigtail	
P137-06N-VGA				Pigtail	
 P137-06N-VGA-V2				Pigtail	
 P137-06N-VGAV2B				Pigtail	
 P139-06N-DP				Pigtail	
P139-06N-DP4K6B				Pigtail	
50 Pack					
P136-06N-HVV2BP	DisplayPort (M) 1.2	HD15 (F) HDMI (F)	Full HD - 1920 x 1200 (1080p)	Pigtail	

DisplayPort Extenders

Extend 4k DisplayPort signals up to 70m away.



Key points:

- Uses readily available Cat5e or Cat6 solid conductor cable
- Supports UHD resolutions up to 4K @ 30 Hz (4:4:4) for crystal-clear video
- Power over Cable (PoC) technology provides power to either unit via Cat6 cable
- Plug-and-play operation with no software required for easy, immediate installation

Ideal for:

- Restaurants
- Schools
- Offices
- Digital Signage

Part number	Connections		Video				Number of Ports	Daisy-chainable Cascadable	Power Source Type
	Connector A	Connector B	Number of Monitors	Max Resolution	HDCP	DP			
Signal booster									
B127A-010-H	RJ45 (F)	RJ45 (F)	-	4K x 2K @ 60Hz	1.4 2.2	1.2	1	-	USB
Extender Kit									
B127A-111-BDTD	DisplayPort (F) HDMI (F) RJ45 (F)	2x RJ45 (F) DisplayPort (F) Toslink (F)	1	4K @ 30 Hz	1.4 2.2	1.2a	-	4	Int AC Adapter
B127A-111-BDTH	DisplayPort (F) HDMI (F) RJ45 (F)	HDMI (F) 2x RJ45 (F) Toslink	2	4K @ 60 Hz	2.2	1.2a	-	4	Int AC Adapter
Over Cat6 Cable									
B127A-1A1-BDBD	DisplayPort (F) HDMI (F) RJ45 (F) 2x 3.5MM (F) Micro USB-B (F)	DisplayPort (F) RJ45 (F) 2x USB-A (F) Toslink (F) 3.5MM (F) Toslink (F)	2	4K @ 30 Hz	2.2	1.2a	-	-	Int AC Adapter
B127A-1A1-BDBH	DisplayPort (F) HDMI (F) RJ45 (F) 2x 3.5MM (F) Micro USB-B (F)	HDMI (F) RJ45 (F) 2x USB-A (F) Toslink (F) 2x 3.5MM (F)	1	4K @ 60 Hz	1.4 2.2	1.2a	-	-	Int AC Adapter
B127A-1A1-BDFH	DisplayPort (F) HDMI (F) RJ45 (F)	HDMI (F) RJ45 (F)	1	4K @ 60 Hz	1.4 2.2	1.2a	-	-	Int AC Adapter
B127F-1A1-5M-DD	Micro USB-B (F) DisplayPort (F) HDMI (F) LC (F)	2x USB-A (F) DisplayPort (F) LC (F)	2	4K @ 30 Hz	1.4 2.2	1.2a	-	-	Int AC Adapter
B150-1A1-HDMI	DisplayPort (M) RJ45 (F) Micro USB-B (F)	HDMI (F) RJ45 (F) Micro USB-B (F)	1	1920 x 1080 @ 60Hz	1.3	1.2	1	-	USB
Over cat6 cable & wallplate form factor									
B127A-1A1-BDFH	DisplayPort (F) HDMI (F) RJ45 (F)	HDMI (F) RJ45 (F)	1	4K @ 60 Hz	1.4 2.2	1.2a	-	-	Int AC Adapter

Audio Cables

Connect a device with a 3.5 mm jack to a sound system with RCA inputs or a sound system with RCA inputs to a device with a 3.5 mm jack.



Key points:

- Perfect for your PC, notebook, MP3 player or iPod
- Molded cable with built-in strain relief

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Cable		Length	Angled	Color	
	Connector A	Connector B	Technology	Type			Cable Jacket	
A102-02M	Toslink (M)	Toslink (M)	Toslink/SPDIF Stereo Audio	Passive	2 m	-	Black	Black
A102-03M	Toslink (M)	Toslink (M)	Toslink/SPDIF Stereo Audio	Passive	3 m	-	Black	Black
A102-04M	Toslink (M)	Toslink (M)	Toslink/SPDIF Stereo Audio	Passive	4 m	-	Black	Black
P312-001	3.5MM (M)	3.5MM (M)	Stereo Audio	Passive	31 cm	-	Black	Black
P312-006	3.5MM (M)	3.5MM (M)	Stereo Audio	Passive	1,83 m	-	Black	Black
P312-006-RA	3.5MM (M)	3.5MM (M)	Stereo Audio	Passive	1,83 m	Right	Black	Black
P312-010	3.5MM (M)	3.5MM (M)	Stereo Audio	Passive	3,05 m	-	Black	Black
P312-012	3.5MM (M)	3.5MM (M)	Stereo Audio	Passive	3,66 m	-	Black	Black
P312-015	3.5MM (M)	3.5MM (M)	Stereo Audio	Passive	4,57 m	-	Black	Black
P312-025	3.5MM (M)	3.5MM (M)	Stereo Audio	Passive	7,62 m	-	Black	Black
P313-06N-WH	3.5MM (M)	2x 3.5MM (F)	Stereo Audio	Passive	15 m	-	White	White
P313-001	3.5MM (M)	2x 3.5MM (F)	Stereo Audio	Passive	31 cm	-	Black	Black
Extension Cable								
P311-006	3.5MM (M)	3.5MM (F)	Stereo Audio	Passive	1,83 m	-	Black	Black
P311-010	3.5MM (M)	3.5MM (F)	Stereo Audio	Passive	3,05 m	-	Black	Black
P311-025	3.5MM (M)	3.5MM (F)	Stereo Audio	Passive	7,62 m	-	Black	Black

Audio Adapter Cables

Connect a device with a 3.5 mm jack to a sound system with RCA inputs or a sound system with RCA inputs to a device with a 3.5 mm jack.



Key points:

- Perfect for your PC, notebook, MP3 player or iPod
- Molded cable with built-in strain relief

Ideal for:

- Office
- Classroom
- Conference room
- Trade show
- Lobbies

Part number	Connections		Cable		Length	Cable Jacket		Color	
	Connector A	Connector B	Technology	Type		Material	Rating	Cable Jacket	
P314-006	3.5MM (M)	2x RCA (M)	Stereo Audio	Passive	1,83 m	PVC	VW-1	Black	Black
P314-012	3.5MM (M)	2x RCA (M)	Stereo Audio	Passive	3,7 m	PVC	VW-1	Black	Black
P318-06N-FMM	3.5MM 4-POSITION (F)	2x 3.5MM (M)	Stereo Audio	Passive	15,2 cm	PVC	VW-1	Black	Black

Wireless Video Extenders

Allows you to control your IR-enabled device from 200 m away without it being in direct line of sight.



Key points:

- IR pass through allows use of the source's remote while near the display with no latency
- Accepts IR signal frequencies from 20–60 kHz: compatible with all your IR devices
- Durable aluminum housings dissipate heat to keep units functioning at their peak

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Connections		Power Source Type
	Connector A	Connector B	
B164-101-WIR	3.5MM (F)	3.5MM (F)	USB

Video Couplers

Connects two video cables to create one longer cable.



Key points:

- Change Male ended DVI cable to Female
- Extend up to 2 HDMI, DisplayPort or DVI cables

Ideal for:

- Restaurant
- Lecture Halls
- Conference room

Part number	Product Type	Connections		Video			Color
		Connector A	Connector B	Max Supported Video Resolution	HDCP	DP	
P162-000	Coupler Gender Changer	DVI-I (F)	DVI-I (F)		-	-	Beige
P164-000	Coupler Gender Changer	HDMI (F)	HDMI (F)			-	Black
P164-000-8K6	Coupler Gender Changer	HDMI (F)	HDMI (F)	8k @ 60Hz	1.4 2.2	-	Black
P164-000-KPBK8K	Keystone/Panel-Mount Coupler	HDMI (F)	HDMI (F)	8k @ 60Hz	1.4 2.2	-	Black
P168-000	Coupler Gender Changer	DisplayPort (F)	DisplayPort (F)		2.2	1.2	Black
P310-000	Coupler Gender Changer	3.5MM (F)	3.5MM (F)		-	-	Black



Industrial-grade IT solutions

Server Racks & Cabinets

Copper Network Cables

Fiber Network Cables

Industrial Switches

Transceivers

USB Solutions

AV Solutions

Power over Ethernet (PoE)

SmartRack Industrial Enclosures

Locking metal enclosure protects your outdoor equipment against theft, damage, tampering, and excess moisture and debris.



Key points:

- NEMA 4 enclosure provides protection against water, ice, snow and other moisture
- Includes metal and plastic backplates to accommodate a wide range of equipment
- Comes fully assembled and ready for wall or pole mounting using included hardware

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/ Logistics facilities
- Dusty, outdoor IT installations

Part number	Dimensions (cm)						Doors		Side panels	Mounting rails	Cable entry	Color
	Height		Width (cm)	Depth		Static load (Kg)	Front	Rear				
	U	(cm)		Rack Depth	(cm)							
Surface-Mount Enclosures												
SRIN4101010	-	25	25	Mid	25	91	Solid	Solid	Yes			Gray
SRIN410106	-	25	25	Shallow	15	91	Solid	Solid	Yes			Gray
SRIN410146	-	25	35	Shallow	15	91	Solid	Solid	Yes			Gray
SRIN4101410	-	25	35	Mid	25	91	Solid	Solid	Yes			Gray
SRIN412126	-	30	30	Shallow	15	91	Solid	Solid	Yes			Gray
SRIN4121210	-	30	30	Mid	25	91	Solid	Solid	Yes			Gray
SRIN414146	-	35	35	Shallow	15	91	Solid	Solid	Yes			Gray
SRIN4141410	-	35	35	Mid	25	91	Solid	Solid	Yes	Plastic and metal mounting panel, document holder	Bottom cutout with removable cover	Gray
SRIN418186	-	45	45	Shallow	15	91	Solid	Solid	Yes			Gray
SRIN4181810	-	45	45	Mid	25	91	Solid	Solid	Yes			Gray
SRIN410106R	-	25	25	Shallow	15	91	Solid	Solid	Yes			Red
SRIN4101410R	-	25	35	Mid	25	91	Solid	Solid	Yes			Red
SRIN4121210R	-	30	30	Mid	25	91	Solid	Solid	Yes			Red
SRIN4181810R	-	45	45	Mid	25	91	Solid	Solid	Yes			Red
SRIN410106Y	-	25	25		15	91	Solid	Solid	Yes			Yellow
SRIN4101410Y	-	25	35		25	91	Solid	Solid	Yes			Yellow
Wall-Mount Enclosures												
SRN4G6U	6	34	61	Shallow	47	91	Solid	Yes	Yes			Gray
SRN4G6UDP	6	34	61	Deep	59	91	Solid	Solid	Yes			Gray
SRN4G9US	9	48	61	Mid	76	91	Solid	Solid	Yes			Gray
SRN4G9USDP	9	48	61	Deep	86	91	Solid	Solid	Yes			Gray
SRN4G12U	12	61	61	Mid	64	91	Solid	Solid	Yes	Adjustable equipment mounting rail (10-32)		Gray
SRN4G12US	12	61	61	Shallow	76	91	Solid	Solid	Yes			Gray
SRN4G12USDP	12	61	61	Deep	86	91	Solid	Solid	Yes			Gray
SRN4G12UHD	12	65	61	Mid	92	91	Vented	Vented	Yes			Gray
SRN4G18UHD	18	91	61	Mid	92	91	Solid	Solid	Yes			Gray
SRX12UBFFD	12	64	60	Mid	98	453	Solid	Solid	Yes			Black

Cat5e Copper Cables

Connects Gigabit Ethernet equipment in industrial environments that require protection against dust and moisture.



Key points:

- IP68 Rating Denotes Resistance to Dust and Water
- Heavy Shielding Protects Your Network Data from Destructive Line Noise
- Supports Power over Ethernet (PoE) to Cut Down on Power Supplies

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/ Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Shielding		Length	Network compatibility	Cable Jacket Material	Cable Jacket Rating	Conductor material	Color
	Cable shielding	Conductor shielding						
Molded								
N206-PC03-IND	Yes	STP	1 m	1 Gbps	PBT	CMX	Stranded Copper	Black
N206-PC10-IND	Yes	STP	3,05 m	1 Gbps	PBT	CMX	Stranded Copper	Black
N206-PC16-IND	Yes	STP	4,88 m	1 Gbps	PBT	CMX	Stranded Copper	Black
N206-PC23-IND	Yes	STP	7,01 m	1 Gbps	PBT	CMX	Stranded Copper	Black
N206-PC33-IND	Yes	STP	10,05 m	1 Gbps	PBT	CMX	Stranded Copper	Black
N206-PC50-IND	Yes	STP	15,24 m	1 Gbps	PBT	CMX	Stranded Copper	Black

Cat6 Copper Cables

Connects Gigabit Ethernet and PoE equipment in industrial environments that require protection against dust and moisture.



Key points:

- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
- Supports power over ethernet to save your money and give you more installation choices

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/ Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Shielding		Length	Network compatibility	Cable Jacket Material	Cable Jacket Rating	Conductor material	Color		
	Cable shielding	Conductor shielding								
Molded										
N200P-003BL-IND	No	UTP	-	-	91 cm	1 Gbps	PVC	CMR-LP/LP5	Solid Copper	Black
N200P-010BL-IND	No	UTP	-	-	3,05 m	1 Gbps	PVC	CMR-LP/LP5	Solid Copper	Black
N200P-016BL-IND	No	UTP	-	-	4,88 m	1 Gbps	PVC	CMR-LP/LP5	Solid Copper	Black
N200P-023BL-IND	No	UTP	-	-	7,01 m	1 Gbps	PVC	CMR-LP/LP5	Solid Copper	Black
N200P-033BL-IND	No	UTP	-	-	10,05 m	1 Gbps	PVC	CMR-LP/LP5	Solid Copper	Black
N200P-050BL-IND	No	UTP	-	-	15,24 m	1 Gbps	PVC	CMR-LP/LP5	Solid Copper	Black

M12 X-Code Cat6 Copper Cables

Connects Gigabit Ethernet network equipment in industrial and other harsh environments subject to vibration, humidity and extreme temperatures.



Key points:

- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
- Supports 60W PoE to save you expense and effort of powering PoE devices individually
- UL CMR-LP certified to meet high-temperature safety standards in PoE applications

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/ Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Connections		Shielding				Length	Network compatibility	Jacket Rating	Conductor material	Color
	Connector A	Connector B	Cable	Conductor							
NM12-601-01M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	1 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-601-02M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	2 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-601-03M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	3 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-601-05M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	5 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-601-10M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	10 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-602-01M-BL	M12 X-Code	RJ45	No	UTP	-	-	1 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-602-02M-BL	M12 X-Code	RJ45	No	UTP	-	-	2 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-602-03M-BL	M12 X-Code	RJ45	No	UTP	-	-	3 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-602-05M-BL	M12 X-Code	RJ45	No	UTP	-	-	5 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-602-10M-BL	M12 X-Code	RJ45	No	UTP	-	-	10 m	1 Gbps	CMR-LP	Solid Copper	Blue
Right Angled											
NM12-603-01M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	1 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-603-02M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	2 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-603-03M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	3 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-603-05M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	5 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-603-10M-BL	M12 X-Code	M12 X-Code	No	UTP	-	-	10 m	1 Gbps	CMR-LP	Solid Copper	Blue
NM12-604-01M-BL	M12 X-Code	RJ45	No	UTP	-	-	1 Gbps	CMR-LP	Solid Copper	Blue	
NM12-604-02M-BL	M12 X-Code	RJ45	No	UTP	-	-	1 Gbps	CMR-LP	Solid Copper	Blue	
NM12-604-03M-BL	M12 X-Code	RJ45	No	UTP	-	-	1 Gbps	CMR-LP	Solid Copper	Blue	
NM12-604-05M-BL	M12 X-Code	RJ45	No	UTP	-	-	1 Gbps	CMR-LP	Solid Copper	Blue	
NM12-604-10M-BL	M12 X-Code	RJ45	No	UTP	-	-	1 Gbps	CMR-LP	Solid Copper	Blue	

M12 X-Code Cat6a Copper Cables

Connects Gigabit Ethernet network equipment in industrial and other harsh environments subject to vibration, humidity and extreme temperatures.



Key points:

- Designed to withstand vibration, moisture and extreme temperatures in harsh environments
- IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
- Supports 60W PoE to save you expense and effort of powering PoE devices individually
- UL CMR-LP certified to meet high-temperature safety standards in PoE applications
- Blue PVC jacket easy to identify quickly in field devices, controllers and switches

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Connections		Shielding				Length	Network compatibility	Jacket Rating	Conductor material	Color
	Connector A	Connector B	Cable	Conductor							
NM12-6A1-01M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	1 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A1-02M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	2 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A1-03M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	3 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A1-05M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	5 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A1-10M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	10 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A2-01M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	1 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A2-02M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	2 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A2-03M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	3 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A2-05M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	5 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A2-10M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	10 m	10 Gbps	CMR-LP	Solid Copper	Blue

Right Angled

NM12-6A3-01M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	1 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A3-02M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	2 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A3-03M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	3 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A3-05M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	5 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A3-10M-BL	M12 X-Code	M12 X-Code	Yes	F/UTP	Foil	-	10 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A4-01M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	1 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A4-02M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	2 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A4-03M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	3 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A4-05M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	5 m	10 Gbps	CMR-LP	Solid Copper	Blue
NM12-6A4-10M-BL	M12 X-Code	RJ45	Yes	F/UTP	Foil	-	10 m	10 Gbps	CMR-LP	Solid Copper	Blue

OM3 Multimode Fiber Patch Cables

Connects fiber optic Ethernet equipment in industrial environments that require protection against dust and moisture.



Key points:

- 10G Duplex Multimode Cable Designed for Outdoor or Harsh Indoor Environments
- IP68 Rating Denotes Resistance to Dust and Water
- Color-Coded to Avoid Misidentification That Can Cause Costly Downtime

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Connections		Length	Colors		Cable Jacket		Number of Fibers	Fiber Type	Endface Polish
	Connector A	Connector B		Cable Jacket	Connector	Material	Rating			
N820-01M-IND	LC	LC	1 m	Aqua	Beige	PVC	OFNR	2	50/125	PC
N820-02M-IND	LC	LC	2 m	Aqua	Beige	PVC	OFNR	2	50/125	PC
N820-05M-IND	LC	LC	5 m	Aqua	Beige	PVC	OFNR	2	50/125	PC
N820-10M-IND	LC	LC	10 m	Aqua	Beige	PVC	OFNR	2	50/125	PC

Industrial Network Switches

Industrial-grade switch expands Ethernet connectivity to factory floors and other environments with space constraints and wide temperature ranges.



Key points:

- Easy-to-read LEDs indicate connection and activity status for all 5 Ethernet ports
- Plug-and-play operation with no software or configuration required before use

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Number of ports		PoE+ Ports	Switching Capacity	Terminal block	Operating Temp. Range	USB & Console Ports	Mounting Support
	RJ45	SFP						
Unmanaged Fast Ethernet Switches								
NFI-U05	5	-	-	1 Gbps	3-Pin, 12-48 VDC	-40° to 75°C	-	DIN/Wall Mount (Slots)
NFI-U05A	5	-	-	1 Gbps	3-Pin, 12-48 VDC	-40° to 75°C	-	DIN/Wall Mount (Slots)
NFI-U08-1	8	-	-	1.6 Gbps	3-Pin, 18-30 VDC	-40° to 75°C	-	DIN/Wall Mount (Brackets)
NFI-U08-2	8	-	-	1.6 Gbps	2-Pin, 12-48 VDC	-40° to 75°C	-	DIN Mount
NFI-U08-A	8	-	-	1.6 Gbps	6-Pin 12-48 VDC	-40° to 75°C	-	DIN Mount
NFI-U08-2A	8	-	-	1.6 Gbps	6-Pin 12-48 VDC	-40° to 75°C	-	DIN Mount
Unmanaged Gigabit Ethernet Switches								
NGI-U05E (EIP Q05)	5	-	-	10 Gbps	3-Pin 12-48 VDC	-40° to 75°C	-	DIN Mount
NGI-U08	8	-	-	16 Gbps	6-Pin, 9-57 VDC Redundant Power Inputs	-40° to 75°C	-	DIN Mount
NGI-U08A (EIP Qo5)	8	-	-	16 Gbps	6-Pin 12-48 VDC	-40° to 75°C	-	DIN Mount
NGI-U08C2	8	2 (Dedicated)	-	20 Gbps	6-Pin, 24-48 VDC Redundant Power Inputs	-40° to 75°C	-	DIN Mount
NGI-U16	16	-	-	32 Gbps	2-Pin, 12-48 VDC	-40° to 75°C	-	DIN Mount
Unmanaged Gigabit Ethernet Switches with PoE								
NGI-U05POE4	5	0	4 (≤ 30W Each; ≤ 120W Total)	10 Gbps	2-Pin, 24-57 VDC	-10° to 60°C	-	DIN Mount
NGI-U05C2POE4	5	2 (Dedicated)	4 (≤ 30W Each; ≤ 120W Total)	14 Gbps	2-Pin, 24-57 VDC	-10° to 60°C	-	DIN Mount
NGI-U08C2POE8	8	2 (Dedicated)	8 (≤ 30W Each; ≤ 240W Total)	20 Gbps	6-Pin 24-57 VDC Redundant Power Inputs	-40° to 75°C	-	DIN Mount
Managed Gigabit Ethernet Switches								
NGI-M04C2	4	2	-	12 Gbps	6-Pin 20-57 VDC Redundant Power Inputs	-40° to 75°C	-	DIN Mount
NGI-M05-C1	5	1	-	12 Gbps	6-Pin 20-57 VDC Redundant Power Inputs	-40° to 75°C	-	DIN Mount
NGI-M08C2	8	2	-	20 Gbps	6-Pin 24-48 VDC Redundant Power Inputs	-40° to 75°C	Yes	DIN Mount
NGI-M08C4POE8-2	8	4	8 (≤ 30W Each 120W/24VDC ; 240W/48VDC)	24 Gbps	6-Pin 24-57 VDC Redundant Power Inputs	-40° to 75°C	Yes	DIN Mount
NGI-M08POE8-L2	8	-	8 (≤ 30W Each 120W/24VDC ; 240W/48VDC)	16 Gbps	6-Pin 24-57 VDC Redundant Power Inputs	-40° to 75°C	Yes	DIN Mount
Lite Managed Gigabit Ethernet Switches								
NGI-S04C2	4	2	-	12 Gbps	6-Pin 20-60 VDC Redundant Power Inputs	-10° to 60°C	-	DIN Mount
NGI-S05C2POE4	5	2	4 (≤ 30W Each 120W/24VDC ; 240W/48VDC)	14 Gbps	2-Pin	-10° to 60°C	-	DIN Mount
NGI-S08C2POE8	8	2	8 (≤ 30W Each 120W/24VDC ; 240W/48VDC)	20 Gbps	6-Pin 24-57 VDC Redundant Power Inputs	-10° to 60°C	-	DIN Mount
NGI-S16	16	-	-	32 Gbps	6-Pin 12-60 VDC Redundant Power Inputs	-10° to 60°C	-	DIN Mount

Transceivers

Industrial transceiver module links a Gigabit Ethernet network fiber cable to the SFP port on a switch, firewall or other network device.



Key points:

- Hot-swappable interface lets you install and uninstall without shutting down
- Supports bi-directional Gigabit Ethernet data transfer rates up to 1.25 Gbps

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Technology	Connections		Brand Compatibility	Data Transfer Rate	Transmission Distance	Operating Temp. Range
		Connector A	Connector B				
N2861-1P25GLXD1	Singlemode	SFP (M)	LC (F)	TRENDnet	1 Gbps	10 km	-40° to 85°C
N2861-1P25GSXD	Multimode	SFP (M)	LC (F)	TRENDnet	1 Gbps	550 m	-40° to 85°C

USB 3.1 Gen 1 Cables

Connects high-speed USB 3.0 equipment in industrial environments that require protection against dust and moisture.



Key points:

- Shielded USB 3.0 Cable Recommended for Outdoor or Harsh Indoor Environments
- IP68 Rating Denotes Resistance to Dust and Water
- Heavy Shielding Protects Your Network Data from Destructive Line Noise

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Connections		Cable type	Length	Cable Jacket Color
	Connector A	Connector B			
U325-003-IND	USB-A	USB-A	Passive	91 cm	Black
U325-006-IND	USB-A	USB-A	Passive	1,83 m	Black
U325-010-IND	USB-A	USB-A	Passive	3,05 m	Black
U325-013-IND	USB-A	USB-A	Passive	3,96 m	Black

USB Adapters

USB to serial converter lets you connect four 9-pin serial devices to your computer or laptop's USB-A port.



Key points:

- Connects Up to Four 9-Pin Serial Devices to Your Computer, Laptop or Tablet's USB-A Port
- Auto-detects and -switches RS-422 and RS-485 serial devices
- Rugged All-Metal Housing Designed to Last in Harsh Industrial Applications
- Operate serial-based medical instruments, such as bedside monitors

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Number of Ports	Connections		Power Consumption (Watts)	USB Specification	Driver Required	Length
		Connector A	Connector B				
U208-002-IND	2	USB-B (F)	2x DB9 (M)	4.5	USB 2.0 (up to 480 Mbps)	Yes	-
U208-004-IND	4	USB-B (F)	4x DB9 (M)	4.5	USB 2.0 (up to 480 Mbps)	Yes	-
U209-30N-IND	-	USB-A (M)	DB9 (M)	-	USB 2.0 (up to 480 Mbps)	Yes	76 cm



USB Hubs

Rugged industrial-grade hub adds 4 USB 2.0 ports to your computer for connecting industrial printers, sensors and other USB devices.



Key points:

- Rugged metal housing designed to withstand harsh warehouse and factory environments
- ESD protection to ±15 kV cuts potential static damage to your connected peripherals
- Plug-and-play operation with no software required for easy, immediate installation

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Data Ports

Part number	Host connector	Data Ports						Gbps Ethernet	Power Source Type	ESD Protection	Operating Temp. Range	Mounting Support
		USB-A 2.0	USB 3.1 Gen 1	USB-A 3.2 Gen 1	USB-B	USB-C	USB-C PD Charging					
U223-004-IND	USB-A	4	-	-	-	-	480 Mbps	3-Pin Terminal Block	15KV	0° to 60°C	Wall/DIN	
U223-004-IND-1	USB-A	4	-	-	-	-	480 Mbps	3-Pin Terminal Block	15KV	0° to 60°C	Wall/DIN	
U223-007-IND	USB-A	7	-	-	-	-	480 Mbps	3-Pin Terminal Block	15KV	0° to 60°C	Wall/DIN	
U223-007-IND-1	USB-A	7	-	-	-	-	480 Mbps	3-Pin Terminal Block	15KV	0° to 60°C	Wall/DIN	
U360-004-IND	USB-A	-	4	-	-	-	5 Gbps	3-Pin Terminal Block	20KV	0° to 60°C	Wall/DIN	
U360-007-IND	USB-A	-	7	-	-	-	5 Gbps	3-Pin Terminal Block	20KV	0° to 60°C	Wall/DIN	
U360-010-IND	USB-A	-	10	-	-	-	5 Gbps	3-Pin Terminal Block	20KV	0° to 60°C	Wall/DIN	
U460-2A2C-IND	USB-C	-	-	2	-	2	10 Gbps	2-wire terminal block/LPS 12V DC-24V DC	15KV	0° to 50°C	-	
U460-4A3C-IND	USB-C	-	-	4	-	3	10 Gbps	2-wire terminal block/LPS 12V DC-24V DC	15KV	0° to 50°C	-	

USB Extenders

Industrial-grade transmitter/receiver combo connects a laptop or PC to as many USB peripherals up to 100 m away.



Key points:

- Supports USB 2.0 speeds up to 300 Mbps to ensure reliable data transfers
- Power over Cable (PoC) provides power to the transmitter via Cat5/6 cable
- Industrial-grade metal housings withstand harsh warehouse and factory environments

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Number of Ports	Gbps Ethernet	Transmission Distance	Power source	Power Over Cable	ESD Protection	Operating Temp. Range	Mounting Support
B203-101-IND	1	480 Mbps	45 m	AC Adapter	Yes	15KV	0° to 50°C	DIN
B203-101-IND-ER	1	300 Mbps	100 m	AC Adapter	Yes	15KV	0° to 40°C	DIN
B203-104-IND	4	480 Mbps	45 m	AC Adapter	Yes	15KV	0° to 40°C	DIN
B203-104-IND-ER	4	300 Mbps	100 m	AC Adapter	Yes	15KV	0° to 40°C	DIN

HDMI Cables

Connects high-speed 4K audio/video and Ethernet equipment in industrial environments that require protection against dust and moisture.



Key points:

- IP68-rated cable resists dust and endure immersion in 1.5 m of water up to 60 min*
- Supports UHD resolutions up to 4K (4:4:4) for crystal-clear video
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Complies with HDCP 2.2 standards to display up-to-date 4K video content

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Max resolution supported	Connections		Length	Cable type	Signal Transmission	Operating Temp. Range	cable jacket		COLOR	
		Connector A	Connector B					Material	Rating	Cable Jacket	Connector
P569-003-IND	4K @60 Hz	HDMI	HDMI	91 cm	Passive	Bidirectional	-10° to 50°C	PVC	VW-1	Black	Black
P569-006-IND2	4K @60 Hz	HDMI	HDMI	1,83 m	Passive	Bidirectional	-10° to 50°C	PVC	VW-1	Black	Black
P569-012-IND	4K @60 Hz	HDMI	HDMI	3,66 m	Passive	Bidirectional	-10° to 50°C	PVC	VW-1	Black	Black
P569-012-IND2	4K @60 Hz	HDMI	HDMI	3,66 m	Passive	Bidirectional	-10° to 50°C	PVC	VW-1	Black	Black

Couplers

Connects Ethernet or fiber optic equipment in industrial environments that require protection against dust, debris and moisture.



Key points:

- Connect Ethernet, Fiber, USB or HDMI equipment in Industrial environments that require protection against dust, debris and moisture.

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Connections		Shielding		PoE Type	Color
	Connector A	Connector B	Cable shielding	Conductor shielding		
N206-BC01-IND	RJ45 (F)	RJ45 (F)	Yes	STP	Type 4 High-Power (100W, IEEE 802.3bt)	Black
N455-BC01-IND	Multimode LC (F)	Multimode LC (F)	-	-	-	Black
P569-000-FF-IND	HDMI (F)	HDMI (F)	-	-	-	Black
U325-000-IND	USB 3.0	USB 3.0	-	-	-	Black

PoE Injectors & Extenders

Industrial-grade PoE+ injectors uses existing Cat6 cable to supply up to 90W power + data up to 100m to a PoE device connected to a non-PoE switch.



Key points:

- Gigabit Extender Lets You Cascade Your Existing PoE/PoE+ Connection up to 400 M
- Supports Gigabit Ethernet data transfer speeds up to 1 Gbps
- Supports Power over Ethernet to Save You Money and Give You More Installation Choices
- Industrial-grade IP30 metal housing ready for DIN railmounting with included

Ideal for:

- Manufacturing plants
- Production floors
- Warehouses/Logistics facilities
- Dusty, outdoor network or Digital Signage installations

Part number	Transmission Distance	Power Source	PoE Type	Max PoE budget	Mounting Support	Operating Temp. Range
Industrial Injectors						
NPOEI-60W-1G	Up to 100 m	Dual 24 – 57 VDC Terminal Block	Type 3 PoE++/UPoE (60W, IEEE 802.3bt)	60W	DIN-Rail Rackmount Wall-mount	-40° to 75°C
NPOEI-90W-1G	Up to 100 m	Dual 24 – 57 VDC Terminal Block	Type 4 PoE++/UPoE (100W, IEEE 802.3bt)	90W	DIN-Rail Rackmount Wall-mount	-40° to 75°C

Part number	Voltage Compatibility (VAC)	Input		Power Consumption (Watts)	Technology				Cable		PoE Type
		Frequency	Plug Type		Cat5/5e	Cat6	Cat6a	Cat8	Connector A	Connector B	
Injectors											
NPOE-30W-1G-INT	Up to 240V	50/60 Hz	BS1363 Schuko	30W	Yes	Yes	Yes	-	RJ45 (F)	RJ45 (F)	Type 2 PoE+ (30W)
Extenders											
NPOE-EXT-1G30	-	-	-	30W	Yes	Yes	Yes	-	RJ45 (F)	RJ45 (F)	Type 2 PoE+ (30W)
NPOE-EXT-1G30WP Water resistant (IP65)	-	-	-	30W	Yes	Yes	Yes	-	RJ45 (F)	RJ45 (F)	Type 2 PoE+ (30W)
NPOE-EXT-2X1G30 Water resistant (IP67)	-	-	-	95W	Yes	Yes	Yes	-	RJ45 (F)	2x RJ45 (F)	Type 4 PoE++ (100W)
Splitters											
NPOE-SPL-G-5VMU	5VDC	-	-	-	Yes	Yes	-	-	RJ45 (F)	RJ45 (M) Micro USB-B (M)	

WAP Enclosures

Locking enclosure protects your Wi-Fi access point against theft, damage or tampering inside offices, dorms and other indoor areas.



Key points:

- Wall-Mount enclosure secures and organizes your router/modem or wireless
- Access point Locks Securely to Help Prevent Damage, Tampering or Theft
- Easy to Mount with the included Hardware

Ideal for:

- Telecommunications
- Server room
- Indoor or outdoor router/modem or Wi-Fi access point

Part number	Dimensions				Material of Construction	Colors	Compliance
	Height		Width	Depth			
	(U)	(cm)	(cm)	Max (cm)			
EN1111	0U	28,2 cm	28,2 cm	11,2 cm	ABS Plastic	White	RoHS
EN1309N4	0U	35,71 cm	25,1 cm	13,9 cm	UL 94 V-1 Classified PC Plastic	White	RoHS
EN1511N4LATCH	0U	38,6 cm	28,2 cm	10,1 cm	UL 94 V-1 Classified PC Plastic	White	NEMA 4/RoHS
EN1812	0U	45,5 cm	30,2 cm	12,9 cm	PC Plastic	White	RoHS
Accessories - Mounting Brackets							
ENBRKT	0U	6,5 cm	17,8 cm	21,8 cm	-	White	RoHS
ENBRKTCVR	0U	19,5 cm	24 cm	29 cm	-	White	RoHS



Healthcare

Power Solutions
Safe-IT Cables
Display Mounts

UPS Systems

Line-interactive UPS provides basic battery backup with UL 60601-1 compliance for use in medical facilities, including patient care areas.



Key points:

- IEC 60601-1 compliant
- Approved for Use in Patient Care Vicinities
- Lead acid & Lithium Battery Technology
- Breathe new life into your UPS: replacement battery cartridge available

Ideal for:

- Hospitals
- Medical centers
- Dr. clinics
- Patientcare facilities

Part number	Battery	Output capacity	Nominal AC Voltage	Runtime (Half/Full Load)	Hospital-Grade AC Outlets (1)	Communication ports	AC Input Cord Length	AC Input Inlet
SMX700HG	SLA	700VA / 450W	230 V	36/14.5 min	6 (C13)	Serial & USB	15.2 cm	C14
SMX1200XLHG	SLA	1kVA / 750W	230 V	27.5/11 min. +	6 (C13)	Serial & USB	15.2 cm	C14
SMX700HGL	Lithium Iron	700VA / 450W	230 V	42/18 min	6 (C13)	Serial & USB	15.2 cm	C14
SMX1200XLHGL	Lithium Iron	1kVA / 750W	230 V	28/10 min. +	6 (C13)	Serial & USB	15.2 cm	C14

Replacement battery cartridge

RBC53L	UPS Replacement 36VDC Lithium-ion (LiFePO4) Battery Cartridge for Select Lithium-ion UPS
RBC36-SLT	UPS Replacement 36VDC Battery Cartridge for Select SLT UPS compatible with

⁽¹⁾ Backup runtimes vary with load, battery condition and other factors. Increase runtimes for "+" models by connecting optional external battery packs.

⁽²⁾ Lithium Iron Phosphate (LiFePO4) battery with a 10,000-cycle life (20-30 times the cycle life of traditional batteries).

Isolation Transformers

Transformer with full CAN/ES/IEC/EN 60601-1 listing offers line isolation, step-up and step-down capabilities, and continuous noise filtering in protecting medical electronic equipment used in patient-care vicinities.



Key points:

- Protects sensitive equipment from EMI/RFI line noise and surges
- Cumulative leakage current less than 100 µA
- Automatically shuts down all outlets in case of overload
- Line isolation, continuous noise filtering and 240 joules of AC surge protection
- Step-up, step-down or pass-through Dual-Voltage 115/230V operation

Ideal for:

- Hospitals
- Medical centers
- Dr. clinics
- Patientcare facilities
- Applications requiring dual-voltage step-up/down

Part number	Output	Nominal AC Voltage	Hospital-Grade AC Outlets (1)	AC Input Inlet
IS300HGDV	300W	115/230V	4 (C13)	C14
IS600HGDV	600W	115/230V	6 (C13)	C14
IS1000HGDV	1000W	115/230V	8 (C13)	C14
IS1800HGDV	1800W	115/230V	8 (C13)	C20

Power Inverter/Chargers

Power Inverter/Chargers for Mobile Medical Equipment, powers equipment used in healthcare facilities inside and outside patient care areas. 230V - IEC 60601-1



Key points:

- All-in-one inverter/charger/controller powers equipment on mobile medical carts
- Works with both SLA and LiFePhos batteries to best fit your power requirements
- Internal ATS powers connected equipment and recharges battery simultaneously
- Rugged Construction Sure to Stand Up to Demanding Environments

Ideal for:

- Hospitals
- Healthcare facilities

Part number	Output	Battery	Runtime ⁽¹⁾	Battery Charge	AC Outlets	Communication ports	Expandable Runtime
HCINT150SL	150W	SLA or LiFePhos 12VDC	up to 6 hours	Equal to discharge time (9-20A)	(1) C13	USB	Yes
HCINT350SNR	150W	SLA or	up to 6 hours	Equal to discharge time (9-20A)	(1) C13	USB	Yes

⁽¹⁾ Up to 6 hours typical runtime in standard configuration. Runtime varies depending on battery condition and load.

Accessories

Part number	Description
HCBATTERYCABLE	Power Cable Kit for Healthcare Power Modules/Inverters/Chargers, 3 ft. (0.91 m)
HCFLUSHRUI	Remote Control Module for Healthcare Products - for Medical Power Modules/Inverters/Chargers



Eaton's electrical business is a global leader with deep regional application expertise in power distribution and circuit protection; power quality, backup power and energy storage; control and automation; life safety and security; structural solutions; and harsh and hazardous environment solutions. Through end-to-end services, channel and an integrated digital platform & insights Eaton is powering what matters across industries and around the world, helping customers solve their most critical electrical power management challenges.

For more information, visit [Eaton.com](https://www.eaton.com)