



Powering Business Worldwide

For more information, visit Eaton.com/HealthcareHub

HOSPITAL-GRADE POWER STRIPS AND SURGE PROTECTORS

Power Strips Approved for Use Inside of Patient Care Vicinity

Standard Power Strips



PS-402-HG-OEM
UL 1363A, 4 Outlets, 15A,
2 ft. Cord, Safe-IT



PS-407-HG-OEM
UL 1363A, 4 Outlets, 15A,
7 ft. Cord, Safe-IT



PS-415-HG-OEM
UL 1363A, 4 Outlets, 15A,
15 ft. Cord, Safe-IT



PS-607-HG-OEM
UL 1363A, 6 Outlets, 15A,
7 ft. Cord, Safe-IT



PS607HG20AOEM
UL 1363A, 6 Outlets, 20A,
7 ft. Cord, Safe-IT



PS615HG20AOEM
UL 1363A, 6 Outlets, 20A,
15 ft. Cord, Safe-IT



PS625HG20AOEM
UL 1363A, 6 Outlets, 20A,
25 ft. Cord, Safe-IT



PS-615-HG-OEM
UL 1363A, 6 Outlets, 15A,
15 ft. Cord, Safe-IT

15A Power Strips with Safety Covers



PS-406-HGULTRA
UL 2930, 4 Outlets, 15A,
6 ft. Cord, Safe-IT



PS-415-HGULTRA
UL 2930, 4 Outlets, 15A,
15 ft. Cord, Safe-IT

Specialty Cords



PS-410-HGOEMCC
UL 1363A, 4 Outlets, 15A,
3 ft. Coiled Cord, Safe-IT



PS-415-HG-OEMRA
UL 1363A, 4 Outlets, 15A,
15 ft. Cord, Right-Angle Plug, Safe-IT

Load-Monitoring Power Strips with Safety Covers



PS-402-HG-OEMLM
UL 1363A, 4 Outlets, Load Monitoring,
2 ft. Cord, Safe-IT



PS-415-HG-OEMLM
UL 1363A, 4 Outlets, Load Monitoring,
15 ft. Cord, Safe-IT



PS-607-HG-OEMLM
UL 1363A, 6 Outlets, Load Monitoring,
7 ft. Cord, Safe-IT



PS-615-HG-OEMLM
UL 1363A, 6 Outlets, Load Monitoring,
15 ft. Cord, Safe-IT

Dual-Ground Protection with Safety Covers



PS-606-HGDG
UL 2930, Dual-Ground Protection, 6
Outlets, 15A, 6 ft. Cord, Safe-IT



PS-615-HG-OEMRA
UL 1363A, 6 Outlets, 15A,
15 ft. Cord, Right-Angle Plug, Safe-IT

Surge Protectors Approved for Use in Patient Care Vicinity



SPS406HGULTRA
UL 2930, 1410 Joules, 4 Outlets,
6 ft. Cord, Safe-IT



SPS415HGULTRA
UL 2930, 1410 Joules, 4 Outlets,
15 ft. Cord, Safe-IT

Power Strips for Use Outside of Patient Care Vicinity

Standard Power Strips



PS-415-HG
UL 1363, 4 Outlets, 15 ft. Cord, Safe-IT



PS-602-HG
UL 1363, 6 Outlets, 1.5 ft. Cord, Safe-IT



PS-606-HG
UL 1363, 6 Outlets, 6 ft. Cord, Safe-IT



PS-615-HG
UL 1363, 6 Outlets, 15 ft. Cord, Safe-IT

USB Charging



PS-415-HGUSB
UL 1363, 4 Outlets, USB-A, USB-C, 15A,
15 ft. Cord, Safety Covers, Safe-IT



PS-602-HGUSB
UL 1363, 6 Outlets, USB-A, USB-C,
15A, 2 ft. Cord, Safety Covers, Safe-IT



PS-615-HGUSB
UL 1363, 6 Outlets, USB-A, USB-C, 15A,
15 ft. Cord, Safety Covers, Safe-IT

Rack-Mount Power Strip



RS1215-HG
1U Rack-Mount, UL 1363, 12 Outlets, 15A, 15 ft. Cord



PS-606-HGUSB
UL 1363, 6 Outlets, USB-A, USB-C, 15A,
6 ft. Cord, Safety Covers, Safe-IT

Surge Protectors for Use Outside of Patient Care Vicinity



SPS606HGRA
UL 1363, 1050 Joules, 6 Outlets,
6 ft. Cord, Right-Angle Plug



SPS610HGRA
UL 1363, 1050 Joules, 6 Outlets,
10 ft. Cord, Right-Angle Plug



SPS-615-HG
UL 1363, 1050 Joules, 6 Outlets, 15 ft. Cord



ISOBAR6ULTRAHG
Isobar, UL 1363, 3330 Joules, 6 Outlets, 15 ft. Cord

Antimicrobial Protection

Safe-IT™ products help reduce the presence of bacteria and other germs on frequently handled equipment.

To learn more, visit Eaton.com/HealthcareHub.



See reverse side for more solutions for healthcare environments.

SOLUTIONS FOR HEALTHCARE ENVIRONMENTS

Hospital-Grade Multi-Device UV Charging Stations



CS16USBWHG
16 USB Ports
for iPad & Android Tablets,
UV Light Sanitizing, Safe-IT



CSC32USBWHG
32 USB Ports
for iPad & Android Tablets,
UV Light Sanitizing, Safe-IT



CSC32ACWHG
32 AC Outlets
for Laptops & Chromebooks,
UV Light Sanitizing, Safe-IT

Hospital-Grade UPS Systems Approved for Patient Care Vicinity



SMART700HG
700VA 450W, UL 60601-1, 4 Outlets



SMART700HGL
700VA 450W, UL 60601-1, 4 Outlets,
Lithium Battery



SMART1200XLHG
1kVA 750W, UL 60601-1, 4 Outlets



SMART1200XLHGL
1kVA 750W, UL 60601-1, 4 Outlets,
Lithium Battery

Mobile Workstations



WWSS1DWSTAA
Monitor Arm, Keyboard Tray,
Locking Drawer, Casters, TAA



WWSS2DWSTAA
Two Adjustable Shelves, Two Drawers,
Casters, TAA



WWSSRSTAA
Four Shelves, Casters, TAA

Mounting Clamps for Medical-Grade Power Strips



PSCLAMP
Removable Drip Shield,
Power Cord Manager

Medical-Grade Ethernet Network Isolators for Patient Care Vicinity



N234-MI-BX
RJ45 Feedthrough,
IEC 60601-1, TAA



N234-MI-KJ
Keystone, RJ45 Feedthrough,
IEC 60601-1, TAA



N234-MI-06N-BX
RJ45, F/M, IEC 60601-1,
6 in. Cable, TAA

Medical-Grade Mobile Power Retrofit Kits



HCRK
300W, 90 Amp-Hour Battery,
3 Outlets



HCRK-54
300W, 54 Amp-Hour Battery,
3 Outlets



HCRK-36
300W, 36 Amp-Hour Battery,
3 Outlets

Medical-Grade USB Galvanic Isolator for Patient Care Vicinity



U234-000-UGI
6kV 1-Minute Insulation, IEC 60601-1,
2MOPP Certified, UL/cUL, TAA

AV Extenders for Medical Applications



B127M-004-H
HDMI over Cat6 Splitter



B127M-100-H
HDMI over Cat6 Receiver



B127M-101-H
HDMI over Cat6 Extender Kit

Hospital-Grade Isolation Transformers Approved for Patient Care Vicinity



IS300HGDV
Dual-Voltage 115/230V 300W,
UL 60601-1, 4 C13 Outlets, TAA



IS600HGDV
Dual-Voltage 115/230V 600W,
UL 60601-1, 6 C13 Outlets, TAA



IS1000HGDV
Dual-Voltage 115/230V 1000W,
UL 60601-1, 8 C13 Outlets, TAA



IS1800HGDV
Dual-Voltage 115/230V 1800W,
UL 60601-1, 8 C13 Outlets, TAA

Hospital-Grade Power Cords



P006-025-HG15
5-15P to C13, Green Dot, 15A,
125V, 14 AWG, 25 ft., Black



P006-L06-HG10
5-15P to Locking IEC C13, Green
Dot, 10A, 125V, 18 AWG, 6 ft., Black



P022AB-015-HG
5-15P to 5-15R, Green Dot, 13A,
125V, 16 AWG, 15 ft., Black, Safe-IT



P024-015-GY-HG
5-15P to 5-15R, Green Dot, 15A,
125V, 14 AWG, 15 ft., Gray

See reverse for power strips and surge protectors.