



## Eaton Tripp Lite series hospital-grade power strips (UL 1363) with USB charging

### Power and charge devices outside the patient care vicinity

Eaton Tripp Lite series hospital-grade power strips with USB charging distribute power to equipment in areas outside the patient care vicinity. USB-C and USB-A ports allow two essential devices, such as a smartphone and tablet, to charge at the same time while leaving outlets available for AC equipment. The power strips meet UL 1363 standards for use in labs, pharmacies, nursing stations, administration areas and other locations outside patient care vicinities.

### Charge mobile devices outside patient care vicinities

#### USB charging

A USB-C port and USB-A port provide power to charge smartphones, tablets and other essential mobile devices. When used alone, the USB-C port provides USB Power Delivery (PD) up to 30W.

### Enhance safety

#### Premium safety features

The power strips meet UL 1363 standards for use outside patient care vicinities. The outlets and input plug are hospital-grade quality and identified with green dots.

- Switchless design helps prevent accidental shutdown of connected equipment.
- Locking plastic safety covers are included to block access to unused outlets.
- 15A resettable circuit breaker shuts down AC input if the connected equipment load is drawing too much power.



### Promote a cleaner and healthier work environment

#### Antimicrobial protection

As part of the Safe-IT™ family of products, these power strips have antimicrobial protection to help resist the growth of bacteria, viruses, fungi, mold and mildew.

**Safe-IT™**  
AntiMICROBIAL  
PRODUCTS

### Conveniently access product information

#### Easy Asset QR code

Scan the QR code on the side of the power strip for quick access to product resources and other critical information.

### Install on a stable surface

#### Built-in mounting flanges

The flanges on the metal housing enable installation on a flat, stable surface.

**EATON**

Powering Business Worldwide

## Feature focus



Model: PS-615-HGUSB

- 1 **Input power cord with hospital-grade plug**
- 2 **USB-C PD charging port**  
Power delivery port provides up to 30W when used alone.
- 3 **USB-A charging port**
- 4 **Hospital-grade outlets**
- 5 **Mounting flanges**  
Built-in flanges on both ends facilitate mounting on a flat surface.
- 6 **Antimicrobial coating**

### Easy Asset QR code

Scan the code to quickly access product information.



### Outlet safety covers

The included safety covers block access to unused outlets.



### Resettable circuit breaker

If the strip is overloaded, the breaker cuts power to outlets.



## Specifications

Catalog number	PS-615-HGUSB	PS-606-HGUSB	PS-602-HGUSB	PS-415-HGUSB
Nominal AC input voltage/amps	120V/15A			
UL compliance	UL 1363			
AC outlets	6 (5-15R-HG)			4 (5-15R-HG)
Input cord length	15 ft.	6 ft.	2 ft.	15 ft.
Input plug type	5-15P-HG			
USB charging ports	2 (USB-C PD and USB-A)			
Overload protection	15A circuit breaker			
Unit size, H x W x D	13.63 x 2.5 x 1.65 in.			8.54 x 2.5 x 1.66 in.
Warranty	Lifetime limited			

Due to continuous improvement programs, all specifications are subject to change without notice.

To learn more, visit [TrippLite.Eaton.com](https://TrippLite.Eaton.com)



Eaton  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2024 Eaton  
All Rights Reserved  
Printed in USA  
BR153191EN / 24-06-231  
August 2024

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



**EATON**  
Powering Business Worldwide