



## Eaton's Tripp Lite series P-Lock power cords

### Prevent accidental cable disconnections

Eaton's Tripp Lite series P-Lock power cords provide a secure connection between power distribution units (PDUs) and computers, servers and switches in data center environments. Locking tabs on both sides of the plug click into place to secure the plug in a compatible PDU P-Lock outlet. The secure connection helps prevent IT equipment from becoming accidentally disconnected and causing expensive downtime.

#### Create secure connections

Locking tabs on the sides of the plug allow the P-Lock power cords to create secure connections that standard power cords cannot match.

- Cords with a P-Lock C14 connector are compatible with Eaton PDU G4 PDUs and other PDUs with P-Lock C13 or C39 outlets.
- Cords with a P-Lock C20 connector are compatible with Eaton PDU G4 PDUs and other PDUs with P-Lock C19 or C39 outlets.



#### Upgrade PDU cables

Replace a non-locking cable, extend an existing connection or upgrade an entire PDU installation with P-Lock power cords. The cords are UL certified and made with high-quality materials for better performance and durability.

- P004-series P-Lock cords comply with UL and VDE standards for use in North America and Europe.
- Heavy-duty P-Lock cords have a thicker wire gauge and a higher amp rating than similar cords.

#### Improve cable management

Available in installer-preferred colors, the P-Lock power cords can be used to color-code installations. Color-coding makes it easier to trace cords between devices and power sources to help prevent accidental disconnection and downtime. For example, "A" and "B" feeds can have different color cords, creating a way to visually confirm that IT devices are properly connected to dual power sources.

#### Reduce cord clutter

Right-sizing cables reduces cord clutter in crowded server racks to improve airflow around IT equipment and make fans more efficient. Reducing cord clutter also makes maintenance easier and improves the appearance of the rack. Tripp Lite series P-Lock cables are available in lengths from two feet to 10 feet, providing the perfect cord length for each connection.



*P-Lock cables fit securely into compatible outlets to reduce the risk of disconnection and ensure IT equipment stays powered.*



*Powering Business Worldwide*

Feature focus (See Specifications below for model-specific configurations)

Connector types



Specifications

Catalog number	Cord length	Color	Quantity
C13 to P-Lock C14 power cord — 10A, 250V, 18 AWG, North America & Europe rated			
P004-E02	2 ft. (0.6 m)	Black	1
P004-E03	3 ft. (0.9 m)	Black	1
P004-E04	4 ft. (1.2 m)	Black	1
P004-E06	6 ft. (1.8 m)	Black	1
P004-E10	10 ft. (3.1 m)	Black	1
Heavy-duty C13 to P-Lock C14 power cord — 15A, 250V, 14 AWG			
P005-E02	2 ft. (0.6 m)	Black	1
P005-E02-6	2 ft. (0.6 m)	Black	6
P005-E02-ABL-6	2 ft. (0.6 m)	Blue	6
P005-E02-ARD-6	2 ft. (0.6 m)	Red	6
P005-E03	3 ft. (0.9 m)	Black	1
P005-E03-6	3 ft. (0.9 m)	Black	6
P005-E03-ABL-6	3 ft. (0.9 m)	Blue	6
P005-E03-ARD-6	3 ft. (0.9 m)	Red	6
P005-E03-AWH-6	3 ft. (0.9 m)	White	6
P005-E04	4 ft. (1.2 m)	Black	1
P005-E04-6	4 ft. (1.2 m)	Black	6
P005-E04-ABL-6	4 ft. (1.2 m)	Blue	6
P005-E04-ARD-6	4 ft. (1.2 m)	Red	6
P005-E06	6 ft. (1.8 m)	Black	1
P005-E06-6	6 ft. (1.8 m)	Black	6
P005-E06-ABL-6	6 ft. (1.8 m)	Blue	6
P005-E06-ARD-6	6 ft. (1.8 m)	Red	6
P005-E06-AWH-6	6 ft. (1.8 m)	White	6
P005-E10	10 ft. (3.1 m)	Black	1
P005-E10-6	10 ft. (3.1 m)	Black	6
P005-E10-ABL-6	10 ft. (3.1 m)	Blue	6
P005-E10-ARD-6	10 ft. (3.1 m)	Red	6

Catalog number	Cord length	Color	Quantity
Heavy-duty C15 to P-Lock C14 power cord — 15A, 250V, 14 AWG			
P018-E03	3 ft. (0.9 m)	Black	1
P018-E03-6	3 ft. (0.9 m)	Black	6
P018-E03-ABL-6	3 ft. (0.9 m)	Blue	6
P018-E03-ARD-6	3 ft. (0.9 m)	Red	6
P018-E06	6 ft. (1.8 m)	Black	1
P018-E06-6	6 ft. (1.8 m)	Black	6
P018-E06-ABL-6	6 ft. (1.8 m)	Blue	6
P018-E06-ARD-6	6 ft. (1.8 m)	Red	6
Heavy-duty C13 to P-Lock C20 power cord — 15A, 100-250V, 14 AWG			
P032-E02	2 ft. (0.6 m)	Black	1
P032-E03	3 ft. (0.9 m)	Black	1
P032-E04	4 ft. (1.2 m)	Black	1
P032-E06	6 ft. (1.8 m)	Black	1
Heavy-duty C19 to P-Lock C20 power cord — 20A, 250V, 12 AWG			
P036-E03	3 ft. (0.9 m)	Black	1
P036-E03-6	3 ft. (0.9 m)	Black	6
P036-E03-ABL-6	3 ft. (0.9 m)	Blue	6
P036-E03-ARD-6	3 ft. (0.9 m)	Red	6
P036-E03-AWH-6	3 ft. (0.9 m)	White	6
P036-E04	4 ft. (1.2 m)	Black	1
P036-E04-6	4 ft. (1.2 m)	Black	6
P036-E04-ABL-6	4 ft. (1.2 m)	Blue	6
P036-E04-ARD-6	4 ft. (1.2 m)	Red	6
P036-E04-AWH-6	4 ft. (1.2 m)	White	6
P036-E06	6 ft. (1.8 m)	Black	1
P036-E06-6	6 ft. (1.8 m)	Black	6
P036-E06-ABL-6	6 ft. (1.8 m)	Blue	6
P036-E06-ARD-6	6 ft. (1.8 m)	Red	6
P036-E06-AWH-6	6 ft. (1.8 m)	White	6

Learn more about Tripp Lite series locking power cords at [TrippLite.Eaton.com](https://www.computersupply.com)