

D

C

B

A

EVMOGU23X-E G4 METERED OUTLET

FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT, POWER, AND ENERGY METERING FOR INPUT; CURRENT METERING FOR BRANCH	EATON/SOURIAU UTG SERIES 8-PIN CONNECTOR CORDSETS NOT INCLUDED, MUST BE ORDERED SEPARATELY	(24) IEC 60320 C13 (18) EATON C39 - COMBO C13/C19	0° TO 60° C 32° TO 140° F
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
72.01" (1829mm) LENGTH 2.05" (52mm) WIDTH 2.56" (65mm) DEPTH ALUMINUM CHASSIS, BLACK	1P: 100-240V~, 16-63A, or 3P DELTA: 100-240V~, 16-55A, or 3P WYE: 100-240 / 173-415V~, 16-32A 50/60Hz; USE WITH EZ1 SERIES CORDSET (CBL3XX-XX)	100-240V~ 10A PER C13, 16A PER C39 16A MAX PER SECTION NOT TO EXCEED INPUT CORDSET RATING	cTUVus CE, UKCA, RCM
CIRCUIT BREAKERS	COMMUNICATION	ACCESSORIES	REGULATORY MODEL
(6) 20A 2-POLE LISTED	G4 eNMC, DUAL GIGABIT ETHERNET WITH NETWORK CASCADING, POWER REDUNDANCY PORT, EMP PORT, 2xUSB-C, MENU PIXEL LCD, ADVANCED CYBERSECURITY	INCLUDED SPK045 - INSTALLATION OPTIONAL USB-C TO RS232 ADAPTER - U209-006-RJ45XC OPTIONAL ENVIRONMENTAL PROBE - EMPDT1H1C2	EMOF-ZBAK-G28K

