



# Current Promotions

**Instant rebates up to \$75 when you purchase from participating resellers**

Order from participating resellers:



amazon.com



Connection  
we solve IT

Insight



PROVANTAGE

## Product Categories

### ▶ Power Solutions

[UPS Systems](#)

[Surge Protectors](#)

[Power Strips](#)

### ▶ Storage & Mount Solutions

[Rack Enclosures](#)

[Display Mounts](#)

[Cooling](#)

### ▶ Connectivity Solutions

[KVMs](#)

[Network Connectivity](#)

[Digital Signage Connectivity](#)

[USB Solutions](#)

[USB-C Solutions](#)

## Power Solutions

### UPS Systems—INSTANT REBATES UP TO \$50

Model	Instant Rebate*	Description
<a href="#">INTERNET650U1</a>	\$2	650VA/330W, tel/Ethernet, USB, 4.5 min.
<a href="#">ECO900LCDU2</a>	\$5	900VA/480W, tel/Ethernet, USB, 7.8 min.
<a href="#">OMNISMART500TU</a>	\$5	500VA/360W, tel/Ethernet, USB, AVR, 10 min.
<a href="#">OMNI700LCDT</a>	\$6	700VA/350W, tel/Ethernet, USB, AVR, 10 min.
<a href="#">SMART550USB2</a>	\$5	550VA/300W, USB, AVR, 12 min.
<a href="#">SMART1000RM1U</a>	\$30	1000VA/800W, USB/DB9, AVR, 14 min., rack-mount
<a href="#">SMART1000RM2U</a>	\$30	1000VA/800W, USB/DB9, AVR, 15 min., rack-mount
<a href="#">SMART1500RM2UN</a>	\$50	1500VA/1350W, USB/DB9, AVR, 13 min., rack-mount



\*Instant rebates available through 9/30/19. Some accounts excluded.

“min.” represents half-load runtime in minutes; may vary based on load and battery condition.

## Surge Protectors—INSTANT REBATES UP TO \$4

Model	Instant Rebate*	Description
<a href="#">TLP310USBC</a>	\$2	3 outlets + 2 USB, 510 joules, 10-ft. cord, desk clamp
<a href="#">TLP366CUBEUSBB</a>	\$4	3 outlets + 6 USB, 540 joules, 6-ft. cord, 2-piece cube
<a href="#">TLM446USBB</a>	\$2	4 outlets + 4 USB, 450 joules, 6-ft. cord, metal
<a href="#">TLM526USBB</a>	\$2	5 outlets + 2 USB, 450 joules, 6-ft. cord, metal
<a href="#">TLP6SLUSBB</a>	\$1	6 outlets + 2 USB, 1050 joules, direct plug-in
<a href="#">TLP606DMUSB</a>	\$1.50	6 outlets + 2 USB, 2100 joules, 6-ft. cord, clamp mount
<a href="#">TLP648USBC</a>	\$4	6 outlets + 3 USB, 1080 joules, 8-ft. cord, desk clamp

\*Instant rebates available through 9/30/19. Some accounts excluded.



## Power Strips—INSTANT REBATES UP TO \$3

Model	Instant Rebate*	Description
<a href="#">PSSS2C</a>	\$1	Mounting clamps for PS- and SS-series power strips
<a href="#">PSC240410USBB</a>	\$3	4 outlets + 4 USB, 10-ft. cord, 24-in. strip
<a href="#">PSC360610USBB</a>	\$3	6 outlets + 6 USB, 10-ft. cord, 36-in. strip

\*Instant rebates available through 9/30/19. Some accounts excluded.



## Storage & Mount Solutions

### Rack Enclosures—INSTANT REBATES UP TO \$75

Model	Instant Rebate*	Description
<a href="#">SRW6UDPVRT</a>	\$20	6U wall-mount rack, low profile, wide, 200-lb. capacity
<a href="#">SRW12USG</a>	\$40	12U wall-mount rack, clear acrylic door, 200-lb. capacity
<a href="#">SR2400</a>	\$50	42U value-series enclosure, 2,400-lb. capacity
<a href="#">SR42UB</a>	\$75	42U standard enclosure, 3,000-lb. capacity

\*Instant rebates available through 9/30/19. Some accounts excluded.



### Display Mounts—INSTANT REBATES UP TO \$30

Model	Instant Rebate*	Description
<a href="#">DWM1742MA</a>	\$5	Swivel/tilt wall mount with arms, 17" to 42" display
<a href="#">DWTPSC4555M</a>	\$5	Heavy-duty tilt portrait wall mount, 45" to 55" display
<a href="#">DWFPC4570M</a>	\$3	Heavy-duty fixed portrait wall mount, 45" to 70" display
<a href="#">DMCS1732S</a>	\$5	Mobile workstation with monitor mount, 17" to 32" display
<a href="#">DMCSD3545M</a>	\$20	Rolling monitor stand, dual display, 2 x 35" to 45" displays
<a href="#">DMCS3270XP</a>	\$20	Rolling monitor stand, 32" to 70" display
<a href="#">DMCS3770L</a>	\$5	Rolling monitor stand, 37" to 70" display
<a href="#">DMCS60100XX</a>	\$30	Rolling monitor stand, 60" to 100" display

\*Instant rebates available through 9/30/19. Some accounts excluded.



### Cooling—\$20 INSTANT REBATE

Model	Instant Rebate*	Description
<a href="#">SRCOOL12K</a>	\$20	12K BTU portable cooling unit

\*Instant rebates available through 9/30/19. Some accounts excluded.



## KVMs—INSTANT REBATES UP TO \$30

Model	Instant Rebate*	Description
<a href="#">B002-DV1A2</a>	\$10	2-port secure KVM switch, DVI to DVI
<a href="#">B002-DP2AC4</a>	\$30	4-port secure KVM switch, DisplayPort to DisplayPort

\*Instant rebates available through 9/30/19. Some accounts excluded.



## Network Connectivity—INSTANT REBATES UP TO \$8

Model	Instant Rebate*	Description
<a href="#">N052-P24</a>	\$1.50	24-port Cat5e patch panel, PoE+ compliant
<a href="#">N252-P24</a>	\$1.50	24-port Cat6 patch panel, PoE+ compliant
<a href="#">N785-P01-LC-MM1</a>	\$8	Gigabit multimode fiber to Ethernet converter, LC connector, 550 m, PoE+ compliant
<a href="#">N785-P01-SC-MM1</a>	\$3	Gigabit multimode fiber to Ethernet converter, SC connector, 550 m, PoE+ compliant
<a href="#">N785-P01-SC-MM2</a>	\$6	Gigabit multimode fiber to Ethernet converter, SC connector, 2 km, PoE+ compliant
<a href="#">NPOE-30W-1G</a>	\$1.50	Gigabit PoE+ midspan active injector
<a href="#">P006-010</a>	\$0.50	AC power cable, 5-15P to C13, 10 ft., black

\*Instant rebates available through 9/30/19. Some accounts excluded.



## Digital Signage Connectivity—INSTANT REBATES UP TO \$5

Model	Instant Rebate*	Description
<a href="#">B118-002-UHD</a>	\$4	2-port 4K 3D HDMI splitter
<a href="#">B118-004-UHD</a>	\$2	4-port 4K 3D HDMI splitter
<a href="#">B118-008-UHD</a>	\$5	8-port 4K 3D HDMI splitter
<a href="#">P116-003-HD-U</a>	\$2	VGA to HDMI converter adapter
<a href="#">P134-000</a>	\$0.72	DisplayPort to DVI cable adapter
<a href="#">P134-06N-VGA</a>	\$2.50	DisplayPort to VGA active adapter cable, 6 in.
<a href="#">P136-06N-HDV-4K</a>	\$2	DisplayPort 1.2 to VGA/DVI/HDMI all-in-one adapter
<a href="#">P136-06N-UHD-V2</a>	\$1.50	DisplayPort 1.2 to HDMI active converter, 6 in.
<a href="#">P137-000-VGA</a>	\$3	Mini DisplayPort 1.2 to active VGA adapter
<a href="#">P137-06N-DVI</a>	\$0.75	Mini DisplayPort to DVI adapter cable, 6 in., white
<a href="#">P137-06N-DVIB</a>	\$0.75	Mini DisplayPort to DVI adapter cable, 6 in., black
<a href="#">P137-06N-HDMI</a>	\$0.50	Mini DisplayPort to HDMI adapter cable, 6 in.
<a href="#">P137-06N-VGA</a>	\$0.50	Mini DisplayPort to active VGA adapter, 6 in.
<a href="#">P566-006</a>	\$0.65	HDMI to DVI adapter cable, 6 ft.
<a href="#">P568-003</a>	\$0.20	High-speed HDMI cable, 3 ft.
<a href="#">P568-003-2A</a>	\$0.34	High-speed HDMI 2.0a cable, 3 ft.
<a href="#">P568-006-2A</a>	\$0.40	High-speed HDMI 2.0a cable, 6 ft.
<a href="#">P568-010</a>	\$0.50	High-speed HDMI cable, 10 ft.
<a href="#">P568-010-2A</a>	\$0.54	High-speed HDMI 2.0a cable, 10 ft.
<a href="#">P568-015-2A</a>	\$0.72	High-speed HDMI 2.0a cable, 15 ft.
<a href="#">P568-01M-2A</a>	\$0.34	High-speed HDMI 2.0a cable, 1 m
<a href="#">P568-02M-2A</a>	\$0.50	High-speed HDMI 2.0a cable, 2 m
<a href="#">P568-03M-2A</a>	\$0.54	High-speed HDMI 2.0a cable, 3 m
<a href="#">P569-003</a>	\$0.30	High-speed HDMI cable with Ethernet, 3 ft.
<a href="#">P569-006</a>	\$1	High-speed HDMI cable with Ethernet, 6 ft.
<a href="#">P580-003</a>	\$0.50	DisplayPort cable with latches, 3 ft.
<a href="#">P581-003-VGA</a>	\$1.50	DisplayPort to active VGA cable, 3 ft.
<a href="#">P581-006-VGA</a>	\$2.25	DisplayPort to active VGA cable, 6 ft.
<a href="#">P581-006-VGA-V2</a>	\$1.25	DisplayPort 1.2 to active VGA cable, 6 ft.
<a href="#">P583-006-BK</a>	\$0.50	Mini DisplayPort to 4K DisplayPort adapter, 6 ft.



\*Instant rebates available through 9/30/19. Some accounts excluded.

## USB Solutions—INSTANT REBATES UP TO \$5

Model	Instant Rebate*	Description
<a href="#">M100-003-GY-MAX</a>	\$1	Heavy-duty USB-A to lightning cable, 3 ft.
<a href="#">M100-006-GY-MAX</a>	\$1	Heavy-duty USB-A to lightning cable, 6 ft.
<a href="#">U038-003-GY-MAX</a>	\$0.30	Heavy-duty USB-A to USB-C cable, 3 ft.
<a href="#">U038-006-GY-MAX</a>	\$0.40	Heavy-duty USB-A to USB-C cable, 6 ft.
<a href="#">U050-003-GY-MAX</a>	\$1	Heavy-duty USB-A to USB Micro-B cable, 3 ft.
<a href="#">U050-006-GY-MAX</a>	\$1	Heavy-duty USB-A to USB Micro-B cable, 6 ft.
<a href="#">U209-000-R</a>	\$0.50	USB-A to serial adapter, 5 ft.
<a href="#">U209-005-COM</a>	\$1	USB to serial adapter cable, 5 ft.
<a href="#">U280-002-W12</a>	\$1	2-port USB wall travel charger
<a href="#">U280-007-CQC-ST</a>	\$1.50	7-port USB Quick Charge 3.0 charging station
<a href="#">U344-001-HDMI-R</a>	\$3	USB 3.0 to HDMI dual monitor external video graphics card adapter
<a href="#">U360-004-4A-AL</a>	\$1.50	4-port USB 3.0 slim hub
<a href="#">U360-004-MINI</a>	\$2.50	4-port USB 3.0 portable hub
<a href="#">U360-007</a>	\$5	7-port USB 3.0 hub
<a href="#">U436-06N-GB</a>	\$0.50	USB-C to Gigabit network adapter

\*Instant rebates available through 9/30/19. Some accounts excluded.



## USB-C Solutions—INSTANT REBATES UP TO \$11

Model	Instant Rebate*	Description
<a href="#">U442-DOCK10-S</a>	\$2	Docking station, USB-C to 4K HDMI, USB-A, micro SD, PD charging
<a href="#">U442-DOCK11-S</a>	\$11	Docking station, USB-C to 4K HDMI, USB-A, SD/micro SD, Ethernet, PD charging
<a href="#">U444-003-DP-BE</a>	\$2	USB-C to DisplayPort adapter cable, 3 ft.
<a href="#">U444-003-H4K6BE</a>	\$2	USB-C to 4K @ 60 Hz HDMI adapter cable, 3 ft.
<a href="#">U444-003-H4K6BM</a>	\$2	USB-C to 4K @ 60 Hz HDMI adapter cable, 3 ft.
<a href="#">U444-003-H4K6WE</a>	\$2	USB-C to 4K @ 60 Hz HDMI adapter cable, white, 3 ft.
<a href="#">U444-006-DP</a>	\$2	USB-C to DisplayPort cable, 6 ft.
<a href="#">U444-006-DP-BE</a>	\$2	USB-C to DisplayPort adapter cable, 6 ft.
<a href="#">U444-006-H4K6BE</a>	\$2	USB-C to 4K @ 60 Hz HDMI adapter cable, 6 ft.
<a href="#">U444-006-H4K6BM</a>	\$2	USB-C to 4K @ 60 Hz HDMI adapter cable, 6 ft.
<a href="#">U444-006-H4K6WE</a>	\$2	USB-C to 4K @ 60 Hz HDMI adapter cable, white, 6 ft.
<a href="#">U444-06N-HDV4KB</a>	\$2	USB-C to HDMI/DVI/VGA adapter

\*Instant rebates available through 9/30/19. Some accounts excluded.



Order from participating resellers:

