

# Tripp Lite Digital Tower Line-Interactive UPS Systems





Multifunction LCD Status Screen

## Reliable Power and Advanced Protection for Computers and Electronics

Featuring a multifunction LCD status screen and a compact tower form factor, Tripp Lite's Digital Tower UPS Systems provide reliable power and advanced protection for a wide range of home and office electronics, including computer systems and audio/video components.

### **Key Features**

- Multifunction LCD screen shows real-time power data, including input/output voltage, input/output frequency, battery charge level, battery voltage, estimated runtime remaining, connected equipment load level, connected equipment wattage and protection status
- Load capacity up to 1500 VA can support a small office or home theater setup
- Automatic Voltage Regulation (AVR) protects equipment by adjusting abnormal voltages to safe levels
- Reliable battery backup supports a desktop computer for up to 90 minutes during power failures (75W load)
- Surge protection and EMI/RFI noise filtering prevent equipment damage and malfunctions
- Tel/Ethernet (RJ45) jacks protect telephone, fax, modem, DSL or network connections
- Coaxial jacks protect cable, satellite or DVR connections
- HID-compliant USB port and free PowerAlert data-saving software enable unattended system shutdown and file saves during extended outages
- 3-year limited warranty

#### **Feature Focus**





- A Multifunction LCD
- **B** Power Button
- **O** USB Port

- Surge-Only Outlets
- **Battery-Protected Outlets**
- Tel/Ethernet Jacks

- **G** Coaxial Jacks
- H Circuit Breaker

#### **SPECIFICATIONS**







Model:	SMART1300LCDT	OMNI1500LCDT	SMART1500LCDT
Load Capacity:	1300 VA/720 W	1500 VA/810 W	1500 VA/900 W
Outlets (NEMA 5-15R):	8 (4 battery-supported, 4 surge-only)	10 (5 battery-supported, 5 surge-only)	10 (5 battery-supported, 5 surge-only)
Nominal AC Input:	120 V, 60 Hz	120 V, 50/60 Hz	120 V, 50/60 Hz
Input Plug Type:	NEMA 5-15P	NEMA 5-15P	NEMA 5-15P
Input Cord Length:	6 ft. (1.8 m)	6 ft. (1.8 m)	6 ft. (1.8 m)
Desktop Computer Runtime:	64 minutes (75 W)	55 minutes (75 W)	90 minutes (75 W)
½ Load Runtime:	10 minutes (360 W)	7.5 minutes (405 W)	10 minutes (450 W)
Communication Ports:	USB (HID-compliant)	USB (HID-compliant)	USB (HID-compliant)
Data Line Protection:	Tel/Ethernet and Coaxial	Tel/Ethernet and Coaxial	Tel/Ethernet and Coaxial
Ultimate Lifetime Insurance:*	\$250,000	\$250,000	\$250,000
Unit Dimensions:	8 x 5.75 x 15.4 in. (203 x 146 x 391 mm)		
Standards Compliance:	Tested to UL 1778 (USA), CSA (Canada), NOM (Mexico), FCC A (EMI), RoHS		

<sup>\*</sup> Ultimate Lifetime Insurance is valid in the U.S., Canada and Puerto Rico. Go to www.tripplite.com for complete terms and conditions.

Tripp Lite manufactures more than 2,500 IT infrastructure solutions for data centers, server rooms, network closets, office, home and other applications. Go to www.tripplite.com for more information.



