TRIPPILITE Hospital-Grade Power Cords

## **Safe Connections for Healthcare Settings**



**HG Power Cords** Green dots on the NEMA 5-15P plug indicate the cord is hospital grade.



HG Power Cords with **Clear Connectors** Clear connectors allow inspection of internal components.



Coiled HG Power Cord P006-C08-HG10 coiled cord resists tangles and saves space.



HG Power Cords with Locking C13 Connector C13 connector has a locking design to resist accidental disconnection from equipment, even during frequent repositioning.

Tripp Lite's hospital-grade power cords provide a safe solution for powering electronics in medical facilities. The cords connect computers, scanners, lab equipment, mobile carts and other medical equipment to a grounded hospital-grade AC outlet. Ideal as replacements for old or lost cords, these hospital-grade power cords meet stringent standards to help protect patients and staff from shock hazards. All models have a lifetime limited warranty.

## **Key Features**

- Cords are tested to ANSI/UL 62 and 817 and CAN/CSA C22.2 no. 21 and 49 to safely provide power.
- NEMA 5-15P plugs have green dots and are clearly marked "Hospital Grade" for easy identification.
- SJT jacket and fully molded connectors provide durability and long service life.

Model	Nominal AC Voltage	Maximum Input Amps	Wire Gauge	Male Connector	Female Connector	Connector Color	Cord Length
HG POWER CORDS	Voltage	input Amps	Gauge	connector	Connector	COIOI	Length
P006-003-HG10	125V	10A	18 AWG	5-15P HG	C13	Black	2 ft (1)
							3 ft. (1 m)
P006-006-HG10	125V	10A	18 AWG	5-15P HG	C13	Black	6 ft. (1.8 m)
P006-C08-HG10	125V	10A	18 AWG	5-15P HG	C13	Black	8 ft. (2.4 m) Coiled*
P006-010-HG10	125V	10A	18 AWG	5-15P HG	C13	Black	10 ft. (3 m)
P006-015-HG10	125V	10A	18 AWG	5-15P HG	C13	Black	15 ft. (4.6 m)
P006-025-HG15	125V	15A	14 AWG	5-15P HG	C13	Black	25 ft. (7.6 m)
HG POWER CORDS WITH	CLEAR CONNEC	TORS					
P006-003-HG13CL	125V	13A	16 AWG	5-15P HG	C13	Clear	3 ft. (1 m)
P006-006-HG13CL	125V	13A	16 AWG	5-15P HG	C13	Clear	6 ft. (1.8 m)
P006-010-HG13CL	125V	13A	16 AWG	5-15P HG	C13	Clear	10 ft. (3 m)
P006-015-HG13CL	125V	13A	16 AWG	5-15P HG	C13	Clear	15 ft. (4.6 m)
NEW! HG POWER CORE	S WITH LOCKING	C13 CONNECTOR	2				
P006-L03-HG10	125V	10A	18 AWG	5-15P HG	Locking C13	Black	3 ft. (1 m)
P006-L06-HG10	125V	10A	18 AWG	5-15P HG	Locking C13	Black	6 ft. (1.8 m)
P006-L10-HG10	125V	10A	18 AWG	5-15P HG	Locking C13	Black	10 ft. (3 m)
P006-L15-HG10	125V	10A	18 AWG	5-15P HG	Locking C13	Black	15 ft. (4.6 m)
P006-L25-HG15	125V	15A	14 AWG	5-15P HG	Locking C13	Black	25 ft. (7.6 m)

led cord resists tangles and takes up less space than a standard 8 ft. core

## Learn more about Tripp Lite's full line of hospital-grade solutions at www.tripplite.com.

