



Powering and Connecting Your World

NEW PRODUCT ANNOUNCEMENT

Mobile Interactive Display

Promote Collaboration and Communication with an All-in-One Presentation Platform



Tripp Lite's Mobile Interactive Display integrates a 4K touchscreen, HD webcam and wireless networking to connect local and remote teams.

Perfect for:

Conference rooms, classrooms, huddle spaces and improvised meeting areas.

Tripp Lite's Mobile Interactive Display, DMCSTP65CBP, enables dynamic presentations and encourages group collaboration and communication in everything from brainstorming sessions to distance learning. The display integrates a 65-inch 4K touchscreen, built-in PC, heavy-duty mobile stand and rechargeable lithium-ion battery system.

A high-definition webcam and wireless networking connect local and remote teams in corporate, education, healthcare, commercial, hospitality, retail and government settings. Users can share ideas from any location, allowing organizations with work-from-home strategies to thrive. The display can be rolled wherever it is needed and operated on battery power if required.

Key Benefits

DYNAMIC INTERACTIVITY

- Patented touchscreen technology provides a low-latency, ultra-fast response to your fingers or the included stylus pens.
- The touchscreen detects up to 20 simultaneous touch points to accommodate multiple users.

AUDIOVISUAL EXCELLENCE

- 65-inch 4K flat-panel display and built-in 40-watt speaker system provide a best-in-class experience.

VERSATILE COMPATIBILITY

- Embedded Android operating system and built-in touch-enabled Windows 10 PC provide a flexible presentation platform.
- The display is compatible with a wide array of applications and hardware, including Windows, Android, Chrome, iOS and MacOS devices.

COLLABORATIVE COMMUNICATION

- Wireless networking allows anyone to participate in meetings and presentations from any location.
- Detachable 1080p webcam with wide-angle view captures the entire meeting area.
- Remote screen sharing capability increases opportunities for audience engagement.

EFFORTLESS MOBILITY

- Heavy-duty 4-inch swivel casters provide smooth rolling for easy resource sharing; locks keep the stand in position while at rest.
- Lithium-ion battery system supports up to 90 minutes of use without plugging into a wall outlet, providing placement flexibility.

Feature Focus



A HD Webcam

Detachable HD webcam with noise-canceling microphone supports 1080p video resolutions.



B 4K Touchscreen

65-inch touchscreen works with your fingers or the included stylus pens.



C Wi-Fi Connectivity

The display includes antennas for connection to a wireless network.



D Rechargeable Battery System

A lithium-ion battery provides up to 90 minutes of power when a wall outlet is not available.




E Heavy-Duty Casters

4-inch swivel casters with locks enable smooth rolling.



Input & Output Ports



Front and rear panels feature connections for peripherals and video sources. See Specifications below.

Remote Control

Use the remote control to access the touchscreen display. Front-panel buttons and on-screen display menus offer other control options.



Stylus Pens

Two pens and replacement tips are included.



SPECIFICATIONS

MODEL: DMCSTP65CBP

Screen Size	65 in.
Maximum Video Resolution	3840 x 2160 (4K x 2K) @ 60 Hz
Number of Touch Points	20
Input Ports	Front: HDMI; USB 2.0; USB for touch Rear: (3) HDMI; DisplayPort; VGA; USB for camera; (3) USB 2.0 – Android only; (2) USB 2.0; (2) USB 3.0; (2) USB for touch; (3) 3.5 mm audio
Output Ports	Rear: (2) HDMI; (2) 3.5 mm stereo audio
Ethernet Interface	(2) RJ45 (100 Mbps)
Serial Interface	RS-232 (DB9)
Wireless Interface	4 large antennas, 2 small antennas

See triplite.com for compliance information. * Runtime varies depending on load and other conditions.

Control Options	Remote control, front-panel buttons, on-screen menus/touch input
Display Height Adjustment (Above the Floor)	47 to 65 in.
Tilt Adjustment	-10° to +5°
Input Voltage	120V
Input Plug/Cord Lg.	NEMA 5-15P/6 ft.
Mobile Power Source	Lithium iron phosphate (LFP) battery
Battery Runtime*	Up to 90 minutes
Overall H x W x D	91.1 (max.) x 58.7 x 27.6 in.
Limited Warranty	2 Years



Learn more about Tripp Lite's
Mobile Interactive Display at triplite.com.



Tripp Lite Corporate Headquarters
1111 West 35th Street, Chicago, IL 60609 USA
773.869.1773 | triplite.com