



EXCLUSIVE NEW PRODUCTS!
PDUs with Surge Protection

Network-Grade Metered PDUs with Best-in-Class Isobar Surge Protection



PDUMH20-ISO
(front and back)



The new models add premium Isobar surge protection to Tripp Lite's field-proven line of network-grade rack PDUs.

Reliable Power Distribution with Best-in-Class Surge Protection

In a small IT installation like a network cabinet, you may decide that battery backup isn't a priority. Or you may not have space in your rack or your budget for a UPS system. But that doesn't mean you need to leave your equipment completely exposed to power problems like damaging transient surges and disruptive EMI/RFI line noise.

Tripp Lite's newest metered rack PDUs add 3,840 joules of Isobar® surge protection to 14 network-grade outlets. Metered PDUs with surge protection combine the best features of two of Tripp Lite's most popular product lines in a compact 1U housing that's a perfect fit for a wide range of IT applications.

Key Features



PDUMH20-ISO



PDUMH15-ISO

- A** NEMA 5-15R Outlets
- B** NEMA 5-15/20R Outlets
- C** Load Meter
- D** Surge Status LEDs
- E** Detachable Mounting Ears
- F** Circuit Breaker
- G** Ground Connection
- H** 15 ft. Input Cord

Specifications



Model	Surge Rating	Nominal AC Voltage (50/60 Hz)	Max Input Current	Load Meter	Input Plug Type	Input Cord Length	Outlets (Type)	On/Off Switch
1U Metered PDUs with Isobar Surge Protection								
PDUMH15-ISO	3,840 J	120V (100-127V)	15A ^(A)	Yes	5-15P	15 ft.	14 (5-15R)	None
PDUMH20-ISO	3,840 J	120V (100-127V)	20A ^(A)	Yes	L5-20P / 5-20P ^(B)	15 ft.	14 (2 5-15R, 12 5-15/20R)	None
1U Isobar Surge Protectors								
ISOBAR12ULTRA	3,840 J	120V (110-125V)	15A	No	5-15P	15 ft.	12 (5-15R)	Covered
IBAR12-20T	3,840 J	120V (110-125V)	20A	No	L5-20P	15 ft.	12 (2 5-15R, 10 5-15/20R)	Covered
IBAR12-20ULTRA	3,840 J	120V (110-125V)	20A	No	5-20P	15 ft.	12 (2 5-15R, 10 5-15/20R)	Covered
1U Economy Surge Protector								
DRS-1215	3,000 J	120V (110-125V)	15A	No	5-15P	15 ft.	14 (5-15R)	Covered

Accessories

PDUSIDEBRKT	Mounts compatible 1U PDUs vertically.	P006-004-RD	4 ft. 5-15P to C13 cord (10A, 18 AWG).	P007-010	10 ft. 5-15P to C13 cord (15A, 14 AWG).
P006-003	3 ft. 5-15P to C13 cord (10A, 18 AWG).	P006-004-YW	4 ft. 5-15P to C13 cord (10A, 18 AWG).	P034-010	10 ft. 5-15P to C19 cord (15A, 14 AWG).
P006-004	4 ft. 5-15P to C13 cord (10A, 18 AWG).	P007-002	2 ft. 5-15P to C13 cord (15A, 14 AWG).	P049-010	10 ft. 5-20P to C19 cord (20A, 12 AWG).
P006-004-BL	4 ft. 5-15P to C13 cord (10A, 18 AWG).	P007-003	3 ft. 5-15P to C13 cord (15A, 14 AWG).	P350-10N-10	10-pack of 10 in. hook-and-loop cable ties.
P006-004-GN	4 ft. 5-15P to C13 cord (10A, 18 AWG).	P007-006	6 ft. 5-15P to C13 cord (15A, 14 AWG).	P352-07N-100	100-pack of 7.5 in. nylon zip ties.

(A) Agency-derated to 80% of maximum. (B) Includes an adapter to convert the twist-lock L5-20P plug to a straight-blade 5-20P plug.

Tripp Lite manufactures more than 3,000 IT infrastructure solutions for data centers, server rooms, network closets and other applications. Visit www.tripplite.com for more information.

© 2015 Tripp Lite. All trademarks are the sole property of their respective owners. Photos may differ slightly from actual products. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

