

SMARTONLINE® UNITY PF UPS — INDUSTRY-LEADING VALUE



You buy a UPS to avoid problems, so it's maddening when it actually causes headaches, backaches and even downtime. Finally, there's an intelligent, networked UPS that lightens your workload while protecting critical equipment from unexpected power loss:

- Smart batteries provide accurate runtime data throughout their lifespan
- Batteries also record first-use date for proactive battery replacement alerts that prevent battery failure downtime
- Self-aligning blind-mate connections for batteries and bypass PDUs enable lighter, easier single-person installation and maintenance without downtime or need for electrician assistance
- Controllable outlet banks with programmable auto-probe feature provide remote automated load control for self-healing device reboots and runtime prioritization during outages

5kVA Power Value Ratio: Tripp Lite vs. Channel Competitors

Model	Estimated Street Price (USD)	Watts	Full-Load Runtime (min.)	Half-Load Runtime (min.)	Rack Size	120V XFMR	Maint. Bypass	Power Value Ratio (Longer Bars Are Better) = (Full-Load Runtime + Half-Load Runtime) x Watts ÷ Estimated Street Price	
Tripp Lite – All models feature unity (1.0) power factor, pure sine wave output, ENERGY STAR® 2.0, SNMP card, easy-access management console, temperature-compensated charging and front-panel LCD.									
SU5KRT3UHV	4000	5000	5.0	14.0	3U	No	No	23.75	<div style="width: 85%;"></div>
SU5KRT3UHVMB	4725	5000	5.0	14.0	3U	No	Yes	20.11	<div style="width: 75%;"></div>
SU5KRT3JTF	4800	5000	5.0	14.0	5U	Yes	No	19.79	<div style="width: 70%;"></div>
SU5KRT3JTFMB	5775	5000	5.0	14.0	5U	Yes	Yes	16.45	<div style="width: 55%;"></div>
SU5KRT3UG	3725	5000	5.0	14.0	3U	No	No	25.50	<div style="width: 90%;"></div>
SU5KRT3UGMB	4500	5000	5.0	14.0	3U	No	Yes	21.11	<div style="width: 80%;"></div>
SU5KRT3UHW	3425	5000	5.0	14.0	3U	No	No	27.74	<div style="width: 95%;"></div>
SU5KRT3UHWMB	4125	5000	5.0	14.0	3U	No	Yes	23.03	<div style="width: 85%;"></div>
SU5KRT3UX	3625	5000	5.0	14.0	3U	No	No	26.21	<div style="width: 90%;"></div>
APC®									
SRT5KRMXLT	4800	4800	3.5	10.7	3U	No	No	14.20	<div style="width: 60%;"></div>
SRT5KRMXLT-5KTF	5350	4800	3.5	10.7	5U	Yes	No	12.74	<div style="width: 50%;"></div>
SRT5KRMXLTUS	4925	4800	3.5	10.7	3U	No	No	13.84	<div style="width: 55%;"></div>
SRT5KRMXLT-IEC	4775	4800	3.5	10.7	3U	No	No	14.27	<div style="width: 60%;"></div>
SRT5KXLT	4500	4800	3.5	10.7	Tower	No	No	15.15	<div style="width: 65%;"></div>
SRT5KXLT-5KTF	5300	4500	4.0	11.8	Tower	Yes	No	13.42	<div style="width: 55%;"></div>
SRT5KXLTUS	4775	4800	3.5	10.7	Tower	No	No	14.27	<div style="width: 60%;"></div>
SRT5KXLT-IEC	4650	4800	3.5	10.7	Tower	No	No	14.66	<div style="width: 65%;"></div>
SRT5KRMXLW-HW	4900	4500	4.0	11.8	3U	No	No	14.51	<div style="width: 60%;"></div>
SRT5KXLI	4525	4500	4.0	11.8	Tower	No	No	15.71	<div style="width: 65%;"></div>
Eaton®									
9PX5K	4250	4500	3.0	10.0	3U	No	No	13.76	<div style="width: 55%;"></div>
9PX5KTF5	5000	4500	3.0	10.0	6U	Yes	No	11.70	<div style="width: 45%;"></div>
9PX5KP1	5125	4500	3.0	10.0	6U	Yes	XFMR	11.41	<div style="width: 45%;"></div>
9PX5KP2	5125	4500	3.0	10.0	6U	Yes	XFMR	11.41	<div style="width: 45%;"></div>
CyberPower®									
OL5KRTHD	3875	5000	2.3	6.4	2U	No	No	11.23	<div style="width: 40%;"></div>



Powering and Connecting Your World

See Next Page for 6kVA Models

SMARTONLINE® UNITY PF UPS — INDUSTRY-LEADING VALUE



- Add one or more smart external battery packs for extended runtime ([BP192V12RT3US](#) – 3U Rack BP)
- 4-post rack-mounting hardware included; 2-post rack-mounting hardware available*
- Add [2-9USTAND](#) for tower
- Add [SU30ACORD](#) to convert hardwire-only input to L6-30P

* Order [2POSTRMKITWM](#) for models without "MB" suffix.
Order [2POSTRMKITMB](#) for models with "MB" suffix.
Add an extra [2POSTRMKITWM](#) for all 5U models.

6kVA Power Value Ratio: Tripp Lite vs. Channel Competitors

Model	Estimated Street Price (USD)	Watts	Full-Load Runtime (min.)	Half-Load Runtime (min.)	Rack Size	120V XFMR	Maint. Bypass	Power Value Ratio (Longer Bars Are Better) = (Full-Load Runtime + Half-Load Runtime) x Watts ÷ Estimated Street Price	
Tripp Lite – All models feature unity (1.0) power factor, pure sine wave output, ENERGY STAR® 2.0, SNMP card, easy-access management console, temperature-compensated charging and front-panel LCD.									
SU6KRT3UHV	4300	6000	3.0	8.5	3U	No	No	16.05	
SU6KRT3UHVMB	5050	6000	3.0	8.5	3U	No	Yes	13.66	
SU6KRT3UJTF	5400	6000	3.0	8.5	5U	Yes	No	12.78	
SU6KRT3UJTFMB	6075	6000	3.0	8.5	5U	Yes	Yes	11.36	
SU6KRT3UG	4000	6000	3.0	8.5	3U	No	No	17.25	
SU6KRT3UGMB	4725	6000	3.0	8.5	3U	No	Yes	14.60	
SU6KRT3UHW	3700	6000	3.0	8.5	3U	No	No	18.65	
SU6KRT3UHWMB	4325	6000	3.0	8.5	3U	No	Yes	15.95	
SU6KRT3UJX	3900	6000	3.0	8.5	3U	No	No	17.69	
SU6KRT3UJXMB	4625	6000	3.0	8.5	3U	No	Yes	14.92	
APC®									
SRT6KRMXLT-IEC	5650	6000	2.3	8.3	4U	No	No	11.26	
SRT6KRMXLT-5KTF	5900	6000	2.3	8.3	6U	Yes	No	10.78	
SRT6KXLT	5175	6000	2.3	8.3	Tower	No	No	12.29	
SRT6KXLTUS	5450	6000	2.3	8.3	Tower	No	No	11.67	
SRT6KXLT-IEC	5325	6000	2.3	8.3	Tower	No	No	11.94	
SRT6KXLT-5KTF	6150	6000	2.3	8.3	Tower	Yes	No	10.34	
SRT6KRMXLI	5400	6000	2.5	8.7	4U	No	No	12.44	
SRT6KXLI	5325	6000	2.5	8.7	Tower	No	No	12.62	
Eaton®									
9PX6K	4675	5400	3.0	8.0	3U	No	No	12.71	
9PX6KUS	5575	5400	3.0	8.0	3U	No	No	10.65	
9PX6K-10	4875	5400	3.0	8.0	3U	No	No	12.18	
9PX6KTF5	5425	5400	3.0	8.0	6U	Yes	No	10.95	
9PX6KP1	5575	5400	3.0	8.0	6U	Yes	XFMR	10.65	
9PX6KP2	5575	5400	3.0	8.0	6U	Yes	XFMR	10.65	
CyberPower®									
OL6KRTHD	4200	6000	1.4	4.9	2U	No	No	9.00	



Powering and Connecting Your World

presaleshelp@tripplite.com
773.869.1773 | tripplite.com