



SmartRack™ Premium Rack Solutions

Best Value

Highly competitive pricing makes them easy to attach to sales of servers and network equipment

Quick

Toolless keyhole mounting speeds installation of PDUs and cable managers

Easy

Easy indexing system simplifies vertical mounting rail adjustment

Versatile

Guaranteed compatibility with all EIA-310 compliant 19 in. rackmount equipment

Durable

Load capacity up to 3,000 lb stationary and 2,250 lb rolling.



SRW12US

SR42UB

SR42UBCL

Enclosure Types

- Standard (-UB)**
 With removable doors and side panels. Ship fully assembled.
- Expansion (-UBEXP)**
 Like standard models, but without side panels. For buying applications.
- Colocation (-UBCL)**
 With two compartments and separate, lockable doors.
- Wide (-UBWD)**
 29.5 in. (750 mm) width keeps PDUs and cables from blocking airflow.
- Knockdown (-UBKD)**
 In sections for easy transport and quick assembly in tight spaces.
- Shock Pallet (-UBSP1)**
 1,250 lb capacity pallet and ramps for pre-configuration and reshipment.
- Wall-Mount (SRW12US)**
 Mounts to walls or fits under desks in offices with limited floor space.

Model	Rack Space	Enclosure Type
SmartRack Enclosures		
SRW12US	12U	Wall-Mount
SR25UB	25U	Standard
SR25UBKD	25U	Knockdown
SR25UBSP1	25U	Shock Pallet
SR42UB	42U	Standard
SR42UBCL	42U	Colocation
SR42UBEXP	42U	Expansion
SR42UBKD	42U	Knockdown
SR42UBSP1	42U	Shock Pallet
SR42UBWD	42U	Wide
SR48UB	48U	Standard
SR48UBCL	48U	Colocation
SR48UBEXP	48U	Expansion
SR48UBKD	48U	Knockdown
SR48UBSP1	48U	Shock Pallet
SmartRack Open Frame Racks		
SR2POST	45U	2-Post; 800 lb Capacity
SR2POST25	25U	2-Post; 800 lb Capacity
SR4POST	45U	4-Post; 1,000 lb Capacity
SR4POST13	13U	4-Post; 1,000 lb Capacity

Customize Your Rack Solution with Tripp Lite's Full Line of Accessories (See Reverse)

For More Information:
Contact Your Tripp Lite Representative





Rack Accessories

Tripp Lite Rack Accessory Compatibility Matrix

		Compatibility			
		2-Post Open Frame Racks	4-Post Open Frame Racks	Wall-Mount Enclosure	25/42/48U Enclosures
Model	Description				
Airflow Optimization / Cooling Accessories					
SRFAN3U	3U Fan Panel – 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	✓	✓	✓	✓
SRXFAN3U	3U Fan Panel – 230V (3 high-performance fans; 210 CFM; C14 inlet.)	✓	✓	✓	✓
SRFANROOF	Roof-Mounted Fan Panel – 120V (6 high-performance fans; 420 CFM; 5-15P plug; toolless mounting.)				✓
SRXFANROOF	Roof-Mounted Fan Panel – 230V (6 high-performance fans; 420 CFM; C14 inlet; toolless mounting.)				✓
SR1UPANEL10	1U Blanking Panel Kit (10 pieces; toolless mounting.)		✓	✓	✓
SR1UPANEL50	1U Blanking Panel Kit (50 pieces; toolless mounting.)		✓	✓	✓
SR1UBRUSH	1U Cable Pass-Through Panel with Brush Strip (Brush strip blocks unwanted airflow.)	✓	✓	✓	✓
SRSKIRT	Rack Enclosure Skirt Kit (Brush strip blocks unwanted airflow at bottom.)				✓
SRGASKET	Airflow Optimization Kit (Prevents recirculation of warm air through side gaps.)				✓
Cable Management Accessories					
SRCABLERING1U	1U Horizontal Cable Manager (Flexible ring type.)	✓	✓	✓	✓
SRCABLERING2U	2U Horizontal Cable Manager (Flexible ring type.)	✓	✓	✓	✓
SRCABLEDUCT1U	1U Horizontal Cable Manager (Finger duct with cover.)	✓	✓	✓	✓
SRCABLEDUCTVRT	6 ft Vertical Cable Manager (Finger duct with cover; toolless mounting.)	✓	✓		✓
SRCABLERINGVRT	6 ft Vertical Cable Manager (Flexible ring type; toolless mounting.)	✓	✓		✓
SRCABLETRAY	Roof-Mounted Cable Trough (Provides cable routing and power/data cable segregation.)				✓
SRCABLETRAYEXP	Roof-Mounted Cable Trough – Vertical Expansion (Requires SRCABLETRAY.)				✓
SRCABLELADDER	10 ft x 1 ft Cable Ladder (Includes 2 sections; requires SRCABLETRAY.)	✓	✓		✓
PDUMVROTATEBRKT	Bracket allows vertical PDU outlets to face the rear of the rack enclosure for improved access and airflow.	✓	✓	✓	✓
P350-10N-10	10 in. x 5/8 in. Hook-and-Loop Cable Ties (10-pack.)	✓	✓	✓	✓
Mobility Accessory					
SRCASTER	Heavy-Duty Rolling Caster Kit (Includes 4 casters. Casters are included with 25/42/48U enclosures.)		✓	✓	✓
Mounting Accessories					
SRCAGENUTS	Square Hole Hardware Kit (Includes 50 cage nuts, screws and washers.)		✓	✓	✓
SRSCREWS	Threaded Hole Hardware Kit (Includes 50 #12-24 screws and washers.)	✓			
SREXTENDER	Rack Enclosure Extension Frame (Increases maximum mounting depth to 43.75 in.)				42/48U Only
2POSTRMKITWM	Universal 2-Post Rackmount Kit (Supports 2U to 4U UPS systems and battery packs.)	✓			
4POSTRAILKIT	4-Post Rack Rail Kit (Supports rackmount cabinets up to 250 lb.)		✓	✓	✓
UPSHDEARKIT	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb from front vertical rails.)	✓	✓	✓	✓
Security / Monitoring Accessories					
SRCOMBO	Door Handles with Combination Lock (2-pack for front and rear doors; includes bypass key.)				✓
SRSWITCH	Magnetic Door Switch Kit (2-pack for front and rear doors; requires ENVIROSENSE.)			✓	✓
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched/monitored PDU.)	✓	✓	✓	✓
SNMPWEBCARD	Adds network interface to UPS systems for remote monitoring and control via SNMP, Web or telnet.	✓	✓	✓	✓
Shelves					
SRSHELF2P	2U Cantilever Fixed Shelf (60 lb capacity; 18 in. depth.)	✓	✓	✓	✓
SRSHELF4PHD	Heavy-Duty Fixed Shelf (250 lb capacity; 26 in. depth.)		✓		✓
SRSHELF4PSLHD	Heavy-Duty Sliding Shelf (100 lb capacity; 26 in. depth.)		✓		✓
SRSHELF4PSL	Standard Sliding Shelf (50 lb capacity; 26 in. depth.)		✓		✓
SRSHELF4PKYBD	Keyboard Shelf (25 lb capacity; 16 in. depth.)		✓		✓
Stability Accessories					
SRBOLTDOWN	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	✓	✓		✓
SRSTABILIZE	Anti-Tip Stabilizing Plate Kit (Provides extra stability for standalone enclosures.)				✓
1U Rackmount Consoles (Include keyboard, touchpad and color LCD. Fold like a laptop and slide into 1U rack drawer for compact storage and easy access. Connect to KVM switch or server.)					
B021-000-17	Console with 17 in. color LCD. Includes PS/2 cable kit.	Add B019-000	✓	✓	✓
B021-000-19	Console with 19 in. color LCD. Includes PS/2 and USB cable kit.	Add B019-000	✓	✓	✓
1U Rackmount Console KVM Switches (Include KVM switch, keyboard, touchpad and color LCD. Fold like a laptop and slide into 1U rack drawer for compact storage and easy access.)					
B020-008-17	Console KVM with 17 in. color LCD and 8-port switch. Add P774-series cables for PS/2; add P776-series cables for USB.*	Add B019-000	✓	✓	✓
B020-016-17	Console KVM with 17 in. color LCD and 16-port switch. Add P774-series cables for PS/2; add P776-series cables for USB.*	Add B019-000	✓	✓	✓
B040-008-19	Console KVM with 19 in. color LCD and 8-port switch. Add P780-series cables for PS/2 or USB.*	Add B019-000	✓	✓	✓
B040-016-19	Console KVM with 19 in. color LCD and 16-port switch. Add P780-series cables for PS/2 or USB.*	Add B019-000	✓	✓	✓

* Add one cable kit per server connected. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. SmartRack is a trademark of Tripp Lite.

**For More Information:
Contact Your Tripp Lite Representative**

