









SOLUTIONS FOR PATIENT-CARE VICINITIES



Resident safety depends on compliance with regulations that govern the use of power strips in long-term care facilities.

With the adoption of the 2012 edition of the National Fire Protection Association® (NFPA) 101 - Life Safety Code (LSC) and the NFPA 99 - Health Care Facilities Code (HCFC), the Centers for Medicare and Medicaid Services (CMS) now allows power strips in resident rooms of long-term care facilities. This includes nursing-home and assisted-living-facility rooms that do not use line-operated electrical appliances for diagnostic, treatment or monitoring purposes (patient care vicinities).

Our products include hospital-grade plugs and outlets that meet UL 1449 (3rd Edition) and UL 1363 standards and are now allowed by CMS. These surge protectors and power strips are ideal for use with lamps, phone chargers, radios, TVs, stereos, PCs, printers and video game systems.

Plus, all Tripp Lite medical- and hospital-grade power strips and surge protectors now include a patented antimicrobial coating. This silver ionic coating meets JIS Z 2801:2000 standards and keeps patients and staff healthier by inhibiting the growth of bacteria that can lead to healthcare-acquired infections.









Specifications

•	The second secon	AND AND ADDRESS OF THE PARTY OF				
Model	Nominal AC Voltage/Amps	UL Compliance	Surge Protection Rating	AC Outlets	AC Input Cord Length	AC Input Plug Type
Hospital-Grade Surge Protectors (For use outside patient care vicinities only.)						
ISOBAR6ULTRAHG	120V/12A	UL 1363 & UL 1449 (3rd Ed.)	3,330 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS-615-HG	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS610HGRA	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	10 ft.	5-15P HG (Right Angle)
SPS606HGRA	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	6 ft.	5-15P HG (Right Angle)
Hospital-Grade Power Strips (For use outside patient care vicinities only.)						
PS-615-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	15 ft.	5-15P HG
PS-606-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	6 ft.	5-15P HG
PS-602-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	1.5 ft.	5-15P HG
PS-415-HG	120V/15A	UL 1363	n/a	4 (5-15R HG)	15 ft.	5-15P HG
Medical-Grade Power Strips for Patient Care Vicinities						
PS-406-HGULTRA	120V/15A	UL 60601-1 (1)	n/a	4 (5-15R HG)	6 ft.	5-15P HG
PS-415-HGULTRA	120V/15A	UL 60601-1 (1)	n/a	4 (5-15R HG)	15 ft.	5-15P HG
SPS415HGULTRA	120V/15A	UL 60601-1 (1)	1,410 joules	4 (5-15R HG)	15 ft.	5-15P HG
OEM-Series Power Strips for Mobile Applications In Patient Care Vicinities (Specialty-Purpose Relocatable Power Strips)						
PS625HG20AOEM	120V/20A	UL 1363A	n/a	6 (5-15/20R HG)	25 ft.	5-20P HG
PS615HG20AOEM	120V/20A	UL 1363A	n/a	6 (5-15/20R HG)	15 ft.	5-20P HG
PS607HG20AOEM	120V/20A	UL 1363A	n/a	6 (5-15/20R HG)	7 ft.	5-20P HG
PS-615-HG-OEM	120V/15A	UL 1363A	n/a	6 (5-15R HG)	15 ft.	5-15P HG
PS-607-HG-OEM	120V/15A	UL 1363A	n/a	6 (5-15R HG)	7 ft.	5-15P HG
PS-415-HG-OEM	120V/15A	UL 1363A	n/a	4 (5-15R HG)	15 ft.	5-15P HG
PS-407-HG-OEM	120V/15A	UL 1363A	n/a	4 (5-15R HG)	7 ft.	5-15P HG
PS-402-HG-OEM	120V/15A	UL 1363A	n/a	4 (5-15R HG)	2 ft.	5-15P HG
PS-410-HGOEMCC	120V/15A	UL 1363A	n/a	4 (5-15R HG)	3 to 10 ft. (2)	5-15P HG
PS410HGOEMX	120V/15A	UL 1363A	n/a	4 (5-15R HG)	10 ft.	5-15P HG
Hospital-Grade Surge Protectors for Administrative Vicinities (3,5) (Relocatable Power Strips with Surge Protection)						
ISOBAR6ULTRAHG	120V/15A	UL 1363 & UL 1449 (3rd Ed.)	3,330 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS-615-HG	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS606HGRA	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	6 ft. (4)	5-15P HG (Right Angle)
SPS610HGRA	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	10 ft. (4)	5-15P HG (Right Angle)
Medical-Grade USB Wall Charger for Patient Care Vicinities						
U280-001-W2-HG	120V/2.5A	UL 60601-1(1)	n/a	1 USB Port	n/a	1-15P
Accessories						
PSCLAMP	Pre-Assembled Locking Pole Mount Clamp. Compatible with Tripp Lite Medical-Grade Power Strips. Fits a diameter from 1" to 21/4".					
HGOUTLETCVR	Reusable locking safety covers prevent the connection of unauthorized devices—tool required for removal. Compatible with all NEMA 5-15R HG receptacles.					
PSHGCOVERKIT	Replacement duplex outlet covers for Tripp Lite medical-grade power strips and surge protectors. Includes 4 replacement covers and attachment hardware.					

All models have nominal 120V input/output, hospital-grade plug and hospital-grade outlets. Agency approved to UL standard shown; additional certifications vary by model. (1) Meets the standards of a medical device when installed properly. (2) Coiled cord. (3) Also suitable for use in other areas outside patient care vicinities. (4) Right-angle plug. (5) The models listed here are suggestions. Any hospital-grade solution in this flyer can be used in Administrative Areas.

For more information, contact:







