

STACK THE RACK

with Tripp Lite, Your One-Stop Shop



SOLUTIONS FOR EVERY NEED!

Network & Data Center | Government | Healthcare
Digital Signage | Education | Retail

SUBMIT BIDS!

Cables \$500 min. | \$2.5K Everything Else | \$10K to Register!

A RACKS

OVER 145 MODELS

- #1 wall-mount rack vendor
- 2U to 58U models available
- Wall-mount, open frame, colocation, extra-wide & -deep models
- Competitive pricing with 5-year warranties
- Custom solutions available

B COOLING SOLUTIONS

- #1 portable cooling vendor
- 2K & 7K BTU rack-mount; 12K, 18K & 24K portable & 33K BTU row-based units
- Zero-maintenance designs

C NETWORK SWITCHES

- Managed & unmanaged switches with up to 27 ports
- Select models feature built-in 12-outlet PDU
- Select models feature PoE+ (Power over Ethernet)

D CABLES & CONNECTIVITY

OVER 2,000 SOLUTIONS

- #2 cable vendor
- FireWire, Fiber Optic, Cat5e/6, Cat8
- SATA, SCSI, patch panels
- HDMI, VGA, DVI, DisplayPort
- Bids start as low as \$500
- Lifetime warranties & custom solutions

E UPS SYSTEMS

OVER 375 MODELS

- #2 UPS system vendor
- 300VA to 210kVA capacities
- Line-interactive & true on-line rack-mount models (single- & 3-phase)
- Expandable runtime options
- Up to \$250,000 insurance & 3-year warranties

F POWER DISTRIBUTION UNITS

OVER 180 MODELS

- #2 PDU vendor
- Basic, metered & networked (monitored & switched) models
- Patented ATS PDUs
- Select models feature built-in LX platform interface
- Custom solutions available

G KVM SWITCHES

OVER 80 MODELS

- #1 console KVM vendor
- 4-, 8-, 16-, 32- & 64-port models
- 1U rack-mount & rack/console designs, with or without IP remote access

See reverse for Tripp Lite's top-selling data center solutions.

TRIPP LITE DATA CENTER SOLUTIONS

UPS SYSTEMS

Tripp Lite Model	Output Capacity	Outlets + Ports
SmartPro® Rack-Mount UPS Systems—Advanced protection for servers		
SMART500RT1U	500VA/300W	7+USB+DB9
SMART750RM1U	750VA/600W	6+USB+DB9
SMART750RMXL2U	750VA/600W	6+USB+DB9
SMART1000RM1U	1000VA/800W	6+USB+DB9
SMART1000RM2U	1000VA/800W	6+USB+DB9
SMART1000RMXL2U	1000VA/900W	8+USB+DB9
SMART1500RM2U	1500VA/1350W	8+USB+DB9
SMART1500RMXL2UA	1500VA/1350W	8+USB+DB9
SMART2200RM2U	2200VA/1920W	8+USB+DB9
SMART2200RMXL2U	2200VA/1920W	8+USB+DB9
SMART3000RM2U	3000VA/2250W	9+USB+DB9
SMART3000RMXL2U	3000VA/2880W	9+USB+DB9
SMART5000RT3U	5000VA/4000W	14+(2) USB+(2) DB9
SmartOnline® Rack-Mount UPS Systems—Ideal for mission-critical equipment		
SU750RTLXL2U	750VA/600W	6+tel/Ethernet+USB+DB9
SU750RTLXCD2U	750VA/675W	6+tel/Ethernet+USB+DB9
SU1000RTLXL2UA	1000VA/800W	6+tel/Ethernet+USB+DB9
SU1000RTLXCD2U	1000VA/900W	6+tel/Ethernet+USB+DB9
SU1500RTLXL2UA	1500VA/1200W	6+tel/Ethernet+USB+DB9
SU1500RTLXCD2U	1500VA/1350W	6+tel/Ethernet+USB+DB9
SU2200RTLXL2UA	2200VA/1600W	7+tel/Ethernet+USB+DB9
SU2200RTLXCD2U	2200VA/1800W	7+tel/DSL+USB+DB9
SU3000RTLXL2U	3000VA/2700W	7+tel/Ethernet+USB+DB9
SU3000RTLXL3U	3000VA/2400W	9+tel/Ethernet+USB+DB9
SU3000RTLXR3U	3000VA/2400W	9+tel/Ethernet+USB+DB9
SU3000RTLXCD3U	3000VA/2700W	9+tel/Ethernet+USB+DB9
SU5000RT3U	5000VA/3500W	16+(2) DB9
SU6000RT4U	6000VA/4200W	12+USB+DB9
SU8000RT3U	8000VA/7200W	6+USB+DB9
SU8000RT4U	8000VA/5600W	8+Hardwire+USB+DB9
SU10000RT3U	10,000VA/9000W	6+Hardwire+DB9
SU10KRT3UHV	10,000VA/9000W	Hardwire+USB+(2) DB9
SU12000RT4U	12,000VA/8400W	13+Hardwire+USB+DB9
SU12000RT4UHW	12,000VA/8400W	Hardwire+USB+DB9
SU16000RT4U	16,000VA/11,200W	13+Hardwire+USB+DB9

NETWORK SWITCHES

Tripp Lite Model	Description
NG8	8-Port Unmanaged Switch
NG8POE	8-Port Unmanaged Switch with PoE+
NGS8C2POE	8-Port Managed Switch with PoE+, 2 SFP Ports
NG16	16-Port Unmanaged Switch
NGS16C2	16-Port Managed Switch, 2 SFP Ports
NG24	24-Port Unmanaged Switch, 2 SFP Ports
NSS-G24D2P24	24-Port Managed Switch with PoE+, 2 SFP Ports, 12-Outlet PDU
NSU-G24C2	24-Port Ethernet Switch, 2 SFP Ports, 12-Outlet PDU

POWER DISTRIBUTION UNITS (PDUS)

Tripp Lite Model	Mounting	Nominal Voltage	Input Type/Plug	Outlet (Qty.) Type
Basic				
PDU1215	Horiz./Vert.	120V	5-15P	(13) 5-15R
PDU1220	Horiz./Vert.	120V	5-20P	(13) 5-15/20R
PDU1230	Horiz./Vert.	208/240V	L6-30P	(4) C19, (16) C13
PDU2430	Horiz./Vert.	120V	L5-30P	(24) 5-15R
PDUV30HV	Vertical	208/240V	L6-30P	(6) C19, (32) C13
Metered				
PDUMH15AT (ATS)	Horizontal	120V	2 x 5-15P	(8) 5-15R
PDUMH20AT (ATS)	Horizontal	120V	2 x 5-20P, L5-20P	(16) 5-15/20R
PDUMV30	Vertical	120V	L5-30P	(24) 5-15/20R
Monitored				
PDUMNH15	Horizontal	120V	5-15P	(8) 5-15R
PDUMNH30HV	Horizontal	208/240V	L6-30P	(4) C19, (12) C13
Switched				
PDUMH15NET	Horizontal	120V	5-15P	(16) 5-15R
PDUMH20HVNET	Horizontal	200-240V	C20/L6-20P	(8) C13
PDUMH20HVATNET (ATS)	Horizontal	200-240V	2 x IEC-320-C20	(8) C13, (2) C19
PDUMH30HVNET	Horizontal	208/240V	L6-30P	(16) C13
PDUMH30HVATNET (ATS)	Horizontal	208/240V	2 x L6-30P	(16) C13, (2) C19, (1) L6-30R

RACK ENCLOSURES AND OPEN FRAME RACKS

Tripp Lite Model	Size	Type	Capacity
Enclosures			
SR12UB	12U	Extended Depth	1,000 lb.
SR18UB	18U	Extended Depth	1,000 lb.
SR25UB	25U	Standard	3,000 lb.
SR2400	42U	Value Series	2,400 lb.
SR42UB	42U	Standard	3,000 lb.
SR42UBDP	42U	Extended Depth	3,000 lb.
SR42UBWD	42U	Extended Width	3,000 lb.
SR45UB	45U	Standard	3,000 lb.
SR48UB	48U	Standard	3,000 lb.
Wall-Mount Enclosures			
SRW6U	6U	Non-Swinging	200 lb.
SRW9U	9U	Non-Swinging	200 lb.
SRW10US	10U	Swinging	200 lb.
SRW12U	12U	Non-Swinging	200 lb.
SRW12US	12U	Swinging	200 lb.
SRW12U13	12U	Non-Swinging	200 lb.
SRW12US33	12U	Swinging, 33" Depth	250 lb.
SRW12USG	12U	Swinging, Glass Door	200 lb.
SRW18US	18U	Swinging, Heavy-Duty	250 lb.
SRW26US	26U	Swinging, Heavy-Duty	250 lb.
Open Frame Racks			
SR2POST	45U	2-Post Rack	800 lb.
SR2POST25	25U	2-Post Rack	800 lb.
SR4POST	45U	4-Post Rack	1,000 lb.
SR4POST13	13U	4-Post Rack	1,000 lb.
SR42UBEXPND	42U	4-Post Rack, Heavy-Duty	3,000 lb.

COOLING SOLUTIONS

Tripp Lite Model	Description
SRCOOL2KWMM	Air-Conditioning Unit for Wall-Mount Enclosures, 2,000 BTU, 120V, 60 Hz
SRCOOL7KRM	Rack-Mounted Air-Conditioning Unit, 7,000 BTU, 120V, 60 Hz
SRCOOL12K	Portable Air-Conditioning Unit, 12,000 BTU, 120V, 60 Hz
SRCOOL18K	Portable Air-Conditioning Unit, 18,000 BTU, 208/240V, 60 Hz
SRCOOL24K	Portable Air-Conditioning Unit, 24,000 BTU, 208/240V, 60 Hz
SRCOOL33K	Row-Based Air-Conditioning Unit, 33,000 BTU, 208/240V, 50/60 Hz
SRCOOL60KWC	In-Row Chilled Water Cooling Unit, 204,000 BTU, 208-230V, 50/60 Hz

CABLE MANAGEMENT ACCESSORIES

Tripp Lite Model	Description
NCM-JHC08-25	J-Hook Cable Support, 3/4", Batwing, 25 Pack
NCM-JHC20-25	J-Hook Cable Support, 2", Batwing, 25 Pack
NCM-JHW20-25	J-Hook Cable Support, 2", Wall Mount, 25 Pack
SRCABLEDUCT1U	1U Horizontal Cable Manager (Finger duct with cover)
SRCABLEDUCT1UHD	1U Horizontal Cable Manager (Finger duct with dual-hinged cover)
SRCABLELADDER	10 ft. x 1 ft. Cable Ladder (Includes two sections; requires SRCABLETRAY for connection to enclosure; requires SRLADDERATTACH for connection to wall or open frame rack)
SRCABLEDUCTVRT	6 ft. Vertical Cable Manager (Double finger duct with cover)
SRCABLETRAY	Roof-Mounted Cable Trough (Routes cable and separates power/data cables)
SRCABLEVRT3	High-Capacity Vertical Cable Manager (3 in. wide, double finger duct with cover, toolless mounting)
SRVRTBAR	42U Vertical Cable Management Bars
SRVRTBAR45	45U Vertical Cable Management Bars

KVM CONSOLES AND SWITCHES

Tripp Lite Model	Description
1U Rack-Mount Console KVM Switches	
B020-008-17	8-Port w/17" LCD
B020-016-17	16-Port w/17" LCD
B020-016-17-IP	16-Port w/17" LCD and IP Remote Access
B020-U08-19-IP	8-Port w/19" LCD and IP Remote Access
B020-U08-19-K	8-Port w/19" LCD and 8 PS2/USB Combo Cables
B020-U16-19-K	16-Port w/19" LCD and 8 PS2/USB Combo Cables
B040-016-19	16-Port w/19" LCD
B070-008-19	8-Port w/19" LCD
B070-016-19	16-Port w/19" LCD
B070-016-19-IP	16-Port w/19" LCD and IP Remote Access
1U Rack-Mount Consoles	
B021-000-17	w/17" LCD
B021-000-19	w/19" LCD
1U Rack-Mount Cat5 KVM Switches	
B072-008-1	8-Port
B072-016-IP4	16-Port w/IP Remote Access
B072-032-IP4	32-Port w/IP Remote Access
B064-032-04-IPG	32-Port w/IP Remote Access
1U Rack-Mount Basic USB/PS2 KVM Switches	
B022-U08-IP	8-Port w/IP Remote Access
B042-004	4-Port w/On-Screen Display
B042-008	8-Port w/On-Screen Display
B042-016	16-Port w/On-Screen Display

NETWORK CONNECTIVITY

Tripp Lite Model	Description
Cat5/5e Cables	
N002-001-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 1 ft.
N002-002-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 2 ft.
N002-003-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 3 ft.
N002-004-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 4 ft.
N002-005-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 5 ft.
N002-007-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 7 ft.
N002-010-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 10 ft.
N002-014-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 14 ft.
N002-015-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 15 ft.
N002-020-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 20 ft.
N002-030-BL	Cat5e Molded Patch Cable, RJ45 M/M, Blue, 30 ft.
N002-050-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 50 ft.
N002-075-BL*	Cat5e Molded Patch Cable, RJ45 M/M, Blue, 75 ft.
N002-100-BK*	Cat5e Molded Patch Cable, RJ45 M/M, Black, 100 ft.
N007-100-GY**	Cat5e Outdoor-Rated Molded Patch Cable, RJ45 M/M, Gray, 100 ft.
N007-150-GY**	Cat5e Outdoor-Rated Molded Patch Cable, RJ45 M/M, Gray, 150 ft.
Cat6 Cables	
N201-001-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 1 ft.
N201-002-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 2 ft.
N201-003-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 3 ft.
N201-004-BL*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Blue, 4 ft.
N201-005-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 5 ft.
N201-007-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 7 ft.
N201-010-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 10 ft.
N201-015-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 15 ft.
N201-020-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 20 ft.
N201-030-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 30 ft.
N201-050-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 50 ft.
N201-075-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 75 ft.
N201-100-BK*	Cat6 Snagless Molded Patch Cable, RJ45 M/M, Black, 100 ft.

*Available in other colors.

For more information, contact:

Tripp Lite Pre-Sales Tech Support
773.869.1236 • solutions@tripplite.com



Powering and Connecting Your World