

STORM SEASON *is here again!*



is your Shelter from the Storm

Add Tripp Lite power protection to every purchase to prevent equipment downtime, damage and data loss caused by severe weather

YOU HAVE...

Servers, switches, networking equipment



NOW ADD...

Tripp Lite rack-mount UPS systems, PDUs, rack enclosures, KVM switches and cooling



YOU HAVE...

PCs, workstation, computer peripherals and accessories



NOW ADD...

Tripp Lite desktop UPS systems and surge protectors



YOU HAVE...

Tablets, Chromebooks



NOW ADD...

Tripp Lite USB and AC charging stations and carts



YOU HAVE...

TVs, digital displays, monitors



NOW ADD...

Tripp Lite digital signage and connectivity solutions



Powering and Connecting
Your World

Get started with a sampling of power protection, housing and cooling on the back!

SURGE PROTECTORS



Tripp Lite Model	Outlets/Cord
TLP606B	6/6 ft.
TLP606USB	6 + USB/6 ft.
TLP606DMUSB	6 + USB (with mounting clamp)/6 ft.
TLP608RUSBB	6 + USB/8 ft.
TLP712B	7/12 ft.
TLP725	7/25 ft.
SUPER7TEL15	7 + RJ11/15 ft.
TLP808	8/8 ft.
TLP810NET	8 + RJ11/RJ45/Coax/10 ft.
ISOBAR4ULTRA	4/6 ft.
ISOBAR6ULTRA	6/6 ft.
ISOBAR8ULTRA	8/12 ft.
IBAR12	12/15 ft.
IBAR12-20ULTRA*	12/15 ft.

*20A circuit breaker.

POWER DISTRIBUTION UNITS (PDUs)



Tripp Lite Model	Mounting	Nominal Voltage	Input Type/Plug	Outlet (Qty.) Type
Basic				
PDU1215	Horiz./Vert.	120V	5-15P	(13) 5-15R
PDU1220	Horiz./Vert.	120V	5-20P	(13) 5-15/20R
Metered				
PDUMH15AT (ATS)	Horizontal	120V	2 x 5-15P	(8) 5-15R
PDUMH20AT (ATS)	Horizontal	120V	2 x 5-20P, L5-20P	(16) 5-15/20R
Monitored				
PDUMNH30HV	Horizontal	208/240V	L6-30P	(4) C19, (12) C13
PDUMNV30HV2LX	Vertical	208/230V	L6-30P	(6) C19, (36) C13
Switched				
PDUMH20HVATNET (ATS)	Horizontal	200-240V	2 x IEC-320-C20	(8) C13, (2) C19
PDUMH30HVATNET (ATS)	Horizontal	208/240V	2 x L6-30P	(16) C13, (2) C19, (1) L6-30R

RACKS AND COOLING SOLUTIONS

Tripp Lite Model	Size	Type	Capacity
Enclosures			
SR12UB	12U	Extended Depth	1,000 lb.
SR18UB	18U	Extended Depth	1,000 lb.
SR24UB	24U	Standard	1,000 lb.
Wall-Mount Enclosures			
SRW6U	6U	Non-Swinging	200 lb.
SRW9U	9U	Non-Swinging	200 lb.
SRW10US	10U	Swinging	200 lb.
SRW12U	12U	Non-Swinging	200 lb.
SRW12US	12U	Swinging	200 lb.
SRW12U13	12U	Non-Swinging	200 lb.
SRW18US	18U	Swinging	250 lb.
Open Frame Racks			
SRWO12UHD	12U	Wall-Mount	200 lb.
SRWO8U22	8U/12U/22U	Expandable Wall-Mount	150 lb.
SR2POST	45U	2-Post Rack	800 lb.
SR4POST	45U	4-Post Rack	1,000 lb.
Cooling Solutions			
SRCOOL7KRM	Rack-Mount Air-Conditioning Unit, 7,000 BTU, 120V, 60 Hz		
SRCOOL12K	Portable Air-Conditioning Unit, 12,000 BTU, 120V, 60 Hz		
SRCOOL18K	Portable Air-Conditioning Unit, 18,000 BTU, 208/240V, 60 Hz		
SRCOOL24K	Portable Air-Conditioning Unit, 24,000 BTU, 208/240V, 60 Hz		
SRCOOLNETLX	Web card for remote cooling management and monitoring of SRCOOL12K		

UPS SYSTEMS

Tripp Lite Model	Outlets	½ Load Runtime*
Compact UPS Systems		
BC350	6	10
★ INTERNET550U	8	5.6
INTERNET750U	12	9.4
AVR550U	8	5.5
★ AVR750U	12	8.6
AVR900U	12	8.4
Digital Tower and Rack-Mount UPS Systems		
SMART1300LCDT	8	10
OMNI1500LCDT	10	7.5
SMART1500LCDT	10	10
OMNI900LCD	8	10
SMART1000LCD	8	10
SMART1200LCCD	8	12
SMART1500LCD	8	11.8
SMC10002URM	6	15.6
SMC15002URM	8	17.7
SmartPro Rack-Mount UPS Systems		
SMART500RT1U	7	14.6
SMART750RM1U	6	16.2
SMART1000RM1U	6	13.2
SMART1500RM2U	8	13
SMART1500RMXL2UA	8	14+
SMART2200RM2U	8	12
SMART2200RMXL2U	8	12+
★ SMART3000RM2U	9	10+
★ SMART3000RMXL2U	9	10+
SmartOnline Rack-Mount UPS Systems		
SU750RTXL2U	6	11+
SU1000RTXL2UA	6	14+
★ SU1000RTXLCD2U	6	14+
SU1500RTXL2UA	6	14+
★ SU1500RTXLCD2U	6	14+
SU2200RTXL2UA	7	14+
★ SU2200RTXLCD2U	7	12+
SU3000RTXL2U	7	15+
SU3000RTXL3U	9	14+
★ SU3000RTXLCD3U	9	11+
Tripp Lite Model	Description	
SNMP Cards for Remote Access		
WEBCARDLX	Web card for remote management of compatible Tripp Lite UPS systems	
WEBCARDLXMINI	Web card for remote management of compatible Tripp Lite UPS systems	

*Represented in minutes, may vary based on load and battery condition.

+ Features expandable runtime with optional external battery packs.



Powering and Connecting
Your World

21-07-040