



Powering and Connecting Your World

Add Mobility to Your Temperature-Check Station

Flexibility is vital as organizations implement thermal-imaging technology to screen employees, students, visitors and patrons for fever. Rolling display carts, like Tripp Lite's DMCS3270XP, provide mobility and placement options for temperature-check stations.

Instead of a permanent installation, a display and thermal-imaging camera can be mounted on the cart and rolled where needed, offering a simple, cost-effective way to share technology within a facility. The cart also provides temporary digital signage to communicate important information.



Model: DMCS3270XP



EASY MOBILITY

- Swivel casters provide smooth rolling from room to room; locking feature keeps the cart in position while at rest.

BROAD COMPATIBILITY

- Cart accommodates screens from 32 to 70 inches.
- VESA-compliant mounting brackets provide no-hassle display installation.

CONVENIENT ADJUSTABILITY

- The height of the display can be raised or lowered to improve viewing angles.
- Tilt adjustment helps eliminate glare.
- Screen can be rotated for portrait or landscape viewing.

SPACE FOR COMPONENTS

- Upper shelf accommodates a thermal-imaging camera, webcam or small projector.
- Lower shelf holds a laptop, tablet or video source.
- Cable management openings reduce cord clutter for a clean, professional look.

Perfect for:

Offices, schools, public buildings, casinos and entertainment venues.

Feature Focus: DMCS3270XP



- A** Upper Shelf for Thermal-Imaging Camera, Webcam or Small Projector
- B** VESA-Compliant Mounting Brackets
- C** 90° Rotatable Mounting Plate
- D** Cable Management Pass-Through Openings
- E** Height-Adjustable Support Column
- F** Handle to Guide Movement
- G** Lower Shelf for Laptop, Tablet or Video Source
- H** Lockable Casters

Model: DMCS3270XP



SPECIFICATIONS

Model	DMCS3270XP
For Screen Sizes	32 to 70 in. (Flat/Curved)
Number of Displays	1
Max. Weight Capacity	150 lb.
VESA Mounting Patterns	200 x 200, 200 x 300, 200 x 400, 300 x 200, 300 x 300, 300 x 400, 400 x 200, 400 x 300, 400 x 400, 500 x 200, 500 x 300, 500 x 400, 600 x 300, 600 x 400
Display Height Adjustment (Above the Floor)	47 to 63 in.
Viewing Orientation	Landscape or Portrait (Rotatable)
Tilt Adjustment	-12° to +5°
Primary Construction	Aluminum, Steel
Unit Dimensions (H x W x D)*	81.5 x 32.6 x 27.6 in.
Unit Weight	46.2 lb.
Limited Warranty	5 Years

*Height listed is maximum height.

Learn more about Tripp Lite's full line of display solutions at tripplite.com.



Tripp Lite Corporate Headquarters
1111 West 35th Street, Chicago, IL 60609 USA
773.869.1773 | tripplite.com