



Powering and Connecting
Your World

COMPANY PROFILE

From office desktop to critical infrastructure, Tripp Lite products and solutions power and connect the computers, networking equipment and electronic devices that form the foundation of our digital world. Headquartered in Chicago since 1922, Tripp Lite serves customers in more than 90 countries worldwide.

Industry-Leading Value:

Tripp Lite provides a good balance of industry-leading features, high quality and competitive cost, stretching budgets without sacrificing performance.

Proven Product Reliability:

Tested and certified to strict reliability, compatibility and safety standards, Tripp Lite products protect some of the world's largest companies and data centers from damage, downtime and data loss.

Commitment to Service:

Tripp Lite's Chicago-based, in-house technical specialists and application engineers are available by phone, email and chat to provide quick answers and customized solutions. Tripp Lite's website provides user-friendly product finders, up-to-date specifications and detailed documentation around the clock.

Ready for Today and Tomorrow:

For nearly a century, Tripp Lite has evolved to meet customer needs and industry trends. From edge to data center, Tripp Lite continues to develop innovative and practical products and solutions to support connected technologies, IT infrastructure and enterprise applications.

Tripp Lite

1111 W. 35th Street
Chicago, IL 60609 USA

773.869.1773

www.tripplite.com



Manufacturing
Excellence.



PRODUCT LINES

Office/Desktop UPS Systems

- Reliable battery backup, voltage correction and surge/noise protection for small servers, desktop computers and other home and office electronics
- 90+ models from 300VA to 1,500VA
- Standby or line-interactive (AVR) operation

Network/Server UPS Systems

- Continuous power for critical systems
- 175+ single-phase models from 500VA to 20kVA
- 80+ 3-phase models from 10kVA to 400kVA
- Line-interactive (AVR) or on-line operation

Power Distribution Units (PDUs)

- 190+ models with up to 48 outlets and 28.8kW
- Horizontal (1U/2U) or vertical (0U) form factor
- Single-phase or 3-phase input

Rack Enclosures

- 50+ floor-standing models from 12U to 48U
- 50+ wall-mount models from 2U to 26U
- Rack equipment shipping cases from 2U to 10U
- Up to 3,000 lb. weight capacity

Open Frame Racks

- 20+ floor-standing models from 12U to 58U
- 10+ wall-mount models from 2U to 22U
- Up to 3,000 lb. weight capacity

Close-Coupled Cooling Solutions

- Efficient air conditioning up to 33,000 BTU
- Standard NEMA input plugs
- Automatic restart after outages
- Network management support

KVMs & Rack Consoles

- Server control from a single console (keyboard, mouse and monitor) with up to 64 KVM ports
- 75+ desktop and rack-mount models
- IP models include remote network access

Console Servers

- Remote access to serial and network devices via Ethernet, Wi-Fi, cellular or analog modem
- Up to 48 RJ45 serial ports in 1U
- Fail-safe access to critical systems

Micro Data Centers

- 40 pre-configured single-rack models with 10U to 40U usable rack space and 1.5kVA to 10kVA (N+N) power for IT equipment
- Floor-standing and wall-mount options
- Available as kits and fully tested assemblies
- Wide range of options for customization

Cables and Connectivity

- 2,000+ models of network (fiber and copper), audio/video, digital signage, USB, computer, storage, device, charging and power cables
- Adapters, extenders, splitters, hubs, switches, converters, couplers, jacks, wall plates, patch panels, tools, testers and docks also available

Surge Protectors and Power Strips

- 160+ surge protectors with up to 24 outlets, 5100 joules and \$500,000 insurance
- 90+ power strips with up to 24 outlets
- Isobar® models also include isolated filter banks

Charging Solutions

- Charge (USB or AC), sync, secure and organize up to 48 laptops or tablets
- 50+ charging carts, charging stations, standalone USB chargers and mobile power banks

Display Mounts

- 70+ models for displays up to 100 in. and 350 lb.
- Wall, desk and ceiling TV/monitor mounts
- Mobile TV/monitor carts

Network Switches

- 20+ models with up to 24 Gigabit Ethernet ports
- Up to 300W PoE budget; desktop or 1U rack housing; managed or unmanaged; with or without uplink ports; with or without built-in PDU

Healthcare Power Solutions

- 60+ products for hospital/medical environments, including power strips, surge protectors, UPS systems, isolation transformers, power cords and mobile power supplies

Custom Products

- Racks, cables, PDUs and UPS systems tailored to match technical specifications, schedules, cost requirements, facilities, personnel and policies
- In-house engineering delivers custom products without delaying projects or breaking budgets

Additional Tripp Lite Products

- Replacement UPS Batteries
- TAA-Compliant Products
- Power Management Tools and Software
- Power Inverters
- Power Conditioners
- Isolation Transformers
- DC Power Supplies
- Laptop/Tablet/Smartphone Accessories
- Adjustable-Height Desks and Workstations