



## NEW PRODUCT ANNOUNCEMENT

### Wireless Access Point Enclosures

# House and Protect Access Points Indoors and Outdoors

Model: EN1812 (Exterior)



Model: EN1812  
(Interior; WAP not included)

 Compatible

Tripp Lite's new SmartRack® enclosures provide a purpose-built solution to house and protect wireless access points (WAPs), routers and other networking components. Designed for Cisco WAPs, the enclosures are also compatible with most other brands of access points (APs). Enclosures are available in indoor and indoor/outdoor models for a wide variety of corporate, retail, hospitality, healthcare and education environments.

### Features

- Heavy-duty impact-resistant plastic construction is transparent to wireless signals to ensure strong connectivity.
- Universal T-bar bracket (included) accommodates most brands of access points.
- Enclosures surface mount to wall or ceiling with user-supplied fasteners.

### INDOOR ENCLOSURES

- A key lock deters theft, damage and tampering.
- Vents help prevent heat build-up.
- Cable knockouts provide easy cable entry.
- Cutouts allow mounting directly over wall/telecom outlets.

#### Perfect for:

Offices, retail locations, hotels, residence halls and other indoor areas

### INDOOR/OUTDOOR ENCLOSURES (NEMA 4)

- NEMA 4 rating indicates protection from dust and water.
- Enclosures are suitable for washdown environments.

#### Perfect for:

Stadiums, auditoriums, gymnasiums, warehouses and outdoor locations

## INDOOR ENCLOSURES



### SPECIFICATIONS

Model	EN1111	EN1812
Closure Type	Fully Hinged Door with Key Lock	Fully Hinged Door with Key Lock
Enclosure Material	Impact-Resistant Plastic	Impact-Resistant Plastic
Unit Dimensions H x W x D	11.1 x 11.1 x 4.4 in. (281.8 x 281.8 x 111.8 mm)	18 x 12 x 5.1 in. (457.2 x 304.7 x 130.8 mm)
Unit Weight	3.3 lb. (1.5 kg)	5.7 lb. (2.6 kg)
Warranty	5-Year Limited	5-Year Limited

Enclosures are PCI DSS and RoHS compliant.

## INDOOR/OUTDOOR ENCLOSURES (NEMA 4)



### SPECIFICATIONS

Model	EN1309N4	EN1511N4LATCH
Closure Type	Screw-On Cover with Gasket	Hinged Door with Gasket and Latch Closure; accepts a lock or tamper-evident seal (not included)
NEMA Rating	NEMA 4	NEMA 4
Enclosure Material	Impact-Resistant Plastic	Impact-Resistant Plastic
Unit Dimensions* H x W x D	13.4 x 9.1 x 4 in. (339.7 x 230.1 x 101.9 mm)	15.7 x 12.6 x 5.1 in. (398.3 x 319.2 x 128.5 mm)
Unit Weight	2.6 lb. (1.2 kg)	5.3 lb. (2.4 kg)
Warranty	5-Year Limited	5-Year Limited

Enclosures are RoHS compliant. \*Includes mounting tabs.

Learn more about Tripp Lite's full line of IT infrastructure solutions at [www.triplite.com](http://www.triplite.com).



Tripp Lite Corporate Headquarters  
1111 W. 35th Street, Chicago, IL 60609 USA  
773.869.1773 | [www.triplite.com](http://www.triplite.com)