

## PX USB Power Supply 12VDC 1000mA

MODEL NUMBER: 0SU70042



### Highlights

- External power supply for the PX USB (0SU70028)
- Provides an alternative to power the PX USB instead of Power Over Ethernet (PoE)
- Input: 100-240V, 50/60Hz, 0.5A
- Output: 12V, 1000mA

### System Requirements

- PX USB (0SU70028)

### Package Includes

- External Power Supply
- NEMA 1-15P, CEE 7/16 European Plug, BS1363 UK Plug, AS 3112 Australian Plug adapters

### Description

The PX USB (0SU70028) remote access unit can be powered using Power Over Ethernet (PoE) or an external power supply. The 0SU70042 external power supply is not included with the PX USB, and is required if Power Over Ethernet (PoE) is not a viable option. It comes with multiple connector types (NEMA 1-15P, CEE 7/16 European Plug, BS1363 UK Plug, AS 3112 Australian Plug), allowing you to use the version appropriate to your power source. Input: 100-240V, 50/60Hz, 0.5A. Output: 12V, 1000mA.

### Features

- External power supply for the PX USB (0SU70028)
- Provides an alternative to power the PX USB instead of Power Over Ethernet (PoE)
- Includes multiple connector types (NEMA 1-15P, CEE 7/16 European Plug, BS1363 UK Plug, AS 3112 Australian Plug)
- Input: 100-240V, 50/60Hz, 0.5A
- Output: 12V, 1000mA

## Specifications

OVERVIEW	
UPC Code	654518210507
Accessory Type	Power Supply
Accessory Class	KVM Switch Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.00 x 5.40 x 6.40
Shipping Dimensions (hwd / cm)	10.16 x 13.72 x 16.26
Shipping Weight (lbs.)	0.70

Shipping Weight (kg)	0.32
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	6-month limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.