

Minicom PX USB - Remote KVM access with Power-on-Cable (POC)

MODEL NUMBER: 0SU70068



Description

Complete access to your computer - any time, anywhere

Completing the OOB Remote Support package

Virtual Media capability for each server

Complete remote support for mission critical applications

Scalable centralized management

Features

- Single port, palm-sized device
- Virtual Media for complete remote management
- Absolute Mouse Support for reduced installation hassle
- BIOS level access over IP connection
- Management system enabled

Highlights

- Single port, palm-sized device
- Virtual Media for complete remote management
- Absolute Mouse Support for reduced installation hassle
- BIOS level access over IP connection
- Management system enabled
- Cost-effective & easily scalable
- Ideal for isolated/widely distributed servers
- Power over Ethernet & external power option
- Includes one Power-on-Cable (POC) - Model #0SU60020
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- Compatible with Windows 98 and higher, Novell, Linux, SUN Solaris and Mac

Resolution

- Host Computer: Supports video resolutions up to 1600 x 1200 @ 85Hz
- Client Computer: Recommended - client computer resolution should be higher than resolution on the host computer

Package Includes

- PX USB
- Power-on-Cable (POC)



- Cost-effective & easily scalable
- Ideal for isolated/widely distributed servers
- Power over Ethernet & external power option
- Includes one Power-on-Cable (POC) - Model #0SU60020
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

- USB Cable Kit
- Rackmount Hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	654518212174
PHYSICAL	
Color	Silver
Shipping Dimensions (hwd / cm)	19.05 x 18.29 x 3.81
Shipping Dimensions (hwd / in.)	7.50 x 7.20 x 1.50
Shipping Weight (kg)	1.04
Shipping Weight (lbs.)	2.30
Unit Dimensions (hwd / cm)	3.3 x 1.05 x 8
Unit Dimensions (hwd / in.)	1.2 x 4.13 x 3.15
Unit Weight (kg)	0.30
Unit Weight (lbs.)	0.66
ENVIRONMENTAL	
Storage Temperature Range	-40°C to 70°C / -40°F to 158°F
Relative Humidity	80% Non-Condensing
Operating Temperature	0°C to 40°C / 32°F to 104°F
COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	1
PC/Server Connections	VGA; USB; PS/2
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cat5 KVM Switch	No
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>