

Industrial Power Strip, 5-Outlet, 6 ft. (1.8 m) Cord, Switchless

MODEL NUMBER: 602



Highlights

- 5 outlets
- 6-ft. (1.83 m) cord
- 8.6-in. overall length
- No switch

Package Includes

- 602 Power Strip
- Warranty information
- Instruction manual

Description

The 602 Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes five NEMA 5-15R output receptacles with 1.188-inch center-to-center spacing, six-foot (1.8-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 602 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, 15A resettable circuit breaker and attractive blue/gray color scheme.

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center outlet spacing
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15-amp power handling capacity with circuit breaker
- 6-ft. (1.83 m) AC line cord

Specifications

OVERVIEW	
UPC Code	037332108937
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(5) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 5
Right-Angle Outlets	No
Outlet Spacing	1.188 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	Gray
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Blue; Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45
Outlets Measurement (Center to Center)	1.18 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.00 x 5.30 x 9.80
Shipping Dimensions (hwd / cm)	5.08 x 13.46 x 24.89
Shipping Weight (lbs.)	1.60
Shipping Weight (kg)	0.73
Unit Dimensions (hwd / in.)	1.500 x 8.750 x 2.500
Unit Dimensions (hwd / cm)	18.7 x 6.35 x 3.8
Outlet Spacing	1.188 in.
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	

Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.