

Waber-by-Tripp Lite 5-Outlet Industrial Power Strip, 15-ft. Cord, Switchless

MODEL NUMBER: 602-15



Highlights

- 5 outlets
- 15-ft. cord
- 8.6-in. overall length
- No switch
- All-metal housing

Package Includes

- 602-15 Power Strip
- Warranty information
- Instruction manual

Description

The Waber-by-Tripp Lite 602-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center spacing, 15-foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 602-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, 15-amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 5 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 5 NEMA 5-15R output receptacles with 1.188-inch center-to-center outlet spacing
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15-amp power handling capacity with circuit breaker
- 15-foot AC line cord

Specifications

OVERVIEW	
UPC Code	037332113443
OUTPUT	



Frequency Compatibility	50 / 60 Hz
Output Receptacles	(5) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Spacing	1.188 in.
Outlet Orientation	Single row of 5
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Integrated Cord Clip	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	14.10 x 2.70 x 6.10
Shipping Dimensions (hwd / cm)	35.81 x 6.86 x 15.49
Shipping Weight (lbs.)	2.70
Shipping Weight (kg)	1.22
Unit Dimensions (hwd / in.)	7.38 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	18.7 x 6.35 x 3.8
Material of Construction	Metal
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Receptacle Color	Black
Color (AC Line Cord)	Black
Color	Gray
Outlets Measurement (Center to Center)	30mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Anti-Microbial Protected	No
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363
Canada	cUL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>