

Waber-by-Tripp Lite 6-Outlet (75.9mm center-to-center spacing) Industrial Power Strip, 6-ft. Cord

MODEL NUMBER: 6NX6



Highlights

- 6 outlets
- 6-ft. cord
- 12.5-in. length
- Master on/off switch
- All-metal housing

Package Includes

- 6NX6 Power Strip
- Warranty information
- Instruction manual

Description

Tripp Lite's 6NX6 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing, 6-ft. AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 6NX6 ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige housing with black receptacles.
 PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R
 ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)
 FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation on a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-ft. AC line cord

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 037332107107 |



| OUTPUT | |
|--|--|
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (6) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (2) Yes |
| Outlet Spacing | 1.520 in. |
| Outlet Orientation | Single row of 6 |
| Right-Angle Outlets | No |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 15A 120V |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 6 |
| Input Cord Length (m) | 1.83 |
| Integrated Cord Clip | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Lighted combination switch / circuit breaker |
| PHYSICAL | |
| Anti-Microbial Protected | No |
| Color | Beige |
| Color (AC Line Cord) | Black |
| Integrated Keyhole Mounting Slots | Yes |
| Keyhole Slot Mounting Measurement (Center to Center) | 240mm |
| Material of Construction | Metal |
| Outlets Measurement (Center to Center) | 75.9mm |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / cm) | 36.07 x 6.60 x 15.49 |
| Shipping Dimensions (hwd / in.) | 14.20 x 2.60 x 6.10 |
| Shipping Weight (kg) | 0.73 |
| Shipping Weight (lbs.) | 1.60 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|-------------------------------------|---------------------------|
| Unit Dimensions (hwd / cm) | 31.75 x 6.35 x 3.8 |
| Unit Dimensions (hwd / in.) | 12.5 x 2.5 x 1.5 |
| CERTIFICATIONS | |
| UL1363 (Power Tap) | UL1363 |
| Canada | cUL |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>