

# Industrial Power Strip, 6-Outlet, 6 ft. (1.8 m) Cord, Beige

MODEL NUMBER: 6SPDX



### Highlights

- 6 outlets
- 6-ft. (1.83 m) cord
- 12.5-in. length
- Lighted master switch
- All-metal housing

### Package Includes

- 6SPDX Power Strip
- Warranty information
- Instruction manual

### Description

The 6SPDX Power Strip offers a convenient method of power distribution in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R outlets with 1.5-inch center-to-center spacing, six-foot (1.8-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes the 6SPDX ideal for distributing alternate waveform UPS or generator power. Features rugged metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige color scheme.

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.520-in. center-to-center spacing
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity
- 6-ft. (1.83 m) AC line cord

## Specifications

OVERVIEW	
UPC Code	037332108234
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V



Powering Business Worldwide



Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
Outlet Spacing	1.520 in.
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted combination switch / circuit breaker
<b>PHYSICAL</b>	
Color	Beige
Material of Construction	Metal
Power Cord Color	Beige
Housing Color	Beige
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	203.20mm
Outlets Measurement (Center to Center)	3.05 in.
Receptacle Color	Beige
Shipping Dimensions (hwd / in.)	2.25 x 6.00 x 14.25
Shipping Dimensions (hwd / cm)	5.72 x 15.24 x 36.20
Shipping Weight (lbs.)	2.41
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	1.500 x 12.500 x 2.500
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Outlet Spacing	1.520 in.
<b>FEATURES &amp; SPECIFICATIONS</b>	



Powering Business Worldwide



Antimicrobial	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.