

## Eaton 9PX 6000VA 5400W 120/208V Online Double-Conversion UPS - Hardwired Input / Output, Cybersecure Network Card, Extended Run, 6U Rack/Tower

MODEL NUMBER: 9PX6KP2



Provides sine wave output, complete battery backup and power protection for mission-critical IT installations, edge networks and other advanced network applications.

### Features

#### 6kVA/5.4kW/120V/208V Battery Backup for IT Installations and Edge Networks

This 9PX rack-mount online double-conversion UPS system features hardwired input and output connections. It provides reliable battery backup and AC power protection against blackouts, brownouts, surges and line noise that can damage valuable IT equipment or destroy data. The 9PX6KP2 is superlative power management for education, commercial, financial or healthcare networking components, including Cisco switches and servers.

#### Expandable Internal Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable valve regulated lead acid (VRLA) battery modules allow you to work through short power failures and give you enough time to safely save files and shut down your system in case of a prolonged blackout. Exclusive ABM technology increases battery life by 50 percent and closely monitors battery health to provide advanced notice when batteries need replacing. You can also connect up to four extended battery modules (9PXEEM180RT, sold separately) for hours of extended runtime.

#### Included Distribution Module Helps Accommodate a Range of Connected Equipment

The 9PXPPDM2 PowerPass Distribution Module permits a step-down voltage from 208V to 120V to allow the connection of a variety of IT components. It also features a maintenance bypass, which lets you service or replace the 9PX6KP2 without powering down any connected equipment.

#### Included Gigabit Network Interface Offers 24/7 Remote Access

The NETWORK-M2 Gigabit network card enables full remote configuration and management, including load shedding, reboots of connected equipment and safe shutdowns. UPS firmware can also be flashed remotely through the NETWORK-M2 without dropping the load, so you don't have to plan for downtime. The card meets both UL 2900-1 and IEC 62443-4-2 standards for cybersecurity, which were developed to address the vulnerability of connected devices to known malware/exploits and to protect business from these risks. The optional Environmental Monitoring Probe Gen 2 (EMPDT1H1C2, sold separately) provides a variety of environmental monitoring capabilities, including temperature and humidity conditions.

#### Rotating LCD Interface Keeps You Informed at a Glance

### Highlights

- Keeps equipment running during outages to allow time for file saves and safe shutdown
- Included NETWORK-M2 Gigabit network card enables full remote access and control
- Exclusive ABM technology with 3-stage charging increases internal battery life by 50%
- Interactive LCD interface keeps you updated on critical load information in real time
- Optional extended battery modules allow extended runtime to keep equipment powered

### Package Includes

- 6000VA 5400W 120/208V 9PX Online Double-Conversion UPS
- 9PXPPDM2 PowerPass Distribution Module
- NETWORK-M2 Gigabit network card
- USB cable
- RS-232 cable
- Tower support stands
- Cable gland for hardwire connection
- Phillips-head screwdriver
- Rack-mounting hardware
- Owner's manual



Powering Business Worldwide

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

The front-panel LCD provides control settings and critical information to help diagnose any issues. The interface rotates to accommodate both rack-mount and tower configurations, and it tilts up to 45 degrees for more comfortable viewing.

**Advanced Communications Ports Allow for Automatic Saves and Shutdowns**

RS-232 and USB ports connect to a serial-enabled device for a variety of communication options (cables are included). A dry-contact relay port can be programmed through the LCD to provide reliable communications to automation and industrial components. The RPO/ROO connectors permit emergency shutdown or remote restart of all connected equipment.

**Versatile Installation Options**

You can mount the 9PX6KP2 in 6U of space in an EIA-standard 19-inch rack using the included 4-post rail kit. You can also adapt it for tower installation using the included support stands. For installation in 2-post rackmounts, one RK2PC mounting kit is required for each UPS, EBM, PPDM, or transformer.

## Specifications

OVERVIEW	
UPC Code	743172039828
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	24.8A
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 220V AC; 230V AC; 240V AC
UPS Input Connection Type	Hardwire
Input Circuit Breakers	20A
Plug Type	Hard-wire
OUTPUT	
Output Capacity (VA)	6000
Output Capacity (kVA)	6
Output Capacity (Watts)	5400
Output Capacity (kW)	5.4
Power Factor	0.9
Crest Factor	3:1
Nominal Voltage Details	100V, 110V, 120V, 200V, 208V, 220V, 230V, 240V
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V; 208V; 240V; 200V; 220V; 230V



Powering Business Worldwide

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Output Receptacles	Hardwire
Individually Controllable Load Banks	Yes
<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	3 min.
Runtime Half Load (min.)	8 min.
Expandable Runtime	Yes
Expandable Runtime Description	Add up to 4 extended battery modules (EBM). Part number <a href="/tripplite.eaton.com/eaton-9px-external-battery-for-9px6k-9px5k-9px3k3un-3u-9PXEBM180RT">9PXEBM180RT</a>
DC System Voltage (VDC)	180
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	<a href="/tripplite.eaton.com/replacement-battery-for-eaton-9px-3kva-6kva-ups-ebm-744-A1974">744-A1974</a>
Battery Replacement Description	Hot-swappable, user replaceable batteries. UPS requires 1 Replacement Battery Cartridge.
Battery Management	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	LCD graphical display
Switches	RPO / ROO
Alarm Cancel Operation	Press ESC to silence the alarm
Audible Alarm	Audible alarm indicates utility failure, low-battery, overload, other UPS/Battery fault or remote shutdown conditions
LED Indicators	4 status-indicating LEDs
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Response Time	0 ms
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount; Tower
Rack Height	6U
Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount; Tower
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="/tripplite.eaton.com/eaton-2-post-rack-mount-rail-kit-for-9px-ups-RK2PC">RK2PC</a> )
Minimum Required Rack Depth (cm)	81.28



Powering Business Worldwide

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Minimum Required Rack Depth (inches)	32
UPS Power Module Weight (kg)	48.08
UPS Power Module Weight (lbs.)	106
Unit Dimensions (hwd / in.)	10.200 x 17.300 x 28.400
Unit Weight (lbs.)	201.000
Unit Weight (kg)	91.17
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
AC Mode Efficiency Rating (100% Load)	93
AC Economy Mode Efficiency Rating (100% Load)	98
<b>COMMUNICATIONS</b>	
Network Management Cards	&nbsp;<a class="productLink" href="//tripplite.eaton.com/eaton-secure-gigabit-network-card-for-ups-systems-NETWORK-M2">NETWORK-M2</a>&nbsp;; &nbsp;<a class="productLink" href="//tripplite.eaton.com/eaton-industrial-gateway-card-mini-slot-for-ups-systems-INDGW-M2">INDGW-M2</a>&nbsp;; &nbsp;<a class="productLink" href="//tripplite.eaton.com/eaton-relay-serial-interface-card-RELAY-MS">RELAY-MS</a>&nbsp;
Communications Interface	Pre-installed network card; RS-232; USB
<b>APPLICATIONS</b>	
UPS Applications	Mission Critical Applications
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	NOM (Mexico); EN 62040-2; cUL Listed
Product Compliance	FCC Part 15 Class A (USA); CE (Europe); FCC (USA); ENERGY STAR Qualified; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Extended Service Plans	<b>ADVANCED DEPOT EXCHANGE</b> 5-YEAR DEPOT REPAIR: 9SW5Y-6000UCExpedited parts coverage for 5 yearsParts, electronics and UPS batteries coverageNext business day shippingTechnical support <b>5-YEAR ON-SITE PLAN: WFLN75XX-7000UC</b> On-site parts and labor coverage for years 5Parts, electronics and UPS batteries coverage24x7 on-site labor coverage, next-day responseNext-day shippingTechnical support



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States



*Powering Business Worldwide*

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.