



Powering Business Worldwide

# Eaton 9PX Extended Battery Module (EBM) used with 9PX8KSP, 9PX10KSP UPS, 3U Rack/Tower

MODEL NUMBER: 9PXEBM360SP



Provides extended runtime for compatible UPS systems in medical, light industrial, automation and other mission-critical IT applications where space is limited.

## Features

### Backup Battery Module Gives Your Compatible Eaton UPS System Extended Runtime

The valve regulated lead acid 9PXEBM360SP offers extended battery runtime when used in conjunction with Eaton's 9PX8KSP and 9PX10KSP split-phase 9PX UPS systems. It can also be daisy-chained for a maximum of four matching battery packs to deliver even longer extended-run operation. Heavy-gauge cabling with high-current DC connectors is included for safe, simple installation.

### Versatile Installation Options

You can mount the 9PXEBM360SP in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit. You can also adapt it for tower installation using the included support stands.

## Specifications

OVERVIEW	
UPC Code	743172040374
INPUT	
Input Phase	Single-Phase
UPS Input Cord Length (ft.)	1
UPS Input Cord Length (m)	0.3
OUTPUT	
Individually Controllable Load Banks	No
BATTERY	

## Highlights

- Connects to expandable Eaton 8kVA to 10kVA 9PX UPS systems to add critical runtime
- Includes heavy-gauge battery cabling with high-current 360V DC connectors
- Daisy-chain connector supports additional battery packs for even longer runtime

## System Requirements

Compatible only with Eaton's 9PX8KSP and 9PX10KSP split-phase 9PX UPS systems

## Package Includes

- 9PXEBM360SP 360V Extended Battery Module
- External battery cable
- Rack-mounting hardware
- Tower support stands
- Quick start guide



Powering Business Worldwide

Battery Type	Valve Regulated Lead Acid (VRLA)
Expandable Runtime	No
DC System Voltage (VDC)	360
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/replacement-battery-for-eaton-9px-3kva-6kva-ups-ebm-744-A1974">744-A1974</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries. EBM requires 2 Replacement Battery Cartridges.
Battery Management	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount; Tower
Rack Height	3U
External Battery Pack Form Factor	Rack/Tower
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Minimum Required Rack Depth (cm)	73.66
Minimum Required Rack Depth (inches)	29
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 25.900
Unit Weight (lbs.)	162.900
Unit Weight (kg)	73.89
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	ANSI/IEEE C62.41; cUL Listed; NOM (Mexico)
Product Compliance	RoHS; CE (Europe); ENERGY STAR Qualified
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Extended Service Plans	<b>ADVANCED DEPOT EXCHANGE</b> Service Part Number: 9SW5Y-18000BCExpedited parts coverage for 5 yearsParts, electronics and UPS batteries coverageNext business day shippingTechnical support <b>5-YEAR ON-SITE PLAN (US ONLY)</b> Service Part Number: WEBN75XX-11000BCOn-site parts and labor coverage for years 5Parts, electronics and UPS batteries coverage24x7 on-site labor coverage, next-day responseNext-day shippingTechnical support



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.