



Line Conditioner - Automatic voltage regulation with surge protection

MODEL NUMBER: **LS604**

Description

Tripp Lite's LS604 automatic voltage regulation system offers complete protection from brownouts, overvoltages and transient surges for computers, printers, fax machines and more. Transformer-based voltage correction circuits maintain usable 120V nominal AC output during brownouts as low as 87V and overvoltages to 140V. Network grade equipment protection offers AC surge and noise suppression. Supports loads up to 600 watts. Includes 4 NEMA5-15R outlets, 6-foot line cord and 3 diagnostic LEDs that display incoming voltage level, surge protection status and line fault conditions. \$10,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

Features

- Maintains usable 120V nominal output during brownouts as low as 87V and overvoltages as high as 140V
- 600 watts output power rating supports 120V loads up to 5 amps
- Network grade surge suppression
- Complete EMI/RFI noise filtering
- 3 diagnostic LEDs indicate input voltage status and surge suppression status
- 4 protected NEMA5-15R outlets
- 6 ft. AC power cord with standard NEMA5-15P input plug
- 2 year manufacturers product warranty
- \$10,000 Ultimate Lifetime connected equipment insurance (USA & Canada Only)

Specifications

OUTPUT	
Output (VA)	600
Output Nominal Voltage	120v / 60Hz
INPUT	
Input Cord Length (ft.)	9
Input Cord Length (m)	1.83
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	3 LEDs indicate incoming voltage status
SURGE / NOISE SUPPRESSION	

Highlights

- Automatically adjusts low or high voltage
- 600 watts continuous
- 4 NEMA 5-15R outlets
- \$10,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Package Includes

- LS604 Line Conditioner
- Mounting hardware
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS AC Suppression Joule Rating	720 joules
EMI / RFI AC Noise Suppression	20 dB
PHYSICAL	
Shipping Weight (lbs.)	5.00
Shipping Weight (kg)	2.27
Unit Dimensions (hwd / in.)	5.75 x 4.25 x 5.25
Unit Dimensions (hwd / cm)	14.6 x 10.8 x 13.34
Material of Construction	Plastic
Form Factors Supported	Small Tower
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>