


## 8-Outlet Foldable Power Strip with 1 Pivot, 120V, 12A, 15-ft. Cord, 5-15P, 24 in.

MODEL NUMBER: PSF2408



### Description

The PSF2408 provides a 12-amp, 120v power strip with 8 standard NEMA 5-15 outlets in a rugged, all-metal, mountable housing that folds in the middle. It allows for both vertical and horizontal mounting with additional mounting clips to ensure the pivot stays in place. The PSF2408 is ideal for a variety of uses including office, rack-mount, workbench, industrial and telecom applications. With a NEMA 5-15P, 15-ft. power cord, you don't have to install it next to outlets you already have; it can be mounted across the room and deliver reliable power where you need it most. With a foldable center pivot, the PSF2408 can go around corners, be used by more than 1 person, and fit in smaller spaces. A lighted and covered On/Off switch helps prevent accidental shut-offs, while a 12-amp circuit breaker guards against dangerous circuit overloads. Its sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory or factory environments.

### Features

**Multi-Outlet, Foldable Power Distribution:** Featuring 8 outlets compatible with all standard electrical equipment, the PSF2408 is an ideal solution for applications or locations that require power to many devices simultaneously. With a foldable center pivot, the PSF2408 can go around corners, be used by more than 1 person, and fit in smaller spaces. The 24-in. housing spaces the outlets 2.48 inches apart from center to center, allowing enough room for most AC adapters and transformers.

**Vertical or Horizontal Mounting:** With vertical or horizontal installation, a rugged housing and plenty of outlets, Tripp Lite's PSF2408 is ideal for point-of-sale and retail display applications as it provides reliable, consistent power service for multiple devices. Tripp Lite's power outlet strips can also be used in home office, workbench and rack enclosure applications. The included mounting hardware allows the PSF2408 to be installed wherever reliable, multi-outlet power distribution is required. Extra mounting clips ensure the pivot stays in place.

### Highlights

- Foldable, single pivot 24-in mountable housing
- 8 standard NEMA 5-15R outlets and a 15 ft. power cord
- Lighted, covered On/Off switch and 12-amp circuit breaker
- Sturdy construction and heavy-duty, all-metal housing

### Package Includes

- PSF2408
- Mounting hardware
- Instruction manual



**Extra Long Power Cord:** Install the PSF2408 far away from its power source and provide power distribution to previously un-powered areas with the extra long, 15-ft. power cord. The [PS2408](#) can be mounted in a different area, or a completely different room from where it draws AC power, putting you in control of getting reliable power service where you need it most.

**Premium Safety Features:** The lighted On/Off switch features a translucent cover that eliminates accidental shut-offs while still allowing you to see whether the PSF2408 is operational with a glance. A built-in, 12-amp circuit breaker prevents dangerous circuit overloads that could damage equipment. The breaker immediately shuts off AC input to the [PS2408](#) when it detects that the equipment load is drawing too much power.

**Heavy-Duty Housing:** The PSF2408's rugged, all-metal housing is durably constructed making it a great solution for industrial, retail display and workbench applications.

## Specifications

MODEL TEXT	
Key Benefit	Foldable design is ideal for using around corners and tight spaces, by multiple users, or anywhere you need a flexible power strip that can fold in half to accommodate multiple environments.
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Output (Watts)	1500
Circuit Breaker (amps)	12
Outlet Spacing	1.18 in 1st segment and 2.25 in second segment
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Connection Type	Nema 5-15P
Input Plug Features	Black
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Input Cord Gauge Type	14/3 SJT
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	



Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	1.26 x 1.62 x 24.94
Unit Dimensions (hwd / cm)	3.20 x 4.11 x 63.65
Unit Weight (lbs.)	2.88
Unit Weight (kg)	1.31
Material of Construction	Aluminum
Included Mounting Accessories	Includes mounting clips
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
<b>CERTIFICATIONS</b>	
Certifications	UL 60950
cUL / CSA (Canada)	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>