

Detachable redundant PDU option for select SmartOnline UPS - Hardwired input / L6-30R, C19 output

MODEL NUMBER: **SUPDMB20K**



Description

SUPDMB20K combines the output of two compatible [SU8000RT3UPM](#) or [SU10000RT3UPM](#) UPS power modules for fault-tolerant N+1 or increased capacity configurations. Manual bypass feature enables hot-swappable replacement of both power modules with no disruption in power to connected equipment. (IMPORTANT > compatible only with [SU8000RT3UPM](#) and [SU10000RT3UPM](#) power modules built after 6/2010 with built-in USB and PARALLEL back panel data connections).

Features

<p> </p>

Highlights

- Converts compatible SmartOnline 8 and 10kVA high-voltage UPS configurations for N+1 redundancy or increased capacity when used along with a 2nd compatible UPS power module
- Manual bypass feature enables hot-swappable replacement of both power modules while connected equipment runs uninterrupted
- Hardwired input / L6-30R and C19 output connections

System Requirements

- For use only with configurations involving two compatible [SU8000RT3UPM](#) or [SU10000RT3UPM](#) power modules (requires two of the same model power module built after 6/2010 originally shipping with built-in USB and PARALLEL back panel data connections)

Package Includes

- SUPDMB20K parallel PDU
- Parallel cable
- Owner's Manual

Specifications

OVERVIEW	
Accessories Type	PDU Module



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C19; (2) L6-30R
Output Nominal Voltage	200-240VAC
Overload Protection	2 double pole 30A breakers, 8 double pole 20A breakers
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 230; 240; 220
PHYSICAL	
Shipping Dimensions (hwd / in.)	10 x 23.9 x 12.1
Shipping Dimensions (hwd / cm)	25.4 x 60.7 x 30.7
Shipping Weight (lbs.)	14.52
Shipping Weight (kg)	6.6
Unit Dimensions (hwd / in.)	20.5 x 7 x 4.5
Unit Dimensions (hwd / cm)	52.1 x 17.8 x 11.4
Unit Weight (lbs.)	14.52
Unit Weight (kg)	6.6
Material of Construction	Sheet metal
CERTIFICATIONS	
Certifications	Tested to UL1778 4th Edition (USA), CSA (Canada), EN62040-1
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>