

Micro USB to USB OTG Host Adapter Cable, 5-Pin USB Micro-B to USB-A (M/F), White, 6 in.

MODEL NUMBER: **U052-06N-WH**



Description

The **U052-06N-WH** Micro USB to USB OTG Host Adapter Cable is ideal for expanding the capabilities of your On-the-Go (OTG) smartphone or tablet by connecting it to a variety of USB peripherals. By adding removable storage via thumb drive or connecting a USB keyboard or mouse to your OTG device, you can use it to share data and download videos and presentations.

This six-inch adapter is plug-and-play with no software, drivers or external power supply needed. Just connect its USB Micro-B plug to your OTG-enabled device, and connect the USB peripheral to the adapter's USB 2.0 port. You can also connect a USB hub to the adapter to create more USB ports and connect more USB devices.

Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI interference. Molded nickel-plated connectors with gold-plated contacts ensure excellent conductivity. Integral strain relief ensures the adapter and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

Features

Connects a USB-A Peripheral to Your OTG-Enabled Mobile Device

- Ideal for sharing data and downloading video
- Allows connection of USB hub to connect more devices
- Plug and play—no software, drivers or external power supply

Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts

Highlights

- Plug and play—no software, drivers or external power supply
- Premium double shielding for error-free signal quality
- Molded nickel-plated connectors with gold-plated contacts
- Twisted 28/24 AWG data/power lines
- Allows connection of USB hub to connect more devices

System Requirements

- OTG-enabled smartphone, tablet or other mobile device

Package Includes

- **U052-06N-WH** Micro USB to USB OTG Host Adapter Cable (M/F), White, 6 in.



- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

MODEL TEXT	
Key Benefit	Connects a USB peripheral, such as a thumb drive or keyboard/mouse, to OTG-enabled smartphones, tablets and other devices. Ideal for sharing data and downloading video.
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	White
CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	MICRO-USB B (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>