


32-Port USB Charging Station with Syncing, 5V 80A (400W) USB Charger Output, 2U Rack-Mount

MODEL NUMBER: **U280-032-RM**



Description

The U280-032-RM 32-Port USB Charging Station charges and syncs up to 32 tablets, smartphones and other USB-equipped devices at the same time. Recommended for schools, offices and other environments where multiple USB devices are used, this unit provides up to 5V, 2.4A (12W) of power to each port—plenty for charging battery-intensive devices like the iPad®, iPod®, iPhone® and Android® tablets and smartphones. LED indicators signal the ports in use.

This 32-port charging station supports USB 2.0 data transfer rates up to 480 Mbps and is backward compatible with previous USB generations. To keep up with current technology, a mini-USB firmware port enables software upgrades that allow the charging station to support newer devices.

In addition to charging, the U280-032-RM syncs any USB device using its compatible software—Apple® iTunes® or Apple Configurator, for instance. An included USB cable attaches to the unit's USB-B port and the USB-A port on a computer for syncing purposes.

The durable steel housing mounts in 2U of an EIA-standard 19-inch rack using the included hardware. It also includes four rubber mounting feet for installing the unit on a level surface that can sustain its weight and the weight of the connected cables. An included power cord connects to both the unit's C14 rear inlet and a standard AC power outlet.

Features

Charges Up to 32 Tablets, Smartphones and Other USB Devices

- Recommended for schools, offices and other environments where multiple USB devices are used
- Compatible devices include iPad, iPod, iPhone and Android tablets and smartphones
- Provides up to 5V, 2.4A (12W) of charging power to each port

Highlights

- Maximum charge output of 2.4A per USB port
- Supports USB 2.0 data transfer rates up to 480 Mbps
- Syncs any USB device using its compatible software
- Enables future software upgrades to support newer devices
- Mounts in 2U of EIA-standard 19 in. rack

System Requirements

- Tablet, smartphone or other smart device with USB port
- Computer with available USB port (if syncing)

Package Includes

- U280-032-RM 32-Port USB Charging Station
- NEMA 5-15P to C13 power cord, 10 ft.
- USB 2.0 A/B cable, 6 ft.
- (4) Rubber mounting feet
- Mounting hardware
- Owner's manual



- LED indicators signal ports in use
- Backward compatible with previous USB generations
- Supports data transfer rates up to 480 Mbps

Also Syncs Devices via Connected Computer

- Syncs USB devices using its compatible software, such as iTunes or Apple Configurator
- Included USB cable connects USB-B port and computer's USB-A port

Mini-USB Firmware Port

- Enables future software upgrades to support newer devices

Easy Installation and Connection

- Mounts in 2U of EIA-standard 19 in. rack using included hardware
- Also installs on level surface using included rubber feet
- Conveniently configures for professional, educational or personal installation
- 10 ft. NEMA 5-15P to C13 power cord included
- Durable steel housing

TAA-Compliant

- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

MODEL TEXT	
Key Benefit	2U rack-mountable USB charger with integrated hub charges and syncs up to 32 tablets, smartphones and other mobile devices. Recommended for schools, offices and other environments where multiple USB devices are used.
OUTPUT	
Charging Ports / Amps	(32) 2.4A
Charging Method	USB
INPUT	
Nominal Input Voltage(s) Supported	110V AC; 115V AC; 120V AC
Input Frequency	50/60Hz
Input Current	5A
PHYSICAL	
Shipping Dimensions (hwd / in.)	8.07 x 17.13 x 20.47



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	20.50 x 43.51 x 51.99
Shipping Weight (lbs.)	16.31
Shipping Weight (kg)	7.40
Unit Dimensions (hwd / in.)	3.41 x 17.3 x 11.88
Unit Dimensions (hwd / cm)	8.66 x 43.94 x 30.18
Unit Weight (lbs.)	13.1
Unit Weight (kg)	5.94
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 95 F (0 to 35 C)
Storage Temperature Range	5 to 122 F (-15 to 50 C)
Relative Humidity	5% to 95% RH, Non-Condensing
AC Mode BTU / Hr. (Full Load)	381.98
AC Mode Efficiency Rating (100% Load)	74.57
Operating Elevation (ft.)	10,000
Operating Elevation (m)	3,000
CONNECTIONS	
Ports	32
Side A - Connector 1	USB A (FEMALE)
CERTIFICATIONS	
Certifications	Tested to UL 60950-1: 2007, CAN/CSA-C22.2 No. 60950-1:07, IEC 60950, FCC & IEC Class B, NOM, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>