

Universal Reversible USB 2.0 Hi-Speed Cable, 28/24AWG (Reversible A to 5Pin Micro B M/M), 6-ft.

MODEL NUMBER: **UR050-006-24G**



Description

Tripp Lite's [UR050-006-24G](#) 6-ft. USB 2.0 A to Micro-B cable features a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Micro-USB is the latest generation of USB connector, and is found on Cell Phones, PDA's, USB On-the-Go (OTG) devices, Digital Cameras, Tablets and more. Constructed of premium double-shielded cable with tinned copper braid and aluminum mylar foil featuring twisted 28AWG data lines and 24AWG power lines. 24AWG power lines allow for charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge. USB 2.0 rated cable handles 480Mbps data transfer rates.

Features

- USB Universal / Reversible A Male to Micro-B Male
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

Specifications

| MODEL TEXT | |
|-------------|---|
| Key Benefit | Universal / Reversible "A" connector allows plugging in any direction |

Highlights

- Universal / Reversible "A" Male to Micro-B Male
- Constructed of 24AWG power lines for the charging of higher powered devices such as tablets, which standard 28AWG Micro USB cables can't sufficiently charge
- Premium double-shielded cable with tinned copper braid and aluminum mylar foil features twisted 28AWG data lines and 24AWG power lines
- Supports USB 2.0 data transfer rates up to 480Mbps

System Requirements

- Digital devices that use the USB Micro-B Female socket

Package Includes

- 6-ft. USB2.0 Universal / Reversible A to Micro-USB B Device Cable, 28/24AWG (A Male to Micro-B Male)



| INPUT | |
|-------------------------------------|---------------------------|
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.8 |
| PHYSICAL | |
| Color | Black |
| ENVIRONMENTAL | |
| Operating Temperature Range | -10/+75° C (14 to 167° F) |
| Storage Temperature Range | -20/+80° C (-4 to 176° F) |
| CONNECTIONS | |
| Side A - Connector 1 | REVERSIBLE USB A (MALE) |
| Side B - Connector 1 | MICRO-USB B (MALE) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>