

# Composite Video Gold Cable (RCA M/M), 12-ft.

MODEL NUMBER: A004-012



### Description

Tripp Lite's premium 12 ft. Composite Video Gold Cable offers superior video quality, resulting in brighter, more saturated colors, and sharper images. A Silver-Plated Copper Coaxial Center Conductor, with a low-loss dielectric, prevents signal loss and rejects video noise for the best possible picture.

### Features

- Superb video clarity resulting in brighter colors and sharper images
- Premium grade, 99.99% Pure Copper Center Conductor with Silver Plating
- 6-cut, RCA connector, with split tip center pin, ensures a precise connection
- 24kt gold plating resists corrosion and provides increased durability
- True 75 ohm impedance for widest bandwidth
- Abrasion resistant flexible PVC jacket

## Specifications

OVERVIEW	
UPC Code	037332121837
CONNECTIONS	
Side A - Connector 1	RCA (MALE)
Side B - Connector 1	RCA (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Length (ft.)	12

### Highlights

- High-Purity Copper Coaxial Cable for improved signal transfer and low energy loss
- Double-shielded construction for maximum EMI/RFI protection
- Silver-Plated Center Conductor for the best performance at higher video frequencies
- Excellent noise isolation with 100% aluminum/mylar foil and braid shielding

### System Requirements

- Home theater equipment with RCA digital audio/video connectors

### Package Includes

- 12 ft. Composite Video Gold Cable



Powering Business Worldwide



Cable Length (m)	3.66
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.39
Shipping Weight (kg)	0.18
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.