

S-Video Gold Cable (MD4 M/M), 6-ft.

MODEL NUMBER: A012-006



Highlights

- Constructed of high quality , 99.99% pure solid copper conductors
- True 75 ohm impedance for maximum bandwidth
- Double-shielded construction provides superior protection against EMI/RFI
- Excellent noise isolation with 100% aluminum mylar foil/braid shielding

System Requirements

- Home theater equipment with S-Video connectors

Package Includes

- 6 ft. S-Video Gold Cable

Description

Tripp Lite's Premium S-Video Gold Cable offers superior video quality, resulting in brighter, more saturated colors, and sharper images. S-Video separates brightness from color, using two separate coaxial conductors to create clean, accurate signals.

Features

- Superb video clarity resulting in brighter colors and sharper images
- Premium-grade, 99.99% pure copper conductors
- 24kt gold precision machined connector provides solid contact and resistance to corrosion
- Double-shielding ensures maximum protection against electromagnetic and radio frequency interference

Specifications

OVERVIEW	
UPC Code	037332121851
Technology	S-Video
CONNECTIONS	
Side A - Connector 1	S-VIDEO (MALE)
Side B - Connector 1	S-VIDEO (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Length (ft.)	6



Powering Business Worldwide



Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.34
Shipping Weight (kg)	0.15
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.