

BNC All-in-One Keystone/Panel Mount Coupler (F/F), 75 Ohms

MODEL NUMBER: **A230-001-KP**



Highlights

- Gold-plated contacts for optimal signal transfer
- Panel mount adapter for securing to podium or kiosk
- Snaps easily into standard data wall plate or patch panel
- Compatible with all BNC coaxial cables
- Rated for 75 ohms

Package Includes

- A230-001-KP BNC All-in-One Keystone/Panel Mount Coupler (F/F), 75 Ohms

Connects two BNC coaxial cables to create one longer cable. Snaps into keystone cutout of a wall plate or patch panel. Or use the included panel mount adapter for installation in a podium or kiosk.

Description

The A230-001-KP BNC Keystone/Panel Mount Coupler (F/F) connects two BNC coaxial cables to create one longer connection. Its keystone design snaps easily into the cutout of a wall plate or patch panel. An optional BNC panel mount coupler is included for securing the keystone jack to a podium or kiosk. Compatible with all BNC coaxial cables, the A230-001-KP features molded nickel-plated connectors with gold-plated contacts for optimal signal transfer. Rated for 75 ohms.

Features

Strengthens Your BNC Coaxial Connection

- Connects 2 BNC coaxial cables for a longer cable run
- Keystone design for easy snap-in installation in wall plate or patch panel
- Includes panel mount connector for installation in podium or kiosk
- Molded nickel-plated connectors with gold-plated contacts for optimum signal transfer
- Compatible with all BNC coaxial cables
- Rated for 75 ohms

Specifications

OVERVIEW	
UPC Code	037332199669
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	White
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
CONNECTIONS	
Side A - Connector 1	BNC (FEMALE)
Side B - Connector 1	BNC (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	RG59/RG6
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>