

Inverters & Inverter/Chargers - Remote Control Module

MODEL NUMBER: APSRM

Description

Tripp Lite's APSRM provides remote monitoring and control of PowerVerter PLUS and PowerVerter APS Inverter systems that support the remote control module connector feature. Compact housing, mountable via 4 user supplied screws, includes 6 LEDs, a 2 position switch and detachable 50 foot remote cable with modular RJ style connectors. When used in conjunction with a PowerVerter PLUS inverter system, APSRM reports status via 3 built-in battery voltage level LEDs, 3 load level LEDs and power off/on control via built in switch. When used in conjunction with a PowerVerter APS inverter/charger/auto-transfer system, APSRM reports status via 3 built-in battery voltage level LEDs, plus 3 LED indicators for load level, inverter power and line power availability. Package ships with two user installable labels to properly identify controls when used either with a PowerVerter PLUS or PowerVerter APS system. Includes 50 foot remote cable.

Features

- APSRM works in conjunction with PowerVerter PLUS and PowerVerter APS inverters that support the remote module connector feature
- Enables remote inverter power off/on control and status monitoring in applications, such as automotive
 or marine, where access to inverter front panel controls and indicators is not convenient or safely
 possible
- Built-in status LEDs indicate 7 different levels of battery charge, from low to high, plus 2 flashing programs to indicate excessive discharge or overcharge condition
- When used in conjunction with PowerVerter PLUS systems, APSRM indicates 6 levels of output load capacity, plus 1 flashing program to indicate overload condition
- When used in conjunction with PowerVerter APS systems, APSRM indicates load levels of over 90%, inverter power operation and line power operation
- Mountable with 4 user supplied screws
- Includes 50 ft cable

Specifications

OVERVIEW		
UPC Code	037332117540	
Accessory Type	Remote Control Module	
Accessory Class	Power Inverter Accessories	
INPUT		
Voltage Compatibility (VDC)	NA NA	
ОИТРИТ		
Pure Sine Wave Output	No	
Nominal Output Voltage(s) Supported	100V	
Output Receptacles	5-15/20R	

Highlights

- Intuitive "traffic light" LED readouts
- Complete remote monitoring and control

Package Includes

- APSRM remote control accessory
- 50 foot control cable
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Continuous Output Capacity (Watts)	0	
PHYSICAL		
Shipping Dimensions (hwd / cm)	19.68 x 20.32 x 3.81	
Shipping Dimensions (hwd / in.)	7.75 x 8.00 x 1.50	
Shipping Weight (kg)	0.64	
Shipping Weight (lbs.)	1.40	

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies