

## Protect It! 8-Outlet A/V Surge Protector, 10-ft. Cord, 3240 Joules, Tel/Modem/Coax Protection

MODEL NUMBER: AV810



### Highlights

- 8 outlets / 10-ft. cord with space saving right angle plug
- 3240 joule rating
- 2-line High Definition 2.2 GHz (gold) coaxial surge protection
- 1-line tel/modem surge protection

### Package Includes

- AV810 Gold Series Audio Video Surge / Spike Suppressor
- 6 ft. coaxial cable
- 6 ft. phone cord
- Instruction manual with warranty information

### Description

Tripp Lite's AV810 Gold Series Audio Video Surge / Spike Suppressor provides high performance protection (3240 joules) stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to the heaviest transient surges. Two pairs of HD 2.2 GHz coax line suppression jacks protect any two type F coax lines for cable-TV, satellite, broadcast antenna or cable modems. 1 set of RJ11 jacks offers surge suppression for pay-per-view HD satellite systems, dial-up and DSL modems. The AV810 offers 8 total outlets, 10-foot cord with space-saving right angled plug and diagnostic LEDs with audible alarm to warn of wiring problems and suppressor damage. Integrated child-safety outlet covers safely seal off unused outlets. Black high impact plastic housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of Audio Video systems. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- 3240 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Phone line surge suppression protects both dialup and DSL modems, plus fax machines, cordless phones and more (pair of RJ11 jacks, 2-wire, 1 line, includes 6-ft. phone cable)
- Two sets of coax jacks protect cable modems, plus satellite, cable TV and broadcast antennas (pair of type N coax jacks, includes 6-ft. coax cable. One set provides digital broadband quality and can handle 2.2GHz bandwidths)
- Long 10 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Lighted power switch with integrated 15A circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Audible alarm offers notification of suppressor damage
- Attractive black suppressor housing with keyhole mounting tabs allow versatile placement options

- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

| OVERVIEW                           |   |
|------------------------------------|---|
| UPC Code                           | 037332144423  |
| INPUT                              |   |
| Nominal Input Voltage(s) Supported | 120V AC   |
| Recommended Electrical Service     | 120V, 15A   |
| Input Cord Gauge Type              | 14 gauge; SJT   |
| Voltage Compatibility (VAC)        | 120   |
| Maximum Surge Amps                 | 216000  |
| Input Plug Type                    | NEMA 5-15P  |
| Input Cord Length (ft.)            | 10  |
| Right-Angle Plug                   | Yes   |
| Input Cord Length (m)              | 3.05  |
| Integrated Cord Clip               | No  |
| OUTPUT                             |   |
| Frequency Compatibility            | 50 / 60 Hz  |
| Output Receptacles                 | (8) 5-15R   |
| Circuit Breaker (amps)             | 15  |
| Transformer Accommodation          | (6) Yes   |
| Outlet Orientation                 | Single row of 5, plus a second row of 3 for transformer accommodation                     |
| Right-Angle Outlets                | No  |
| Outlet Safety Covers Detail        | Includes built-in sliding outlet safety covers  |
| USER INTERFACE, ALERTS & CONTROLS  |   |
| Diagnostic LED(s)                  | Yes   |
| Switches                           | Combination AC circuit breaker and 2-position red illuminated on/off power switch         |
| Audible Alarm                      | Audible alarm   |
| Diagnostic LED Details             | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION          |   |
| AC Suppression Joule Rating        | 3240  |
| AC Suppression Response Time       | < 1 ns  |
| Protection Modes                   | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression        |



Powering Business Worldwide



|  |   |
|--|---|
| UL1449 Let Through Rating                                  | 330/400/400   |
| EMI / RFI Filtering  | Up to 40 dB   |
| Automatic Shut-Off   | No  |
| <b>DATALINE SURGE SUPPRESSION</b>                          |   |
| Telephone/DSL Protection Details                           | 1 line  |
| Cable (Coax) Protection                                    | Yes   |
| Cable (Coax) Protection Details                            | 1 line  |
| Network (Ethernet) Protection                              | No  |
| Telephone/DSL Protection                                   | Yes   |
| <b>PHYSICAL</b>  |   |
| Color  | Black   |
| Material of Construction                                   | Plastic   |
| Power Cord Color   | Black   |
| Mounting Holes or Slots                                    | Yes   |
| Slot or Hole Mount Measurement (Center to Center)          | Distance between horizontal slots = 75mm; Distance between vertical slots = 41.6mm  |
| Receptacle Color   | Gray  |
| Shipping Dimensions (hwd / in.)                            | 10.70 x 2.20 x 8.80   |
| Shipping Dimensions (hwd / cm)                             | 27.18 x 5.59 x 22.35  |
| Shipping Weight (lbs.)                                     | 2.60  |
| Shipping Weight (kg)                                       | 1.18  |
| Unit Dimensions (hwd / in.)                                | 4.860 x 9.550 x 1.510   |
| Unit Dimensions (hwd / cm)                                 | 12.34 x 24.26 x 3.84  |
| Unit Weight (lbs.)   | 2.02  |
| Unit Weight (kg)   | 0.92  |
| <b>FEATURES &amp; SPECIFICATIONS</b>                       |   |
| Rotatable Outlets  | No  |
| Antimicrobial  | No  |
| <b>WARRANTY &amp; SUPPORT</b>                              |   |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty   |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$250,000 &nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &nbsp; |



*Powering Business Worldwide*



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.