

Isobar 6-Outlet A/V Surge Protector, 6-ft. Cord, 3330 Joules, Tel/Coax Protection

MODEL NUMBER: AVBAR6



Highlights

- 6 outlets / 6-ft. cord with space saving right angle plug
- 3330 joule rating
- Isolated Filter Banks
- 2-line High Definition 2.2 GHz (gold) coaxial surge protection
- 1-line tel/modem surge protection
- All-metal housing

Description

Tripp Lite's AVBAR6 Platinum Series Isobar Audio Video Surge / Spike Suppressor provides premium protection (3330 joules) stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small-to-medium Audio/Video installations: high-definition video displays, HD Cable / HD satellite sources and A/V receivers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 6 outlets (widely spaced outlets accommodate up to 2 transformers and plug-in safety covers), 2-line HD 2.2 Ghz coaxial protection and 1-line tel/modem protection safeguard an entire A/V system. \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). Includes all-metal housing, three diagnostic LEDs (Line OK, Grounded & Protected) and 6-ft. cord with a right-angle plug. Additional accessories include; 6-ft. coaxial cable and 6-ft. phone cord.

Features

- 3330 joules surge / spike suppression protection rating
- EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- Isolated Filter Banks eliminate interference between connected components
- All-metal housing safely withstands the strongest surges
- 6 surge-protected NEMA 5-15R AC outlets safeguard an Audio / Video system
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected components against surge damage...for life!
- Widely spaced outlets accommodate up to 2 transformers
- Four plug-in safety covers protect against accidental contact
- 2 sets of surge-protected Type F gold HD 2.2 GHZ coaxial connectors (with included 6-ft. coaxial cable) safeguard components on cable, satellite or antenna line
- 1-line tel/modem surge protection (with included 6-ft. phone cord) safeguards personal video recorders (Satellite, PVRs) on a single dial-up line.
- 6-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a Audio

Video system

- 3 diagnostic LEDs alert user to protection, line power and fault status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- All-metal housing (black) stands up to the most demanding environments
- Tested to UL and cUL, RoHS compliant

Specifications

OVERVIEW	
UPC Code	037332144362
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V, 15A
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	135000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	12
Transformer Accommodation	(2) Yes
Right-Angle Outlets	Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and illuminated 2-position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm line power, protection and fault status
SURGE / NOISE SUPPRESSION	



Powering Business Worldwide



AC Suppression Joule Rating	3330
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	330V
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	2 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Metal
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between horizontal tabs = 210.79mm; Distance between vertical tabs = 58.17mm
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 39.45mm; Distance between vertical outlets = 39.30mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.50 x 7.20 x 12.30
Shipping Dimensions (hwd / cm)	6.35 x 18.29 x 31.24
Shipping Weight (lbs.)	3.50
Shipping Weight (kg)	1.59
Unit Dimensions (hwd / in.)	2.500 x 9.000 x 3.500
Unit Dimensions (hwd / cm)	6.35 x 22.86 x 8.89
Unit Weight (lbs.)	2.8
Unit Weight (kg)	1.27
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.