

Administrative management is accomplished through the Administration and Security Management 1.2 utility. This free download (see Support tab above) provides management of user credentials, logs, EDID locking and restoring factory defaults. The Admin and Security Management 1.2 utility is available for Windows only. For managing Mac computers connected to the KVM, settings must be applied through a Windows PC.

2-Port Dual-Monitor Secure KVM Switch, DisplayPort - 4K, NIAP PP3.0, Audio, TAA

MODEL NUMBER: B002A-DP2A2



NIAP-certified KVM switch lets you switch between 2 computers with government- and military-level security and data protection.

Features

2-Port DisplayPort KVM Switch Is Ideal for Applications That Demand Secure Networks

This two-port KVM switch is recommended for any government, military, financial or healthcare environment where tight security of sensitive data is of utmost importance in a world of constantly changing cyberthreats. Each KVM port is an electronically isolated channel, making it impossible for data to be transferred between connected computers through the KVM. The dual-monitor switch supports crystal-clear Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz.

NIAP PP3.0 Certified to Meet Today's Top Information Assurance Standards

This KVM switch is certified by NIAP (National Information Assurance Partnership), which is operated by the National Security Agency (NSA), to the latest Common Criteria Protection Profile for Peripheral Sharing Switches Version 3.0. Discrete processing paths to each connected system prevent data leakage, transfer and crosstalk between adjacent ports. Peripheral isolation enables data to flow from device to host only.

Top-of-the-Line Security Features Keep Your Data Safe

Special protection prevents re-programming of firmware, so the switch's KVM logic remains unaltered. The keyboard buffer clears automatically after data transmission, ensuring no information is left stored. Plus, you can only access connected computers via buttons on the switch's panel. Other port-switching methods, such as On-Screen Display (OSD) and Hotkey Commands, have been excluded to further ensure data integrity.

Anti-Tampering Protection Prevents Physical Breaches

If the housing is opened, internal anti-tamper switches will disable the unit, causing it to become inoperable and the front-panel LEDs to flash repeatedly. Seals on the enclosure will provide visual evidence of tampering.

Maintains Constant Keyboard and Mouse Emulation for Smooth No-Delay Switching

Full USB device filtering ensures support for keyboard and mouse only. This KVM switch also supports secure video emulation and EDID learning, which prevents unwanted data from transmitting through the DDC lines. Both keyboard/mouse and video emulation controllers restrict discovery of newly connected peripherals or monitors during switching operations, shielding your computers from potential

Highlights

- Safely and securely switches between 2 isolated computers with different security levels
- Certified to NIAP/Common Criteria Protection Profile for Peripheral Sharing Switches V3.0
- Dual-monitor support enables convenient multitasking and increased productivity
- Supports UHD resolutions up to 4K @ 30 Hz for crystal-clear video
- Complies with Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Control up to 2 computers with different security levels from a single monitor/keyboard/mouse
- Protect private information, such as medical or military intelligence data, from cyberattacks

System Requirements

- DisplayPort monitors
- Wired USB mouse/keyboard with no internal hub or composite device functions (wireless mouse/keyboard not supported)
- Computer with DisplayPort and USB ports
- Computer and speakers with 3.5 mm stereo audio port (optional)
- Windows, Mac, Linux or any



vulnerabilities.

Accessory Cable Kits - P783-006-DP and P783-010-DP

Designed specifically for the B002A-DP2A2, Tripp Lite's P783-006-DP and P783-010-DP KVM cable kits (sold separately) help eliminate unnecessary clutter and save you money by combining cables into one convenient kit. These cables comply with HDCP 2.2 and DisplayPort 1.2 standards and support USB 2.0 speeds up to 480 Mbps.

TAA-Compliant for GSA Schedule Purchases

The B002A-DP2A2 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

other major operating system

Package Includes

- B002A-DP2A2 2-Port NIAP
PP3.0-Certified DisplayPort
KVM Switch
- External power supply w/NEMA
1-15P plug & 5 ft. cord (Input:
100–240V, 50/60 Hz, 0.8A;
Output: 12V 2A)
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332261526
Technology	DisplayPort; USB
VIDEO	
Max Supported Video Resolution	3840 x 2160 @30Hz
Max Supported Color Depth	36-bit Deep Color
Chroma Sub Sampling	4:4:4
INPUT	
Voltage Compatibility (VAC)	100; 110; 125; 127; 200; 208; 220; 230; 240
Redundancy - Dual Power Inputs	No
External Power Supply Plug(s)	NEMA 1-15P North America
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
External Power Supply Output Specs (V / A)	12V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve



External Power Supply Certifications	FCC; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x2) GREEN / PORT SELECTION, (x2) BLUE / EDID (PUSH-BUTTON), (x2) GREEN / VIDEO CONSOLE
PHYSICAL	
Color	Black
Material of Construction	Metal
Rackmountable	No
Unit Dimensions (hwd / in.)	8.8 x 2.63 x 6.69
Unit Packaging Type	Box
Unit Weight (kg)	1.75
Unit Weight (lbs.)	3.85
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	4 to 140 F (-20 to 60 C)
Relative Humidity	0% to 80%, Non-Condensing
COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	DisplayPort; USB
Side A - Connector 1	3.5MM (FEMALE)
Side A - Connector 2	(2) DISPLAYPORT (FEMALE)
Side A - Connector 3	(2) USB A (FEMALE)
Side B - Connector 1	(2) 3.5MM (FEMALE)
Side B - Connector 2	(4) DISPLAYPORT (FEMALE)
Side B - Connector 3	(2) USB B (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	Displayport
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	Displayport
FEATURES & SPECIFICATIONS	



Number of Users	1
NIAP-Certified Secure	Yes
Port Selection	Pushbutton
Displayport Specification	1.2
USB Specification	USB 1.1 (up to 12 Mbps)
Common Access Card (CAC) Support	No
Cat5 KVM Switch	No
STANDARDS & COMPLIANCE	
Certifications	Certified to NIAP PP3.0
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>