

## 2-Port USB-C KVM Dock - 4K HDMI, USB 3.2 Gen 1, USB-A Hub, Remote Selector, 85W PD Charging, Black

MODEL NUMBER: B003-HC2-DOCK1



Controls a USB-C laptop and a USB-C smartphone using one centralized HDMI monitor and USB keyboard/mouse.

### Features

**Connects 2 USB-C Sources to a Single HDMI Monitor, Keyboard and Mouse**This Desktop KVM/Docking Station lets you access, control, boot and reboot 2 USB-C sources at the same time. Both USB-C sources share one HDMI monitor, USB keyboard and USB mouse, which saves space on your desk or workspace.

**Supports USB-C DisplayPort Alternate Mode for Transmitting Audio/Video Signals**By connecting the included USB-C cable to a source device that supports USB DisplayPort Alt Mode, you can output 4K video and digital audio to a compatible monitor, television or projector without installing special software drivers. The B003-HC2-DOCK1 lets you build a workstation for multitasking by giving you the ability to extend screens, connect USB peripherals and switch between sources with ease.

**Transmits Crystal-Clear 4K Video**The HDMI port support 4K resolutions up to 3840 x 2160 at 30 Hz.

**USB Hub Lets You Share Peripherals between Computers**The built-in two-port USB 3.1 Gen1 hub allows you to share USB peripherals, such as printers, hard drives, scanners, webcams and flash drives, between both connected computers/sources. The hub is backward compatible with USB 2.0 and 1.1 devices.

**USB-C PD 3.0 Charging Port Charges the Connected Notebook, Tablet or Other Device**The USB-C Power Delivery 3.0 port supports power output up to 85W, which is sufficient for charging and powering the connected source device, such as an Android smartphone or Chromebook. Just connect the device's AC wall charger to the USB-C PD port.

**Switching Between Computers Is Fast and Easy**Connect the included remote port selector to the specified port on the B003-HC2-DOCK1 and simply press the button anytime you want to switch between your USB-C sources. White LEDs indicate which computer is currently selected.

**Cables Are Included for Fast and Simple Setup**Connect your two USB-C sources using the included USB-C (M/M) cables. The plug-and-play B003-HC2-DOCK1 requires no drivers, so you can connect and use it immediately. It works with all major operating systems, including Windows and Mac.

### Highlights

- Converts audio/video signals from sources supporting USB-C DisplayPort Alt Mode
- HDMI port supports UHD resolutions up to 4K @ 30 Hz for crystal-clear video
- USB-C PD 3.0 port supports 85W power output for charging host computer
- USB 3.2 Gen 1 data ports allow connection of flash drives and other peripherals
- Remote port selector allows fast one-touch switching between connected devices

### Applications

- Control 2 USB-C devices using one keyboard, mouse and HDMI display
- Extend or mirror your laptop or PC monitor on multiple displays to aid in multitasking and increase productivity
- Save money and space by sharing USB peripherals, such as a printer and external hard drive, between 2 connected computers

### System Requirements

- Source device(s) with USB-C output
- Display device with HDMI input
- Computer with Windows 10 and above, USB-C port and USB-C DisplayPort Alt Mode compliance



- Computer with Mac OS X 10.12 and above and USB-C port
- Smartphone with Android 8.0 and above, USB-C port and USB-C DisplayPort Alt Mode compliance
- iPad Pro 3rd gen (2018) with iOS 12.1 and above
- This USB-C KVM dock does not support Apple iPhone

#### Package Includes

- B003-HC2-DOCK1 2-Port USB-C KVM Dock, Black
- Remote port selector
- (2) USB-C cables (M/M), 1 m
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332256621
Technology	HDMI; PD Charging; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1)
INPUT	
Bus Powered	Yes
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Port 1/2 (White)
PHYSICAL	
Color	Black
Material of Construction	Aluminum



Rackmountable	No
Unit Dimensions (hwd / in.)	5.63 x 4.69 x 0.96
Unit Packaging Type	Box
Unit Weight (kg)	0.38
Unit Weight (lbs.)	0.83
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	-4 to 140°F (-20 to 60°C)
Relative Humidity	0% to 80% RH, Non-Condensing
Power Provided to Connected Device(s)	USB-C PD 3.0 Port: 100W (20V/5A), USB-C Port 1: 85W, USB-C Port 2: 10W
<b>COMMUNICATIONS</b>	
IP Remote Access	No
<b>CONNECTIONS</b>	
Ports	2
PC/Server Connections	USB
Side A - Connector 1	(3) USB C (FEMALE)
Side B - Connector 1	HDMI (FEMALE); (2) USB A (FEMALE)
Computer Keyboard and Mouse Interface	USB
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	HDMI
<b>FEATURES &amp; SPECIFICATIONS</b>	
Number of Users	1
NIAP-Certified Secure	No
Port Selection	Remote Selector
Max Supported Video Resolution	3840 x 2160 @ 30Hz
HDMI Specification	1.4
HDCP Specification	1.4
USB Hub Ports	Yes
Number of USB Hub Ports	2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cat5 KVM Switch	No
Max Supported Color Depth	36-bit Deep Color
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>