

8-Port 1U Rack-Mount KVM Switch, PS/2

MODEL NUMBER: **B004-008**



Description

Tripp Lite's B004-008, 8-Port KVM Switch, is a low-cost solution for IT managers needing a KVM switch for up to 8 CPU's. Use on a desktop or in the rack; comes with 19" rackmount hardware. This switch provides two convenient methods to access any PC connected to the unit: Port Selection buttons located on the front panel, or, Hot-Key commands from the keyboard. A powerful Quick View Scan Mode feature allows you to auto-scan and monitor the activities of all installed operating PC's, one-by-one. Choose from three different cable lengths to connect from the switch to the CPU: P750-006, P750-010, or P750-015. (For computers with USB keyboard and mouse inputs, use Tripp Lite B015-000, PS/2 to USB converter, in conjunction with the P750 cable kit). For a more feature rich 8-port KVM switch, with On Screen Display (OSD) menu functions, as well as expandability, see Tripp Lite B042-008. Constructed of heavy-duty steel housing.

Features

- Control up to 8 PC's from a single console
- No software required - Switch between ports via front panel push buttons or hotkey commands
- Quick View Scan Mode for monitoring selected PC's
- PS/2 and Serial Mouse emulation provided for system boot-up
- Microsoft Intellimouse Pro, Logitech FirstMouse, FirstMouse+ support
- SVGA, VGA, and MultiSync monitor support
- Push Button LED display for easy status monitoring
- Rack mountable in 19" system rack - mounting hardware included with switch
- Hot Pluggable - add or remove PC's without powering down the switch
- Compatible with all major operating systems
- Superior Video Quality: 1920x1440; DDC2B
- Constructed of heavy-duty steel housing
- 19"W x 6"D x 1.75"H - 6.25lbs

Highlights

- Low Cost Switching Solution
- Does not require software or complicated setup simply Plug and Play
- Ultra-Compact – occupies only 1U rack space

System Requirements

- PS/2 mouse
- PS/2 keyboard
- Computer with PS/2 mouse and keyboard ports or an available USB port
- 1 P750-Series PS/2 KVM cable kit per PS/2 computer; or, 1 P750-Series PS/2 KVM cable kit and 1 B015-000 PS/2 to USB adapter per USB computer
- Compatible with all major operating systems

Package Includes

- 8 Port KVM Switch (Rackmount Ready)
- Optional AC Power Adapter - (Input: 100-240V, 50/60Hz, 0.5A Output: 9V/1.44A)
- Manual



Specifications

OVERVIEW	
UPC Code	037332125323
AC Adapter	(Input: 100-240V, 50/60Hz, 0.5A Output: 9V/1.44A)
Console	No
Max CPU	8
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.25 x 21.75 x 11.50
Shipping Dimensions (hwd / cm)	10.80 x 55.24 x 29.21
Shipping Weight (lbs.)	6.80
Shipping Weight (kg)	3.08
Unit Dimensions (hwd / in.)	1.75 x 19 x 6
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 15.24
Unit Weight (lbs.)	6.25
Unit Weight (kg)	2.83
Color	Black
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys
IP Remote Access	Yes
CONNECTIONS	
Ports	8
PC/Server Connections	VGA; USB; PS/2
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No
Cat5 KVM Switch	No
Technology	PS/2; USB; VGA/SVGA
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>