

## 2-Port DisplayPort KVM Switch with Audio, Cables and USB 3.0 SuperSpeed Hub

MODEL NUMBER: B004-DPUA2-K



Control 2 DisplayPort computers using one DisplayPort monitor, USB keyboard and USB mouse. Connect USB 3.0 peripherals, such as hard drives and webcams, and share them between computers.

### Features

#### Access and Control 2 Computers with One KVM Switch

- Switch between computers using keyboard hotkeys or front-panel buttons
- Auto Scan feature cycles between computers at regular intervals for at-a-glance observation of activity
- Monitor's EDID information sent to connected computer when selected
- Supports DisplayPort 1.1

#### Independent Audio Switching

- 3.5 mm mini-stereo speaker and microphone jacks allow sharing of audio equipment between computers
- Listen to audio files on one computer while accessing the other computer
- Supports 2-channel stereo audio

#### Independent USB 3.0 Peripheral Sharing

- 2-port USB 3.0 SuperSpeed hub allows connection of peripherals, such as webcams, flash drives, printers and scanners
- Print documents from one computer while accessing the other computer
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Backward compatible with USB 2.0 and USB 1.1 devices

#### Compatible with All Major Operating Systems

- Easy to set up with no software or drivers to install
- Supports digital video resolutions up to 2560 x 1600, including 1080p
- Works with Windows, Mac, Linux and Sun
- All necessary cables included

### Highlights

- Connect peripherals to built-in 2-port USB 3.0 hub
- Switch between computers via front buttons or keyboard hotkeys
- Supports digital video resolutions up to 2560 x 1600
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Supports Displayport 1.1
- Includes all necessary DisplayPort, USB 3.0 and audio cables

### System Requirements

- DisplayPort-enabled monitor
- USB keyboard and mouse
- Speaker and microphone with 3.5 mm mini-stereo plugs (for audio)
- Computer with USB port (need USB 3.0 port for USB 3.0 speeds)
- Computer with 3.5 mm mini-stereo jacks (for audio)
- Compatible with all major operating systems

### Package Includes

- B004-DPUA2-K 2-Port DisplayPort KVM Switch
- (2) DisplayPort cables, 4-ft. (1.22 m)
- (2) USB 3.0 Type-A to Type-B cables, 4-ft. (1.22 m)
- (2) 3.5 mm mini-stereo cables, 4-ft. (1.22 m)
- External power supply (Input: 100/240V, 50/60 Hz, 0.5A; Output: 9V, 2A)
- Universal plug adapters (NEMA 1-15P, CEE 7/16, BS1363, and AS3112)
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

## Specifications

OVERVIEW	
UPC Code	037332188625
Technology	DisplayPort; Stereo Audio
VIDEO	
Max Supported Video Resolution	2560 x 1600 @60Hz
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
AC Power Adapter Output Specs (V / A)	9V / 2A
AC Power Adapter Cord Length (ft.)	6
AC Power Adapter Cord Length (m)	1.83
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
POWER	
Power Source Type	AC Adapter
DC Barrel Plug	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	5.8
CONNECTIONS	
Number of Ports	2
PC/Server Connections	USB; DisplayPort
Side A - Connector 1	(2) DISPLAYPORT (FEMALE)
Side A - Connector 2	(2) USB 3.0 B (FEMALE)
Side A - Connector 3	(4) 3.5MM (FEMALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
Side B - Connector 2	(2) USB 3.0 A (FEMALE)
Side B - Connector 3	(2) USB A (FEMALE)
Side B - Connector 4	(2) 3.5MM (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	Displayport
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	Displayport



Powering Business Worldwide

TRIPP LITE  
SERIES

Connector Plating	Nickel
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Red (USB); White (Selected PC)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Cable Jacket Color	Black
Shipping Dimensions (hwd / in.)	6.90 x 8.10 x 5.50
Shipping Dimensions (hwd / cm)	17.53 x 20.57 x 13.97
Shipping Weight (lbs.)	3.00
Shipping Weight (kg)	1.36
Unit Dimensions (hwd / in.)	1.800 x 6.500 x 3.500
Unit Packaging Type	Box
Unit Weight (lbs.)	1.3
Unit Weight (kg)	0.59
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0-90% non-condensing
BTUs	19.8 BTU/Hr
<b>COMMUNICATIONS</b>	
IP Remote Access	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
Number of USB Hub Ports	2
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
NIAP-Certified Secure	No
Number of Users	1
Autoscan (Y,N)	Y
Port Selection	Pushbutton; Hotkey
Displayport Specification	1.1
Driver Required	No
Autoscan Duration	10 to 60 seconds (DEFAULTS AT 10, USER DEFINABLE IN 10 SECOND INTERVALS).



Powering Business Worldwide

TRIPP LITE  
SERIES

STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; GS; BS; RCM; CB
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.