

# 2-Port Compact USB KVM Switch with Audio and Cable

MODEL NUMBER: B004-VUA2-K-R



2-port Compact USB KVM Switch with optional audio and microphone switching function allows you to access control boot and reboot two USB-enabled computers from a single keyboard monitor and mouse

## Features

- Fast, easy switching via keyboard hot keys, push buttons or software
- Plug-and-play setup - no software required
- Hot-swap capability allows easy addition or removal of computers without powering down the switch or other computers
- Speaker and microphone connections allow sharing of audio components between systems (standard 3.5 mm audio connections)
- Independent audio switching allows you to listen to audio from one computer while switching to the other computer
- Supports video resolutions up to 2048 x 1536 (standard 15-pin VGA connectors)
- Supports Microsoft® IntelliMouse® and the scrolling wheel on most mice]
- Compact design saves desk space
- Does not require an AC adapter
- Compatible with all major operating systems
- Includes two, 6-ft. (1.83 m) Cable Kits

## Highlights

- Fast, easy switching via keyboard hot keys, push buttons or software (not required)
- PC and Mac compatible
- Allows sharing of audio components between systems; listen to music from one computer while switching to the other computer
- Compact design saves desk space
- No AC adapter required
- (x2) 6-ft. (1.83 m) USB KVM Cable kits and (x2) 6-ft. (1.83 m) 3.5mm Audio Cable kits included
- Compatible with all major operating systems

## System Requirements

- Console: VGA, SVGA or Multisync Monitor, USB Keyboard and USB Mouse
- Computers: VGA, SVGA or Multisync Monitor Port and USB Port
- Audio (Optional): Speakers with standard 3.5 mm Connectors and a computer with 3.5mm ports
- Compatible with all major operating systems

## Package Includes

- Compact 2-port USB KVM Switch with Audio
- (2) 6-ft. (1.83 m) USB KVM Cable Kits and (2) 6-ft. (1.83 m) 3.5mm Audio Cable Kits
- CD-ROM with KVM Switcher Software
- Owner's Manual with Warranty Information

## Specifications

OVERVIEW	
UPC Code	037332140043
Product Type	KVM
Console	No

Max CPU	1
Technology	VGA/SVGA; Stereo Audio
Host Connector	(2) USB A (FEMALE)
<b>VIDEO</b>	
Video Input	HD15 (FEMALE)
Video Output	HD15 (FEMALE)
Number of Monitors Supported	1
Video Ports	(3) HD15 (FEMALE)
Max Supported Video Resolution	2048 x 1536 @60Hz
<b>AUDIO</b>	
Audio Ports	(2) 3.5MM (FEMALE)
Audio Ports Details	Connect a microphone and speaker via the dual 3.5mm audio ports
Audio Input	3.5mm
Audio Output	Audio
Audio Specification	Stereo Audio
<b>DATA</b>	
Data Ports	(2) USB A (FEMALE)
Data Ports Details	(2) USB-A - USB 2.0
<b>INPUT</b>	
Bus Powered	Yes
Power Source	Bus; USB
<b>POWER</b>	
Power Consumption (Watts)	0.5
<b>CONNECTIONS</b>	
Number of Ports	2
Daisy-Chain Port	No
Firmware Upgrade Port	No
PC/Server Connections	USB; VGA
Side A - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	(2) USB A (FEMALE)
Side B - Connector 3	(2) 3.5MM (FEMALE)

Side B - Connector 4	(2) USB MINI-B 5-PIN (FEMALE)
Included Cable (Side A) - Connector 1	Yes
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	VGA
Connector Plating	Nickel
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Green (Selected PC)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS
Cable Jacket Color	Black
Total Number of Ports	9
Shipping Dimensions (hwd / in.)	3.00 x 7.90 x 7.80
Shipping Dimensions (hwd / cm)	7.62 x 20.07 x 19.81
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
Unit Weight (lbs.)	0.22
Unit Weight (kg)	0.10
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0%-90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
ESD Protection	Yes
<b>COMMUNICATIONS</b>	
Hotkey	Yes
IP Remote Access	No
EDID Compatible	Yes



Powering Business Worldwide



IR Remote Extension Support	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
USB Specification	USB 2.0 (up to 480 Mbps)
NIAP-Certified Secure	No
Number of Users	1
Autoscan (Y,N)	Y
On-Screen Display (OSD)	No
Port Selection	Pushbutton; Hotkey; Software
Driver Required	No
Autoscan Duration	10 - 60 seconds
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.