

2-Port Compact USB KVM Switch with Audio and Cable

MODEL NUMBER: **B004-VUA2-K-R**



Description

The B004-VUA2-K-R is a 2-port Compact USB KVM Switch with optional audio and microphone switching function. It allows you to access, control, boot and reboot two USB-enabled computers from a single console (keyboard, monitor and mouse). The independent audio/mic switching function allows an uninterrupted audio experience - you can continue listening to audio even when you switch to the other computer.

It includes innovative, easy-to-use KVM Switcher Software for Windows and Macintosh platforms. A small client application facilitates your KVM switching operations such as computer selection, hot key sequence programming, auto-scanning, auto-scan delay time programming, independent or simultaneous audio/computer switching and more. Compatible with all major operating systems.

Features

- Fast, easy switching via keyboard hot keys, push buttons or software
- Plug-and-play setup - no software required
- Hot-swap capability allows easy addition or removal of computers without powering down the switch or other computers
- Speaker and microphone connections allow sharing of audio components between systems (standard 3.5 mm audio connections)
- Independent audio switching allows you to listen to audio from one computer while switching to the other computer
- Supports video resolutions up to 2048 x 1536 (standard 15-pin VGA connectors)
- Supports Microsoft® IntelliMouse® and the scrolling wheel on most mice]
- Compact design saves desk space
- Does not require an AC adapter

Highlights

- Fast, easy switching via keyboard hot keys, push buttons or software (not required)
- PC and Mac compatible
- Allows sharing of audio components between systems; listen to music from one computer while switching to the other computer
- Compact design saves desk space
- No AC adapter required
- (x2) 6ft USB KVM Cable kits and (x2) 6ft 3.5mm Audio Cable kits included
- Compatible with all major operating systems

System Requirements

- Console: VGA, SVGA or Multisync Monitor, USB Keyboard and USB Mouse
- Computers: VGA, SVGA or Multisync Monitor Port and USB Port
- Audio (Optional): Speakers with standard 3.5 mm Connectors and a computer with 3.5mm ports
- Compatible with all major operating systems

Package Includes

- Compact 2-port USB KVM Switch with Audio
- (2) 6ft USB KVM Cable Kits and (2) 6ft 3.5mm Audio Cable Kits
- CD-ROM with KVM Switcher



- Compatible with all major operating systems
- Includes two, 6ft Cable Kits

- Software
- Owner's Manual with Warranty Information

Specifications

OVERVIEW	
UPC Code	037332140043
Console	No
Max CPU	2
INPUT	
Bus Powered	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Selected PC)
PHYSICAL	
Shipping Dimensions (hwd / in.)	3.00 x 7.90 x 7.80
Shipping Dimensions (hwd / cm)	7.62 x 20.07 x 19.81
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	1.3 x 4 x 2.6
Unit Weight (lbs.)	0.22
Unit Weight (kg)	0.10
Material of Construction	ABS
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0%-90% RH, Non-Condensing
BTUs	1.7 BTU/Hr
Power Consumption (Watts)	0.5



COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	USB; VGA
Side A - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	(2) USB A (FEMALE)
Side B - Connector 3	(2) 3.5MM (FEMALE)
Computer Keyboard and Mouse Interface	PS/2
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	VGA
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No
Port Selection	Pushbutton; Hotkey; Software
Max Supported Video Resolution	2048 x 1536 @60Hz
USB Specification	USB 1.1 (up to 12 Mbps)
Audio Specification	Stereo Audio
Cat5 KVM Switch	No
Technology	USB; VGA/SVGA; Stereo Audio
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty