

4-Port KVM Switch with Audio, OSD and Peripheral Sharing

MODEL NUMBER: **B006-VUA4-K-R**



Features

- Control up to 4 computers from a single monitor, keyboard and mouse
- Package includes (x2) 4-ft. (1.22 m) and (x2) 6-ft. (1.83 m) USB + Audio KVM cable kits
- P756-010 10-ft. (3.05 m) USB + Audio KVM cable kits are available separately if longer lengths are required
- P757-010 10 ft. PS/2 + Audio KVM cable kits are available separately for connection of PS/2 computers
- Built-in 2-Port USB 2.0 hub allows USB peripherals to be shared amongst computers connected via USB KVM cable kits
- Built-in 3.5mm jacks allow for speaker and microphone audio to be shared amongst the connected computers
- KVM, Audio and USB can be switched independently of each other - Control one computer while listening to audio from a second computer and printing to a USB printer from a third
- Switch the focus of KVM, Audio and USB functionality via pushbuttons, OSD, or hotkey commands
- Includes a mouse switching function that allows focus to be switched between ports by double-clicking the scroll button on a scroll mouse
- Automatically monitor connected computers via Auto Scan Mode
- Provides two levels of security, with 1 Administrator account and up to 4 User accounts
- OSD can be displayed in English, Japanese or German
- Includes rackmount hardware that allows for mounting in a 19in rack
- Includes a PS2 to USB adapter, which allows you to connect a PS/2 keyboard and mouse to control the connected computers
- Supports video resolutions up to 2048 x 1536, DDC2B
- The KVM switch stores the monitor's EDID to optimize display resolution
- Constructed of heavy-duty steel housing
- Compatible with all major operating systems

Specifications

Highlights

- Control up to 4 USB or PS/2 computers from a single monitor, keyboard and mouse
- Package includes 4 USB + Audio KVM cable kits
- Includes a built-in 2-Port USB 2.0 hub for sharing of devices amongst computers connected with a USB KVM cable kit
- Built-in 3.5mm audio jacks allow speaker and microphone audio to be shared amongst the connected computers
- 2-Level security - 1 Administrator and up to 4 Users
- Compatible with all major operating systems

Package Includes

- B006-VUA4-K-R KVM switch
- (4) USB + Audio KVM cable kits
- PS/2 to USB adapter cable
- Firmware upgrade cable
- 19in rackmount hardware
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A / Output: 5.3V, 2.4A)
- Owner's Manual



Powering Business Worldwide



OVERVIEW	
UPC Code	037332152893
Max CPU	4
Technology	USB 2.0 (High Speed); VGA/SVGA; Stereo Audio
VIDEO	
Number of Monitors Supported	1
Max Supported Video Resolution	2048 X 1536, DDC2B
Max Number of Ports (Entire Chain)	4
Extended Mode	No
Mirror Mode	No
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5.3V / 2.4A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
POWER	
Power Source Type	AC Adapter
CONNECTIONS	
Number of Ports	4
Computer/Server Ports	SPHD-18 (VGA, PS/2, USB) 3.5mm Audio Jack (Audio), 3.5mm Audio Jack (Mic)
Daisy-Chain Port	No
Firmware Upgrade Port	No
PC/Server Connections	PS/2; USB; VGA
Side A - Connector 1	(4) HD17 (FEMALE)
Side A - Connector 2	(8) 3.5MM (FEMALE)
Side B - Connector 1	(1) HD15 (FEMALE)
Side B - Connector 2	(4) USB A (FEMALE)
Side B - Connector 3	(4) 3.5MM (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Console Keyboard and Mouse Interface	PS/2; USB
Console Monitor Interface	VGA
PHYSICAL	
Material of Construction	Metal
Rackmountable	No
Shipping Dimensions (hwd / in.)	3.90 x 11.10 x 6.80
Shipping Dimensions (hwd / cm)	9.91 x 28.19 x 17.27
Shipping Weight (lbs.)	4.90
Shipping Weight (kg)	2.22
Unit Dimensions (hwd / in.)	1.600 x 7.900 x 2.750
Unit Dimensions (hwd / cm)	4.06 x 20.07 x 6.99
Unit Weight (lbs.)	1.75
Unit Weight (kg)	0.79
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0% to 80% RH, Non-Condensing
Operating Temperature	32° to 122°F (0° to 50°C)
BTUs	7.1694 BTU/Hr
COMMUNICATIONS	
Hotkey	Yes
Port Control	Push Buttons, Hotkeys, OSD Mouse Switching
IP Remote Access	No
FEATURES & SPECIFICATIONS	
Number of USB Hub Ports	2
USB Specification	USB 2.0 (up to 480 Mbps)
NIAP-Certified Secure	No
Number of Users	1
Autoscan (Y,N)	Y
Autoscan Duration	1 TO 255 SECONDS; USER-DEFINEABLE
STANDARDS & COMPLIANCE	
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL

Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.