

1U Rack-Mount Console with 19-in. LCD, Short-Depth; TAA Compliant

MODEL NUMBER: **B021-000-19-SH**



Description

Tripp Lite's B021-000-19-SH 1U Rackmount Console is the ideal solution for specialized vehicle projects, including rescue services and military specific applications. It can be mounted in as little as a 19" deep rack and features an integrated 19" LCD display, (max native resolution of 1366 x 768), full 104-key keyboard and touch pad, all in a 1U rackmountable housing. It also features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.. Your peripheral device connects to the USB type A port on the front of the unit, and your computer connects to the USB type A port on the back of the unit using a Tripp Lite UR020-Series type A M/M cable. This console is designed for use with a server or a KVM switch with PS/2 or USB console connectors. Constructed of heavy-duty steel housing.

Features

- Mounts in 19" to 30" deep cabinets
- Full 19" LCD display screen, 104-key keyboard, touchpad
- Max native resolution of 1366 x 768
- Auto Sensing External AC Adapter, 6-ft. (Input: 100-240V, 50/60Hz, 1.5A)
- Includes 6-ft. PS/2 cable kit for use with PS/2 KVMs or Servers
- PS/2 to USB adapter included for use with USB KVMs or servers
- Features a USB 2.0 pass-through port for connection of a USB peripheral, such as a flash drive, CAC card reader, etc.
- Single rail, ball bearing slides
- Constructed of heavy-duty steel housing
- Complies with the Federal Trade Agreement Act (TAA) for GSA Schedule purchases

Highlights

- Short-depth console mounts in cabinets with a minimum depth of 19"
- Designed for use with KVMs or Servers that have PS/2 or USB connectors
- 19" LCD Screen with max native 1366 x 768 resolution
- Auto Sensing External Power Supply (Input: 100-240V, 50/60Hz, 1.5A)
- TAA compliant for GSA Schedule purchases

Package Includes

- 1U 19" KVM Console Short-Body
- External AC Power Adapter with C14 Socket (Input: 100-240V, 50/60Hz, 1.5A)
- C13 to 5-15P Power Cord - 6-ft.
- PS/2 Cable Kit - 6-ft.
- PS/2 to USB Adapter
- Owner's Manual



Specifications

OVERVIEW	
UPC Code	037332143853
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A
PRODUCT OVERVIEW	
Product Overview	1U 19" KVM Console Short-Body
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
External Power Supply Output Specs (V / A)	12V / 2.5 A
External Power Supply Cord Length (ft.)	5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.5 x 16.5mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	IEC-320-C14
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; GS; BSMI; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (CAPS LOCK, SCROLL LOCK, NUM LOCK)
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.90 x 23.10 x 24.17
Shipping Dimensions (hwd / cm)	14.99 x 58.67 x 61.39
Shipping Weight (lbs.)	34.30
Shipping Weight (kg)	15.56
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	1.73 x 18.8 x 27.2
Unit Weight (lbs.)	27.13
Unit Weight (kg)	12.31
Material of Construction	SECC (Steel, Electrogalvanized, Cold Rolled, Coil)
Color	Black
Rackmountable	Yes
ENVIRONMENTAL	



Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0% to 80% RH, Non-Condensing
BTUs	(Line Mode) 102 BTU/Hr / (Standby Mode) 17.1 BTU/Hr
Power Consumption (Watts)	(Line Mode) 30W / (Standby Mode) 5W
COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	1
PC/Server Connections	PS/2; USB; VGA
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	USB A (FEMALE)
Side B - Connector 1	USB A (FEMALE)
Computer Keyboard and Mouse Interface	PS/2; USB
Computer Monitor Interface	VGA
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No
Max Supported Video Resolution	1366 x 768 @ 60Hz
USB Specification	USB 2.0 (up to 480 Mbps)
Driver Required	No
Cat5 KVM Switch	No
Technology	PS/2; USB; VGA/SVGA
CERTIFICATIONS	
Certifications	FCC Part 15 Class A, CE, EN 60950-1, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty
(ENG) Built-in Console	
Console Screen Size (inches)	19
Console Screen Aspect Ratio	16:9



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>