

# 4-Port Desktop KVM Switch

MODEL NUMBER: B022-004-R



## Description

Tripp Lite's 4-port B022-004-R KVM Switch is the optimal solution for controlling 4 computers from one keyboard, mouse and monitor. Installation is a snap - just connect the PCs using Tripp Lite's P774-Series (PS/2) or P776-Series (USB) KVM cable kits (Not included). No software or complicated set-up procedures are required. Easily switch between computers via the front-panel push buttons or keyboard hotkey commands.

## Features

- Control 4 computers from a single keyboard, mouse, and monitor
- Supports VGA, SVGA, or Multisync monitors
- Connect to PS/2 and USB computers using Tripp Lite's P774-Series (PS/2) and P776-Series (USB) KVM cable kits (Not included)
- Easy to install - no software required
- Easily select a computer via front-panel push buttons or keyboard hotkeys
- Auto Scan function to monitor computer operation
- Supports Microsoft IntelliMouse and the scrolling wheel on most mice
- Superior video quality - up to 2048x1536; DDC2B
- External power not required
- Compatible with all major operating systems except Mac and Sun

## Highlights

- Control 4 computers with 1 keyboard, monitor and mouse
- Connect to PS/2 and USB computers using Tripp Lite's P774-Series (PS/2) and P776-Series (USB) KVM cable kits (Not included)
- Simple plug-and-play design
- Ultra-slim design takes up minimal space
- Compatible with all major operating systems except Mac and Sun

## System Requirements

- VGA, SVGA or Multisync Monitor with an HD15 port
- PS/2 mouse
- PS/2 keyboard
- PS/2 or USB computer
- P774-Series (PS/2) and/or P776-Series (USB) KVM Cable kit(s); 1 for each connected computer
- Compatible with all major operating systems except Mac and Sun

## Package Includes

- B022-004-R 4 Port KVM Switch
- PS/2 console cable kit
- Owner's manual

# Specifications

OVERVIEW	
UPC Code	037332120243
Console	No
Max CPU	4



Powering Business Worldwide



Technology	PS/2; VGA/SVGA
<b>CONNECTIONS</b>	
Number of Ports	4
Computer/Server Ports	(x4) HD15 (Female)
PC/Server Connections	PS/2; USB; VGA
<b>PHYSICAL</b>	
Color	Silver
LCD Monitor (cm)	Not Applicable
LCD Monitor (in.)	Not Applicable
Shipping Dimensions (hwd / in.)	7.00 x 9.25 x 2.25
Shipping Dimensions (hwd / cm)	17.78 x 23.50 x 5.72
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	2.54 x 20.07 x 7.62
Unit Weight (lbs.)	1.1
Unit Weight (kg)	0.50
<b>COMMUNICATIONS</b>	
Port Control	Push Buttons, Hotkeys
IP Remote Access	No
<b>FEATURES &amp; SPECIFICATIONS</b>	
NIAP-Certified Secure	No
Number of Users	1
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.