

2-Port USB/DVI Cable KVM Switch with Audio, Cables and USB Peripheral Sharing

MODEL NUMBER: **B032-DUA2**



Control 2 computers using one DVI monitor, USB keyboard and USB mouse. Connect a USB 2.0 hub (sold separately) to share USB peripherals, such as printers and hard drives, between computers.

Features

Access and Control 2 Computers with One Keyboard/Mouse/Monitor

- Recommended for home, office, gaming and multimedia applications
- Switch between computers using remote port selector, hotkeys or mouse wheel
- Supports video resolutions up to 1920 x 1200 (1080p)
- Supports 2.1-channel surround sound with full bass
- Listen to audio files on one computer while accessing the other
- Compliant with EDID and HDCP
- Built-in 4-ft. (1.22 m) DVI, USB and audio cables

Independent USB 2.0 Peripheral Sharing

- Adding an optional USB hub (sold separately) to the USB console mouse port allows connection of peripherals, such as printers, hard drives, scanners, webcams and thumb drives

Flexible Keyboard/Mouse Applications

- Console mouse port emulation/bypass supports most mouse drivers and multifunction mice
- Works with multimedia keyboards and wireless keyboards and mice
- Supports Mac and Sun keyboard emulation

Easy Plug-and-Play Setup and Use

- Compatible with Windows, Mac and Linux
- No external power supply, software or drivers to install

Highlights

- Built-in 4-ft. (1.22 m) DVI, USB and audio cables
- Supports video resolutions up to 1920 x 1200 (1080p)
- Supports 2.1-channel surround sound with full bass
- Remote, hotkey and mouse port switching
- Compatible with Windows®, Mac® and Linux®

System Requirements

- DVI monitor
- USB keyboard
- USB mouse
- Computers with DVI and USB ports

Package Includes

- B032-DUA2 2-Port USB/DVI Cable KVM Switch
- Owner's manual



- Switches automatically to other computer when one powers off
- Upgradable firmware
- Takes up no valuable desk space

Specifications

OVERVIEW	
UPC Code	037332200365
Max CPU	2
Technology	DVI; Stereo Audio; USB; USB 2.0 (High Speed)
PHYSICAL	
Shipping Dimensions (hwd / cm)	6.10 x 17.02 x 23.88
Shipping Dimensions (hwd / in.)	2.40 x 6.70 x 9.40
Shipping Weight (kg)	0.59
Shipping Weight (lbs.)	1.30
Unit Dimensions (hwd / cm)	2.65 x 11.30 x 7.65
Unit Dimensions (hwd / in.)	1.04 x 4.45 x 3.01
Unit Weight (kg)	0.48
Unit Weight (lbs.)	1.06
ENVIRONMENTAL	
Operating Temperature Range	32° to 122° F (0° to 50° C)
Storage Temperature Range	-4° to 140° F (-20° to 60° C)
Relative Humidity	0% to 80% RH, Non-Condensing
Power Consumption (Watts)	3.05
COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	DVI; USB
Side A - Connector 1	DVI-D DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side A - Connector 2	(2) USB A (FEMALE)
Side A - Connector 3	(3) 3.5MM (FEMALE)



Side B - Connector 1	(2) DVI-D SINGLE LINK (MALE)
Side B - Connector 2	(4) USB A (MALE)
Side B - Connector 3	(4) 3.5MM (MALE)
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No
Cat5 KVM Switch	No
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>