

## 2-Port USB/HD Cable KVM Switch with Audio/Video, Cables and USB Peripheral Sharing

MODEL NUMBER: B032-HUA2



Control 2 computers using one HDMI monitor, USB keyboard and USB mouse. Connect a USB 2.0 hub (sold separately) to share USB peripherals, such as printers and hard drives, between computers.

### Features

#### Access and Control 2 Computers with One Keyboard/Mouse/Monitor

- Recommended for home, office, gaming and multimedia applications
- Switch between computers using remote port selector, hotkeys or mouse wheel
- Supports video resolutions up to 1920 x 1200 (1080p)
- Supports 2.1-channel surround sound with full bass
- Listen to audio files on one computer while accessing the other
- Compliant with EDID and HDCP
- Built-in 4-ft. (1.22 m) HDMI, USB and audio cables

#### USB 2.0 Peripheral Sharing

- Adding an optional USB hub (sold separately) to the USB console mouse port allows connection of peripherals, such as printers, hard drives, scanners, webcams and thumb drives

#### Flexible Keyboard/Mouse Applications

- Console mouse port emulation/bypass supports most mouse drivers and multifunction mice
- Works with multimedia keyboards and wireless keyboards and mice
- Supports Mac keyboard emulation

#### Easy Plug-and-Play Setup and Use

- Compatible with Windows, Mac and Linux
- No external power supply, software or drivers to install
- Switches automatically to other computer when one powers off
- Upgradable firmware
- Takes up no valuable desk space

### Highlights

- Built-in 4-ft. (1.22 m) HDMI, USB and audio cables
- Supports video resolutions up to 1920 x 1200 (1080p)
- Supports 2.1-channel surround sound with full bass
- Remote, hotkey and mouse port switching
- Compatible with Windows®, Mac® and Linux®

### System Requirements

- HDMI monitor
- USB keyboard
- USB mouse
- Computers with HDMI and USB ports

### Package Includes

- B032-HUA2 2-Port USB/HD Cable KVM Switch
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

## Specifications

OVERVIEW	
UPC Code	037332200396
Max CPU	2
Technology	HDMI; Stereo Audio; USB 2.0 (High Speed)
VIDEO	
Number of Monitors Supported	1
Max Supported Video Resolution	1920 x 1200
Max Number of Ports (Entire Chain)	2
Extended Mode	No
Mirror Mode	No
AUDIO	
Audio Specification	2.1 Channel Surround Sound
INPUT	
Built-In Cable Length (ft.)	4
Built-In Cable Length (m)	1.2
Built-In Cable Length (in.)	48
Built-In Cable Length (cm)	121.9
Redundancy - Dual Power Inputs	No
Bus Powered	Yes
CONNECTIONS	
Number of Ports	2
Daisy-Chain Port	No
Firmware Upgrade Port	No
PC/Server Connections	USB; HDMI
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	(2) USB A (FEMALE)
Side A - Connector 3	(2) 3.5MM (FEMALE)
Side B - Connector 1	(2) HDMI (MALE)
Side B - Connector 2	(4) USB A (MALE)
Side B - Connector 3	(4) 3.5MM (MALE)



Powering Business Worldwide

TRIPP LITE  
SERIES

PHYSICAL	
Color	Black
Material of Construction	Plastic
Cable Jacket Color	Black
Rackmountable	No
Shipping Dimensions (hwd / in.)	2.40 x 6.70 x 9.40
Shipping Dimensions (hwd / cm)	6.10 x 17.02 x 23.88
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0% to 80% RH, Non-Condensing
Operating Temperature	32° to 122°F (0° to 50°C)
COMMUNICATIONS	
Hotkey	Yes
Port Control	Push Buttons, Hotkeys
IP Remote Access	No
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
On-Screen Display (OSD)	No
Port Selection	Hotkey; Mouse; Remote Selector
Driver Required	No
REMOTE ACCESS	
Modem Port	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.